



Ref. Certif. No.

JP-22390-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product

Built-in type Power Supply

Name and address of the applicant

Name and address of the manufacturer

TRACO ELECTRONIC AG  
SIHLBRUGGSTRASSE 111, CH-6340 BAAR, SWITZERLAND

Name and address of the factory

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)

TRACO POWER

Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TMT50105, TMT50112, TMT50115, TMT50124, TMT50148,  
TMT50105C, TMT50112C, TMT50115C, TMT50124C,  
TMT50148CAdditional information (if necessary may also be  
reported on page 2)Additionally evaluated to EN 62368-1:2014/ A11:2017.  
National Differences specified in the CB Test Report.☐ Additional Information on page 2A sample of the product was tested and found  
to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part  
of this Certificate

E141988-A6001-CB-1 issued on 2020-12-13

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2020-12-14

Signature:

Masamichi Takagi

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)



Ref. Certif. No.

**JP-22390-UL**

**Ratings:**

For Models TMT50105, TMT50105C  
Input: 115-230 V~, 50/60 Hz, 1.0-0.6 A,  
Output: 5 VDC, 9.0 A

For Models TMT50112, TMT50112C  
Input: 115-230 V~, 50/60 Hz, 1.0-0.6 A,  
Output: 12 VDC, 4.2 A

For Models TMT50115, TMT50115C  
Input: 115-230 V~, 50/60 Hz, 1.0-0.6 A  
Output: 15 VDC, 3.4 A

For Models TMT50124, TMT50124C  
Input: 115-230 V~, 50/60 Hz, 1.0-0.6 A  
Output: 24 VDC, 2.3 A

For Models TMT50148, TMT50148C  
Input: 115-230 V~, 50/60 Hz, 1.0-0.6 A  
Output: 48 VDC, 1.15 A

**Additional information (if necessary)**



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-12-14

Signature:

Masamichi Takagi