

DC/DC converters 3–300 Watt 4:1 | 12:1

FEATURES

- EN 50155 railway approvals
- Extended temperature range: -40°C to +85°C
- Ruggedized designs, EN 61373 compliant for shock & vibration
- Wide and ultra-wide input voltage ranges: 9–36, 18–75, 43–160, 14–160 VDC
- Suitable for applications in harsh environments

- RIA 12 surge filters
- 3-year warranty

ADDITIONAL QUALIFICATIONS

- IEC/EN/UL 62368-1
- EN 45545-2
- RIA 12, NF F 01-510

