




Order Code	TCK-090
Inductance (each winding)	470 μ H \pm 25% (at 10 kHz / 100 mV)
Impedance (DCR)	60 m Ω max.
Rated Current	1 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-090



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	9.2 max.
B	11.8 max.
C	5.0 max.
Marking	470UH

All specifications valid at +25°C, unless otherwise stated.