




Order Code	TCK-162
Inductance (each winding)	55.6 $\mu\text{H} \pm 25\%$ (at 100 kHz / 1 V)
Impedance (DCR)	30 m Ω max.
Rated Current	1 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-162




Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	6.5 \pm 0.5
B	6.0 \pm 0.4
C	4.5 max.
D	4.3
E	7.7
F	0.91
G	3.0



All specifications valid at +25°C, unless otherwise stated.