




<b>Order Code</b>	<b>TCK-170</b>
<b>Inductance</b>	47 $\mu$ H $\pm$ 20% (100 kHz / 1 V)
<b>Impedance (DCR)</b>	294 m $\Omega$ max.
<b>Rated Current</b>	1.2 A max.
<b>Operating Temperature</b>	-40°C to +125°C
<b>RoHS Exemptions</b>	No Exemptions
<b>Overview Link</b>	<a href="http://www.tracopower.com/overview/tck-170">www.tracopower.com/overview/tck-170</a>



### Impedance Curve



### Outline Dimensions



Dimensions [mm]	
<b>A</b>	4.9 $\pm$ 0.4
<b>B</b>	4.9 $\pm$ 0.4
<b>C</b>	4.2 max.
<b>D</b>	1.5
<b>E</b>	2.1
<b>F</b>	4.0

All specifications valid at +25°C, unless otherwise stated.