



Ref. Certif. No.

**JP-22476-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

**CB TEST CERTIFICATE**

Product

Built-in type Power Supply


Name and address of the applicant



Name and address of the manufacturer

TRACO ELECTRONIC AG.  
SIHLBRUGGSTRASSE 111, CH-6340 BAAR, SWITZERLAND

Name and address of the factory



Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)

TRACO POWER

Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TMT15105, TMT15112, TMT15115, TMT15124, TMT15212, TMT15215, and TMT15105C, TMT15112C, TMT15115C, TMT15124C, TMT15212C, TMT15215C

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/ A11:2017. National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E141988-A6004-CB-1 issued on 2021-01-21

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2021-01-22

Signature:

*M. Takagi*  
Masamichi Takagi



Ref. Certif. No.

**JP-22476-UL**

**Ratings:**

For Models TMT15105, TMT15105C,  
Input: 115-230V~, 50/60Hz, 0.29-0.19A,  
Output: 5VDC, 3A

For Models TMT15112, TMT15112C,  
Input: 115-230V~, 50/60Hz, 0.29-0.19A,  
Output: 12VDC, 1.25A

For Models TMT15115, TMT15115C,  
Input: 115-230V~, 50/60Hz, 0.29-0.19A,  
Output: 15VDC, 1A

For Models TMT15124, TMT15124C,  
Input: 115-230V~, 50/60Hz, 0.29-0.19A,  
Output: 24VDC, 0.625A

For Models TMT15212, TMT15212C,  
Input: 115-230V~, 50/60Hz, 0.28-0.18A,  
Output: ±12VDC, 0.625A

For Models TMT15215, TMT15215C,  
Input: 115-230V~, 50/60Hz, 0.28-0.18A,  
Output: ±15VDC, 0.5A

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2021-01-22

Signature:

Masamichi Takagi