



Ref. Certif. No.

SG PSB-HS-03750

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Power supplies (POWER MODULE)
Name and address of the applicant	Traco Electronic AG Sihlbruggstrasse 111 6340 Baar SWITZERLAND
Name and address of the manufacturer	Traco Electronic AG Sihlbruggstrasse 111, 6340 Baar, SWITZERLAND
Name and address of the factory	Traco Electronic AG Sihlbruggstrasse 111, 6340 Baar, SWITZERLAND
Ratings and principal characteristics	Rated input voltage: 100-240 Vac Rated frequency: 50/60 Hz Rated input current: 275 mA Rated output: (See appendix for details) IP class: IPX0 ta: 50°C
Trade mark	See appendix
Model/type Ref.	TMPS 10-xxx (xxx = 103, 105, 109, 112, 115, 124, 148 representing output voltage)
A sample of the product was tested and found to be in conformity with	IEC 60335-1:2010 IEC 60335-1:2010/AMD1:2013
as shown in the Test Report Ref. No. which forms part of this certificate	081-180872-000

This CB Test Certificate is issued by the National Certification Body

CBS 002910 0001 Rev. 00

Date, 2018-08-29

Page 1 of 2

TÜV SÜD PSB Pte Ltd • 1 Science Park Drive • Singapore 118221

Bill Lin
(Bill Lin)



PSB Singapore

Appendix to CB Certificate

1. Trade mark:



2. Output rating:

Model no.:	Rated output voltage (Vdc)	Rated output current (mA)
TMPS 10-103	3.3	2600
TMPS 10-105	5	2000
TMPS 10-109	9	1100
TMPS 10-112	12	830
TMPS 10-115	15	660
TMPS 10-124	24	410
TMPS 10-148	48	210

(Bill Lin)