



Ref. Certif. No.

DK-110950-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

DC/DC Converter

Name and address of the applicant

TRACO ELECTRONIC AG
SIHLBRUGGSTRASSE 111 BAAR CH-6340 SWITZERLAND

Name and address of the manufacturer

TRACO ELECTRONIC AG
SIHLBRUGGSTRASSE 111 BAAR CH-6340 SWITZERLAND

Name and address of the factory

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

☐ Additional Information on page 2

Trademark (if any)

See page 2

☒ Additional Information on page 2



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TMR 4-xy, TMR 4-xyWI

☒ Additional Information on page 2

Additional information (if necessary may also be reported on page 2)

☒ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

200803901 issued on 2021-03-17

This CB Test Certificate is issued by the National Certification Body



- ☐ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL (Denmark), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP) Marunouchi Trust Tower Main Building 6F 1-8-3 Marunouchi Chiyoda-ku Tokyo 100-0005 JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2021-03-17

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-110950-UL

Additional Model(s):

Series: TMR 4-xy(x can be 12, 24 or 48; y can be 11, 12, 13, 15, 22 or 23), TMR 4-xyWI(x can be 24 or 48, y can be 11, 12, 13, 15, 22 or 23)

Model Name: TMR 4-xy: For Model TMR 4-1211, Input: Nominal: 12 Vdc Range: 9-18 Vdc, 566mA, See test report for details.

Model Name: TMR 4-xyWI: For Model TMR 4-2411WI, Input: Nominal: 24 Vdc Range: 9-36 Vdc, 589mA, See test report for details.

Additionally evaluated to:

EN 62368-1:2014/A11:2017, EN 62368-1:2014

National Difference specified in the CB Test Report

Additional information (if necessary)



- ☐ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-03-17

Signature:

Jan-Erik Storgaard