



## Efficiency vs Load

Typical values for 4.5 - 9 Vin (5 VDC nominal) models


TMR 6-0510




TMR 6-0511




TMR 6-0519




TMR 6-0512




TMR 6-0513




TMR 6-0515




TMR 6-0521



TMR 6-0522



TMR 6-0523




**No load input current.**  
(typical at Vin nominal)

TMR 6-0510	65 mA
Other TMR 6-05xx models	105 mA


## Efficiency vs Load

Typical values for 9- 18 Vin (12 VDC nominal) models


TMR 6-1210




TMR 6-1211




TMR 6-1219




TMR 6-1212




TMR 6-1213




TMR 6-1215




TMR 6-1221



TMR 6-1222



TMR 6-1223




**No load input current.**  
(typical at Vin nominal)

TMR 6-1210	10 mA
Other TMR 6-12xx models	55 mA


## Efficiency vs Load

Typical values for 18 - 36 Vin (24 VDC nominal) models


TMR 6-2410




TMR 6-2411




TMR 6-2419




TMR 6-2412




TMR 6-2413




TMR 6-2415




TMR 6-2421



TMR 6-2422



TMR 6-2423




**No load input current.**  
(typical at Vin nominal)

TMR 6-2410	20 mA
Other TMR 6-24xx models	28 mA


## Efficiency vs Load

Typical values for 36 - 75 Vin (48 VDC nominal) models


TMR 6-4810




TMR 6-4811




TMR 6-4819




TMR 6-4812




TMR 6-4813




TMR 6-4815




TMR 6-4821



TMR 6-4822



TMR 6-4823



**No load input current.**  
(typical at Vin nominal)

all TMR 6-48xx models

14 mA