



Ref. Certif. No.

DK-138460-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

TRACO ELECTRONIC AG
Sihlbruggstrasse 111, CH-6340 Baar, SWITZERLAND

Name and address of the manufacturer

TRACO ELECTRONIC AG
Sihlbruggstrasse 111, CH-6340 Baar, SWITZERLAND

Name and address of the factory

[REDACTED]
[REDACTED]
[REDACTED]

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

Input: 100-240 Vac, 47-63 Hz, 3.0 A max.
Output: See test report for details

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TCI 240-112-J, TCI 240-124-J, TCI 240-148-J, TCI 240-112-T

☒ Additional Information on page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to: EN 62368-1:2014, EN 62368-1:2014/A11:2017
National Differences specified in the CB Test Report.

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

2208005-1-CB issued on 2023-03-01

This CB Test Certificate is issued by the National Certification Body



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Denmark), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2023-03-08

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-138460-UL

Additional Model Detail(s):

TCI 240-112-J, TCI 240-124-J, TCI 240-148-J, TCI 240-112-T, TCI 240-124-T, TCI 240-148-T, TCI 240-112U-J, TCI 240-124U-J, TCI 240-148U-J, TCI 240-112U-T, TCI 240-124U-T, TCI 240-148U-T, TCI 240-112A-J, TCI 240-124A-J, TCI 240-148A-J, TCI 240-112A-T, TCI 240-124A-T, TCI 240-148A-T, ACI 240-xAz, ACI 240-xz, and ACI 240-xUz
(where "x" can be 112, 124, 148; and "z" can be -J or -T)

Additional information (if necessary)



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2023-03-08

Signature:

Jan-Erik Storgaard