



Ref. Certif. No.

DK-113050-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

DC to DC Converter

Name and address of the applicant

TRACO ELECTRONIC AG
Sihlbruggstrasse 111 CH-6340 Baar
Switzerland

Name and address of the manufacturer

TRACO ELECTRONIC AG
Sihlbruggstrasse 111 CH-6340 Baar
Switzerland

Name and address of the factory

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

For model TMR 6-2410WIR:
Input: 9 ~ 36 Vdc, 0.723A
See test report for details.

Trademark (if any)



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TMR 3-x1yaWIRzzzzzzzzz, TMR 6-x1yaWIRzzzzzzzzz,
TMR 6-xyaWlvzzzzzzzzz
☒ Additional Information on page 2

Additional information (if necessary may also be reported on page 2)

☒ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

2010068-CB issued on 2021-04-29

This CB Test Certificate is issued by the National Certification Body



- ☐ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-05-06

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-113050-UL

Additional Model(s):

Series: TMR 6-xyaWlvzzzzzzzz, TMR 3-x1yaWIRzzzzzzzz, and TMR 6-x1yaWIRzzzzzzzz,
(where "v" can be Hl or blank, "x" can be 24 or 48; "x1" can be 24, 48 or 72; "y" can be 1 or 2; "a" can be 0, 1, 9, 2, 3 or 5, "z" can be any alphanumeric character, blank or dash for marketing purpose only and no impact safety related constructions and critical component.)

Additionally evaluated to:

EN 62368-1:2014/A11:2017, EN 62368-1:2014

National Difference specified in the CB Test Report

Additional information (if necessary)



- ☐ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-05-06

Signature:

Jan-Erik Storgaard