



Ref. Certif. No.

DK-106424-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product

AC-DC CONVERTER

Name and address of the applicant

TRACO ELECTRONIC AG  
SIHLBRUGGSTRASSE 111, CH-6340 BAAR, SWITZERLAND

Name and address of the manufacturer

TRACO ELECTRONIC AG  
SIHLBRUGGSTRASSE 111, CH-6340 BAAR, SWITZERLAN

Name and address of the factory

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TMG 501X  
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/A11:2017; National Differences specified in the CB Test Report.

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

201102001 issued on 2020-11-26

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2020-11-30

Signature:

Jan-Erik Storgaard

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)



Ref. Certif. No.

**DK-106424-UL**

**Model Details:**

TMG 501X ("X" can be 05, 12, 15, 24, 48)

**Ratings:**

Input rating: 100-240 V a.c, 1 A max. 47-63 Hz

**DC Output:**

For Model TMG 50105: +5V/ 8000mA

For Model TMG 50112: +12V/ 4167 mA

For Model TMG 50115: +15V/ 3333 mA

For Model TMG 50124: +24V/ 2083 mA

For Model TMG 50148: +48V/ 1040 mA

**Additional information (if necessary)**



UL (US), 333 Pfingsten Rd L 60062, Northbrook, USA

UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-11-30

Signature:

Jan-Erik Storgaard