



**Interocean Technology Corp.** Filing No.: 16A022601E-C

## **Verification of Conformity**

**Applicant : Traco Electronic AG**  
Sihlbruggstrasse 111, 6340 Baar Switzerland

**Product : DC/DC Converter**  
**Model No. : Please refer to page 2**

**On the basis of the tests undertaken, the sample(s) of the above product have been found to comply with the essential requirements of the referenced specifications at the time the tests were carried out.**

### ***Relevant Standard(s) / Specification(s)***

EN 50155: 2007 for EMC, Environmental and Characteristic  
EN 50121-3-2: 2006 for EMC  
EN 60068-2-1: 2007 for Environmental  
EN 60068-2-2: 2007 for Environmental  
EN 60068-2-30: 2005 for Environmental  
EN 61373: 2010 for Environmental

**Issued By:**

  
\_\_\_\_\_  
**Mike Huang / President**

**Date: Apr. 25, 2016**

**Model Numbers**

Model Number	Input Range (VDC)	Full load Input current (A)	Ouput Voltage (VDC)	Full Load (mA)
TEN 40-2410WIRz1z1z1z1z1z1z1	9 ~ 36	4.074	3.3	10000
TEN 40-2411WIRz1z1z1z1z1z1z1	9 ~ 36	4.884	5	8000
TEN 40-2412WIRz1z1z1z1z1z1z1	9 ~ 36	4.883	12	3333
TEN 40-2413WIRz1z1z1z1z1z1z1	9 ~ 36	4.882	15	2666
TEN 40-2415WIRz1z1z1z1z1z1z1	9 ~ 36	4.882	24	1666
TEN 40-2422WIRz1z1z1z1z1z1z1	9 ~ 36	4.936	±12	±1666
TEN 40-2423WIRz1z1z1z1z1z1z1	9 ~ 36	4.937	±15	±1333
TEN 40-2425WIRz1z1z1z1z1z1z1	9 ~ 36	4.883	±24	±833
TEN 40-4810WIRz1z1z1z1z1z1z1	18 ~ 75	2.037	3.3	10000
TEN 40-4811WIRz1z1z1z1z1z1z1	18 ~ 75	2.442	5	8000
TEN 40-4812WIRz1z1z1z1z1z1z1	18 ~ 75	2.415	12	3333
TEN 40-4813WIRz1z1z1z1z1z1z1	18 ~ 75	2.414	15	2666
TEN 40-4815WIRz1z1z1z1z1z1z1	18 ~ 75	2.441	24	1666
TEN 40-4822WIRz1z1z1z1z1z1z1	18 ~ 75	2.468	±12	±1666
TEN 40-4823WIRz1z1z1z1z1z1z1	18 ~ 75	2.468	±15	±1333
TEN 40-4825WIRz1z1z1z1z1z1z1	18 ~ 75	2.441	±24	±833
TEN 40-7210WIRz1z1z1z1z1z1z1	43~160	0.872	3.3	10000
TEN 40-7211WIRz1z1z1z1z1z1z1	43~160	1.045	5	8000
TEN 40-7212WIRz1z1z1z1z1z1z1	43~160	1.027	12	3333
TEN 40-7213WIRz1z1z1z1z1z1z1	43~160	1.033	15	2666
TEN 40-7215WIRz1z1z1z1z1z1z1	43~160	1.033	24	1666
TEN 40-7222WIRz1z1z1z1z1z1z1	43~160	1.044	±12	±1666
TEN 40-7223WIRz1z1z1z1z1z1z1	43~160	1.044	±15	±1333
TEN 40-7225WIRz1z1z1z1z1z1z1	43~160	1.021	±24	±833