

#### **DC/DC Converter**

## **TEA 1HI Series, 1 Watt**

- Highly cost efficient design
- I/O isolation: 4'000 VDC
- Operating temperature range
   -40 to +85 °C without derating
- 5 VDC (±10%) input voltage range
- Unregulated outputs
- Efficiency up to 78%
- Industry standard SIP-7 package
- 3-year product warranty



The TEA 1HI is an unregulated 1 Watt DC/DC SIP-7 converter series with high isolation which is specifically designed to offer a low-cost solution while keeping a high quality standard. This new series focuses on a simple but effective design approach, which minimizes component and labor cost and is complemented with a complete automatization of the manufacturing process. An operating temperature range from -40°C to 85°C without derating and an I/O-isolation of 4'000 VDC enables this series to cover many different applications. The industry standard package of this converter offers a broad application range in any space, cost critical application and is especially suited for high volume projects where simple but reliable products are needed.

| Models       |                                      |                |                |            |
|--------------|--------------------------------------|----------------|----------------|------------|
| Order Code   | Input Voltage                        | Output Voltage | Output Current | Efficiency |
|              | Range                                | nom.           | max.           | typ.       |
| TEA 1-0505HI | <b>4.5 - 5.5 VDC</b><br>(5 VDC nom.) | 5 VDC          | 200 mA         | 78 %       |



| Input Specifications       |  |
|----------------------------|--|
| Input Current - At no load | 28 mA typ.                                       |
| Surge Voltage              | 9 VDC max. (1 s max.)                            |
| Recommended Input Fuse     | 500 mA (slow blow)                               |
|                            | (The need of an external fuse has to be assessed |
|                            | in the final application.)                       |
| Input Filter               | Internal Capacitor                               |

| Voltage Set Accuracy     |                                 | <b>±3% max.</b> (at 60 % load)       |
|--------------------------|---------------------------------|--------------------------------------|
| Regulation               | - Input Variation (1% Vin step) | 1.5% max.                            |
|                          | - Load Variation (10 - 90%)     | 9% max.                              |
| Ripple and Noise         | - 20 MHz Bandwidth              | 100 mVp-p max.                       |
|                          |                                 | 50 mVp-p typ.                        |
| Capacitive Load          |                                 | 1'000 μF max.                        |
| Minimum Load             |                                 | Not required                         |
| Temperature Coefficier   | nt                              | ±0.03 %/K max.                       |
| Start-up Time            |                                 | 30 ms max.                           |
| Short Circuit Protection | 1                               | Limited 1 s max., Automatic recovery |
|                          |                                 | •                                    |

| Safety Specifi | cations                     |  |
|----------------|-----------------------------|--|
| Standards      | - IT / Multimedia Equipment | Designed for IEC/EN/UL 62368-1 (not certified) |

| Relative Humidity      |                                 | ·                     | 95% max. (non condensing)                  |
|------------------------|---------------------------------|-----------------------|--|
| Temperature Ranges     | - Operating Temperature         |                       | -40°C to +95°C                             |
|                        | - Case Temperature              |                       | +105°C max.                                |
|                        | - Storage Temperature           |                       | -55°C to +125°C                            |
| Power Derating         | - High Temperature              |                       | 5 %/K above 85°C                           |
|                        |                                 | See application note: | www.tracopower.com/overview/tea1hi         |
| Cooling System         |                                 |                       | Natural convection (20 LFM)                |
| Switching Frequency    |                                 |                       | 100 kHz typ. (Royer)                       |
| Insulation System      |                                 |                       | Functional Insulation                      |
| Isolation Test Voltage | - Input to Output, 60 s         |                       | 4'000 VDC                                  |
| Isolation Resistance   | - Input to Output, 500 VDC      |                       | 1'000 MΩ min.                              |
| Isolation Capacitance  | - Input to Output, 100 kHz, 1 V |                       | 30 pF typ.                                 |
| Reliability            | - Calculated MTBF               |                       | 2'000'000 h (MIL-HDBK-217F, ground benign) |
| Washing Process        |                                 |                       | Not allowed                                |
| Housing Material       |                                 |                       | Plastic (UL 94 V-0 rated)                  |
| Potting Material       |                                 |                       | Epoxy (UL 94 V-0 rated)                    |
| Pin Material           |                                 |                       | Phosphor Bronze (C5191)                    |
| Pin Foundation Plating |                                 |                       | Nickel (1 µm min.)                         |
| Pin Surface Plating    |                                 |                       | Tin (3 µm min.), bright                    |
| Housing Type           |                                 |                       | Plastic Case                               |
| Mounting Type          |                                 |                       | PCB Mount                                  |
| Connection Type        |                                 |                       | THD (Through-Hole Device)                  |
| Footprint Type         |                                 |                       | SIP7                                       |
| Soldering Profile      |                                 |                       | Lead-Free Wave Soldering                   |
|                        |                                 |                       | 265 °C / 5 s max.                          |
| Weight                 |                                 |                       | 2 g  |

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.



# **II TRACO POWER**

Environmental Compliance - REACH Declaration

- RoHS Declaration

- SCIP Reference Number

www.tracopower.com/info/reach-declaration.pdf

REACH SVHC list compliant REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

Exemptions: 7a, 7c-I

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)


c75f4061-29c7-4520-81da-a857cb7778d0

### **Supporting Documents**

Overview Link (for additional Documents)

www.tracopower.com/overview/tea1hi

### **Outline Dimensions**



Dimensions in mm (inch) 
Tolerances:  $x.x \pm 0.5$  ( $x.xx \pm 0.02$ )  $x.xx \pm 0.25$  ( $x.xxx \pm 0.01$ ) 
Pin dimension tolerance:  $\pm 0.1$  ( $\pm 0.004$ )

| Pinout |            |  |
|--------|------------|--|
| Pin    | Function   |  |
| 1      | +Vin (Vcc) |  |
| 2      | –Vin (GND) |  |
| 5      | –Vout      |  |
| 7      | +Vout      |  |

 $(0.020 \times 0.010)$