



Ref. Certif. No.

DK-107716-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product

AC-DC Power Module

Name and address of the applicant

TRACO ELECTRONIC AG  
SIHLBRUGGSTRASSE 111, CH-6340 BAAR, SWITZERLAND

Name and address of the manufacturer

TRACO ELECTRONIC AG  
SIHLBRUGGSTRASSE 111, CH-6340 BAAR, SWITZERLAND

Name and address of the factory

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

☐ Additional Information on page 2Input: 100-240 Vac, 47-63 Hz, 0.35 A max.  
Output: See test report for details

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

TMG 15105, TMG 15112, TMG 15115, TMG 15124

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/A11:2017; National Differences specified in the CB Test Report.

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

201102401 issued on 2020-12-14

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2020-12-23

Signature:

  
Jan-Erik StorgaardFor full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)