

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switch Mode Power Supply for building-in (DIN Rail)

Name and address of the applicant

Traco Power Solutions Ltd.
Whitemill Industrial Estate Wexford, White Mill Road,
Y35 YH66, Ireland

Name and address of the manufacturer

Traco Power Solutions Ltd.
Whitemill Industrial Estate Wexford, White Mill Road,
Y35 YH66, Ireland

Name and address of the factory

Traco Power Solutions Ltd.
Whitemill Industrial Estate Wexford, White Mill Road,
Y35 YH66, Ireland*Note: When more than one factory, please report on page 2*☐ Additional Information on page 2

Ratings and principal characteristics

See page 3

Trademark / Brand (if any)

TRACO POWER

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

TPC series (see page 2)

Additional information (if necessary may also
be reported on page 2)Additionally evaluated to EN 61010-1:2010 + A1:2019
and EN IEC 61010-2-201:2018; National Differences
specified in the CB Test Report.☒ Additional Information on page 2A sample of the product was tested and found
to be in conformity withIEC 61010-1:2010 + A1:2016
IEC 61010-2-201:2017As shown in the Test Report Ref. No. which
forms part of this Certificate


T223-0014/21, T223-0015/21 (2021-01-11)

This CB Test Certificate is issued by the National Certification Body

SIQ Ljubljana, Mašera-Spasičeva ulica 10, SI-1000 Ljubljana, Slovenia
T +386 1 4778 100, F +386 1 4778 444, info@siq.si, www.siq.siSIQ Ljubljana is accredited by Slovenian Accreditation with accreditation number CP-001 in the
field of certification of products, processes and services.

Date: 2021-01-11

Signature: Bojan Pečavar



Model / Type Ref.:

TRACO POWER Model reference	Manufacturer Model reference
TPC 030-105	030PSC181
TPC 030-112	030PSC182
TPC 030-124	030PSC184
TPC 030-148	030PSC185
TPC 055-112	050PSC182
TPC 055-124	050PSC184
TPC 055-148	050PSC185
TPC 080-112	080PSC182
TPC 080-124	080PSC184
TPC 080-148	080PSC185
TPC 120-112	120PSC182
TPC 120-124	120PSC184
TPC 120-148	120PSC185

Models can be additional marked with xxxxxxxx, where 'x' or 'a' can be any alphanumeric, blank or dash, no impact on safety.

Additional information (if necessary)

Date: 2021-01-11

Signature: Bojan Pečavar



Ratings and principal characteristics:

Model	Input	Output		
	Current [A]	Voltage [DC]	Current [A]	Power [W]
TPC 030-105	0,5 – 0,3	5	4	20
TPC 030-112	0,6 – 0,4	12	2,2	26,4
TPC 030-124	0,7 – 0,4	24	1,25	30
TPC 030-148	0,7 – 0,4	48	0,6	30
TPC 055-112	1,0 – 0,5	12	3,5	42
TPC 055-124	1,2 – 0,7	24	2,3	55
TPC 055-148	1,2 – 0,6	48	1,15	55
TPC 080-112	1,7 – 0,9	12	6,0	72
TPC 080-124	1,8 – 1,0	24	3,3	80
TPC 080-148	1,7 – 1,0	48	1,7	80
TPC 120-112	2,0 – 1,1	12	8,0	96
TPC 120-124	2,6 – 1,4	24	5,0	120
TPC 120-148	2,4 – 1,3	48	2,5	120

Additional information (if necessary)

Date: 2021-01-11

Signature: Bojan Pečavar

