Non-Isolated DC/DC Converter (POL)

TOS 16SIL Series, 16 A

End of life

- Small size, low profile
- SIP version
- Cost-efficient open frame design
- Wide input voltage ranges
- Output voltages trim from 0.75 VDC to 5.0 VDC
- Delivers up to 16 A with minimal derating
- Ultra high efficiency to 95 %
- Fast transient response
- Remote On/Off control
- Wide temperature range -40°C to +85°C
- 3-year product warranty

UL 62368-1 The TOS 16SIL series is a range of high performance non-isolated DC/DC converters with very high efficiency that can supply up to 16 A of output current. These modules provide precisely regulated output voltages which can be set via an external resistor to a value from 0.75 VDC to 5.0 VDC. These converters work over a wide input voltage range of 2.4 to 5.5 VDC or 8.3 to 14.0 VDC. Further features include remote On/Off, under voltage lockout and over current protection. These products have an open-frame construction with very small footprint and are available in an industry standard SIP package. The TOS 16SIL series is fully RoHS compliant and can withstand industry standard handling, cleaning and the high temperatures of lead-free reflow solder processes.

| Models | | | | |
|----------------|----------------|----------------------------|---------------------------|------------|
| Order Code | Output Current | Input Voltage | Output Voltage | Efficiency |
| | max. | Range | nom. (adjustable) | typ. |
| TOS 16-05SIL * | 16'000 mA | 2.4 - 5.5 VDC (5 VDC nom.) | 0.75 VDC (0.75 - 3.3 VDC) | 95 % |
| TOS 16-12SIL * | 10 000 MA | 8.3 - 14 VDC (12 VDC nom.) | 0.75 VDC (0.75 - 5.0 VDC) | 92 % |

Note * End of life

| Input Current | - At no load | 5 Vin models: | 130 mA typ. |
|-----------------------|--------------|-----------------------|--|
| | | 12 Vin models: | 100 mA typ. |
| | | | (at Vout max.) |
| Start-up Voltage | | 5 Vin models: | 2.2 VDC typ. / 2.4 VDC max. |
| | | 12 Vin models: | 7.9 VDC typ. / 8.3 VDC max. |
| Under Voltage Locko | ut | 5 Vin models: | 1.6 VDC min. / 2 VDC typ. / 2.2 VDC max. |
| | | 12 Vin models: | 6.5 VDC min. / 7.5 VDC typ. / 8 VDC max. |
| Reflected Ripple Curr | rent | 5 Vin models: | 100 mAp-p typ. |
| | | 12 Vin models: | 30 mAp-p typ. |
| | | | (with input filter, see application note) |
| Recommended Input | Fuse | 5 Vin models: | 25'000 mA (fast acting) |
| | | 12 Vin models: | 15'000 mA (fast acting) |
| | | | (The need of an external fuse has to be assessed |
| | | | in the final application.) |
| Input Filter | | See application note: | www.tracopower.com/overview/tos16sil |

| Output Voltage Adjustment | | 0.75 Vout models: | 0.75 - 3.3 VDC |
|---------------------------|---------------------------------|-----------------------|---|
| | | | 0.75 - 5.0 VDC |
| | | | (By external trim resistor) |
| | | See application note: | www.tracopower.com/overview/tos16sil |
| | | | (Vin must be at least 0.5 V higher than Vout) |
| Voltage Set Accuracy | | | ±2% max. |
| Regulation | - Input Variation (Vmin - Vmax) | | 0.3% max. |
| | - Load Variation (0 - 100%) | | 0.4% max. |
| Ripple and Noise | - 20 MHz Bandwidth | | 50 mVp-p max. |
| Capacitive Load | | | 5'000 μF max. |
| | | | (ESR >10 mOhm) |
| Minimum Load | | | Not required |
| Temperature Coefficien | t | | ±0.4 %/K max. |
| Start-up Time | | | 8 ms typ. |
| Start-up Overshoot Volta | age | | 3% max. |
| Short Circuit Protection | | | Continuous, Automatic recovery |
| Output Current Limitatio | on | | 180% typ. of lout max. |
| Transient Response | - Peak Variation | | 300 mV typ. (50% Load Step) (5 Vin model) |
| | | | 200 mV typ. (50 % Load Step) (12 Vin model |
| | - Response Time | | 100 μs typ. (50% Load Step) |
| | | | (with 1 µF MLCC 10 µF TC) |

| ons | | |
|-----------------------------|---|--|
| - IT / Multimedia Equipment | | UL 60950-1 |
| | | UL 62368-1 |
| tions | | |
| | | 95% max. (non condensing) |
| - Operating Temperature | | –40°C to +85°C |
| - Case Temperature | | +115°C max. |
| - Storage Temperature | | –55°C to +125°C |
| - High Temperature | | Depending on model |
| | See application note: | www.tracopower.com/overview/tos16sil |
| | | Natural convection (20 LFM) |
| | tions - Operating Temperature - Case Temperature - Storage Temperature | IT / Multimedia Equipment tions Operating Temperature Case Temperature Storage Temperature High Temperature |


All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

| Remote Control | - Voltage Controlled Remote | On: open circuit or Vin max. |
|--------------------------|-----------------------------|---|
| | (passive = on) | Off: 0 to 0.3 VDC |
| | | Refers to 'Remote' and 'GND' Pin |
| | - Off Idle Input Current | 2 mA typ. |
| | | (12 Vin model: Open circuit or (Vin $-$ 4 V) to Vin |
| | | max. for on state) |
| Switching Frequency | | 270 - 330 kHz (PWM) |
| | | 300 kHz typ. (PWM) |
| Insulation System | | Non-isolated |
| Reliability | - Calculated MTBF | 3'200'000 h (MIL-HDBK-217F, ground benign) |
| Washing Process | | According to Cleaning Guideline |
| | | www.tracopower.com/info/cleaning.pdf |
| Environment | - Vibration | MIL-STD-810F |
| | - Thermal Shock | MIL-STD-810F |
| Pin Material | | Copper |
| Pin Foundation Plating | | Nickel (3 - 5 µm) |
| Pin Surface Plating | | Gold (50 - 75 nm), matte |
| Housing Type | | Open Frame |
| Mounting Type | | PCB Mount |
| Connection Type | | THD (Through-Hole Device) |
| Footprint Type | | SIP20 |
| Soldering Profile | | Lead-Free Wave Soldering |
| | | 265°C / 10 s max. |
| Weight | | 6 g |
| Environmental Compliance | e - REACH Declaration | www.tracopower.com/info/reach-declaration.pdf |
| | | REACH SVHC list compliant |
| | | REACH Annex XVII compliant |
| | - RoHS Declaration | www.tracopower.com/info/rohs-declaration.pdf |
| | | Exemptions: 7a, 7c-l |
| | | (RoHS exemptions refer to the component |
| | | concentration only, not to the overall |
| | | concentration in the product (05A rule).) |
| | - SCIP Reference Number | 80e9649b-500c-4b98-9b36-005ecacbc7d1 |

| Supporting Documents | |
|--|--------------------------------------|
| Overview Link (for additional Documents) | www.tracopower.com/overview/tos16sil |

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



Dimensions in mm (inch) Tolerances x.x ± 0.5 (x.xx ± 0.02) Tolerances x.xx ± 0.25 (x.xxx ± 0.01) Pin dimension tolerance ± 0.1 (± 0.004)

| | Pinout | | |
|-----|---------------|--|--|
| Pin | Pin Function | | |
| 1 | +Vout | | |
| 2 | +Vout | | |
| 3 | +Sense | | |
| 4 | +Vout | | |
| 5 | GND | | |
| 6 | GND | | |
| 7 | +Vin | | |
| 8 | +Vin | | |
| 10 | Trim | | |
| 11 | Remote On/Off | | |

© Copyright 2024 Traco Electronic AG

