




<b>Order Code</b>	<b>TCK-141</b>
<b>Inductance</b>	5.6 $\mu$ H $\pm$ 20% (at 100 kHz / 250 mV)
<b>Impedance (DCR)</b>	90 m $\Omega$ max.
<b>Rated Current</b>	3.5 A max.
<b>Operating Temperature</b>	-55°C to +125°C
<b>RoHS Exemptions</b>	No Exemptions
<b>Overview Link</b>	<a href="http://www.tracopower.com/overview/tck-141">www.tracopower.com/overview/tck-141</a>



### Impedance Curve



### Outline Dimensions



Dimensions [mm]	
<b>A</b>	4.0 $\pm$ 0.3
<b>B</b>	4.0 $\pm$ 0.3
<b>C</b>	2.1 max.
<b>D</b>	4.7 max.
<b>E</b>	1.0 $\pm$ 0.3
<b>F</b>	0.6 $\pm$ 0.1
<b>G</b>	2.2
<b>H</b>	6.0
<b>I</b>	1.5

All specifications valid at +25°C, unless otherwise stated.