




| | |
|----------------------------------|--|
| Order Code | TCK-185 |
| Inductance (each winding) | 415 $\mu\text{H} \pm 35\%$ (at 100 kHz / 100 mV) |
| Impedance (DCR) | 5 m Ω max. |
| Rated Current | 16 A max. |
| Operating Temperature | -40°C to +125°C |
| RoHS Exemptions | No Exemptions |
| Overview Link | www.tracopower.com/overview/tck-185 |



Impedance Curve



Outline Dimensions



Dimensions [mm]

| | |
|----------|-------------------------|
| A | 14.45 max. |
| B | 5.0 ± 2 |
| C | 10.0 ± 1 |
| D | 4.0 ± 1 |
| E | $\varnothing 1.0 \pm 1$ |

All specifications valid at +25°C, unless otherwise stated.