




<b>Order Code</b>	<b>TCK-090</b>
<b>Inductance</b> (each winding)	470 $\mu$ H $\pm$ 25% (at 10 kHz / 100 mV)
<b>Impedance</b> (DCR)	60 m $\Omega$ max.
<b>Rated Current</b>	1 A max.
<b>Rated Voltage</b>	500 VDC max. (between windings)
<b>Operating Temperature</b>	-40°C to +105°C
<b>RoHS Exemptions</b>	No Exemptions
<b>Overview Link</b>	<a href="http://www.tracopower.com/overview/tck-090">www.tracopower.com/overview/tck-090</a>



### Impedance Curve



### Outline Dimensions



Dimensions [mm]	
<b>A</b>	9.2 max.
<b>B</b>	11.8 max.
<b>C</b>	5.0 max.
<b>Marking</b>	470UH

All specifications valid at +25°C, unless otherwise stated.