



| | |
|------------------------------|--|
| Order Code | TCK-097 |
| Inductance | 2.2 μ H \pm 20% (at 100 kHz / 250 mV) |
| Impedance (DCR) | 12 m Ω max. |
| Rated Current | 11 A max. |
| Operating Temperature | -40°C to +125°C |
| RoHS Exemptions | No Exemptions |
| Overview Link | www.tracopower.com/overview/tck-097 |



Impedance Curve



Outline Dimensions



| Dimensions [mm] | |
|-----------------|---------------|
| A | 6.5 \pm 0.3 |
| B | 6.5 \pm 0.3 |
| C | 4.2 max. |
| D | 7.6 max. |
| E | 1.6 \pm 0.3 |
| F | 1.2 \pm 0.3 |
| G | 3.0 |
| H | 8.5 |
| I | 2.5 |

All specifications valid at +25°C, unless otherwise stated.