

- Ultra compact 6 Watt converter in DIP-16 metal casing
- High power density of 1,6W/cm³
- 6-side shielded metal case with insulated baseplate
- Wide 2:1 input voltage range: 4.5-12, 9-18, 18-36, 36-75 VDC
- High efficiency (up to 87%) for low thermal loss
- Operating temperature range -40°C to +85°C
- Meets EN 55032 class A (conducted and radiated) with a single input capacitor
- Protection against short circuit
- 3-year product warranty



The TEL 6 is an isolated 6 Watt converters series which comes in an ultra compact DIP-16 metal package. It solidifies the new package standard in this power range with a power density of 1,6 W/cm³ which almost doubles the power density compared to 6 Watt converters in DIP-24 packages. The TEL 6 offers a wide 2:1 input voltage range and featured a high efficiency of up to 87% which enables an operation temperature of up to +70°C at full load and up to 85°C with 60% load. With only a single input capacitor (SMD) the converters comply with conducted and radiated emission standard EN 55032 class A. Overall they feature an economical solution for space critical and cost sensitive applications in instrumentation, IT and industrial electronics.

Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
TEL 6-0911 *	4.5 - 12 VDC (9 VDC nom.)	5 VDC	1'200 mA			82 %
TEL 6-0912 *		12 VDC	500 mA			85 %
TEL 6-0913 *		15 VDC	400 mA			86 %
TEL 6-0915 *		24 VDC	250 mA			87 %
TEL 6-0922 *		+12 VDC	250 mA	-12 VDC	250 mA	85 %
TEL 6-0923 *		+15 VDC	200 mA	-15 VDC	200 mA	85 %
TEL 6-1211 *	9 - 18 VDC (12 VDC nom.)	5 VDC	1'200 mA			79 %
TEL 6-1212 *		12 VDC	500 mA			83 %
TEL 6-1213 *		15 VDC	400 mA			83 %
TEL 6-1215 *		24 VDC	250 mA			85 %
TEL 6-1222 *		+12 VDC	250 mA	-12 VDC	250 mA	85 %
TEL 6-1223 *		+15 VDC	200 mA	-15 VDC	200 mA	85 %
TEL 6-2411 *	18 - 36 VDC (24 VDC nom.)	5 VDC	1'200 mA			81 %
TEL 6-2412 *		12 VDC	500 mA			84 %
TEL 6-2413 *		15 VDC	400 mA			84 %
TEL 6-2415 *		24 VDC	250 mA			84 %
TEL 6-2422 *		+12 VDC	250 mA	-12 VDC	250 mA	85 %
TEL 6-2423 *		+15 VDC	200 mA	-15 VDC	200 mA	84 %
TEL 6-4811 *	36 - 75 VDC (48 VDC nom.)	5 VDC	1'200 mA			81 %
TEL 6-4812 *		12 VDC	500 mA			85 %
TEL 6-4813 *		15 VDC	400 mA			85 %
TEL 6-4815 *		24 VDC	250 mA			85 %
TEL 6-4822 *		+12 VDC	250 mA	-12 VDC	250 mA	86 %
TEL 6-4823 *		+15 VDC	200 mA	-15 VDC	200 mA	86 %

Note * End of life

Input Specifications

Input Current	- At no load	9 Vin models: 15 mA typ. 12 Vin models: 12 mA typ. 24 Vin models: 10 mA typ. 48 Vin models: 10 mA typ.
	- At full load	9 Vin models: 783 mA typ. 12 Vin models: 599 mA typ. 24 Vin models: 297 mA typ. 48 Vin models: 148 mA typ.
Surge Voltage		9 Vin models: 20 VDC max. (1 s max.) 12 Vin models: 25 VDC max. (1 s max.) 24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.)
Under Voltage Lockout		9 Vin models: 3 VDC min. / 3.5 VDC typ. 12 Vin models: 5.5 VDC min. / 6.5 VDC typ. 24 Vin models: 12 VDC min. / 15.5 VDC typ. 48 Vin models: 26 VDC min. / 30 VDC typ.
Reflected Ripple Current		50 mAp-p typ.
Recommended Input Fuse		9 Vin models: 3'150 mA (slow blow) 12 Vin models: 2'000 mA (slow blow) 24 Vin models: 1'000 mA (slow blow) 48 Vin models: 315 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type

Output Specifications

Voltage Set Accuracy		±2% max.
Regulation	- Input Variation (Vmin - Vmax)	single output models: 0.5% max. dual output models: 0.5% max. (Output 1) 1% max. (Output 2)
	- Load Variation (5 - 100%)	single output models: 1% max. dual output models: 1% max. (Output 1) 1.5% max. (Output 2)
	- Cross Regulation (25% / 100% asym. load)	dual output models: 5% max.
Ripple and Noise (20 MHz Bandwidth)	- single output	48 Vin models: 100 mVp-p max. 5 Vout models: 65 mVp-p max. 12 Vout models: 65 mVp-p max. 15 Vout models: 65 mVp-p max. 24 Vout models: 65 mVp-p max.
	- dual output	12 / -12 Vout models: 75 / 75 mVp-p max. 15 / -15 Vout models: 75 / 75 mVp-p max.
Capacitive Load	- single output	5 Vout models: 1'000 µF max. 12 Vout models: 470 µF max. 15 Vout models: 220 µF max. 24 Vout models: 100 µF max.
	- dual output	12 / -12 Vout models: 330 / 330 µF max. 15 / -15 Vout models: 220 / 220 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.03 %/K max.
Start-up Time		150 ms max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		110 - 230% of Iout max.
		160% typ. of Iout max.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Transient Response	- Response Deviation	5% typ. / 8% max. (25% Load Step) (5 Vout models)
	- Response Time	300 µs typ. / 500 µs max. (25% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/tel6
Pollution Degree		PD 2

EMC Specifications

EMI Emissions	- Conducted Emissions	EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	- Radiated Emissions	EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	External filter proposal:	www.tracopower.com/overview/tel6 (Note: Class A emissions can be met using only a single input capacitor.)
EMS Immunity	- Electrostatic Discharge	Air: EN 61000-4-2, ±8 kV, perf. criteria A Contact: EN 61000-4-2, ±6 kV, perf. criteria A
	- RF Electromagnetic Field	EN 61000-4-3, 20 V/m, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-4, ±2 kV, perf. criteria A EN 61000-4-5, ±2 kV, perf. criteria A
	- Conducted RF Disturbances	External filter proposal: www.tracopower.com/overview/tel6 EN 61000-4-6, 10 Vrms, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +85°C
	- Case Temperature	+105°C max.
	- Storage Temperature	-55°C to +125°C
Power Derating	- High Temperature	Depending on model
		See application note: www.tracopower.com/overview/tel6
Cooling System		Natural convection (20 LFM)
Altitude During Operation		5'000 m max.
Regulator Topology		Flyback Converter
Switching Frequency		36 - 427 kHz (PWM, PFM) (Above 50% load PWM is used, below 50% load PFM is used)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'500 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	2'200 pF typ.
Reliability	- Calculated MTBF	1'000'000 h (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Environment	- Vibration	IEC 60068-2-6 5 g, 3 axis, random waveform, 10-150 Hz
	- Mechanical Shock	IEC 60068-2-27 15 g, 3 axis, half sine, 11 ms
	- Thermal Shock	IEC 60068-2-14
Housing Material		Alu alloy, black anodized coating
Base Material		Rynite® FR530 BK507
Potting Material		Epoxy (UL 94 V-0 rated)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.


Pin Material	Brass
Pin Foundation Plating	Nickel (1 - 3 μm)
Pin Surface Plating	Gold (50 - 75 nm), glossy
Housing Type	Metal Case
Mounting Type	PCB Mount
Connection Type	THD (Through-Hole Device)
Footprint Type	DIP16
Soldering Profile	Lead-Free Wave Soldering 265°C / 10 s max.
Weight	7.5 g
Thermal Impedance	- Case to Ambient 20 K/W typ. (at V_{in} min.)
Environmental Compliance	- REACH Declaration www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant - RoHS Declaration www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule)) - SCIP Reference Number c854e753-2226-42b6-acbb-a4745141b4a8

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tel6

Outline Dimensions



Dimensions in mm (inch)
Pin diameter tolerances: ± 0.10 (± 0.004)
General tolerances: ± 0.50 (± 0.020)

Pinout		
Pin	Single	Dual
1	-Vin (GND)	
8	NTC	Common
9	+Vout	
10	-Vout	
16	+Vin (Vcc)	

NTC: Not to connect