


- **Highest power density:**  
40 W in 1" x 2" x 0.4" package
- **Excellent efficiency up to 92 %**
- **Output voltage adjustable**
- **Remote On/Off**
- **Short circuit protection**
- **Over voltage protection**
- **I/O isolation 1500 VDC**
- **Operating temperature range**  
-40°C to +80°C
- **Fully RoHS compliant**
- **3-year product warranty**



The TEN 40N Series is a new range of isolated high performance DC/DC converter modules. Due to the very high efficiency of up to 92% these 40 W converters come with a footprint of only 1.0" x 2.0". The 15 models have a wide 2:1 input voltage range and a tight output voltage regulation. The output voltage is adjustable by external resistor. Remote On/Off and protection against overpower and overvoltage are standard features of these converters. Typical applications are in mobile equipment, instrumentation, distributed power architectures in communication and industrial electronics and everywhere where space on the PCB is critical.

Models						
Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I <sub>max</sub>	Vnom	I <sub>max</sub>	
TEN 40-1210N	9 - 18 VDC (12 VDC nom.)	3.3 VDC	8'000 mA			89 %
TEN 40-1211N		5 VDC	8'000 mA			89 %
TEN 40-1212N		12 VDC	3'330 mA			89 %
TEN 40-1213N		15 VDC	2'670 mA			90 %
TEN 40-1215N		24 VDC	1'670 mA			91 %
TEN 40-1222N		+12 VDC	1'670 mA	-12 VDC	1'670 mA	88 %
TEN 40-1223N		+15 VDC	1'330 mA	-15 VDC	1'330 mA	88 %
TEN 40-2410N	18 - 36 VDC (24 VDC nom.)	3.3 VDC	8'000 mA			90 %
TEN 40-2411N		5 VDC	8'000 mA			91 %
TEN 40-2412N		12 VDC	3'330 mA			91 %
TEN 40-2413N		15 VDC	2'670 mA			91 %
TEN 40-2415N		24 VDC	1'670 mA			91 %
TEN 40-2422N		+12 VDC	1'670 mA	-12 VDC	1'670 mA	89 %
TEN 40-2423N		+15 VDC	1'330 mA	-15 VDC	1'330 mA	89 %
TEN 40-4810N	36 - 75 VDC (48 VDC nom.)	3.3 VDC	8'000 mA			90 %
TEN 40-4811N		5 VDC	8'000 mA			91 %
TEN 40-4812N		12 VDC	3'330 mA			92 %
TEN 40-4813N		15 VDC	2'670 mA			92 %
TEN 40-4815N		24 VDC	1'670 mA			91 %
TEN 40-4822N		+12 VDC	1'670 mA	-12 VDC	1'670 mA	89 %
TEN 40-4823N		+15 VDC	1'330 mA	-15 VDC	1'330 mA	89 %

Options	
TEN-HS4	- Optional Heat Sink: <a href="http://www.tracopower.com/overview/ten-hs4">www.tracopower.com/overview/ten-hs4</a>
TEN-HS6	- Optional Heat Sink: <a href="http://www.tracopower.com/overview/ten-hs6">www.tracopower.com/overview/ten-hs6</a>

**Input Specifications**

Input Current	- At no load	12 Vin models: <b>120 mA typ.</b> (3.3 Vout model) <b>160 mA typ.</b> (5 Vout model) <b>160 mA typ.</b> (12 Vout model) <b>150 mA typ.</b> (15 Vout model) <b>160 mA typ.</b> (24 Vout model) <b>70 mA typ.</b> (12 / -12 Vout model) <b>60 mA typ.</b> (15 / -15 Vout model)
		24 Vin models: <b>75 mA typ.</b> (3.3 Vout model) <b>80 mA typ.</b> (5 Vout model) <b>85 mA typ.</b> (12 Vout model) <b>75 mA typ.</b> (15 Vout model) <b>85 mA typ.</b> (24 Vout model) <b>50 mA typ.</b> (12 / -12 Vout model) <b>45 mA typ.</b> (15 / -15 Vout model)
		48 Vin models: <b>40 mA typ.</b> (3.3 Vout model) <b>50 mA typ.</b> (5 Vout model) <b>50 mA typ.</b> (12 Vout model) <b>50 mA typ.</b> (15 Vout model) <b>50 mA typ.</b> (24 Vout model) <b>65 mA typ.</b> (12 / -12 Vout model) <b>65 mA typ.</b> (15 / -15 Vout model)
	- At full load	12 Vin models: <b>2'470 mA max.</b> (3.3 Vout model) <b>3'750 mA max.</b> (5 Vout model) <b>3'750 mA max.</b> (12 Vout model) <b>3'700 mA max.</b> (15 Vout model) <b>3'670 mA max.</b> (24 Vout model) <b>3'790 mA max.</b> (12 / -12 Vout model) <b>3'790 mA max.</b> (15 / -15 Vout model)
		24 Vin models: <b>1'220 mA max.</b> (3.3 Vout model) <b>1'830 mA max.</b> (5 Vout model) <b>1'830 mA max.</b> (12 Vout model) <b>1'830 mA max.</b> (15 Vout model) <b>1'835 mA max.</b> (24 Vout model) <b>1'870 mA max.</b> (12 / -12 Vout model) <b>1'870 mA max.</b> (15 / -15 Vout model)
		48 Vin models: <b>610 mA max.</b> (3.3 Vout model) <b>920 mA max.</b> (5 Vout model) <b>910 mA max.</b> (12 Vout model) <b>910 mA max.</b> (15 Vout model) <b>918 mA max.</b> (24 Vout model) <b>940 mA max.</b> (12 / -12 Vout model) <b>940 mA max.</b> (15 / -15 Vout model)
Surge Voltage		12 Vin models: <b>25 VDC max.</b> (100 ms max.) 24 Vin models: <b>50 VDC max.</b> (100 ms max.) 48 Vin models: <b>100 VDC max.</b> (100 ms max.)
Under Voltage Lockout		12 Vin models: <b>8.3 VDC typ.</b> 24 Vin models: <b>16.5 VDC typ.</b> 48 Vin models: <b>33 VDC typ.</b>
Reflected Ripple Current		12 Vin models: <b>50 mA<sub>p-p</sub> typ.</b> 24 Vin models: <b>30 mA<sub>p-p</sub> typ.</b> 48 Vin models: <b>20 mA<sub>p-p</sub> typ.</b>

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.



Transient Response	- Response Deviation - Response Time	3% typ. / 5% max. (75% to 100% Load Step) 250 µs typ. (75% to 100% Load Step)
--------------------	---	--

### Safety Specifications

Standards	- IT / Multimedia Equipment  - Certification Documents	CSA-C22.2, No. 60950-1 EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1 <a href="http://www.tracopower.com/overview/ten40n">www.tracopower.com/overview/ten40n</a>
Pollution Degree		PD 3
Over Voltage Category		Not mains connected

### EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class A (with external filter) External filter proposal: <a href="http://www.tracopower.com/overview/ten40n">www.tracopower.com/overview/ten40n</a>
EMS (Immunity)	- Electrostatic Discharge  - RF Electromagnetic Field - EFT (Burst) / Surge  - Conducted RF Disturbances	EN 55024 (IT Equipment) EN 55035 (Multimedia) Air: EN 61000-4-2, ±8 kV, perf. criteria B Contact: EN 61000-4-2, ±6 kV, perf. criteria B EN 61000-4-3, 10 V/m, perf. criteria A EN 61000-4-4, ±2 kV, perf. criteria A EN 61000-4-5, ±1 kV, perf. criteria B Ext. input component: KXG 330 µF, 200 V EN 61000-4-6, 10 Vrms, perf. criteria A

### General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Case Temperature - Storage Temperature	-40°C to +80°C +105°C max. -50°C to +125°C
Power Derating	- High Temperature	Depending on model See application note: <a href="http://www.tracopower.com/overview/ten40n">www.tracopower.com/overview/ten40n</a>
Over Temperature Protection Switch Off	- Protection Mode	110°C typ.
Cooling System		Natural convection (20 LFM)
Remote Control	- Voltage Controlled Remote (passive = on)  - Off Idle Input Current - Remote Pin Input Current	On: 3.5 to 12 VDC or open circuit Off: 0 to 1.2 VDC or short circuit Refers to 'Remote' and '-Vin' Pin 2.5 mA typ. -0.5 to 0.5 mA
Altitude During Operation		6'000 m max.
Switching Frequency		285 kHz typ. (PWM) (24 Vout models) 320 kHz typ. (PWM) (other models)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s - Input to Output, 1 s	1'500 VDC 1'800 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	1'500 pF max.
Reliability	- Calculated MTBF	328'000 h (ML-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline <a href="http://www.tracopower.com/info/cleaning.pdf">www.tracopower.com/info/cleaning.pdf</a>
Housing Material		Alu alloy, black anodized coating
Base Material		Non-conductive FR4 (UL 94 V-0 rated)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.


Potting Material	Epoxy (UL 94 V-0 rated)
Pin Material	Copper Alloy (C6801)
Pin Foundation Plating	Nickel (2.5 µm min.)
Pin Surface Plating	Gold (75 - 125 nm), glossy
Housing Type	Metal Case
Mounting Type	PCB Mount
Connection Type	THD (Through-Hole Device)
Footprint Type	2" x 1"
Soldering Profile	Lead-Free Wave Soldering 260°C / 10 s max.
Weight	30 g
Thermal Impedance	- Case to Ambient 12 K/W typ. 10 K/W typ. (with Heat Sink)
Environmental Compliance	- REACH Declaration <a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a> REACH SVHC list compliant REACH Annex XVII compliant - RoHS Declaration <a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a> Exemptions: 7a (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).) - SCIP Reference Number 9975c105-3aca-40b8-82cc-db9489b95dde

### Supporting Documents

Overview Link (for additional Documents)

[www.tracopower.com/overview/ten40n](http://www.tracopower.com/overview/ten40n)

### Outline Dimensions



h=11.0 (0.43) for 24 VDC output models  
h=10.2 (0.40) for other models

Dimensions in mm (inch)

Tolerances: x.x ±0.25 (x.xx ±0.01)

x.xx ±0.13 (x.xxx ±0.005)

Pin diameter tolerances: x.x ±0.05 (x.xx ±0.002)

### Pinout

Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	Remote On/Off	Remote On/Off
4	+Vout	+Vout
5	-Vout	Common
6	Trim	-Vout