

- Supplementary and reinforced insulation
- I/O isolation 4000 VACrms rated for 300 Vrms working voltage
- 2 x MOOP Medical safety according to AAMI/ANSI ES 60601-1:2005(R) and IEC/EN 60601-1 3rd edition
- Industrial safety to UL/IEC/EN 62368-1
- Wide 2:1 input voltage ranges
- Extended operating temperature range –40°C to 75°C max.
- Input filter meets EN55022, class A
- Continuous short-circuit protection
- High reliability
- 3-year product warranty



The THB 10 series is a range of high performance DC/DC converter modules with double reinforced insulation system. It complies to latest medical safety standard IEC 60601-1 3rd edition for MOOP (Means of Operator Protection). The product comes in a 2"x1" industry standard package. All 12 models features wide 2:1 input voltage range and fully regulated output voltage. The converters offer an economical solution for demanding applications in industrial and medical instrumentation.

Models						
Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
THB 10-1211	9 - 18 VDC (12 VDC nom.)	5.1 VDC	1'600 mA			75 %
THB 10-1212		12 VDC	835 mA			80 %
THB 10-1222		+12 VDC	417 mA	-12 VDC	417 mA	80 %
THB 10-1223		+15 VDC	333 mA	-15 VDC	333 mA	81 %
THB 10-2411	18 - 36 VDC (24 VDC nom.)	5.1 VDC	2'000 mA			76 %
THB 10-2412		12 VDC	835 mA			81 %
THB 10-2422		+12 VDC	417 mA	-12 VDC	417 mA	81 %
THB 10-2423		+15 VDC	333 mA	-15 VDC	333 mA	82 %
THB 10-4811	36 - 75 VDC (48 VDC nom.)	5.1 VDC	2'000 mA			76 %
THB 10-4812		12 VDC	835 mA			81 %
THB 10-4822		+12 VDC	417 mA	-12 VDC	417 mA	81 %
THB 10-4823		+15 VDC	333 mA	-15 VDC	333 mA	82 %

Input Specifications

Input Current	- At no load	12 Vin models: 30 mA typ. 24 Vin models: 20 mA typ. 48 Vin models: 10 mA typ.
	- At full load	12 Vin models: 905 mA typ. (5.1 Vout model) 1'040 mA typ. (12 Vout model) 1'040 mA typ. (12 / -12 Vout model) 1'040 mA typ. (15 / -15 Vout model) 24 Vin models: 560 mA typ. (5.1 Vout model) 515 mA typ. (12 Vout model) 515 mA typ. (12 / -12 Vout model) 515 mA typ. (15 / -15 Vout model) 48 Vin models: 280 mA typ. (5.1 Vout model) 255 mA typ. (12 Vout model) 255 mA typ. (12 / -12 Vout model) 255 mA typ. (15 / -15 Vout model)
Surge Voltage		12 Vin models: 25 VDC max. (1 s max.) 24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.)
Start-up Voltage		12 Vin models: 7 VDC min. / 8 VDC typ. / 9 VDC max. 24 Vin models: 13 VDC min. / 15 VDC typ. / 18 VDC max. 48 Vin models: 30 VDC min. / 33 VDC typ. / 36 VDC max.
Under Voltage Lockout		12 Vin models: 8.5 VDC max. 24 Vin models: 16 VDC max. 48 Vin models: 34 VDC max.
Reflected Ripple Current		12 Vin models: 100 mA typ. 24 Vin models: 50 mA typ. 48 Vin models: 25 mA typ.
Recommended Input Fuse		12 Vin models: 3'000 mA (slow blow) 24 Vin models: 1'500 mA (slow blow) 48 Vin models: 750 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type
Short Circuit Input Power		3 W max.

Output Specifications

Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	single output models: 0.5% max. dual output models: 0.5% max.
	- Load Variation (15 - 100%)	single output models: 1% max. dual output models: 1% max. (Output 1) 1% max. (Output 2)
Ripple and Noise (20 MHz Bandwidth)	- single output	5.1 Vout models: 100 mVp-p max. 12 Vout models: 150 mVp-p max.
	- dual output	12 / -12 Vout models: 150 / 150 mVp-p max. 15 / -15 Vout models: 150 / 150 mVp-p max.
	- single output	5.1 Vout models: 1'000 µF max. 12 Vout models: 470 µF max.
Capacitive Load	- single output	5.1 Vout models: 1'000 µF max. 12 Vout models: 470 µF max.
	- dual output	12 / -12 Vout models: 220 / 220 µF max. 15 / -15 Vout models: 220 / 220 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.05 %/K max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		120% min. of Iout max. 150% typ. of Iout max.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Transient Response	- Response Deviation	3% typ. / 5% max. (75% to 100% Load Step)
	- Response Time	300 µs typ. / 600 µs max. (75% to 100% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment	CSA-C22.2, No. 60950-1 EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Medical Equipment	EN 60601-1 IEC 60601-1 ANSI/AAMI ES 60601-1 CSA-C22.2, No 60601-1 2 x MOOP (Means Of Operator Protection) MOPP (Means Of Patient Protection)
	- Certification Documents	www.tracopower.com/overview/thb10
Pollution Degree		PD 3
Over Voltage Category		Not mains connected

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 60601-1-2 edition 4 (Medical Devices)
	- Radiated Emissions	EN 55011 class A (with external filter) EN 55011 class A (with external filter)
	External filter proposal:	www.tracopower.com/overview/thb10
EMS (Immunity)	- Electrostatic Discharge	EN 60601-1-2 edition 4 (Medical Devices) Air: EN 61000-4-2, ±15 kV, perf. criteria A Contact: EN 61000-4-2, ±8 kV, perf. criteria A
	- RF Electromagnetic Field	EN 61000-4-3, 10 V/m, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-4, ±2 kV, perf. criteria A EN 61000-4-5, ±1 kV, perf. criteria A
		Ext. input component: 330 µF / 35 V (12 Vin models) 330 µF / 50 V (24 Vin models) 330 µF / 100 V (48 Vin models)
	- Conducted RF Disturbances	EN 61000-4-6, 10 Vrms, perf. criteria A
	- PF Magnetic Field	Continuous: EN 61000-4-8, 30 A/m, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +75°C
	- Case Temperature	+95°C max.
	- Storage Temperature	-50°C to +125°C
Power Derating	- High Temperature	2.85 %/K above 60°C
		See application note: www.tracopower.com/overview/thb10
Cooling System		Natural convection (20 LFM)
Altitude During Operation		5'000 m max.
Switching Frequency		120 - 180 kHz (PWM)
		150 kHz typ. (PWM)
Insulation System		Reinforced Insulation
Working Voltage (rated)		300 VAC (acc. to IEC/EN 60601-1)
		1000 VAC (acc. to IEC/EN 62368-1, 60950-1)
Isolation Test Voltage	- Input to Output, 60 s	4'200 VAC
Isolation Resistance	- Input to Output, 500 VDC	10'000 MΩ min.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Isolation Capacitance	- Input to Output, 100 kHz, 1 V	60 pF typ. 80 pF max.
Leakage Current	- Earth Leakage Current	10 µA max.
Reliability	- Calculated MTBF	1'000'000 h (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Housing Material		Non-conductive Plastic (UL 94 V-0 rated)
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Copper Alloy (C6801)
Pin Foundation Plating		Nickel (2.5 µm min.)
Pin Surface Plating		Gold (75 - 125 nm), glossy
Housing Type		Plastic Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		2" x 1"
Soldering Profile		Lead-Free Wave Soldering 260°C / 10 s max.
Weight		24.5 g
Environmental Compliance	- REACH Declaration	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant
	- RoHS Declaration	www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7(a) (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule.))
	- SCIP Reference Number	6643ce60-44b4-4d3b-b3d0-21abce17c45b


Supporting Documents

Overview Link (for additional Documents)


www.tracopower.com/overview/thb10

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



Dimensions in mm (inch)
 Tolerances: x.x ±0.5 (x.xx ±0.02)
 x.xx ±0.25 (x.xxx ±0.01)
 Pin diameter tolerances: x.x ±0.05 (x.xx ±0.002)



Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	No pin	Common
5	-Vout	-Vout