


- Slim profile, for DIN-rail mounting
- Alternative side-mounting for flat panels
- High power factor by active power correction
- Very high efficiency up to 95%
- Power Back immunity
- 150% peak current for 4 s
- Operating temperature range: -40°C to +70°C max.
- Adjustable output voltage
- Short circuit and overload protection
- 3-year product warranty



This generation of DIN-rail power supplies combines the most efficient circuit topology with optimized cost/performance ratio for industrial environments and for electrical control cabinets. They have a very high efficiency of up to 95.0% which allows a very slim package design. The output voltage is adjustable from -2% to +17%. The case offers the potentially useful feature to fix the DIN-rail clip to the side wall for the mounting inside flat panels. Over a period of minimum 4 seconds they can operate with a boost power of 150%. The boost power facilitates the activation of stepper motors, solenoids or actuators. The units operate with a high power factor of up to 99% by active power factor correction which also keeps the input inrush current low. The TIB series are also available with lower nominal power of 80, 120 or 240 Watt (+50% boost power). They come with the safety standard approvals for IEC/EN/UL 62368-1, IEC/EN/UL 61010-1 and UL 508.

Models

| Order Code | Output Power max. | Output Voltage nom. (adjustable) | Output Current max. | Output Current peak | Efficiency typ. |
|-------------|-------------------|----------------------------------|---------------------|---------------------|-----------------|
| TIB 480-124 | 480 W | 24 VDC (23.5 - 28.0 VDC) | 20'000 mA | 30'000 mA | 95 % |
| TIB 480-148 | | 48 VDC (47.0 - 56.0 VDC) | 10'000 mA | 15'000 mA | 95 % |

Options

| | |
|---|---|
| TIB-RMK01 | - Optional Ruggedized DIN-Rail Mounting Clip for EN 61373: www.tracopower.com/overview/tib-rmk01 |
| on demand (backorder with MOQ non stocking item) | - Optional models with certified DC input |

Input Specifications

| | | |
|------------------------|---------------------------|--|
| Input Voltage | - AC Range | Operational Range: 85 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range) |
| | - DC Range | Operational Range: 90 - 350 VDC Certified Range: 100 - 250 VDC Polarity: +DC: L / -DC: N (Models with certified DC input are on-demand.) |
| Input Frequency | | Operational Range: 45 - 65 Hz Certified: 50/60 Hz |
| Power Consumption | - No load & Vin = 230 VAC | 3'500 mW max. |
| | - No load & Vin = 115 VAC | 4'900 mW max. |
| Input Inrush Current | - At 230 VAC | 30 A max. |
| | - At 115 VAC | 15 A max. |
| Power Factor | - At 230 VAC | 0.97 min. (Active Power Factor Correction) |
| | - At 115 VAC | 0.99 min. (Active Power Factor Correction) |
| Recommended Input Fuse | | (The need of an external fuse has to be assessed in the final application.) |

Output Specifications

| | | |
|--|---------------------------------|--|
| Output Voltage Adjustment | | 24 VDC model: 23.5 - 28.0 VDC 48 VDC model: 47.0 - 56.0 VDC (By trim potentiometer) Output power must not exceed rated power! |
| | | ±0.25% max. |
| Voltage Set Accuracy | | ±0.25% max. |
| Regulation | - Input Variation (Vmin - Vmax) | 0.1% max. |
| | - Load Variation (10 - 90%) | 0.5% max. |
| Boost Power | | Output Current peak: See model table Peak power time: 4 s max. (auto switch off) Off Time: 10 s typ. |
| Ripple and Noise (20 MHz Bandwidth) | | 24 VDC model: 100 mVp-p max. 48 VDC model: 200 mVp-p max. |
| | | Infinite |
| Capacitive Load | | Infinite |
| Minimum Load | | Not required |
| Temperature Coefficient | | ±0.02 %/K max. |
| Hold-up Time | - At 230 VAC | 20 ms min. |
| | - At 115 VAC | 20 ms min. |
| Start-up Time | - At 230 VAC | 2'000 ms max. |
| | - At 115 VAC | 2'000 ms max. |
| Short Circuit Protection | | Continuous, Automatic recovery |
| Overload Protection | | Constant Current Mode Switch off after 4 s delay, automatic restart |
| Output Current Limitation | | 155% min. of Iout max. |
| Overvoltage Protection | | 117 - 146% of Vout nom. (depending on model) 32 - 35 VDC (24 VDC model) 56 - 60 VDC (48 VDC model) (In case of an internal error a second voltage regulation loop keeps the output voltage at a save level, the power supply turns off and tries to restart after 10 s.) |
| Transient Response | - Peak Variation | 600 mV max. (10% to 90% Load Step) |
| | - Response Time | 5'000 µs typ. (10% to 90% Load Step) |

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Safety Specifications

| | | |
|-----------------------|---|---|
| Standards | - IT / Multimedia Equipment - Industrial Control Equipment - Measurement, Control & Lab. - Certification Documents | EN 62368-1 IEC 62368-1 UL 62368-1 UL 508 EN 61010-1 EN 61010-2-201 IEC 61010-1 IEC 61010-2-201 UL 61010-1 UL 61010-2-201 www.tracopower.com/overview/tib480 |
| Protection Class | | Class I (Prepared): Connection to PE |
| Pollution Degree | | PD 2 |
| Over Voltage Category | | OVC II |

EMC Specifications

| | | |
|---------------------|--|---|
| EMI (Emissions) | - Conducted Emissions - Radiated Emissions - Harmonic Current Emissions | EN 61000-6-3 (Generic Residential) EN 61204-3 (Low Voltage Power Supplies) EN 50121-3-2 (EMC for Rolling Stock) EN 50121-4 (Railway Application Signalling) EN 55011 class B (internal filter) EN 55032 class B (internal filter) EN 55011 class B (internal filter) EN 55032 class B (internal filter) EN 61000-3-2, class A |
| EMS (Immunity) | - Electrostatic Discharge - RF Electromagnetic Field - EFT (Burst) / Surge - Conducted RF Disturbances - PF Magnetic Field - Voltage Dips & Interruptions - Voltage Sag Immunity | EN 61000-6-2 (Generic Industrial) EN 61204-3 (Low Voltage Power Supplies) EN 50121-3-2 (EMC for Rolling Stock) EN 50121-4 (Railway Application Signalling) Air: EN 61000-4-2, ± 8 kV, perf. criteria A Contact: EN 61000-4-2, ± 4 kV, perf. criteria A EN 61000-4-3, 10 V/m, perf. criteria A EN 61000-4-4, ± 2 kV, perf. criteria B L to L: EN 61000-4-5, ± 1 kV, perf. criteria B L to PE: EN 61000-4-5, ± 2 kV, perf. criteria B EN 61000-4-6, 10 Vrms, perf. criteria A Continuous: EN 61000-4-8, 30 A/m, perf. criteria A 230 VAC / 50 Hz: EN 61000-4-11 20%, 250 periods, perf. criteria C 30%, 25 periods, perf. criteria C 60%, 10 periods, perf. criteria C >95%, 1 period, perf. criteria B >95%, 5 periods, perf. criteria C 115 VAC / 60 Hz: EN 61000-4-11 20%, 250 periods, perf. criteria C 30%, 25 periods, perf. criteria C 60%, 10 periods, perf. criteria C >95%, 1 period, perf. criteria B >95%, 5 periods, perf. criteria C SEMI F47, criteria A |
| EMC / Environmental | - Certification Documents | www.tracopower.com/overview/tib480 |

General Specifications

| | | |
|--------------------|-------------------------|---------------------------|
| Relative Humidity | | 95% max. (non condensing) |
| Temperature Ranges | - Operating Temperature | -40°C to +70°C |

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

| | | |
|--|--|--|
| Power Derating | - High Temperature - Low Input Voltage | 2 %/K above 60°C (at standard operation) 3 %/K above 60°C (at peak power mode) 3 %/V below 90 VAC (at standard operation) 1.5 %/V below 100 VAC (at peak power mode) 1 %/V below 110 VDC (48 Vout DC model) 1 %/V below 100 VDC (other DC models) |
| Over Temperature Protection Switch Off | - Protection Mode | Automatic recovery |
| Cooling System | | Natural convection (20 LFM) |
| Remote Control | - Voltage Controlled Remote | See application note: www.tracopower.com/overview/tib480 (The unit can be controlled by external relay contact or open collector signal.) |
| Altitude During Operation | | 2'000 m max. |
| Regulator Topology | | LCC Converter |
| Switching Frequency | | 70 - 90 kHz (PWM) |
| Insulation System | | Reinforced Insulation |
| Isolation Test Voltage | - Input to Output, 60 s - Input to Case or PE, 60 s - Output to Case or PE, 60 s | 3'000 VAC 1'500 VAC 750 VDC |
| Creepage | - Input to Output - Input to Case or PE - Output to Case or PE | 8 mm min. 4 mm min. 1.5 mm min. |
| Clearance | - Input to Output - Input to Case or PE - Output to Case or PE | 8 mm min. 4 mm min. 1.5 mm min. |
| Isolation Resistance | - Input to Output, 500 VDC | 4'000 MΩ min. |
| Leakage Current | - Earth Leakage Current - Touch Current | 3500 μA max. 880 μA max. |
| Reliability | - Calculated MTBF | 1'000'000 h (IEC 61709) |
| Environment | - Vibration - Mechanical Shock - Mechanical Shock | EN 61373 IEC 60068-2-6 2 g, 3 axis, sine sweep, 10-55 Hz, 11 oct/min (Compliance to EN 61373 only with optional DIN-Rail Clip TIB-RMK01) EN 61373 IEC 60068-2-27 25 g, 3 axis, half sine, 11 ms (Compliance to EN 61373 only with optional DIN-Rail Clip TIB-RMK01) |
| Housing Material | | Aluminum (Chassis) Stainless Steel (Cover) |
| Housing Type | | Metal Case |
| Mounting Type | | DIN-Rail Mount (EN 60715 - 35x7.5mm/35x15mm) |
| Connection Type | | Screw Terminal |
| Weight | | 1'018 g |
| Thermal Impedance | - Case to Ambient | 0.6 K/W typ. |
| Power Back Immunity | | 24 VDC model: 35 V max. 48 VDC model: 60 V max. (When external voltage is supplied above set output voltage and below OVP threshold, the power supply will function normally without switch off or destruction, even if external voltage is applied continuously.) |

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.


| | | |
|---|--|--|
| Power OK Signal - Trigger Threshold - Power OK - Power Off - Pin Specifications | 24 VDC model: 21 - 23 VDC 48 VDC model: 42 - 46 VDC | Relay Output 21 - 23 VDC 42 - 46 VDC Relay contact closed Relay contact open 30 VDC / 1 A max. |
| Status Indicator | Also indicated by green LEDs: front and side | |
| Environmental Compliance - REACH Declaration - RoHS Declaration - SCIP Reference Number | www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7(a), 7(c)-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule)) 01ea7faa-024f-4f9e-962c-7a89c50c26b2 | |

Supporting Documents

Overview Link (for additional Documents)


www.tracopower.com/overview/tib480

Blockdiagram



All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



Alternative side mounting

