

- Encased 150 W power supply with screw connection 2.44" x 4.6" package
- Certification according to IEC/EN/ES 60601-1 edition 3.2 for 2 x MOPP
- Low leakage current <100 µA rated for BF applications
- Risk management process according to ISO 14971 incl. risk management file
- Acceptance criteria for electronic assemblies acc. to IPC-A-610 Level 3
- Active power factor correction >0.95
- Protection class I and II prepared
- Operating up to 5000 m altitude
- 5-year product warranty



The TPP 150 series of 150 Watt AC/DC encased power supplies feature a reinforced double I/O isolation system according to latest medical safety standards (60601-1 edition 3.2, 2 x MOPP). The earth leakage current is below 100 µA which makes the units suitable for BF (body floating) applications. The excellent efficiency of up to 92% allows a high power density for the standard 2.44" x 4.6" packaging format. The full load operating temperature range is -25°C to +70°C while it goes up to 80°C with 40% load derating. The EMC characteristic is dedicated for applications in industrial and domestic medical fields. High reliability is provided by the use of industrial quality grade components and an excellent thermal management. It makes the products an ideal solution for medical devices and for demanding safety and space critical applications.

Models				
Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 150-112	150 W	12 VDC (10.8 - 13.2 VDC)	12'500 mA	91 %
TPP 150-115		15 VDC (13.5 - 16.5 VDC)	10'000 mA	92 %
TPP 150-124		24 VDC (21.6 - 26.4 VDC)	6'250 mA	92 %
TPP 150-128		28 VDC (25.2 - 30.8 VDC)	5'360 mA	92 %
TPP 150-136		36 VDC (32.4 - 39.6 VDC)	4'170 mA	92 %
TPP 150-148		48 VDC (43.2 - 52.8 VDC)	3'130 mA	92 %

### Input Specifications

Input Voltage	- AC Range	Operational Range: <b>85 - 264 VAC</b> (Full Range) Rated Range: <b>100 - 240 VAC</b> (Full Range)
	- DC Range	Operational Range: <b>120 - 370 VDC</b> (Designed for, no certification) Polarity: <b>+DC: L / -DC: N</b>
Input Frequency		Operational Range: <b>47 - 440 Hz</b> Certified: <b>50/60 Hz</b>
Power Consumption	- No load & Vin = 230 VAC	<b>1'000 mW max.</b>
	- No load & Vin = 115 VAC	<b>1'000 mW max.</b>
Input Current	- Full load & Vin = 230 VAC	<b>800 mA max.</b>
	- Full load & Vin = 115 VAC	<b>1'700 mA max.</b>
Input Inrush Current	- At 230 VAC	<b>60 A max.</b>
	- At 115 VAC	<b>35 A max.</b>
Power Factor	- At 230 VAC	<b>0.95 min.</b> (Active Power Factor Correction)
	- At 115 VAC	<b>0.95 min.</b> (Active Power Factor Correction)
Input Protection		<b>T 3.15 A / 250 VAC</b> (Internal Fuse in L & N)
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)

### Output Specifications

Output Voltage Adjustment		<b>±10%</b> (By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		<b>±1% max.</b>
Regulation	- Input Variation (Vmin - Vmax)	<b>0.2% max.</b>
	- Load Variation (0 - 100%)	<b>0.5% max.</b>
Ripple and Noise (20 MHz Bandwidth)	12 VDC model:	<b>120 mVp-p typ.</b> (w/ 1 µF X7R)
	15 VDC model:	<b>150 mVp-p typ.</b> (w/ 1 µF X7R)
	24 VDC model:	<b>220 mVp-p typ.</b> (w/ 1 µF X7R)
	28 VDC model:	<b>220 mVp-p typ.</b> (w/ 1 µF X7R)
	36 VDC model:	<b>250 mVp-p typ.</b> (w/ 1 µF X7R)
	48 VDC model:	<b>250 mVp-p typ.</b> (w/ 0.1 µF X7R)
Capacitive Load	12 VDC model:	<b>10'400 µF max.</b>
	15 VDC model:	<b>6'600 µF max.</b>
	24 VDC model:	<b>2'600 µF max.</b>
	28 VDC model:	<b>1'900 µF max.</b>
	36 VDC model:	<b>1'150 µF max.</b>
	48 VDC model:	<b>650 µF max.</b>
Minimum Load		<b>Not required</b>
Temperature Coefficient		<b>±0.02 %/K max.</b>
Hold-up Time	- At 230 VAC	<b>16 ms min.</b>
	- At 115 VAC	<b>16 ms min.</b>
Start-up Time	- At 230 VAC	<b>1'000 ms max.</b>
	- At 115 VAC	<b>1'000 ms max.</b>
Short Circuit Protection		<b>Continuous, Automatic recovery</b>
Output Current Limitation		<b>115 - 150% of Iout max.</b>
Overvoltage Protection		<b>115 - 135% of Vout nom.</b>
Transient Response	- Response Deviation	<b>3% max.</b> (50% to 75% Load Step)
	- Response Time	<b>500 µs typ.</b> (50% to 75% Load Step)

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

## Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Medical Equipment	EN 60601-1 IEC 60601-1 ANSI/AAMI ES 60601-1 2 x MOPP (Means Of Patient Protection) <a href="http://www.tracopower.com/overview/tpp150">www.tracopower.com/overview/tpp150</a>
	- Certification Documents	
	Protection Class	Class I & II (Prepared); Reinforced Insulation
Pollution Degree		PD 2
Over Voltage Category		OVC II

## EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 60601-1-2 edition 4 (Medical Devices) EN 55011 class B (internal filter) EN 55032 class B (internal filter) FCC 47 Part 15 class B (internal filter) FCC 47 Part 18 class B (internal filter)	
	- Radiated Emissions	EN 55011 class A (internal filter) EN 55032 class A (internal filter) FCC 47 Part 15 class A (internal filter) FCC 47 Part 18 class A (internal filter)	
	- Harmonic Current Emissions	EN 61000-3-2, class A EN 61000-3-2, class D	
	- Voltage Fluctuations & Flicker	EN 61000-3-3	
EMS (Immunity)	- Electrostatic Discharge	EN 60601-1-2 edition 4 (Medical Devices) EN 55024 (IT Equipment) EN 55035 (Multimedia) Air: EN 61000-4-2, $\pm 15$ kV, perf. criteria A Contact: EN 61000-4-2, $\pm 8$ kV, perf. criteria A EN 61000-4-3, 20 V/m, perf. criteria A EN 61000-4-4, $\pm 2$ kV, perf. criteria A L to L: EN 61000-4-5, $\pm 1$ kV, perf. criteria A EN 61000-4-6, 20 Vrms, perf. criteria A	
	- RF Electromagnetic Field	Continuous: EN 61000-4-8, 10 A/m, perf. criteria A	
	- EFT (Burst) / Surge	230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A 60%, 5 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 250 periods, perf. criteria B	
	- Conducted RF Disturbances		
	- PF Magnetic Field		
	- Voltage Dips & Interruptions		
	EMC / Environmental	- Certification Documents	<a href="http://www.tracopower.com/overview/tpp150">www.tracopower.com/overview/tpp150</a>

## General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-25°C to +80°C
	- Storage Temperature	-40°C to +75°C
Power Derating	- High Temperature	Depending on model
	- Low Input Voltage	1.33 %/V below 100 VAC
	See application note:	<a href="http://www.tracopower.com/overview/tpp150">www.tracopower.com/overview/tpp150</a>
Cooling System		Forced air cooling (with internal fan)
Fan Power Source	- Characteristic	Variable fan speed (temperature regulated)
	- Output Voltage	12 VDC
	- Output Current	500 mA max.
Altitude During Operation		5'000 m max.

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Regulator Topology	Flyback Converter
Switching Frequency	45 - 75 kHz (PWM QR)
Insulation System	Reinforced Insulation
Working Voltage (rated)	250 VAC
Isolation Test Voltage	5'000 VAC
- Input to Output, 60 s	2'000 VAC
- Input to Case or PE, 60 s	2'000 VAC
- Output to Case or PE, 60 s	2'000 VAC
Isolation Resistance	100 MΩ min.
- Input to Output, 500 VDC	
Leakage Current	100 μA max.
(at 264 VAC)	
Reliability	786'000 h (MIL-HDBK-217F, ground benign)
- Calculated MTBF	
Environment	IEC 60068-2-6
- Vibration	5 g, 3 axis, sine sweep, 10-500 Hz, 1 oct/min
	IEC 60068-2-27
- Mechanical Shock	50 g, 3 axis, half sine, 11 ms
Housing Material	Alu alloy, black anodized coating
Housing Type	Metal Case
Mounting Type	Chassis Mount
Connection Type	Screw Terminal
Weight	273 g
Environmental Compliance	www.tracopower.com/info/reach-declaration.pdf
- REACH Declaration	REACH SVHC list compliant
	REACH Annex XVII compliant
- RoHS Declaration	www.tracopower.com/info/rohs-declaration.pdf
	Exemptions: 7a, 7c-I
	(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)
- SCIP Reference Number	e6640a60-fb85-49be-a02e-5c46aa46b4fc


## Supporting Documents

Overview Link (for additional Documents)

[www.tracopower.com/overview/tpp150](http://www.tracopower.com/overview/tpp150)

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

### Outline Dimensions



Mounting screw locked torque: max. 5 kgfcm / 0.49 Nm

Max. corner screw penetration depth: 1.8 (0.07)  
 Max. center screw penetration depth: 2.0 (0.08)

The fan's durability is lower compared to the power supply and has only 2 years warranty.

Terminal Block		Molex		Molex	
Input (CON1)		Output (CON2)		Fan (CON3)	
Pin	Function	Pin*	Function	Pin	Function
1	Line	1-3	-Vout	1	-Fan
3	Neutral	4-6	+Vout	2	+Fan

\*Terminal rated for 7 A max.  
 (at higher current connection has to be split)

**CON1:** Terminal Block  
 mates with Screw locked torque MAX 2Kgf.cm/0.2N.m  
 Wire dimension range: 26 - 16 AWG

**CON2:** Terminal Block  
 mates with Screw locked torque MAX 2Kgf.cm/0.2N.m  
 Wire dimension range: 26 - 16 AWG

**CON3:** Molex series  
 mates with Molex crimp terminals: 2759  
 and Molex housing: 22-01-1022