

- Unregulated outputs
- Highest power density 3W SIP-Converter
- Industry standard pinout
- High efficiency up to 89%
- I/O isolation voltage 1000 VDC
- Operating temperature range -40°C to +95°C
- 3-year product warranty



The TRA 3 series are miniature, I/O-isolated 3W DC/DC-converters with unregulated outputs. They are the ideal solution to power drivers and circuits where unregulated DC/DC converters do not meet the input voltage range at load change

Models				
Order Code	Input Voltage Range	Output Voltage nom.	Output Current max.	Efficiency typ.
TRA 3-0511	4.5 - 5.5 VDC (5 VDC nom.)	5 VDC	600 mA	83 %
TRA 3-0519		9 VDC	333 mA	87 %
TRA 3-0512		12 VDC	250 mA	86 %
TRA 3-0513		15 VDC	200 mA	88 %
TRA 3-1211	10.8 - 13.2 VDC (12 VDC nom.)	5 VDC	600 mA	84 %
TRA 3-1219		9 VDC	333 mA	88 %
TRA 3-1212		12 VDC	250 mA	88 %
TRA 3-1213		15 VDC	200 mA	89 %
TRA 3-2411	21.6 - 26.4 VDC (24 VDC nom.)	5 VDC	600 mA	82 %
TRA 3-2419		9 VDC	333 mA	85 %
TRA 3-2412		12 VDC	250 mA	86 %
TRA 3-2413		15 VDC	200 mA	85 %

Input Specifications

Input Current	- At no load	5 Vin models: 50 mA typ. 12 Vin models: 40 mA typ. 24 Vin models: 30 mA typ.
	- At full load	5 Vin models: 700 mA max. 12 Vin models: 285 mA max. 24 Vin models: 150 mA max.
Surge Voltage		5 Vin models: 9 VDC max. (1 s max.) 12 Vin models: 18 VDC max. (1 s max.) 24 Vin models: 30 VDC max. (1 s max.)
Recommended Input Fuse		5 Vin models: 2'000 mA (slow blow) 12 Vin models: 1'000 mA (slow blow) 24 Vin models: 500 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Capacitor

Output Specifications

Voltage Set Accuracy		±3% max. (at 80% load)
Regulation (Unregulated)	- Input Variation (1% Vin step) - Load Variation	1.2% max. See application note: www.tracopower.com/overview/tra3
Ripple and Noise	- 20 MHz Bandwidth	100 mVp-p max.
Capacitive Load		220 µF max.
Minimum Load		2 % of Iout max. (Operation at lower load will not damage the converter, but it may not meet all specifications)
Temperature Coefficient		±0.02 %/K max.
Short Circuit Protection		Limited 0.5 s max., Automatic recovery

Safety Specifications

Standards	- IT / Multimedia Equipment	CSA-C22.2, No. 60950-1 EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1 - Certification Documents www.tracopower.com/overview/tra3
Pollution Degree		PD 3
Over Voltage Category		Not mains connected

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Case Temperature - Storage Temperature	-40°C to +95°C +100°C max. -50°C to +125°C
Power Derating	- High Temperature	5 %/K above 85°C See application note: www.tracopower.com/overview/tra3
Cooling System		Natural convection (20 LFM)
Altitude During Operation		6'000 m max.
Switching Frequency		60 kHz min. (PWM)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s - Input to Output, 1 s	1'000 VDC 1'200 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Isolation Capacitance	- Input to Output, 100 kHz, 1 V	60 pF typ. 120 pF max.
Reliability	- Calculated MTBF	2'000'000 h (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Housing Material		Non-conductive Plastic (UL 94 V-0 rated)
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Nickel-Iron (Alloy 42)
Pin Foundation Plating		Nickel (1 µm min.)
Pin Surface Plating		Tin (3 - 5 µm), matte
Housing Type		Plastic Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		SIP7
Soldering Profile		Lead-Free Wave Soldering 260°C / 10 s max.
Weight		2.2 g
Environmental Compliance	- REACH Declaration	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant
	- RoHS Declaration	www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule),) 482311f2-60f6-4845-a3ce-39ba02ae88f0
	- SCIP Reference Number	


Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tra3

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



Pinout	
Pin	Function
1	+Vin (Vcc)
2	-Vin (GND)
4	-Vout
6	+Vout

Dimensions in mm (inch)
 Tolerances: x.x ±0.25 (x.xx ±0.01)
 x.xx ±0.13 (x.xxx ±0.005)
 Pins: ±0.05 (±0.002)