


- Reinforced I/O-isolation 4200 VAC rated for 1000 VAC working voltage
- Ultra-high isolation peak voltage 8000 VDC (1s)
- Common Mode Transient Immunity (dv/dt) 15 kV/μs
- Operating temperature range -40 to +85°C
- Low no-load power consumption 240 – 480 mW
- Internal EN 55032 class A filter
- High efficiency up to 90%
- 2:1 input voltage range: 9-18, 18-36, 36-75 VDC
- Protection against overload, overvoltage and short circuit
- 3-year product warranty



The new TRI 15 is a high isolation, regulated 15 Watt DC/DC converter series which comes in a compact 2"x1" package. The core characteristic of the TRI 15 series is a sophisticated reinforced isolation system which is able to withstand high test voltages (8000 VDC for 1s and 4200 VAC for 60s) and working voltages (1000 VACrms). Complementing this isolation characteristic is a high Common Mode Transient Immunity of 15 kV/μs. The new design allows to fully integrate an EN 55032 class A filter and greatly reduces the no-load power consumption. High efficiencies up to 90% allow safe operation from -40°C to +65°C without derating and up to +85°C with derating. All models have a wide 2:1 input voltage range and precisely regulated, isolated output voltages. With the latest IT safety certifications (IEC/EN/UL 62368-1) the TRI 15 series is the perfect choice for many demanding applications in the industrial, transportation and instrumentation sectors.

### Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I <sub>max</sub>	Vnom	I <sub>max</sub>	
TRI 15-1211	9 - 18 VDC (12 VDC nom.)	5.1 VDC	3'000 mA			85 %
TRI 15-1212		12 VDC	1'250 mA			88 %
TRI 15-1213		15 VDC	1'000 mA			88 %
TRI 15-1215		24 VDC	625 mA			88 %
TRI 15-1222		+12 VDC	625 mA	-12 VDC	625 mA	88 %
TRI 15-1223		+15 VDC	500 mA	-15 VDC	500 mA	89 %
TRI 15-2411	18 - 36 VDC (24 VDC nom.)	5.1 VDC	3'000 mA			87 %
TRI 15-2412		12 VDC	1'250 mA			88 %
TRI 15-2413		15 VDC	1'000 mA			89 %
TRI 15-2415		24 VDC	625 mA			90 %
TRI 15-2422		+12 VDC	625 mA	-12 VDC	625 mA	90 %
TRI 15-2423		+15 VDC	500 mA	-15 VDC	500 mA	89 %
TRI 15-4811	36 - 75 VDC (48 VDC nom.)	5.1 VDC	3'000 mA			87 %
TRI 15-4812		12 VDC	1'250 mA			87 %
TRI 15-4813		15 VDC	1'000 mA			90 %
TRI 15-4815		24 VDC	625 mA			89 %
TRI 15-4822		+12 VDC	625 mA	-12 VDC	625 mA	89 %
TRI 15-4823		+15 VDC	500 mA	-15 VDC	500 mA	88 %

### Input Specifications

Input Current	- At no load	12 Vin models: <b>20 mA typ.</b> 24 Vin models: <b>15 mA typ.</b> 48 Vin models: <b>10 mA typ.</b>
	- At full load	12 Vin models: <b>1'430 mA typ.</b> 24 Vin models: <b>706 mA typ.</b> 48 Vin models: <b>355 mA typ.</b>
Surge Voltage		12 Vin models: <b>25 VDC max.</b> (100 ms max.) 24 Vin models: <b>50 VDC max.</b> (100 ms max.) 48 Vin models: <b>100 VDC max.</b> (100 ms max.)
Under Voltage Lockout		12 Vin models: <b>7.5 VDC typ.</b> 24 Vin models: <b>15 VDC typ.</b> 48 Vin models: <b>33 VDC typ.</b>
Reflected Ripple Current		12 Vin models: <b>100 mAp-p typ.</b> 24 Vin models: <b>50 mAp-p typ.</b> 48 Vin models: <b>30 mAp-p typ.</b>
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)
Input Filter		<b>Internal Pi-Type</b>

### Output Specifications

Voltage Set Accuracy		<b>±1% max.</b>
Regulation	- Input Variation (Vmin - Vmax)	single output models: <b>0.5% max.</b> dual output models: <b>0.5% max.</b>
	- Load Variation (0 - 100%)	single output models: <b>0.5% max.</b> dual output models: <b>1% max.</b> (Output 1) <b>1% max.</b> (Output 2)
	- Voltage Balance (symmetrical load)	dual output models: <b>2% max.</b>
Ripple and Noise (20 MHz Bandwidth)	- single output	5.1 Vout models: <b>50 mVp-p typ.</b> (w/ 4.7 µF MLCC) 12 Vout models: <b>100 mVp-p typ.</b> (w/ 4.7 µF MLCC) 15 Vout models: <b>100 mVp-p typ.</b> (w/ 4.7 µF MLCC) 24 Vout models: <b>150 mVp-p typ.</b> (w/ 4.7 µF MLCC)
	- dual output	12 / -12 Vout models: <b>100 / 100 mVp-p typ.</b> (w/ 4.7 µF MLCC) 15 / -15 Vout models: <b>100 / 100 mVp-p typ.</b> (w/ 4.7 µF MLCC)
Capacitive Load	- single output	5.1 Vout models: <b>5'100 µF max.</b> 12 Vout models: <b>870 µF max.</b> 15 Vout models: <b>560 µF max.</b> 24 Vout models: <b>220 µF max.</b>
	- dual output	12 / -12 Vout models: <b>440 / 440 µF max.</b> 15 / -15 Vout models: <b>280 / 280 µF max.</b>
Minimum Load		<b>Not required</b>
Temperature Coefficient		<b>±0.02 %/K max.</b>
Start-up Time		<b>30 ms max.</b>
Short Circuit Protection		<b>Continuous, Automatic recovery</b>
Output Current Limitation		<b>150% typ. of Iout max.</b>
Overvoltage Protection		<b>120% typ. of Vout nom.</b>
Transient Response	- Response Deviation	<b>5% max.</b> (75% to 100% Load Step)
	- Response Time	<b>300 µs max.</b> (75% to 100% Load Step)

### Safety Specifications

Standards	- IT / Multimedia Equipment	<b>EN 62368-1</b> <b>IEC 62368-1</b> <b>UL 62368-1</b>
	- Certification Documents	<a href="http://www.tracopower.com/overview/tri15">www.tracopower.com/overview/tri15</a>

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Pollution Degree	PD 2
Over Voltage Category	OVC II

### EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class A (internal filter) EN 55032 class B (with external filter) FCC 47 Part 15 class A (internal filter)
	- Radiated Emissions	EN 55032 class A (with external filter) FCC 47 Part 15 class A (with external filter)
		External filter proposal: <a href="http://www.tracopower.com/overview/tri15">www.tracopower.com/overview/tri15</a>
EMS (Immunity)		EN 55024 (IT Equipment) EN 55035 (Multimedia)
	- Electrostatic Discharge	Air: EN 61000-4-2, ±15 kV, perf. criteria A Contact: EN 61000-4-2, ±8 kV, perf. criteria A
	- RF Electromagnetic Field	EN 61000-4-3, 10 V/m, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-4, ±2 kV, perf. criteria A EN 61000-4-5, ±1 kV, perf. criteria A
		Ext. input component: 12 & 24 Vin models: KY 560 µF    V15P8-M3 48 Vin models: KY 560 µF    V15P10
	- Conducted RF Disturbances	EN 61000-4-6, 10 Vrms, perf. criteria A
	- PF Magnetic Field	Continuous: EN 61000-4-8, 100 A/m, perf. criteria A
EMC / Environmental	- Certification Documents	<a href="http://www.tracopower.com/overview/tri15">www.tracopower.com/overview/tri15</a>

### General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +85°C
	- Case Temperature	+95°C max.
	- Storage Temperature	-50°C to +125°C
Power Derating	- High Temperature	Depending on model
		See application note: <a href="http://www.tracopower.com/overview/tri15">www.tracopower.com/overview/tri15</a>
Cooling System		Natural convection (20 LFM)
Altitude During Operation		4'000 m max.
Switching Frequency		285 kHz typ. (PWM)
Insulation System		Reinforced Insulation
Working Voltage (rated)		1'000 VAC
Isolation Test Voltage	- Input to Output, 60 s	4'200 VAC
	- Input to Output, 1 s	8'000 VDC
Isolation Resistance	- Input to Output, 500 VDC	10'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	80 pF max.
Common Mode Transient Immunity		15 kV/µs min.
Reliability	- Calculated MTBF	1'428'000 h (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline <a href="http://www.tracopower.com/info/cleaning.pdf">www.tracopower.com/info/cleaning.pdf</a>
Housing Material		Plastic (UL 94 V-0 rated)
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Copper Alloy (C6801)
Pin Foundation Plating		Nickel (2 - 4 µm)
Pin Surface Plating		Tin (5 - 7 µm), matte
Housing Type		Plastic Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		2" x 1"
Soldering Profile		Lead-Free Wave Soldering
		260°C / 10 s max.
Weight		30 g

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.


Thermal Impedance	- Case to Ambient	13 K/W typ.
Environmental Compliance	- REACH Declaration	<a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a>
	- RoHS Declaration	REACH SVHC list compliant REACH Annex XVII compliant <a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a>
	- SCIP Reference Number	Exemptions: 7a (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule)) 392146d9-Odd4-4f4f-a973-2de19b07542e

### Supporting Documents

Overview Link (for additional Documents)

[www.tracopower.com/overview/tri15](http://www.tracopower.com/overview/tri15)

### Outline Dimensions



Pinout		
Pin	Single Output	Dual Output
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	No pin	Common
5	-Vout	-Vout

Dimensions in mm (inch)

Tolerances: x.x ±0.5 (x.xx ±0.02)

x.xx ±0.25 (x.xxx ±0.01)

Pin diameter tolerances: x.x ±0.05 (x.xx ±0.002)