

- Compact metal case with screw terminal block
- Universal input 88-264 VAC
- Convection cooled (no-fan)
- High efficiency up to 86%
- Compliance to EN 61000-3-2
- Short circuit, overvoltage and overload protection
- IEC/EN/UL 62368-1 safety approvals
- 3-year product warranty



The TXLN series is a family of encased power supplies designed for a wide range of cost critical applications. With a low profile metal case and screw terminal block connection, they are easy to install in any equipment. These power supplies have universal input and comply with European EMC standards and the Low Voltage Directive (LVD).

Models				
Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TXLN 060-103	40 W	3.3 VDC (3.0 - 3.6 VDC)	12'000 mA	72 %
TXLN 060-105	50 W	5 VDC (4.5 - 5.5 VDC)	10'000 mA	78 %
TXLN 060-112	60 W	12 VDC (10.8 - 13.2 VDC)	5'000 mA	81 %
TXLN 060-115		15 VDC (13.5 - 16.5 VDC)	4'000 mA	83 %
TXLN 060-124		24 VDC (21.6 - 26.4 VDC)	2'500 mA	84 %
TXLN 060-148		48 VDC (43.2 - 52.8 VDC)	1'300 mA	86 %

Options	
on demand (backorder with MOQ non stocking item)	- Optional model with 7.5 VDC / 7'000 mA - Optional model with 30 VDC / 2'000 mA

Input Specifications

Input Voltage	- AC Range	Operational Range: 88 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
	- DC Range	Operational Range: 125 - 375 VDC (Designed for, no certification) Polarity: irrelevant
Input Frequency		Operational Range: 47 - 63 Hz Certified: 50/60 Hz
Power Consumption	- No load & Vin = 230 VAC	500 mW max.
Input Current	- Full load & Vin = 115 VAC	1'600 mA max.
Input Inrush Current	- At 230 VAC	50 A max.
	- At 115 VAC	30 A max.
Input Protection		T 2 A / 250 VAC (Internal Fuse)
Recommended Input Fuse		2'000 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)

Output Specifications

Output Voltage Adjustment		±10% (By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		±3% max. (3.3 Vout model)
		±2% max. (5 Vout model)
		±1% max. (other models)
Regulation	- Input Variation (Vmin - Vmax)	1.5% max. (3.3 Vout model)
		1% max. (5 Vout model)
	- Load Variation (0 - 100%)	0.5% max. (other models)
		3% max. (3.3 Vout model)
Ripple and Noise (20 MHz Bandwidth)	3.3 VDC model:	70 mVp-p max. (w/ 0.1 µF 47 µF)
	5 VDC model:	70 mVp-p max. (w/ 0.1 µF 47 µF)
	7.5 VDC model:	80 mVp-p max. (w/ 0.1 µF 47 µF)
	12 VDC model:	120 mVp-p max. (w/ 0.1 µF 47 µF)
	15 VDC model:	150 mVp-p max. (w/ 0.1 µF 47 µF)
	24 VDC model:	150 mVp-p max. (w/ 0.1 µF 47 µF)
	30 VDC model:	200 mVp-p max. (w/ 0.1 µF 47 µF)
	48 VDC model:	200 mVp-p max. (w/ 0.1 µF 47 µF)
Capacitive Load	3.3 VDC model:	108'000 µF max.
	5 VDC model:	108'000 µF max.
	7.5 VDC model:	108'000 µF max.
	12 VDC model:	72'000 µF max.
	15 VDC model:	54'000 µF max.
	24 VDC model:	18'000 µF max.
	30 VDC model:	9'000 µF max.
48 VDC model:	5'400 µF max.	
Minimum Load		Not required
Temperature Coefficient		±0.03 %/K max.
Hold-up Time	- At 230 VAC	60 ms min.
	- At 115 VAC	16 ms min.
Start-up Time	- At 230 VAC	1'000 ms max.
	- At 115 VAC	1'000 ms max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		105 - 150% of Iout max.
Overvoltage Protection		115 - 140% of Vout nom.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/txln060
Protection Class		Class I (Prepared): Connection to PE
Pollution Degree		PD 2
Over Voltage Category		OVC II

EMC Specifications

EMI Emissions	- Conducted Emissions - Radiated Emissions - Harmonic Current Emissions - Voltage Fluctuations & Flicker	EN 55032 class B (internal filter) EN 55032 class B (internal filter) EN 61000-3-2, class A EN 61000-3-3
EMS Immunity	- Electrostatic Discharge - RF Electromagnetic Field - EFT (Burst) / Surge - Conducted RF Disturbances - PF Magnetic Field - Voltage Dips & Interruptions	EN 55024 (IT Equipment) EN 55035 (Multimedia) Air: EN 61000-4-2, ± 8 kV, perf. criteria A Contact: EN 61000-4-2, ± 4 kV, perf. criteria A EN 61000-4-3, 3 V/m, perf. criteria A EN 61000-4-4, ± 1 kV, perf. criteria A L to L: EN 61000-4-5, ± 1 kV, perf. criteria A L to PE: EN 61000-4-5, ± 2 kV, perf. criteria A EN 61000-4-6, 3 Vrms, perf. criteria A Continuous: EN 61000-4-8, 3 A/m, perf. criteria A 230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 250 periods, perf. criteria C

General Specifications

Relative Humidity		90% max. (non condensing)
Temperature Ranges	- Operating Temperature - Storage Temperature	-20°C to +70°C -40°C to +85°C
Power Derating	- High Temperature - Low Input Voltage	2.5 %/K above 50°C 0.83 %/V below 100 VAC
		See application note: www.tracopower.com/overview/txln060
Cooling System		Natural convection (20 LFM)
Altitude During Operation		2'000 m max.
Regulator Topology		Flyback Converter
Switching Frequency		58 - 72 kHz (PWM)
Insulation System		Reinforced Insulation
Working Voltage (rated)		357 VAC
Isolation Test Voltage	- Input to Output, 60 s - Input to Case or PE, 60 s - Output to Case or PE, 60 s	3'000 VAC 1'800 VAC 500 VAC
Isolation Resistance	- Input to Output, 500 VDC	100 M Ω min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	20'000 pF max.
Leakage Current (at 264 VAC)	- Earth Leakage Current	750 μ A max.
Distance Through Isolation		6 mm
Reliability	- Calculated MTBF	335'000 h (MIL-HDBK-217F, ground benign)
Housing Material		Aluminum
Housing Type		Metal Case
Mounting Type		Chassis Mount
Connection Type		Screw Terminal

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Weight	340 g
Status Indicator	Indicated by green LED
Environmental Compliance	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-1 (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).) 743ccba0-610e-418f-951e-bafa6e2a32cc
- REACH Declaration	
- RoHS Declaration	
- SCIP Reference Number	

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/txln060

Outline Dimensions

Screw Terminal	
Pin	Function
1	AC (L)
2	AC (N)
3	PE
4	-Vout
5	+Vout

Max. terminal screw locked torque: 0.7 Nm

Terminal screws:
5x M3.5

Dimensions in mm
Tolerances:
0-8: ±0.2
8-25: ±0.3
25-80: ±0.5
80-250: ±0.8

Mounting screws
Max. screw penetration depth: 4.5
Max. screw locked torque: 0.8 Nm