

- Compact metal case with screw terminal block
- Universal input 90-264 VAC
- I/O reinforced isolation 3000 VAC
- Active power factor correction >0.9
- Internal EN 55032 class B filter
- High efficiency up to 89%
- Operating temperature range -30°C to 70+°C
- Short circuit, overvoltage and overload protection
Remote ON/OFF function
- IEC/EN/UL 62368-1 safety approvals
- 3-year product warranty



The TXN 100PF is a cost efficient, metal enclosed AC/DC power supplies series and is designed for industrial applications. With a low-profile metal case and screw terminal block connection, they are easy to install in any equipment. Active PFC (>0.9), internal EMC filter, high IO-isolation and wide temperature range qualify them for numerous industrial applications. All models within the TXN 100PF series have universal input (90-264 VAC) and comply with the latest industrial standard IEC/EN/UL 62368-1, European EMC standards and the Low Voltage Directive (LVD).

Models				
Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TXN 100PF-112	100 W	12 VDC (10.8 - 13.2 VDC)	8'500 mA	86 %
TXN 100PF-115		15 VDC (13.5 - 16.5 VDC)	6'700 mA	89 %
TXN 100PF-124		24 VDC (21.6 - 26.4 VDC)	4'200 mA	87 %
TXN 100PF-148		48 VDC (43.2 - 52.8 VDC)	2'100 mA	88 %

Options	
TXN-AUX1	- Optional Cable: www.tracopower.com/overview/txn-aux1
on demand (backorder with MOQ non stocking item)	- Optional model with 36 VDC and 2'800 mA

Input Specifications

Input Voltage	- AC Range	Operational Range: 90 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
	- DC Range	Operational Range: 140 - 340 VDC (Designed for, no certification) Polarity: +DC: L / -DC: N
Input Frequency		Operational Range: 47 - 63 Hz Certified: 50/60 Hz
Power Consumption	- No load & Vin = 230 VAC	2'000 mW max.
	- No load & Vin = 115 VAC	2'000 mW max.
Input Current	- Full load & Vin = 230 VAC	550 mA max.
	- Full load & Vin = 115 VAC	1'100 mA max.
Input Inrush Current	- At 230 VAC	30 A max.
	- At 115 VAC	20 A max.
Power Factor	- At 230 VAC	0.9 min. (Active Power Factor Correction)
	- At 115 VAC	0.95 min. (Active Power Factor Correction)
Input Protection		T 2.5 A / 250 VAC (Internal Fuse in L)
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)

Output Specifications

Output Voltage Adjustment		±8% (36 Vout model) ±10% of Vout nom. (other models) (By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	0.5% max.
	- Load Variation (10 - 90%)	1% max.
Ripple and Noise (20 MHz Bandwidth)	12 VDC model:	100 mVp-p typ. (w/ 0.1 µF 47 µF)
	15 VDC model:	150 mVp-p typ. (w/ 0.1 µF 47 µF)
	24 VDC model:	150 mVp-p typ. (w/ 0.1 µF 47 µF)
	36 VDC model:	200 mVp-p typ. (w/ 0.1 µF 47 µF)
	48 VDC model:	250 mVp-p typ. (w/ 0.1 µF 47 µF)
Minimum Load		Not required
Temperature Coefficient		±0.03 %/K max.
Hold-up Time	- At 230 VAC	16 ms min.
	- At 115 VAC	16 ms min.
Start-up Time	- At 230 VAC	1'000 ms max.
	- At 115 VAC	1'000 ms max.
Short Circuit Protection		Automatic recovery
Output Current Limitation		105 - 135% of Iout max.
Oversvoltage Protection		110 - 140% of Vout nom.
Transient Response	- Response Deviation	3% typ. / 5% max. (50% to 100% Load Step)
	- Response Time	300 µs typ. / 500 µs max. (50% to 100% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/txn100pf
Protection Class		Class I (Prepared): Connection to PE
Pollution Degree		PD 2
Over Voltage Category		OVC II

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

EMC Specifications

EMI (Emissions)	- Conducted Emissions - Radiated Emissions - Harmonic Current Emissions - Voltage Fluctuations & Flicker	EN 55032 class B (internal filter) EN 55032 class B (internal filter) EN 61000-3-2, class A EN 61000-3-3
EMS (Immunity)	- Electrostatic Discharge - RF Electromagnetic Field - EFT (Burst) / Surge - Conducted RF Disturbances - PF Magnetic Field - Voltage Dips & Interruptions	EN 55035 (Multimedia) Air: EN 61000-4-2, ±8 kV, perf. criteria B Contact: EN 61000-4-2, ±4 kV, perf. criteria B EN 61000-4-3, 10 V/m, perf. criteria A EN 61000-4-4, ±2 kV, perf. criteria B L to L: EN 61000-4-5, ±1 kV, perf. criteria B L to PE: EN 61000-4-5, ±2 kV, perf. criteria B EN 61000-4-6, 10 Vrms, perf. criteria A Continuous: EN 61000-4-8, 30 A/m, perf. criteria A 230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria B >95%, 0.5 periods, perf. criteria C >95%, 250 periods, perf. criteria B
EMC / Environmental	- Certification Documents	www.tracopower.com/overview/txn100pf

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Storage Temperature	-30°C to +70°C -40°C to +80°C
Power Derating	- High Temperature - Low Input Voltage	Depending on model Depending on model See application note: www.tracopower.com/overview/txn100pf
Over Temperature Protection Switch Off	- Protection Mode - Measurement Point	105°C typ. (Automatic recovery at 75°C typ.) Transformer
Cooling System		Natural convection (20 LFM)
Remote Control	- Voltage Controlled Remote (passive = on) - Off Idle Input Current - Remote Pin Input Current	Off: 4 to 10 VDC Refers to '+Remote' and '-Remote' Pin On: < 1.0 VDC or open circuit or short circuit 10 mA max. 0.5 to 2.5 mA
Altitude During Operation		5'000 m max.
Regulator Topology		Forward Converter
Switching Frequency		62 - 68 kHz (PWM) 65 kHz typ. (PWM)
Insulation System		Reinforced Insulation
Working Voltage (rated)		235 VAC
Isolation Test Voltage	- Input to Output, 60 s - Input to Case or PE, 60 s - Output to Case or PE, 60 s	4'242 VDC 2'500 VDC 500 VAC
Creepage	- Input to Output - Input to Case or PE - Output to Case or PE	7.1 mm min. 3 mm min. 2 mm min.
Clearance	- Input to Output - Input to Case or PE - Output to Case or PE	7.1 mm min. 3 mm min. 2 mm min.
Isolation Resistance	- Input to Output, 500 VDC	100 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	1'100 pF typ.
Leakage Current	- Earth Leakage Current - Touch Current	1000 μA max. 2000 μA max.
Distance Through Isolation		7.2 mm

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.


Reliability	- Calculated MTBF	290'000 h (MIL-HDBK-217F, ground benign)
Washing Process		Not allowed
Environment	- Vibration - Mechanical Shock	2 g, 3 axis, 60 min, 10-500 Hz, 10 min/cycle 20 g, 3 axis, 3 shocks
Case Ingress Protection		IP 20 (acc. IEC 60529)
Housing Material		Metal Aluminum (Chassis)
Housing Type		Metal Case
Mounting Type		Chassis Mount
Connection Type		Screw Terminal
Weight		430 g
Status Indicator		Indicated by green LED
Environmental Compliance	- REACH Declaration - RoHS Declaration - SCIP Reference Number	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule.)) 3c760ef3-004b-4631-af86-6480b31d25f5

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/txn100pf

Outline Dimensions



Pin connectors

Input/Output		Remote	
Pin	Function	Pin	Function
1	+Vout	1	-Remote
2		2	+Remote
3	-Vout		
4			
5	PE		
6	AC (N)		
7	AC (L)		

Input/Output: Screw terminal, M4x7
 Terminal screw tightening torque: Max. 1.2 Nm