


- Compact open frame power supply with pin connectors
- Universal input range 85 to 264 VAC
- Convection cooled (no-fan)
- Operating temperature range: -20°C to +70°C
- Internal EN55032 class B filter
- Short circuit, overvoltage and overload protection
- IEC/EN/UL 62368-1 safety approvals
- Compliance to EN 61000-3-2
- 3-year product warranty



UL 62368-1 IEC 62368-1

The TXO 45 is a compact 45 Watt AC/DC open frame module with reinforced I/O isolation designed for a wide range of cost sensitive applications. Excellent temperature behaviour allows full load operation from -20°C to +50°C while going up to +70°C with derating. The TXO 45 series features short circuit protection, over current limitation and overvoltage protection and complies with European EMC standards and the Low Voltage Directive (LVD).

Models				
Order Code	Output Power max.	Output Voltage nom.	Output Current max.	Efficiency typ.
TXO 45-112-J	45 W	12 VDC	3'800 mA	85 %
TXO 45-115-J		15 VDC	3'000 mA	85 %
TXO 45-124-J		24 VDC	1'900 mA	85 %
TXO 45-148-J		48 VDC	940 mA	85 %

Options	
<b>TCI 130-DC</b>	- Optional Cable: <a href="http://www.tracopower.com/overview/tci130-dc">www.tracopower.com/overview/tci130-dc</a>
<b>TCI-AC1</b>	- Optional Cable: <a href="http://www.tracopower.com/overview/tci-ac1">www.tracopower.com/overview/tci-ac1</a>
<b>on demand</b> (backorder with MOQ non stocking item)	- Optional model with 36 VDC and 1'250 mA - Optional model with 56 VDC and 800 mA

### Input Specifications

Input Voltage	- AC Range	Operational Range: <b>85 - 264 VAC</b> (Full Range) Rated Range: <b>100 - 240 VAC</b> (Full Range)
	- DC Range	Operational Range: <b>120 - 370 VDC</b> (Designed for, no certification) Polarity: <b>irrelevant</b>
Input Frequency		Operational Range: <b>47 - 63 Hz</b> Certified: <b>50/60 Hz</b>
Power Consumption	- No load & Vin = 230 VAC - No load & Vin = 115 VAC	<b>100 mW max.</b> (Ready to meet ErP directive) <b>100 mW max.</b>
Input Current	- Full load & Vin = 230 VAC - Full load & Vin = 115 VAC	<b>600 mA max.</b> <b>950 mA max.</b>
Input Inrush Current	- At 230 VAC - At 115 VAC	<b>80 A max.</b> <b>40 A max.</b>
Input Protection		<b>T 3.15 A / 250 VAC</b> (Internal Fuse in L)
Recommended Input Fuse		<b>3'150 mA</b> (slow blow) (The need of an external fuse has to be assessed in the final application.)

### Output Specifications

Voltage Set Accuracy		<b>±2% max.</b>
Regulation	- Input Variation (Vmin - Vmax) - Load Variation (10 - 100%)	<b>0.5% max.</b> <b>3% max.</b>
Ripple and Noise (20 MHz Bandwidth)		12 VDC model: <b>120 mVp-p typ.</b> (w/ 10 µF Alu    0.1 µF MLCC) 15 VDC model: <b>150 mVp-p typ.</b> (w/ 10 µF Alu    0.1 µF MLCC) 24 VDC model: <b>240 mVp-p typ.</b> (w/ 10 µF Alu    0.1 µF MLCC) 36 VDC model: <b>360 mVp-p typ.</b> (w/ 10 µF Alu    0.1 µF MLCC) 48 VDC model: <b>480 mVp-p typ.</b> (w/ 10 µF Alu    0.1 µF MLCC) 56 VDC model: <b>560 mVp-p typ.</b> (w/ 10 µF Alu    0.1 µF MLCC)
Capacitive Load		12 VDC model: <b>3'500 µF max.</b> 15 VDC model: <b>2'500 µF max.</b> 24 VDC model: <b>1'350 µF max.</b> 36 VDC model: <b>800 µF max.</b> 48 VDC model: <b>380 µF max.</b> 56 VDC model: <b>270 µF max.</b>
Minimum Load		<b>Not required</b>
Temperature Coefficient		<b>±3 %/K max.</b>
Hold-up Time	- At 230 VAC - At 115 VAC	<b>60 ms min.</b> <b>16 ms min.</b>
Start-up Time	- At 230 VAC - At 115 VAC	<b>1.5 s max.</b> <b>3 s max.</b>
Short Circuit Protection		<b>Continuous, Automatic recovery</b>
Output Current Limitation		<b>110 - 200% of Iout max.</b>
Overvoltage Protection		<b>110 - 170% of Vout nom.</b> (Latch mode)
Transient Response	- Response Deviation - Response Time	<b>3% typ. / 5% max.</b> (50% to 75% Load Step) <b>1 ms typ. / 1.5 ms max.</b> (50% to 75% Load Step)

### Safety Specifications

Standards	- IT / Multimedia Equipment  - Certification Documents	<b>EN 62368-1</b> <b>IEC 62368-1</b> <b>UL 62368-1</b> <a href="http://www.tracopower.com/overview/txo45">www.tracopower.com/overview/txo45</a>
Protection Class		<b>Class I &amp; II</b> (Prepared): <b>Reinforced Insulation</b>
Pollution Degree		<b>PD 2</b>
Over Voltage Category		<b>OVC II</b>

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

## EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class B (internal filter) FCC 47 Part 15 class B (internal filter)	
	- Radiated Emissions	EN 55032 class B (internal filter) FCC 47 Part 15 class B (internal filter)	
	- Harmonic Current Emissions	EN 61000-3-2, class A	
	- Voltage Fluctuations & Flicker	EN 61000-3-3	
EMS (Immunity)	- Electrostatic Discharge	EN 55035 (Multimedia) Air: EN 61000-4-2, $\pm 8$ kV, perf. criteria A Contact: EN 61000-4-2, $\pm 4$ kV, perf. criteria A	
	- RF Electromagnetic Field	EN 61000-4-3, 3 V/m, perf. criteria A	
	- EFT (Burst) / Surge	EN 61000-4-4, $\pm 1$ kV, perf. criteria A	
	- Conducted RF Disturbances	L to L: EN 61000-4-5, $\pm 1$ kV, perf. criteria A	
	- PF Magnetic Field	EN 61000-4-6, 3 Vrms, perf. criteria A	
	- Voltage Dips & Interruptions	Continuous: EN 61000-4-8, 1 A/m, perf. criteria A 230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 250 periods, perf. criteria B	
	EMC / Environmental	- Certification Documents	<a href="http://www.tracopower.com/overview/txo45">www.tracopower.com/overview/txo45</a>

## General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-20°C to +70°C
	- Approved Ambient Temp.	+70°C max. (for 50% load) +50°C max. (for 100% load) (for compliance to 62368-1)
	- Storage Temperature	-40°C to +85°C
Power Derating	- High Temperature	2.5 %/K above 50°C
	- Low Input Voltage	2 %/V below 90 VAC
	See application note:	<a href="http://www.tracopower.com/overview/txo45">www.tracopower.com/overview/txo45</a>
Cooling System		Natural convection (20 LFM)
Altitude During Operation		2'000 m max.
Regulator Topology		Flyback Converter
Switching Frequency		65 kHz typ. (PWM)
Insulation System		Reinforced Insulation
Working Voltage (rated)		576 VAC
Isolation Test Voltage	- Input to Output, 60 s	3'000 VAC (4242 VDC)
Creepage	- Input to Output	6 mm min.
Clearance	- Input to Output	6 mm min.
Isolation Resistance	- Input to Output, 500 VDC	100 M $\Omega$ min.
Leakage Current	- Touch Current	100 $\mu$ A max.
(at 264 VAC / 60 Hz)		
Reliability	- Calculated MTBF	100'000 h (MIL-HDBK-217F, ground benign)
Washing Process		Not allowed
Environment	- Vibration	2.4 g, 3 axis, random waveform, 30 min
	- Mechanical Shock	20 g, 3 axis, 6 shocks
Housing Type		Open Frame
Mounting Type		Chassis Mount
Connection Type		Pin Connector
Weight		120 g

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

[www.tracopower.com/info/reach-declaration.pdf](http://www.tracopower.com/info/reach-declaration.pdf)

- RoHS Declaration

REACH SVHC list compliant

REACH Annex XVII compliant

[www.tracopower.com/info/rohs-declaration.pdf](http://www.tracopower.com/info/rohs-declaration.pdf)

Exemptions: 7a

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule))

- SCIP Reference Number


dae5192c-c3bb-43f9-bd6f-69b1ebc6e6e6

### Supporting Documents

Overview Link (for additional Documents)

[www.tracopower.com/overview/txo45](http://www.tracopower.com/overview/txo45)

### Outline Dimensions



Dimensions in mm (inch)

General tolerances:  $\pm 0.5$  ( $\pm 0.02$ )

Mounting screw tightening torque: 0.59 Nm max. (6.0 kgfcm max.)

### Pin connectors

Input (CN1)		Output (CN2)	
Pin	Function	Pin	Function
1	AC (L)	1	-Vout
3	AC (N)	2	
		3	+Vout
		4	

**Input:** JST series, B3P-VH(LF)(SN), 3.96mm mates with JST crimp terminal: SVH-21T-P1.1 or equivalent and terminal housing: VHR-3N or equivalent

**Output:** JST series, B4P-VH(LF)(SN), 3.96mm mates with JST crimp terminal: SVH-21T-P1.1 or equivalent and terminal housing: VHR-4N or equivalent