

CE EMC TEST REPORT

for

AC DC Power Module

Model : TMPS 03 SERIES

Brand:



Test Report Number:

T161215N13-E

Issued for

TRACO ELECTRONIC AG

SIHLBRUGGSTRASSE 111 CH-6340 BAAR, SWITZERLAND

Issued by

Compliance Certification Services Inc.

Tainan Laboratory

No.8, Jiucengling, Xinhua Dist., Tainan City 712,
Taiwan (R.O.C.)

TEL: 886-6-580-2201

FAX: 886-6-580-2202

Issued Date: January 16, 2017



Note: This report shall not be reproduced except in full, without the written approval of Compliance Certification Services Inc. This document may be altered or revised by Compliance Certification Services Inc. personnel only, and shall be noted in the revision section of the document. The client should not use it to claim product endorsement by TAF, NIST or any government agencies. The test results in the report only apply to the tested sample.

REVISION HISTORY

| Rev. | Issue Date | Revisions | Effect Page | Revised By |
|------|------------------|---------------|-------------|------------|
| 00 | January 16, 2017 | Initial Issue | ALL | Eva Lin |
| | | | | |
| | | | | |
| | | | | |

TABLE OF CONTENTS

| | | |
|--|---|-----------|
| 1 | TEST CERTIFICATION | 4 |
| 2 | TEST RESULT SUMMARY | 5 |
| 3 | EUT DESCRIPTION | 6 |
| 4 | TEST METHODOLOGY | 8 |
| 4.1. | DECISION OF FINAL TEST MODE | 8 |
| 4.2. | EUT SYSTEM OPERATION | 8 |
| 5 | SETUP OF EQUIPMENT UNDER TEST | 9 |
| 5.1. | DESCRIPTION OF SUPPORT UNITS | 9 |
| 5.2. | CONFIGURATION OF SYSTEM UNDER TEST | 9 |
| 6 | FACILITIES AND ACCREDITATIONS | 10 |
| 6.1. | FACILITIES | 10 |
| 6.2. | ACCREDITATIONS | 10 |
| 6.3. | MEASUREMENT UNCERTAINTY | 11 |
| 7 | EMISSION TEST | 12 |
| 7.1. | CONDUCTED EMISSION MEASUREMENT AT AC MAINS PORT | 12 |
| 7.2. | CONDUCTED EMISSION MEASUREMENT AT ANALOGUE/DIGITAL DATA PORTS | 27 |
| 7.3. | RADIATED EMISSION MEASUREMENT | 30 |
| 7.4. | HARMONICS CURRENT MEASUREMENT | 47 |
| 7.5. | VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT | 50 |
| 8 | IMMUNITY TEST | 54 |
| 8.1. | GENERAL DESCRIPTION | 54 |
| 8.2. | GENERAL PERFORMANCE CRITERIA DESCRIPTION | 55 |
| 8.3. | ELECTROSTATIC DISCHARGE (ESD) | 56 |
| 8.4. | RADIATED, RADIO-FREQUENCY, ELECTROMAGNETIC FIELD (RS) | 61 |
| 8.5. | ELECTRICAL FAST TRANSIENT (EFT) | 65 |
| 8.6. | SURGE IMMUNITY TEST | 68 |
| 8.7. | CONDUCTED RADIO FREQUENCY DISTURBANCES (CS) | 71 |
| 8.8. | POWER FREQUENCY MAGNETIC FIELD | 75 |
| 8.9. | VOLTAGE DIP & VOLTAGE INTERRUPTIONS | 77 |
| 9 | PHOTOGRAPHS OF THE TEST CONFIGURATION | 81 |
| APPENDIX 1 - PHOTOGRAPHS OF EUT | | A1 |

1 TEST CERTIFICATION

Product: AC DC Power Module**Model:** TMPS 03 SERIES**Brand****Applicant:** TRACO ELECTRONIC AG

SIHLBRUGGSTRASSE 111 CH-6340 BAAR, SWITZERLAND

Tested: April 11, 2014 ~ June 11, 2014
November 08, 2016 ~ November 09, 2016

| | | |
|------------------------------|---|------------------------|
| Applicable Standards: | EN 55032: 2012+AC: 2013, Class B | EN 55024 : 2010 |
| | EN 61000-3-2: 2014 | IEC 61000-4-2: 2008 |
| | EN 61000-3-3: 2013 | IEC 61000-4-3: 2010 |
| | | IEC 61000-4-4: 2012 |
| | | IEC 61000-4-5: 2014 |
| | | IEC 61000-4-6: 2013 |
| | | IEC 61000-4-8: 2009 |
| | | IEC 61000-4-11: 2004 |

| Deviation from Applicable Standard |
|------------------------------------|
| None |

The above equipment was tested by Compliance Certification Services Inc. for compliance with the requirements of technical standards specified above under the EMC Directive 2014/30/EU. The results of testing in this report apply only to the product/system, which was tested. Other similar equipment will not necessarily produce the same results due to production tolerance and measurement uncertainties.

Approved by:**Jeter Wu**
Assistant Manager**Reviewed by:****Eric Huang**
Assistant Section Manager


2 TEST RESULT SUMMARY

| EMISSION | | | |
|-------------------------|---|--------|----------------------|
| Standard | Item | Result | Remarks |
| EN 55032: 2012+AC: 2013 | Conducted (Power Port) | PASS | Meet Class B limit |
| | Conducted (Analogue/Digital Data Ports) | N/A | No requirement |
| | Radiated (Below 1GHz) | PASS | Meet Class B limit |
| | Radiated (Above 1GHz) | N/A | No requirement |
| EN 61000-3-2: 2014 | Harmonic current emissions | PASS | Meet the requirement |
| EN 61000-3-3: 2013 | Voltage fluctuations & flicker | PASS | Meet the requirement |

| IMMUNITY [EN 55024 : 2010] | | | |
|------------------------------|-----------------------------------|--------|--|
| Standard | Item | Result | Remarks |
| IEC 61000-4-2: 2008 | ESD | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-3: 2010 | RS | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-4: 2012 | EFT | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-5: 2014 | Surge | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-6: 2013 | CS | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-8: 2009 | PFMF | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-11: 2004 | Voltage dips & voltage variations | PASS | Meets the requirements of Voltage Dips: 1) >95% reduction 0.5/1 period Performance Criterion A 2) 30% reduction 25/30 period Performance Criterion A Voltage Interruptions: >95% reduction 250/300 period Performance Criterion B |

Note: 1. The statements of test result on the above are decided by the request of test standard only; the measurement uncertainties are not factored into this compliance determination.
2. The information of measurement uncertainty is available upon the customer's request.

3 EUT DESCRIPTION

| | |
|------------------|---|
| Product | AC DC Power Module |
| Model | TMPS 03 SERIES |
| Brand |  |
| Applicant | TRACO ELECTRONIC AG |
| Housing material | Plastics |
| Identify Number | T161215N13 |
| Received Date | August 09, 2016 |
| Power Source | See Below |

I/O PORT


| I/O PORT TYPES | Q'TY | TESTED WITH |
|----------------|------|-------------|
| 1. AC Power | 1 | AC Source |
| 2. DC Power | 1 | Load |

- Note: 1. Client consigns only eight model samples to test (Model Number: **TMPS 03-103; TMPS 03-105; TMPS 03-109; TMPS 03-112; TMPS 03-115; TMPS 03-124**). Therefore, the testing Lab. just guarantees the unit, which has been tested.
2. For more details, please refer to the User's manual of the EUT.
3. To add a series model is for business necessary. The different of the each model is shown as below:

Model Difference:

| Model Number PCB Mounting (For model with Chassis Mounting, add suffix C) | AC Input Voltage (Range) | Output Voltage | Output Current |
|--|--------------------------|----------------|----------------|
| | | | Max. |
| | VAC | VDC | mA |
| TMPS 03-103 | 85-264 | 3.3 | 900 |
| TMPS 03-105 | | 5 | 600 |
| TMPS 03-109 | | 9 | 333 |
| TMPS 03-112 | | 12 | 250 |
| TMPS 03-115 | | 15 | 200 |
| TMPS 03-124 | | 24 | 125 |

Package Specifications :

| Package Specifications | | | | | | | | | | | | | |
|---|---|-----|----------|---|--------|---|--------|---|----|---|-------|---|-------|
| Mechanical Dimensions | Pin Connections | | | | | | | | | | | | |
|  | <table><tr><th>Pin</th><th>Function</th></tr><tr><td>1</td><td>AC (N)</td></tr><tr><td>2</td><td>AC (L)</td></tr><tr><td>3</td><td>NC</td></tr><tr><td>4</td><td>-Vout</td></tr><tr><td>5</td><td>+Vout</td></tr></table> | Pin | Function | 1 | AC (N) | 2 | AC (L) | 3 | NC | 4 | -Vout | 5 | +Vout |
| Pin | Function | | | | | | | | | | | | |
| 1 | AC (N) | | | | | | | | | | | | |
| 2 | AC (L) | | | | | | | | | | | | |
| 3 | NC | | | | | | | | | | | | |
| 4 | -Vout | | | | | | | | | | | | |
| 5 | +Vout | | | | | | | | | | | | |
| | NC: No Connection | | | | | | | | | | | | |
| <ul style="list-style-type: none">▶ All dimensions in mm (inches)▶ Tolerance: ± 0.5 (± 0.01)▶ Pin diameter $\varnothing 0.6 \pm 0.1$ (0.02 ± 0.004) | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |

4 TEST METHODOLOGY

4.1. DECISION OF FINAL TEST MODE

The EUT was tested together with the above additional components, and a configuration, which produced the worst emission levels, was selected and recorded in this report.

The test configuration/ mode is as the following:

Conduction (Power port) Modes: (Full Load)

| | | | |
|----|-------------|----|-------------|
| 1. | TMPS 03-103 | 4. | TMPS 03-112 |
| 2. | TMPS 03-105 | 5. | TMPS 03-115 |
| 3. | TMPS 03-109 | 6. | TMPS 03-124 |

Conduction (Telecom port) Modes

| | |
|----|-----|
| 1. | Non |
|----|-----|

Radiation Modes: (Full Load)

| | | | |
|----|-------------|----|-------------|
| 1. | TMPS 03-103 | 4. | TMPS 03-112 |
| 2. | TMPS 03-105 | 5. | TMPS 03-115 |
| 3. | TMPS 03-109 | 6. | TMPS 03-124 |

Radiation Modes: (Above 1GHz) (Full Load)

| | |
|----|-----|
| 1. | Non |
|----|-----|

EMS Modes: (Full Load)

| | |
|----|-------------|
| 1. | TMPS 03-103 |
|----|-------------|

4.2. EUT SYSTEM OPERATION

1. Setup whole system for test as shown on setup diagram.
2. Turn on power and check EUT function.
3. Start to test.

Note: Test program is self-repeating throughout the test.

5 SETUP OF EQUIPMENT UNDER TEST

5.1. DESCRIPTION OF SUPPORT UNITS

The EUT has been tested as an independent unit together with other necessary accessories or support units. The following support units or accessories were used to form a representative test configuration during the tests.


| No. | Product | Manufacturer | Model No. | Certify No. | Signal cable |
|-----|---------|--------------|-----------|-------------|--------------|
| 1 | Load | N/A | N/A | N/A | N/A |

| No. | Signal cable description | |
|-----|--------------------------|-------------------------|
| A | AC Power cable | Unshielded, 1.6m, 1pcs. |
| B | DC Power cable | Unshielded, 0.1m, 1pcs. |

NOTE:

- 1) All the equipment/cables were placed in the worst-case configuration to maximize the emission during the test.
- 2) Grounding was established in accordance with the manufacturer's requirements and conditions for the intended use.

5.2. CONFIGURATION OF SYSTEM UNDER TEST



6 FACILITIES AND ACCREDITATIONS

6.1. FACILITIES

All measurement facilities used to collect the measurement data are located at CCS Taiwan Tainan Lab. at

☒ No.8, Jiucengling, Xinhua Dist., Tainan City 712, Taiwan (R.O.C.)

The sites are constructed in conformance with the requirements of ANSI C63.4 and CISPR Publication 22. All receiving equipment conforms to CISPR 16-1-1, CISPR 16-1-2, CISPR 16-1-3, CISPR 16-1-4 and CISPR 16-1-5.

6.2. ACCREDITATIONS

Our laboratories are accredited and approved by the following accreditation body according to ISO/IEC 17025.

| | |
|---------------|-----|
| Taiwan | TAF |
|---------------|-----|

The measuring facility of laboratories has been authorized or registered by the following approval agencies.

| | |
|----------------|-----------------|
| Canada | Industry Canada |
| Germany | TUV NORD |
| Taiwan | BSMI |
| USA | FCC |

Copies of granted accreditation certificates are available for downloading from our web site, <http://www.ccsrf.com>

6.3. MEASUREMENT UNCERTAINTY

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT as specified in CISPR 16-4-2:

| Measurement | | Frequency | Uncertainty |
|-------------------------------|--------------------|---------------------|-------------|
| Power Line Conducted Emission | | 9kHz~30MHz | ±1.39dB |
| Conduction Emission | ISN | 150kHz~30MHz | ±2.56dB |
| | T-ISN | 150kHz~30MHz | ±2.56dB |
| Radiated Emission (10m) | Test Site : OATS-5 | 30 MHz ~200 MHz | ±4.04dB |
| | | 200 MHz ~1000 MHz | ±3.78dB |
| | Test Site : OATS-6 | 30 MHz ~200 MHz | ±3.27dB |
| | | 200 MHz ~1000 MHz | ±2.68dB |
| | Test Site : OATS-7 | 30 MHz ~200 MHz | ±3.56dB |
| | | 200 MHz ~1000 MHz | ±3.25dB |
| Radiated Emission (3m) | Test Site : OATS-5 | 30 MHz ~200 MHz | ±3.45dB |
| | | 200 MHz ~1000 MHz | ±2.55dB |
| | Test Site : OATS-6 | 30 MHz ~200 MHz | ±3.55dB |
| | | 200 MHz ~1000 MHz | ±2.35dB |
| | Test Site : OATS-7 | 30 MHz ~200 MHz | ±3.55dB |
| | | 200 MHz ~1000 MHz | ±2.33dB |
| | Chamber 966 | 1000 MHz ~ 6000 MHz | ±2.65dB |

This uncertainty represents an expanded uncertainty expressed at approximately the 95% confidence level using a coverage factor of k=2.

Consistent with industry standard (e.g. CISPR 22: 2008+I3: 2012, clause 11, Measurement Uncertainty) determining compliance with the limits shall be base on the results of the compliance measurement. Consequently the measure emissions being less than the maximum allowed emission result in this be a compliant test or passing test.

The acceptable measurement uncertainty value without requiring revision of the compliance statement is base on conducted and radiated emissions being less than U_{CISPR} which is 3.6dB and 5.2dB respectively. CCS values (called U_{Lab} in CISPR 16-4-2) is less than U_{CISPR} as shown in the table above. Therefore, MU need not be considered for compliance.

7 EMISSION TEST

7.1. CONDUCTED EMISSION MEASUREMENT AT AC MAINS PORT

7.1.1 LIMITS

| FREQUENCY (MHz) | Class A (dBuV) | | Class B (dBuV) | |
|-----------------|----------------|---------|----------------|---------|
| | Quasi-peak | Average | Quasi-peak | Average |
| 0.15 - 0.5 | 79 | 66 | 66 - 56 | 56 - 46 |
| 0.50 - 5.0 | 73 | 60 | 56 | 46 |
| 5.0 - 30.0 | 73 | 60 | 60 | 50 |

Note:

1. The lower limit shall apply at the transition frequencies.
2. The limit decreases in line with the logarithm of the frequency in the range of 0.15 to 0.50 MHz.
3. All emanations from a class A/B digital device or system, including any network of conductors and apparatus connected thereto, shall not exceed the level of field strengths specified above.

7.1.2 TEST INSTRUMENTS

| Conducted Emission room #1 | | | | |
|----------------------------|------------------------------|-----------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| L.I.S.N. | SCHWARZBECK | NNLK 8130 | 8130124 | AUG. 12, 2014 |
| | Rohde & Schwarz | ESH 3-Z5 | 840062/021 | SEP. 09, 2014 |
| TEST RECEIVER | Rohde & Schwarz | ESCS 30 | 100348 | AUG. 09, 2014 |
| BNC COAXIAL CABLE | CCS | BNC50 | 11 | NOV. 19, 2014 |
| Test S/W | e-3 (5.04211c) R&S (2.27) | | | |

NOTE: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

7.1.3 TEST PROCEDURES

Procedure of Preliminary Test

The EUT was set up as per the test configuration to simulate typical usage per the user's manual. When the EUT is a tabletop system, a wooden table with a height of 0.8 meters is used and is placed on the ground plane as per EN 61000-6-3 (see Test Facility for the dimensions of the ground plane used). When the EUT is a floor-standing equipment, it is placed on the ground plane which has a 3-12 mm non-conductive covering to insulate the EUT from the ground plane.

Support equipment, if needed, was placed as per EN 61000-6-3.

All I/O cables were positioned to simulate typical actual usage as per EN 61000-6-3.

The test equipment EUT installed received main power, 230VAC/50Hz, through a Line Impedance Stabilization Network (LISN), which supplied power source and was grounded to the ground plane.

All support equipment received power from a second LISN.

The EUT test program was started. Emissions were measured on each current carrying line of the EUT using an EMI Test Receiver connected to the LISN powering the EUT.

The Receiver scanned from 150kHz to 30MHz for emissions in each of the test modes.

During the above scans, the emissions were maximized by cable manipulation.

The test mode(s) described in Item 4.1 were scanned during the preliminary test.

After the preliminary scan, we found the test mode described in Item 4.1 producing the highest emission level.

The EUT configuration and cable configuration of the above highest emission levels were recorded for reference of the final test.


Procedure of Final Test

EUT and support equipment were set up on the test bench as per the configuration with highest emission level in the preliminary test.

A scan was taken on both power lines, Line 1 and Line 2, recording at least the six highest emissions. Emission frequency and amplitude were recorded into a computer in which correction factors were used to calculate the emission level and compare reading to the applicable limit.

The test data of the worst-case condition(s) was recorded.

7.1.4 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.1.5 DATA SAMPLE

| Freq. (MHz) | LISN Factor (dB) | Cable Loss (dB) | Meter Reading (dBuV) | Measured Level (dBuV) | Limits (dBuV) | Over Limits (dBuV) | Detector |
|-------------|------------------|-----------------|----------------------|-----------------------|---------------|--------------------|----------|
| x.xx | 9.6 | 0.1 | 15.7 | 25.4 | 46 | -20.6 | QP |

Freq. = Emission frequency in MHz
 LISN Factor = Insertion loss of LISN and Pulse Limiter
 Cable Loss = Insertion loss of Cable (LISN to EMI Tester Receiver)
 Meter Reading = Uncorrected Analyzer/Receiver reading
 Measured Level = Read Level + Factor
 Limit = Limit stated in standard
 Over Limit = Reading in reference to limit
 Peak = Peak Reading
 QP = Quasi-peak Reading
 AV = Average Reading

Calculation Formula


1. Measured Level (dBuV) = LISN Factor (dB) + Cable Loss (dB) + Meter Reading (dBuV)
2. Over Limit (dBuV) = Measured Level (dBuV) – Limits (dBuV)

7.1.6 TEST RESULTS

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-103 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Vis Liang | | |

LINE

(The chart below shows the highest readings taken from the final data.)




- Note:
1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
 2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-103 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Vis Liang | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-105 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Vis Liang | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-105 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Vis Liang | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-109 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Vis Liang | | |

LINE

(The chart below shows the highest readings taken from the final data.)




- Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-109 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Vis Liang | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-112 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Vis Liang | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-112 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Vis Liang | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-115 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Vis Liang | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-115 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Vis Liang | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-124 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Vis Liang | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-124 | Test Mode | Full Load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Vis Liang | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)



Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

7.2. CONDUCTED EMISSION MEASUREMENT AT ANALOGUE/DIGITAL DATA PORTS

7.2.1. LIMITS

For Class A Equipment

| FREQUENCY (MHz) | dBuV | |
|-----------------|------------|---------|
| | Quasi-peak | Average |
| 0.15 - 0.5 | 79 | 66 |
| 0.50 - 30.0 | 73 | 60 |

Note: The limits decrease linearly with the logarithm of the frequency in the range 0.15 MHz to 0.5 MHz.

For Class B Equipment

| FREQUENCY (MHz) | Voltage Limit (dBuV) | | Current Limit (dBuA) | |
|-----------------|----------------------|---------|----------------------|---------|
| | Quasi-peak | Average | Quasi-peak | Average |
| 0.15 - 0.5 | 84 ~ 74 | 74 ~ 64 | 40 ~ 30 | 30 ~ 20 |
| 0.5 - 30.0 | 74 | 64 | 30 | 20 |

Note: The limits decrease linearly with the logarithm of the frequency in the range 0.15 MHz to 0.5 MHz.

7.2.2. TEST INSTRUMENTS

| Conducted Emission room # 1 | | | | |
|-----------------------------|---------------------------|--------------------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| L.I.S.N. | SCHWARZBECK | NNLK 8130 | 8130124 | AUG. 12, 2014 |
| TEST RECEIVER | Rohde & Schwarz | ESCS 30 | 100348 | SEP. 09, 2014 |
| BNC COAXIAL CABLE | CCS | BNC50 | 11 | AUG. 09, 2014 |
| T-ISN | SCHAFFNER | ISN PLC-25-30 | 23391 | NOV. 19, 2014 |
| ISN | FCC | F-071115-1057-1-09 | 111130 | SEP. 10, 2014 |
| Test S/W | e-3 (5.04211c) R&S (2.27) | | | |

Note:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R = No Calibration Request.

7.2.3. TEST PROCEDURE

Selecting ISN for unscreened cable or a current probe for screened cable to take measurement.

The port of the EUT was connected to the remote side support equipment through the ISN/Current Probe and communication in normal condition.

Making a overall range scan by using the test receiver controlled by controller and record at least six highest emissions for showing in the test report.

Emission frequency and amplitude were recorded into a computer in which correction factors were used to calculate the emission level and compare reading to the applicable limit.

In case of measuring on the screened cable, the current limit shall be applied; otherwise the voltage limit should be applied.


The following test mode was scanned during the preliminary test:

N/A

After the preliminary scan, we found the following test mode(s) producing the highest emission level and test data of the worst case was recorded.

N/A

7.2.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.2.5. DATA SAMPLE

| Freq. (MHz) | Reading (dBuV) | Factor (dB) | Result (dBuV) | Limit (dBuV) | Margin (dB) | Detector (P/Q/A) |
|----------------|-------------------|----------------|------------------|-----------------|----------------|---------------------|
| x.xx | 62.95 | 0.55 | 63.50 | 84 | -20.50 | Q |

Freq. = Emission frequency in MHz
Reading = Uncorrected Analyzer/Receiver reading
Factor = Insertion loss of LISN + Cable Loss
Result = Reading + Factor
Limit = Limit stated in standard
Margin = Reading in reference to limit
P = Peak Reading
Q = Quasi-peak Reading
A = Average Reading

Calculation Formula

Margin (dB) = Result (dBuV) – Limit (dBuV)

7.2.6. TEST RESULTS

※ **Note:** No applicable, the EUT doesn't have LAN Port or Modem port.

7.3. RADIATED EMISSION MEASUREMENT

7.3.1. LIMITS

Below 1GHz

| FREQUENCY (MHz) | dBuV/m (At 10m) | |
|-----------------|-----------------|---------|
| | Class A | Class B |
| 30 ~ 230 | 40 | 30 |
| 230 ~ 1000 | 47 | 37 |

Note: The lower limit shall apply at the transition frequencies.

Above 1GHz

| FREQUENCY (MHz) | Class A (dBuV/m) (At 3m) | | Class B (dBuV/m) (At 3m) | |
|-----------------|--------------------------|------|--------------------------|------|
| | Average | Peak | Average | Peak |
| 1000 ~ 3000 | 56 | 76 | 50 | 70 |
| 3000 ~ 6000 | 60 | 80 | 54 | 74 |

Note: The lower limit shall apply at the transition frequencies.

According to EN55032:2012+AC:2013, the measurement frequency range shown in the following table:

| Highest frequency generated or used within the EUT or on which the EUT operates or tunes (MHz) | Upper frequency of measurement range (MHz) |
|--|---|
| Less than 108 | 1000 |
| 108-500 | 2000 |
| 500-1000 | 5000 |
| Above 1000 | 5 times of the highest frequency or 6GHz, whichever is less |

7.3.2. TEST INSTRUMENTS

| Open Area Test Site # 5 | | | | |
|-------------------------|----------------------------|-------------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| TEST RECEIVER | Rohde & Schwarz | ESCS 30 | 100294 | JUN. 24, 2014 |
| TYPE N COAXIAL CABLE | SUHNER | RG_214_U/2X | 5 | NOV. 18, 2014 |
| BILOG ANTENNA | Sunol sciences | JB1 | A070506-1 | SEP. 11, 2014 |
| Test Software | EMI e-3 / AUDIX (5.04211c) | | | |

| Open Area Test Site # 7 | | | | |
|-------------------------|----------------------------|-------------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| TEST RECEIVER | Rohde & Schwarz | ESCS30 | 100343 | FEB. 26, 2015 |
| EMI Test Receiver | Rohde & Schwarz | ESCI3 | 101336 | JAN. 17, 2015 |
| TYPE N COAXIAL CABLE | SUHNER | RG_214_U/2X | 7 | NOV. 18, 2014 |
| BILOG ANTENNA | Sunol sciences | JB1 | A013105-1 | SEP. 11, 2014 |
| Test Software | EMI e-3 / AUDIX (5.04211c) | | | |

| Above 1GHz Used | | | | |
|-------------------------|----------------------------|------------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| EMI Receiver | R&S | ESVS10 | 833206/012 | JUN. 29, 2014 |
| Horn Antenna | Com-Power | AH-118 | 071032 | DEC. 05, 2014 |
| Pre-Amplifier | HP | 8447F | 2944A03817 | FEB. 13, 2015 |
| Pre-Amplifier | EMCI | EMC 012645 | 980097 | FEB. 16, 2015 |
| TYPE N COAXIAL CABLE | SUHNER | CHA9513 | 6 | DEC. 18, 2014 |
| BI-LOG Antenna | Sunol | JB1 | A070506-2 | SEP. 09, 2014 |
| Pre-Amplifier | EMCI | EMC 012645 | 980097 | FEB. 16, 2015 |
| Test Software | EMI e-3 / AUDIX (5.04211c) | | | |
| Spectrum Analyzer | R&S | FSU | 200789 | JUL. 01, 2014 |
| ROHDE&SCHWARZ | Signal Analyzer | FSV 40 | 101073 | APR. 25, 2015 |

Note:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R. = No Calibration Request.

7.3.3. TEST PROCEDURE

Procedure of Preliminary Test

The equipment was set up as per the test configuration to simulate typical usage per the user's manual. When the EUT is a tabletop system, a wooden turntable with a height of 0.8 meters is used which is placed on the ground plane. When the EUT is a floor standing equipment, it is placed on the ground plane which has a 15 cm non-conductive covering to insulate the EUT from the ground plane.

Support equipment, if needed, was placed as per EN 55032.

All I/O cables were positioned to simulate typical usage as per EN 55032.

The antenna was placed at 10 meter away from the EUT as stated in per EN 55032. The antenna connected to the Spectrum Analyzer via a cable and at times a pre-amplifier would be used.

The Analyzer / Receiver quickly scanned from 30MHz to 1000MHz. The EUT test program was started. Emissions were scanned and measured rotating the EUT to 360 degrees and positioning the antenna 1 to 4 meters above the ground plane, in both the vertical and the horizontal polarization, to maximize the emission reading level.

The test mode(s) described in Item 4.1 were scanned during the preliminary test:

After the preliminary scan, we found the test mode described in Item 4.1 producing the highest emission level.

The EUT and cable configuration, antenna position, polarization and turntable position of the above highest emission level were recorded for the final test.

Procedure of Final Test


EUT and support equipment were set up on the turntable as per the configuration with highest emission level in the preliminary test.

The Analyzer / Receiver scanned from 30MHz to 1000MHz. Emissions were scanned and measured rotating the EUT to 360 degrees, varying cable placement and positioning the antenna 1 to 4 meters above the ground plane, in both the vertical and the horizontal polarization, to maximize the emission reading level.


Recorded at least the six highest emissions. Emission frequency, amplitude, antenna position, polarization and turntable position were recorded into a computer in which correction factors were used to calculate the emission level and compare reading to the applicable limit and only Q.P. reading is presented.

The test data of the worst-case condition(s) was recorded.

7.3.4. TEST SETUP



Above 1 GHz



For For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.3.5. DATA SAMPLE

| Freq. (MHz) | Reading (dBuV/m) | Factor (dB) | Result (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Detector (P/Q) | Pol. (H/V) |
|----------------|---------------------|----------------|--------------------|-------------------|----------------|-------------------|---------------|
| x.xx | 14.0 | 12.2 | 26.2 | 30 | -3.8 | Q | H |

Freq. = Emission frequency in MHz
Reading = Uncorrected Analyzer/Receiver reading
Factor = Antenna Factor + Cable Loss - Amplifier Gain
Result = Reading + Factor
Limit = Limit stated in standard
Margin = Reading in reference to limit
P = Peak Reading
Q = Quasi-peak Reading
H = Antenna Polarization: Horizontal
V = Antenna Polarization: Vertical

Calculation Formula

Margin (dB) = Result (dBuV/m) – Limit (dBuV/m)

Above 1GHz

| Freq. | Reading | AF | C loss | Pre-amp | Filter | Level | Limit | Margin | Mark |
|----------|---------|--------|--------|---------|--------|----------|----------|--------|---------|
| (MHz) | (dBμV) | (dBμV) | (dB) | (dB) | (dB) | (dBμV/m) | (dBμV/m) | (dB) | (P/Q/A) |
| XXXX. XX | 56.00 | 25.14 | 2.07 | 41.77 | 0.72 | 42.16 | 70.00 | -27.84 | P |

Freq. = Emission frequency in MHz
Reading = Uncorrected Analyzer/Receiver reading
AF = Antenna Factor
C loss = Insertion loss of cable
Pre-amp = Pre-amplifier Gain
Filter = Insertion loss of filter
Level = Reading+AF+C loss-Pre-amp+Filter
Limit = Limit stated in standard
Margin = Reading in reference to limit
Mark: P = Peak Reading
Q = Quasi-peak Reading
A = Average Reading

Calculation Formula


Margin (dB) =Level (dBuV/m) – Limit (dBuV/m)

7.3.6. TEST RESULTS

Below 1GHz

| | | | |
|---------------------------------|--------------|-----------------------------|-----------|
| Model No. | TMPS 03-103 | Test Mode | Full Load |
| Environmental Conditions | 29°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested by | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|--------------|-----------------------------|-----------|
| Model No. | TMPS 03-103 | Test Mode | Full Load |
| Environmental Conditions | 29°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested by | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|--------------|-----------------------------|-----------|
| Model No. | TMPS 03-105 | Test Mode | Full Load |
| Environmental Conditions | 20°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |


(The chart below shows the highest readings taken from the final data.)



Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)
2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|--------------|-----------------------------|-----------|
| Model No. | TMPS 03-105 | Test Mode | Full load |
| Environmental Conditions | 20°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-109 | Test Mode | Full load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|-----------------|-----------------------------|-----------|
| Model No. | TMPS 03-109 | Test Mode | Full load |
| Environmental Conditions | 25.9°C , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-112 | Test Mode | Full load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-112 | Test Mode | Full load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBUV/m) = Read Level (dBUV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBUV/m)-Limit Line(dBUV/m)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-115 | Test Mode | Full load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-115 | Test Mode | Full load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|----------------|-----------------------------|-----------|
| Model No. | TMPS 03-124 | Test Mode | Full load |
| Environmental Conditions | 25.9°C, 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

| | | | |
|---------------------------------|-----------------|-----------------------------|-----------|
| Model No. | TMPS 03-124 | Test Mode | Full load |
| Environmental Conditions | 25.9°C , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)



Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

Above 1GHz

※ No applicable, since the highest frequency of the internal sources of the EUT is less than 108MHz, the measurement shall only be made up to 1 GHz.

7.4. HARMONICS CURRENT MEASUREMENT

7.4.1. LIMITS OF HARMONICS CURRENT MEASUREMENT

| Limits for Class A equipment | | Limits for Class D equipment | | |
|------------------------------|--------------------------------------|------------------------------|--|--------------------------------------|
| Harmonics Order n | Max. permissible harmonics current A | Harmonics Order n | Max. permissible harmonics current per watt mA/W | Max. permissible harmonics current A |
| Odd harmonics | | Odd Harmonics only | | |
| 3 | 2.30 | 3 | 3.4 | 2.30 |
| 5 | 1.14 | 5 | 1.9 | 1.14 |
| 7 | 0.77 | 7 | 1.0 | 0.77 |
| 9 | 0.40 | 9 | 0.5 | 0.40 |
| 11 | 0.33 | 11 | 0.35 | 0.33 |
| 13 | 0.21 | 13 | 0.30 | 0.21 |
| 15<=n<=39 | 0.15x15/n | 15<=n<=39 | 3.85/n | 0.15x15/n |
| Even harmonics | | | | |
| 2 | 1.08 | | | |
| 4 | 0.43 | | | |
| 6 | 0.30 | | | |
| 8<=n<=40 | 0.23x8/n | | | |

Note:

- Class A and Class D are classified according to item 7.4.3.
- According to section 7 of EN 61000-3-2, the above limits for all equipment except for lighting equipment having an active input power > 75 W and no limits apply for equipment with an active input power up to and including 75 W.

7.4.2. TEST INSTRUMENTS

| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
|--------------------------------|-------------------------|--|---------------|-----------------|
| Harmonic & Flicker Test System | Teseq | Proflin 2105(NSG 1007/CCN 1000-1) | 1504A02655 | 03/02/2017 |
| Software | Win2100v4 Version 4.5.8 | | | |

Note: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

7.4.3. TEST PROCEDURE

The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the maximum harmonic components under normal operating conditions for each successive harmonic component in turn.

The classification of EUT is according to section 5 of EN 61000-3-2.

The EUT is classified as follows:

Class A: Balanced three-phase equipment, Household appliances excluding equipment as Class D, Tools excluding portable tools, Dimmers for incandescent lamps, audio equipment, equipment not specified in one of the three other classes.


Class B: Portable tools; Arc welding equipment which is not professional equipment.

Class C: Lighting equipment.

Class D: Equipment having a specified power less than or equal to 600 W of the following types: Personal computers and personal computer monitors and television receivers.

The correspondent test program of test instrument to measure the current harmonics emanated from EUT is chosen. The measure time shall be not less than the time necessary for the EUT to be exercised.

7.4.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.4.5. TEST RESULTS

| | | | |
|---------------------------------|----------------------------|---------------------|---|
| Environmental Conditions | ---°C, ---% RH, ---mbar | Test Results | --- |
| Tested By | --- | Limits | Class <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D |

Note:

1. Limits classified according to item 7.4.3.
2. According to clause 7 of EN 61000-3-2: 2006, equipment with a rated power of 75W or less, no limits apply. The test result is only for reference.

Test result of EN 61000-3-2

※ For the equipment with a rated power of 75 W or less, limits are not specified in this standard.

7.5. VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT**7.5.1. LIMITS OF VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT**

| TEST ITEM | LIMIT | REMARK |
|---------------|-------|--|
| P_{st} | 1.0 | P_{st} means short-term flicker indicator. |
| P_{lt} | 0.65 | P_{lt} means long-term flicker indicator. |
| T_{dt} (ms) | 500 | T_{dt} means maximum time that dt exceeds 3 %. |
| d_{max} (%) | 4% | d_{max} means maximum relative voltage change. |
| dc (%) | 3.3% | dc means relative steady-state voltage change |

7.5.2. TEST INSTRUMENTS

| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
|--------------------------------|-------------------------|-----------------------------------|---------------|-----------------|
| Harmonic & Flicker Test System | Teseq | Proflin 2105(NSG 1007/CCN 1000-1) | 1504A02655 | 03/02/2017 |
| Test S/W | Win2100v4 Version 4.5.8 | | | |


NOTE: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

7.5.3. TEST PROCEDURE

The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the most unfavorable sequence of voltage changes under normal operating conditions.

During the flick measurement, the measure time shall include that part of whole operation cycle in which the EUT produce the most unfavorable sequence of voltage changes. The observation period for short-term flicker indicator is 10 minutes and the observation period for long-term flicker indicator is 2 hours.

7.5.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.5.5. TEST RESULTS

| | | | |
|---------------------------------|---------------------------------|------------------|-----------|
| Observation Period (Tp) | 600 Seconds | Test Mode | Full Load |
| Environmental Conditions | 25 deg.C, 48 % RH, 1028 mbar | Tested by | Yuna Lin |

Test result of EN 61000-3-3

Flicker Test Summary per EN/IEC61000-3-3 (Run time)


| | | |
|---|-----------------------------------|-----------------------|
| EUT: Equipment under test | | Tested by: Yuna.Lin |
| Test category: All parameters (European limits) | | Test Margin: 100 |
| Test date: 2016/11/8 | Start time: PM 03:37:53 | End time: PM 03:48:23 |
| Test duration (min): 10 | Data file name: F-000015.cts_data | |
| Customer: TRACO ELECTRONIC AG | | |
| Equipment Under Test: AC DC Power Module | | |
| Model:TMPS 03-103 | | |
| Test Result: Pass | Status: Test Completed | |

P_{st} and limit line

European Limits



Plt and limit line



Parameter values recorded during the test:

Vrms at the end of test (Volt): 230.65

| | | | | |
|-------------------------------|-------|------------------|-------|------|
| Highest dt (%): | 0.00 | Test limit (%): | N/A | N/A |
| T-max (mS): | 0 | Test limit (mS): | 500.0 | Pass |
| Highest dc (%): | 0.00 | Test limit (%): | 3.30 | Pass |
| Highest dmax (%): | 0.03 | Test limit (%): | 4.00 | Pass |
| Highest Pst (10 min. period): | 0.064 | Test limit: | 1.000 | Pass |
| Highest Plt (2 hr. period): | 0.028 | Test limit: | 0.650 | Pass |

8 IMMUNITY TEST

8.1. GENERAL DESCRIPTION

| Product Standard | EN 55024: 2010 | |
|--|----------------|---|
| | Test Type | Minimum Requirement |
| Basic Standard, Specification, and Performance Criterion required | IEC 61000-4-2 | Electrostatic Discharge – ESD: Air Discharge: 2, 4, 8kV; Contact Discharge: 2, 4 kV (Direct/Indirect) Performance Criterion B |
| | IEC 61000-4-3 | Radio-Frequency Electromagnetic Field Susceptibility Test – RS: 80 ~1000 MHz, 3V/m, 80% AM(1kHz), Performance Criterion A |
| | IEC 61000-4-4 | Electrical Fast Transient/Burst - EFT, AC Power Port: 1kV DC Power Port: 0.5kV Signal Ports and Telecommunication Ports: 0.5kV Performance Criterion B |
| | IEC 61000-4-5 | Surge Immunity Test: 1.2/50 us Open Circuit Voltage, 8 /20 us Short Circuit Current, Power Port ~ Line to line: 1kV, Line to ground: 2kV Performance Criterion B |
| | IEC 61000-4-6 | Conducted Radio Frequency Disturbances Test - CS: 0.15 ~ 80 MHz, 3Vrms, 80% AM, 1kHz, Performance Criterion A |
| | IEC 61000-4-8 | Power frequency magnetic field immunity test 50/60Hz, 3A/m Performance Criterion A |
| | IEC 61000-4-11 | Voltage Dips: 1)>95% reduction 0.5/1 period Performance Criterion B 2)30% reduction 25/30 period Performance Criterion C Voltage Interruptions: 1)>95% reduction 250/300 period Performance Criterion C |

8.2. GENERAL PERFORMANCE CRITERIA DESCRIPTION

| | |
|--------------------|---|
| Criteria A: | The apparatus shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed below a performance level specified by the manufacturer, when the apparatus is used as intended. The performance level may be replaced by a permissible loss of performance. If the manufacturer does not specify the minimum performance level or the permissible performance loss, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended. |
| Criteria B: | <p>After test, the apparatus shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed, after the application of the phenomenon below a performance level specified by the manufacturer, when the apparatus is used as intended. The performance level may be replaced by a permissible loss of performance.</p> <p>During the test, degradation of performance is however allowed. However, no change of operating state if stored data is allowed to persist after the test. If the manufacturer does not specify the minimum performance level or the permissible performance loss, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.</p> |
| Criteria C: | <p>Temporary loss of function is allowed, provided the functions is self-recoverable or can be restored by the operation of controls by the user in accordance with the manufacturer instructions.</p> <p>Functions, and/or information stored in non-volatile memory, or protected by a battery backup, shall not be lost.</p> |

8.3. ELECTROSTATIC DISCHARGE (ESD)**8.3.1. TEST SPECIFICATION****Basic Standard:** IEC 61000-4-2**Discharge Impedance:** 330 ohm / 150 pF**Discharge Voltage:** Air Discharge: 2, 4, 8kV;
Contact Discharge: 4 kV (Direct/Indirect)**Polarity:** Positive & Negative**Number of Discharge:** Minimum 10 times at each test point**Discharge Mode:** Single Discharge
1 second minimum**8.3.2. TEST INSTRUMENT**

| IMMUNITY SHIELDED ROOM | | | | |
|------------------------|--------------|----------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| ESD Simulator | NoiseKen | ESS-2002 | ESS04Z3762 | MAR. 16, 2015 |

NOTE: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

8.3.3. TEST PROCEDURE

The discharges shall be applied in two ways:

a) Contact discharges to the conductive surfaces and coupling planes:

The EUT shall be exposed to at least 200 discharges, 100 each at negative and positive polarity, at a minimum of four test points. One of the test points shall be subjected to at least 50 indirect discharges to the center of the front edge of the **Horizontal Coupling Plane (HCP)**. The remaining three test points shall each receive at least 50 direct contact discharges. If there is no direct contact test points are available, then at least 200 indirect discharges shall be applied in the indirect mode. Test shall be performed at a maximum repetition rate of one discharge per second.


b) Air discharges at slots and apertures and insulating surfaces:

On those parts of the EUT where it is not possible to perform contact discharge testing, the equipment should be investigated to identify user accessible points where breakdown may occur. Such points are tested using the air discharge method. This investigation should be restricted to those area normally handled by the user. A minimum of 10 single air discharges shall be applied to the selected test point for each such area.

The basic test procedure was in accordance with IEC 61000-4-2:

- a) The EUT was located 0.1 m minimum from all side of the **HCP** (dimensions 1.6m x 0.8m).
- b) The support units were located another table 30 cm away from the EUT, but direct support unit was/were located at same location as EUT on the HCP and keep at a distance of 10 cm with EUT.
- c) The time interval between two successive single discharges was at least 1 second.
- d) Contact discharges were applied to the non-insulating coating, with the pointed tip of the generator penetrating the coating and contacting the conducting substrate.
- e) Air discharges were applied with the round discharge tip of the discharge electrode approaching the EUT as fast as possible (without causing mechanical damage) to touch the EUT. After each discharge, the ESD generator was removed from the EUT and re-triggered for a new single discharge. The test was repeated until all discharges were complete.
- f) At least ten single discharges (in the most sensitive polarity) were applied at the front edge of each **HCP** opposite the center point of each unit of the EUT and 0.1 meters from the front of the EUT. The long axis of the discharge electrode was in the plane of the **HCP** and perpendicular to its front edge during the discharge.
- g) At least ten single discharges (in the most sensitive polarity) were applied to the center of one vertical edge of the **Vertical Coupling Plane (VCP)** in sufficiently different positions that the four faces of the EUT were completely illuminated. The **VCP** (dimensions 0.5m x 0.5m) was placed vertically to and 0.1 meters from the EUT.

8.3.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

TABLE-TOP EQUIPMENT

The configuration consisted of a wooden table 0.8m high standing on the **Ground Reference Plane**. The **GRP** consisted of a sheet of aluminum at least 0.25mm thick, and 2.5m square connected to the protective grounding system. A **Horizontal Coupling Plane** (1.6m x 0.8m) was placed on the table and attached to the **GRP** by means of a cable with 940k Ω total impedance. The equipment under test, was installed in a representative system as described in section 7 of EN 61000-4-2, and its cables were placed on the **HCP** and isolated by an insulating support of 0.5mm thickness. A distance of 1m minimum was provided between the EUT and the walls of the laboratory and any other metallic structure.

FLOOR-STANDING EQUIPMENT

The equipment under test was installed in a representative system as described in section 7 of IEC 61000-4-2, and its cables were isolated from the Ground Reference Plane by an insulating support of 0.1m thickness. The GRP consisted of a sheet of aluminum that is at least 0.25mm thick, and 2.5m square connected to the protective grounding system and extended at least 0.5m from the EUT on all sides.

8.3.5. TEST RESULTS

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 23°C | Humidity | 45% RH |
| Pressure | 1028mbar | Tested By | Sam Shen |
| Required Passing Performance | | Criterion B | |



| Air Discharge | | | | | | | |
|---------------|-------------------------------------|-------------------------------------|-------------------------------------|-------------------------------------|--------------------------|--|--|
| Test Points | Test Levels | | | Results | | | |
| | ± 2 kV | ± 4 kV | ± 8 kV | Pass | Fail | Performance Criterion | |
| Front | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Back | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Left | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Right | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Top | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Bottom | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B | |

| Contact Discharge | | | | | | | |
|-------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|---|--|
| Test Points | Test Levels | | | Results | | | |
| | ± 2 kV | ± 4 kV | ± 8 kV | Pass | Fail | Performance Criterion | |
| Front | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B | |
| Back | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B | |
| Left | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B | |
| Right | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B | |
| Top | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B | |
| Bottom | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B | |

| Discharge To Horizontal Coupling Plane | | | | | | | |
|--|--------------------------|-------------------------------------|--------------------------|-------------------------------------|--------------------------|--|--|
| Side of EUT | Test Levels | | | Results | | | |
| | ± 2 kV | ± 4 kV | ± 8 kV | Pass | Fail | Performance Criterion | |
| Front | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Back | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Left | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Right | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |

| Discharge To Vertical Coupling Plane | | | | | | | |
|--------------------------------------|--------------------------|-------------------------------------|--------------------------|-------------------------------------|--------------------------|--|--|
| Side of EUT | Test Levels | | | Results | | | |
| | ± 2 kV | ± 4 kV | ± 8 kV | Pass | Fail | Performance Criterion | |
| Front | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Back | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Left | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |
| Right | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | |

The Photo for Discharge Points of EUT



Red Dot —Air Discharged

8.4. RADIATED, RADIO-FREQUENCY, ELECTROMAGNETIC FIELD (RS)

8.4.1. TEST SPECIFICATION

Basic Standard: IEC 61000-4-3
Frequency Range: 80 MHz ~1000 MHz
Field Strength: 3; 10 V/m for 80 MHz ~1000 MHz
Modulation: 1kHz Sine Wave, 80%, AM Modulation
Frequency Step: 1 % of preceding frequency value
Polarity of Antenna: Horizontal and Vertical
Test Distance: 3 m
Antenna Height: 1.5m

8.4.2. TEST INSTRUMENT

| 966 RS Chamber | | | | |
|--------------------------------------|----------------|-------------------|----------------------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | SYNNEX | BTO –LMIW300 – GB | A41202-0031 | N.C.R. |
| LCD Monitor | Acer | AL1715sm | ETL13071994430236 6RH01 | N.C.R. |
| Keyboard | SYNNEX | 5211A | G4430091266 | N.C.R. |
| Amplifier Freq. Range :80MHz~1GHz | AR | 150W1000M3 | 310037 | N.C.R. |
| Amplifier Freq. Range :0.8~3GHz | AR | 60S1G3M3 | 310102 | N.C.R. |
| Digital SIGNAL GENERATOR | HP | ESG-D3000A | US36260655 | JUN. 08 ,2015 |
| RF Power Meter | BOONTON | 4232A-01-02 | 122202 | MAY. 27, 2015 |
| Log – Periodic Antenna | AR | AT5080 | 309817 | N.C.R. |
| Software | RS SW1005 R1_4 | | | |


NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R. = No Calibration Required.

8.4.3. TEST PROCEDURE

The test procedure was in accordance with IEC 61000-4-3.

- a) The testing was performed in a fully anechoic chamber. The transmit antenna was located at a distance of 3 meters from the EUT.
- b) The frequency range is swept from 80 MHz to 2700 MHz, with the signal 80% amplitude modulated with a 1kHz sine-wave. The rate of sweep did not exceed 1.5×10^{-3} decade/s, where the frequency range is swept incrementally, the step size was 1% of preceding frequency value.
- c) The dwell time at each frequency shall be not less than the time necessary for the EUT to be able to respond.
- d) The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

8.4.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

Note:

TABLETOP EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-3 was placed on a non-conductive table 0.8 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

FLOOR-STANDING EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-3 was placed on a non-conductive wood support 0.1 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

8.4.5. TEST RESULTS

| | | | |
|-------------|----------|------------------------------|-------------|
| Temperature | 26°C | Humidity | 51% RH |
| Pressure | 1028mbar | Dwell Time | 2.86 sec. |
| Tested By | Sam Shen | Required Passing Performance | Criterion A |

| Frequency (MHz) | Polarity | Azimuth | Field Strength (V/m) | Performance Criterion | Result | Observation |
|-----------------|----------|---------|----------------------|--|--------|-------------|
| 80 ~ 1000 | V&H | 0 | 3 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| 80 ~ 1000 | V&H | 90 | 3 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| 80 ~ 1000 | V&H | 180 | 3 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| 80 ~ 1000 | V&H | 270 | 3 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |

For Strict:

| | | | |
|-------------|----------|------------------------------|-------------|
| Temperature | 26°C | Humidity | 51% RH |
| Pressure | 1028mbar | Dwell Time | 2.86 sec. |
| Tested By | Sam Shen | Required Passing Performance | Criterion A |

| Frequency (MHz) | Polarity | Azimuth | Field Strength (V/m) | Performance Criterion | Result | Observation |
|-----------------|----------|---------|----------------------|--|--------|-------------|
| 80 ~ 1000 | V&H | 0 | 10 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| 80 ~ 1000 | V&H | 90 | 10 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| 80 ~ 1000 | V&H | 180 | 10 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| 80 ~ 1000 | V&H | 270 | 10 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |

NOTE: There was no change compared with the initial operation during the test.

8.5. ELECTRICAL FAST TRANSIENT (EFT)

8.5.1. TEST SPECIFICATION

Basic Standard: IEC 61000-4-4

Test Voltage: AC Power Port: 2kV
DC Power Port: ---kV
Signal Ports and Telecommunication Ports: ---kV

Polarity: Positive & Negative

Repetition Rate: 5 kHz

Impulse Wave-shape: 5/50 ns

Burst Duration: 15 ms

Burst Period: 300 ms

Test Duration: Not less than 1 min.

8.5.2. TEST INSTRUMENT


| Immunity Shield Room | | | | |
|------------------------------|---------------|----------------|--------------------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | IBM | M/T 8183 - ICV | 99BG137 | N.C.R. |
| VGA Monitor | Acer | 1555 | 917160230584200572P5C431 | N.C.R. |
| Keyboard | HP | KB - 0133 | B69360MGAPEOK5 | N.C.R. |
| EMC Pro IMMUNITY TEST SYSTEM | KeyTek | EMCpro | 0312231 | APR. 07, 2015 |
| Test S/W | CE Ware 3.00b | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R.= No Calibration Required.

8.5.3. TEST PROCEDURE

- Both positive and negative polarity discharges were applied.
- The length of the "hot wire" from the coaxial output of the EFT generator to the terminals on the EUT should not exceed 1 meter.
- The duration time of each test sequential was 1 minute.
- The transient/burst waveform was in accordance with IEC 61000-4-4, 5/50ns.

8.5.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

Note:

TABLETOP EQUIPMENT

The configuration consisted of a wooden table (0.1m high) standing on the Ground Reference Plane. The GRP consisted of a sheet of aluminum (at least 0.25mm thick and 2.5m square) connected to the protective grounding system. A minimum distance of 0.5m was provided between the EUT and the walls of the laboratory or any other metallic structure.

FLOOR-STANDING EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-4 and its cables, were isolated from the Ground Reference Plane by an insulating support that is 0.1-meter thick. The GRP consisted of a sheet of aluminum (at least 0.25mm thick and 2.5m square) connected to the protective grounding system.

8.5.5. TEST RESULTS

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 25°C | Humidity | 48% RH |
| Pressure | 1028mbar | Tested By | Sam Shen |
| Required Passing Performance | | Criterion B | |

| Test Point | Polarity | Test Level (kV) | Performance Criterion | Result | Observation |
|------------|----------|-----------------|--|--------|-------------|
| L | +/- | 0.5 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| N | +/- | 0.5 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| L+N | +/- | 0.5 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |

For Strict:

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 25°C | Humidity | 48% RH |
| Pressure | 1028mbar | Tested By | Sam Shen |
| Required Passing Performance | | Criterion B | |

| Test Point | Polarity | Test Level (kV) | Performance Criterion | Result | Observation |
|------------|----------|-----------------|--|--------|-------------|
| L | +/- | 2 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| N | +/- | 2 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| L + N | +/- | 2 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |

NOTE: 1. There was no change compared with initial operation during the test.

8.6. SURGE IMMUNITY TEST

8.6.1. TEST SPECIFICATION

Basic Standard: IEC 61000-4-5

Wave-Shape: Combination Wave
1.2/50 us Open Circuit Voltage
8/20 us Short Circuit Current

Test Voltage: AC Power Port~ line to line: 1kV, line to ground: ---kV
DC Power Port~ line to earth: ---kV
Signal and Telecommunication Ports ~ line to ground: ---kV

Generator Source Impedance: 2 ohm between networks
12 ohm between network and ground

Polarity: Positive/Negative

Phase Angle: 0^0 / 90^0 / 180^0 / 270^0

Pulse Repetition Rate: 2 times / min. (maximum)

Number of Tests: 5 positive and 5 negative at selected points

8.6.2. TEST INSTRUMENT

| Immunity Shield Room | | | | |
|-------------------------|--------------------|-----------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| CDN | EMC-PAPTNER | CDN-UTP8 | CDN-UTP8-1504 | 11/26/2017 |
| Ultra Compact Simulator | EM TEST | UCS 500N7 | P1552169754 | 03/10/2017 |
| Test S/W | iec.control v5.4.4 | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R. = No Calibration Required.

8.6.3. TEST PROCEDURE

a) For EUT power supply:

The surge is applied to the EUT power supply terminals via the capacitive coupling network. Decoupling networks are required in order to avoid possible adverse effects on equipment not under test that may be powered by the same lines, and to provide sufficient decoupling impedance to the surge wave. The power cord between the EUT and the coupling/decoupling networks was shorter than 2m in length.


b) For test applied to unshielded un-symmetrically operated interconnection lines of EUT:

The surge was applied to the lines via the capacitive coupling. The coupling / decoupling networks didn't influence the specified functional conditions of the EUT. The interconnection line between the EUT and the coupling/decoupling networks was shorter than 2m in length.

c) For test applied to unshielded symmetrically operated interconnection / telecommunication lines of EUT:

The surge was applied to the lines via gas arrestors coupling. Test levels below the ignition point of the coupling arrestor were not specified. The interconnection line between the EUT and the coupling/decoupling networks was shorter than 2m in length.

8.6.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

8.6.5. TEST RESULTS

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 25°C | Humidity | 48% RH |
| Pressure | 1028mbar | Tested By | Sam Shen |
| Required Passing Performance | | Criterion B | |

| Test Point | Polarity | Test Level (kV) | Performance Criterion | Result | Observation |
|------------|----------|-----------------|--|--------|-------------|
| L - N | +/- | 1 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |

8.7. CONDUCTED RADIO FREQUENCY DISTURBANCES (CS)

8.7.1. TEST SPECIFICATION

Basic Standard: IEC 61000-4-6
Frequency Range: 0.15 MHz ~ 80 MHz
Field Strength: 10 Vrms
Modulation: 1kHz Sine Wave, 80%, AM Modulation
Frequency Step: 1 % of preceding frequency value
Coupled cable: Power Mains, Unshielded
Coupling device: CDN-M2 (2 wires)

8.7.2. TEST INSTRUMENT

| CS Test Site (IEC/EN 61000-4-6) | | | | |
|--|----------------|-------------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | HP | d330 uT | SGH3480LTH | N.C.R. |
| VGA Monitor | NEC | JC-1572VMA | 6600645RA | N.C.R. |
| Keyboard | IBM | KB - 8923 | 1021424 | N.C.R. |
| CS Frankonia EMVMess-System GmbH | FRANKONIA | CIT-10/75 | 102C3220 | JUN 10, 2015 |
| FCC Coupling Decoupling Network Freq. range : 150KHz~230MHz | FRANKONIA | CDN M2+M3 | A3011095 | JUN. 09, 2015 |
| FCC EM Injection Clamp | ----- | F-203I-23mm | 449 | NOV. 17, 2014 |
| Test S/W | CS-EN61000-4-6 | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R.= No Calibration Required.

8.7.3. TEST PROCEDURE

The EUT shall be tested within its intended operating and climatic conditions.


The test shall be performed with the test generator connected to each of the coupling and decoupling devices in turn, while the other non-excited RF input ports of the coupling devices are terminated by a 50-ohm load resistor.

The frequency range was swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80 % amplitude. The signal was modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. The sweep rate was 1.5×10^{-3} decades/s. Where the frequency range is swept incrementally, the step size was 1 % of preceding frequency value from 150 kHz to 80 MHz.

The dwell time at each frequency was less than the time necessary for the EUT to be exercised, and able to respond. Sensitive frequencies such as clock frequency(ies) and harmonics or frequencies of dominant interest, was analyzed separately.

An attempt was made to fully exercise the EUT during testing, and to fully interrogate all exercise modes selected for susceptibility.

8.7.4. TEST SETUP



Note:

1. The EUT is setup 0.1m above Ground Reference Plane
2. The CDNs and / or EM clamp used for real test depend on ports and cables configuration of EUT.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

Note:

TABLETOP AND FLOOR-STANDING EQUIPMENT

The equipment to be tested is placed on an insulating support of 0.1 meters height above a ground reference plane. All relevant cables shall be provided with the appropriate coupling and decoupling devices at a distance between 0.1 meters and 0.3 meters from the projected geometry of the EUT on the ground reference plane.

8.7.5. TEST RESULTS

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 25°C | Humidity | 46% RH |
| Pressure | 1028mbar | Tested By | Sam Shen |
| Required Passing Performance | | Criterion A | |

| Frequency Band (MHz) | Field Strength (Vrms) | Cable | Injection Method | Performance Criterion | Result | Observation |
|----------------------|-----------------------|----------|------------------|--|--------|-------------|
| 0.15 ~ 80 | 3 | AC Power | CDN-M2 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |

For Strict:

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 25°C | Humidity | 46% RH |
| Pressure | 1028mbar | Tested By | Sam Shen |
| Required Passing Performance | | Criterion A | |

| Frequency Band (MHz) | Field Strength (Vrms) | Cable | Injection Method | Performance Criterion | Result | Observation |
|----------------------|-----------------------|----------|------------------|--|--------|-------------|
| 0.15 ~ 80 | 10 | AC Power | CDN-M2 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B | PASS | |

NOTE: 1. There was no change compared with initial operation during the test.

8.8. POWER FREQUENCY MAGNETIC FIELD

8.8.1. TEST SPECIFICATION

Basic Standard: IEC 61000-4-8

Frequency Range: 50/60Hz

Field Strength: 30 A/m

Observation Time: 1 minute

Inductance Coil: Rectangular type, 1mx1m

8.8.2. TEST INSTRUMENT


| Power Frequency Magnetic Field Immunity Test (IEC/EN 61000-4-8) | | | | |
|---|--------------|----------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Magnetic field generator | Schaffner | MFO 6501 | 154 | MAR. 24, 2015 |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R. = No Calibration Required.

8.8.3. TEST PROCEDURE

- The equipment is configured and connected to satisfy its functional requirements. It shall be placed on the GRP with the interposition of a 0.1m thick insulating support.
- The equipment cabinets shall be connected to the safety earth directly on the GRP via the earth terminal of the EUT.
- The power supply, input and output circuits shall be connected to the sources of power supply, control and signal.
- The cables supplied or recommended by the equipment manufacturer shall be used. 1 meter of all cables used shall be exposed to the magnetic field.

8.8.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

TABLETOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

FLOOR-STANDING EQUIPMENT

The equipment shall be subjected to the test magnetic field by using induction coils of suitable dimensions. The test shall be repeated by moving and shifting the induction coils, in order to test the whole volume of the EUT for each orthogonal direction. The test shall be repeated with the coil shifted to different positions along the side of the EUT, in steps corresponding to 50 % of the shortest side of the coil. The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

8.8.5. TEST RESULTS

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 25°C | Humidity | 46% RH |
| Pressure | 1028mbar | Tested By | Sam Shen |
| Required Passing Performance | | Criterion A | |

| DIRECTION | Field Strength (A/m) | Performance Criterion | Result | Observation |
|-----------|----------------------|--|--------|-------------|
| X | 1 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| Y | 1 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| Z | 1 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |

For Strict:

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 25°C | Humidity | 46% RH |
| Pressure | 1028mbar | Tested By | Sam Shen |
| Required Passing Performance | | Criterion A | |

| DIRECTION | Field Strength (A/m) | Performance Criterion | Result | Observation |
|-----------|----------------------|--|--------|-------------|
| X | 30 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| Y | 30 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |
| Z | 30 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D | PASS | |

NOTE: There was no change compared with initial operation during the test.

8.9. VOLTAGE DIP & VOLTAGE INTERRUPTIONS**8.9.1. TEST SPECIFICATION****Basic Standard:** IEC 61000-4-11**Test duration time:** Minimum three test events in sequence**Interval between event:** Minimum 10 seconds**Phase Angle:** 0° / 45° / 90° / 135° / 180° / 225° / 270° / 315° / 360°**Test cycle:** 3 times**8.9.2. TEST INSTRUMENT**


| Immunity shielded room | | | | |
|------------------------------|---------------|----------------|--------------------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | IBM | M/T 8183 - ICV | 99BG137 | N.C.R. |
| VGA Monitor | Acer | 1555 | 917160230584200572P5C431 | N.C.R. |
| Keyboard | HP | KB - 0133 | B69360MGAPEOK5 | N.C.R. |
| EMC Pro IMMUNITY TEST SYSTEM | KeyTek | EMCpro | 0312231 | APR. 07, 2015 |
| Test S/W | CE Ware 3.00b | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R.= No Calibration Required.

8.9.3. TEST PROCEDURE

- The EUT and support units were located on a wooden table, 0.8 m away from ground floor.
- Setting the parameter of tests and then perform the test software of test simulator.
- Conditions changes to occur at 0 degree crossover point of the voltage waveform.
- Recording the test result in test record form.

8.9.4. TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

8.9.5. TEST RESULTS

| | | | |
|------------------------------|---|-----------|----------|
| Temperature | 25°C | Humidity | 48 % RH |
| Pressure | 1028 mbar | Tested by | Sam Shen |
| Required Passing Performance | Criterion B: >95% reduction 0.5 periods Criterion C: 30% reduction 25 periods & >95% reduction 250 periods | | |


| Test Power: 230Vac, 50Hz | | | | |
|--------------------------|----------------------|---|--------|-------------|
| Voltage (% Reduction) | Duration (Period) | Performance Criterion | Result | Observation |
| >95 | 0.5 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | PASS | |
| 30 | 25 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | PASS | |
| >95 | 250 | <input type="checkbox"/> A <input checked="" type="checkbox"/> B <input type="checkbox"/> C | PASS | |

9 PHOTOGRAPHS OF THE TEST CONFIGURATION

CONDUCTED EMISSION TEST




RADIATED EMISSION TEST



FLICK TEST



ESD TEST



RS TEST




EFT TEST




SURGE TEST



CS TEST



PFMF TEST



Voltage Dips / Interruptions Test

