

Traco Power

Model: TBL 030-112

EMC – Test Report

Amendment to EMC-Report: EMC_TBL030-112_16.02.09

EUT: Traco Power - Model: TBL 030-112

Serial No.: 31248702776

Manufacturer No.: 030PSL182

Manufacturer: Convertec Ltd.
Whitemill Industrial Estate
Wexford
Republic of Ireland

Tester: Gunnar Tapper, Convertec Ltd

Date: 29/07/2014

It should be noted, that combining two or more CE compliant finished appliances does not automatically produce a compliant system. The manufacturer of an apparatus or a fixed installation as defined in the “Guide for the EMC Directive 2004/108EC, 21. May 2007” is responsible for the EMC-compliance of the final apparatus.

Table of Contents

1. Electrostatic Discharge Immunity Test3

1.1. Test Set-Up:.....3

1.2. Electrostatic Discharge Immunity Test Results4

3. Conducted RF Immunity Test at AC Mains Terminals.....5

3.1. Test Setup5

3.2. Conducted RF Immunity Test Results6

4. Conducted RF Immunity Test at DC Output Terminals.....7

4.1. Test Setup:7

4.2. Conducted RF Immunity Test Results8

5. Radiated RF Immunity Test9

5.1. Test Setup9

5.2. Radiated RF Immunity Test Results10

6. Power Frequency Magnetic Field Immunity Test 11

6.1. Test Setup11

6.2. Power Frequency Magnetic Field Immunity Test Results12

7. Voltage Sag Immunity Test (Semi F47)..... 14

7.1. Test Setup14

7.2. Voltage Sag Immunity test Results (Semi F47)15

8. Summary..... 19


1. Electrostatic Discharge Immunity Test

Equipment under Test: TBL 030-112
EUT Serial No.: 31248702776
Customer Spec: CS-XXXPSL.doc
Date: 29/07/2014
Standards: IEC61000-6-2: 2005 referring to IEC 61000-4-2: 2000

Notes:

- EUT tested under normal operating conditions of 230V 50Hz input at full nominal load (12V/2.5A Resistive).
- Since the EUT output is isolated from earth, a 470K HV resistor was placed between output and Earth to provide a discharge path between spikes.
- Contact discharge tests shall be applied to all areas exposed to the end user under final installation using ESD gun SEDS 200.
- Test voltage shall be increased from 2kV up to the max 8kV/4kV (air/contact) as required by the standard IEC/EN 61000-4-2.
- At least 10 discharges were applied per test point (in both polarities).
- A time interval between discharges of a least 1s was used.
- The ESD generator was held perpendicular to the test point wherever possible for repeatability of results.
- In the case of air discharges, the trigger is engaged at about 20cm and the tester is moved quickly toward the test point until a spark occurs and trigger is released.

1.1. Test Set-Up:



1.2. Electrostatic Discharge Immunity Test Results

All exposed metal screw heads and ground planes were tested as contact test points and also as air test points. The connector pins and all vents and inlets were also tested as air test points.

	Contact Test points:	Air Test points:
EUT	PASS	PASS

Conclusion:

The EUT still functions as expected after tests therefore it meets classification B in accordance with IEC61000-4-2.

PASS

Environmental conditions during ESD Test

	Environmental condition required according IEC61000-4-2	Environmental conditions measured
Ambient Temperature in [°C]	15 - 35	24.7
Air Humidity in [%]	30 - 60	48.3
Atmospheric Pressure in [kPa]	86.0 - 106.0	100.57

Environmental conditions during the test:

☒ kept

☐ not kept

3. Conducted RF Immunity Test at AC Mains Terminals

Equipment under Test: TBL 030-112
EUT Serial No.: 31248702776
Customer Spec: CS-XXXPSL.doc
Date: 29/07/2014
Standard: IEC61000-6-2: 2005 referring to IEC 61000-4-6:2004


- Notes:**
- EUT tested under normal operating conditions of 230V 50Hz input at full nominal load (12V/2.5A Resistive).
 - Test carried out using test generator “EM Test CWS 500N”, Coupling/Decoupling network “EM Test CDN M2/M3”, an attenuator “EM Test ATT6/75” and measurement instrument “Agilent 34410A”.
 - Unit tested to IEC61000-4-6 test level 3.

3.1. Test Setup


Test Equipment Settings:

Frq. start [MHz]	Level start [V]	Frq. stop [MHz]	Level stop [V]	Frq. step	td [s]	tp [s]	Modulation
0.150	10.0	80.000	10.0	1.0 %	0.5	0.0	AM 1kHz 80%

Test Setup:



3.2. Conducted RF Immunity Test Results



Conclusion:

The EUT meets Classification A (Ref. Section 9, IEC 61000-4-6).
The test results were evaluated in relation to the Customer Specification CS-XXXPSL.doc and the output did not change by more than +/-120mV therefore the EUT was considered to have PASSED the tests.

PASS

4. Conducted RF Immunity Test at DC Output Terminals

Equipment under Test: TBL 030-112
EUT Serial No.: 31248702776
Customer Spec: CS-XXXPSL.doc
Date: 29/07/2014
Standard: IEC61000-6-2: 2005 referring to IEC 61000-4-6:2004

Notes:


- EUT tested under normal operating conditions of 230V 50Hz input at full nominal load (12V/2.5A Resistive).
- Test carried out using test generator “EM Test CWS 500N”, Coupling/Decoupling network “EM Test CDN M2/M3”, an attenuator “EM Test ATT6/75”, measurement instrument “Agilent 34410A” and FCC-801-M2-50A Coupling/Decoupling network.
- Unit tested to IEC61000-4-6 test level 3.

4.1. Test Setup:


Test Equipment Settings:

Frq. start [MHz]	Level start [V]	Frq. stop [MHz]	Level stop [V]	Frq. step	td [s]	tp [s]	Modulation
0.150	10.0	80.000	10.0	1.0 %	0.5	0.0	AM 1kHz 80%

Test Setup:



4.2. Conducted RF Immunity Test Results



Conclusion:
Meets Classification A (Ref. Section 9, IEC 61000-4-6)
Test Results were evaluated in relation to the Customer Specification
CS-XXXPSL.doc and the output did not change by more than +/-120mV therefore the
EUT was considered to have PASSED the tests.

PASS

5. Radiated RF Immunity Test

Equipment under Test: TBL 030-112
EUT Serial No.: 31248702776
Customer Spec: CS-XXXPSL.doc
Date: 29/07/2014
Standard: IEC61000-6-2: 2005 referring to IEC61000-4-3: 2004

Notes:


- EUT tested under normal operating conditions of 230V 50Hz input at full nominal load (12V/2.5A Resistive).
- Test carried out using test generator “EM Test CWS 500N”, Antenna BicoLOG 30100 X and Digitizing Multi Meter “Agilent 34405A”
- Measurement was carried out in a shielded room
- The input power port of the EUT was connected to mains via a 1.5m 3-core cable
- The output power port of the EUT was connected to the resistor bank via 1.5m long single core wires –wire size 14AWG

5.1. Test Setup


Test Equipment Settings:

Frq. start [MHz]	Level start [V]	Frq. stop [MHz]	Level stop [V]	Frq. step	td [s]
80.0	10.0	1000.0	10.0	1.0 %	1

Test Setup:



5.2. Radiated RF Immunity Test Results



Conclusion:
The EUT meets classification A (Ref. Section 9, IEC 61000-4-3). The test results were evaluated in relation to the Customer Specification CS-XXXPSL.doc and the output did not change by more than +/-120mV therefore the EUT was considered to have PASSED the tests.

PASS

6. Power Frequency Magnetic Field Immunity Test

Equipment under Test: TBL 030-112
EUT Serial No.: 31248702776
Customer Spec: CS-XXXPSL.doc
Date: 29/07/2014
Standard: IEC61000-6-2: 2005 referring to IEC61000-4-8: 2001

Notes:


- EUT tested under normal operating conditions of 230V 50Hz input at full nominal load (12V/2.5A Resistive).
- Test carried out using test generator “Chroma Programmable AC Source”, “1meter x 1meter 100 turn Induction Coil” and measurement instrument “Agilent 34405A”.
- Unit only required to meet test level 4 but tested to IEC61000-4-8 test levels 5.

6.1. Test Setup



Test Equipment Settings:

Test generator settings			
Frequency	AC Current through Induction Coil (Arms)	Magnetic Field Strength (A/m)	Applied Field duration [s]
50Hz	1	100	Continuous
60Hz	1	100	Continuous
50Hz	10	1000	3
60Hz	10	1000	3

Test Setup:



6.2. Power Frequency Magnetic Field Immunity Test Results



Conclusion:

The EUT meets classification A (Ref. Section 9, IEC 61000-4-8). The test results were evaluated in relation to the Customer Specification CS-XXXPSL.doc and the output did not change by more than +/-120mV therefore the EUT was considered to have PASSED the tests.

PASS


7. Voltage Sag Immunity Test (Semi F47)

Equipment under Test: TBL 030-112
EUT Serial No.: 31248702776
Customer Spec: CS-XXXPSL.doc
Date: 29/07/2014
Standard: SEMI F47-0706

Notes:

- EUT tested under operating conditions of 230V and 115V 50Hz input at full nominal load (12V/2.5A Resistive).
- Test carried out using test generator using Voltage Sag Generator: Schaffner NSG1003: Dropout and Variation Simulator and Oscilloscope Tektronix: TDS2014C.
- Pass/Fail Criteria for Subsystems and Components-Voltage sag immunity testing of subsystems and components should meet the following as required by Semi-F47:
 - A. Performs at full rated operation.
 - B. May not perform at full rated operation but recovers operation without operator and/or host controller intervention. Must not send error signals to the equipment host controller indicating when full rated operation is not achieved.
 - C. May not perform at full rated operation but recovers operation without operator and/or host controller intervention. May send signals to the equipment host controller indicating when full rated operation is not achieved.
 - D. Does not perform at full rated operation and requires an operator and/or host controller intervention for recovering.

7.1. Test Setup



7.2. Voltage Sag Immunity test Results (Semi F47)

Input Voltage = 230VAC, Output = 12V,2.5A

Voltage Sag	Duration	Duration	Output Voltage	% delta of nominal output voltage	Semi F47	Criteria
[V]	[s]	[cycles]	[V]	DUT 50Hz [%]	[%]	[Class]
207	20	1000	11.99	0.1	90	A
207	10	500	11.99	0.1	90	A
184	10	500	11.99	0.1	80	A
184	1	50	11.99	0.1	80	A
184	0.5	25	11.99	0.1	80	A
161	0.5	25	11.99	0.1	70	A
161	0.5	10	11.99	0.1	70	A
115	0.2	10	11.99	0.1	50	A
115	0.02	1	11.99	0.1	50	A
0	0.02	1	11.99	0.1	0	A

*Yellow indicates the required Voltage SAG Immunity Levels. Other levels are recommended.




Figure 1: TBL 030-112/ 0-1000 cycles




Figure 2: TBL 030-112/ 0-100 cycles

Input Voltage = 115VAC, Output = 12V, 2.5A

Voltage Sag	Duration	Duration	Output Voltage	% delta of nominal output voltage	Semi F47	Criteria
[V]	[s]	[cycles]	[V]	DUT 50Hz [%]	[%]	[Class]
103.5	20	1000	11.99	0.1	90	A
103.5	10	500	11.99	0.1	90	A
92	10	500	11.99	0.1	80	A
92	1	50	11.99	0.1	80	A
92	0.5	25	11.99	0.1	80	A
80.5	0.5	25	11.98	0.1	70	A
80.5	0.5	10	11.98	0.2	70	A
57.5	0.2	10	11.23	6.5	50	B
57.5	0.02	1	11.74	2.2	50	B
0	0.02	1	11.61	3.2	0	B




Figure 3: TBL 030-112/ 0-1000 cycles




Figure 4: TBL 030-112/ 0-100 cycles

Conclusion:

The EUT meets classification B (Ref. SEMI F47-0706). The test results were evaluated in relation to the Customer Specification CS-XXXPSL.doc and the EUT was considered to have PASSED the tests.

PASS

8. Summary

Regulation	Class/Test Level	Result	Comments
IEC61000-6-2: 2005 + IEC 61000-4-2:2005			
Electrostatic Discharge			
- Air Discharge	+/- 2/8kV (Class B)	PASS	
- Contact Discharge	+/- 2/4kV (Class B)	PASS	
IEC61000-6-2: 2005 + IEC61000-4-6:2004			
Conducted Input RF Immunity	Level III 10V (Class A)	PASS	
Conducted Output RF Immunity	Level III 10V (Class A)	PASS	
Signal Ports RF Immunity	Level III 10V (Class A)	n/a	
IEC61000-6-2: 2005 + IEC61000-4-3:2004			
Radiated RF Immunity	Level III 10V (Class A)	PASS	
IEC61000-6-2: 2005 + IEC61000-4-8: 2001			
Power Frequency Magnetic Field Immunity	Level 5 (Class A)	PASS	
SEMI F47-0706			
Semi F47 Voltage SAG Immunity			
-AC Supply (230VAC and 115VAC)	(Class B)	PASS	
IEC61000-6-2:2005 + IEC 61000-4-11:2004			
Voltage Dips			

List of Equipment Used:

Description	Model No.	Manufacturer	Serial No.
EMC Analyzer	E7402A	Agilent	MY45119210
LISN 1	PMM L2-16	PMM	1230L00301
LISN 2	FCC-801-M2-50A	FCC	3035
LISN 3	NSLK 8127	Schwarzbeck	8127683
RF Current Probe	F-33-1	FCC	759
Transient Limiter	11947A	Agilent	3107A03645
Precision Power Meter	LMG95	Zimmer	10790709
ESD Gun	SESD 200	Schloder	142261
Surge Generator	PSURGE 4010	Haefely	583 334-63
Burst generator	PEFT 4010	Haefely	080 981-08
Coupling Capacitor	IP4A	Haefely	171241
Electronic Load	ELA 500	Zentro-Electrik	63145803
High Power Resistors	n/a	n/a	n/a
Multimeter	34405A	Agilent	TW46290007
Multimeter	34405A	Agilent	TW46290015
Multimeter	34410A	Agilent	MY47012359
Multimeter	1906	TTI	n/a
High frequency generator	CWS 500N	EM Test	V0847104427
Coupling/Decoupling Network	CDN M2/M3	EM Test	1108-34
Attenuator	ATT6/75	EM Test	1107-53
Oscilloscope	TDS1002	Tektronix	C016388
Oscilloscope	TDS2014C	Tektronix	C010602
Programmable AC Source	61604	Chroma	ABR000000672
DC power supply	SM 7020 - D	Delta electronika	014604000011
DC power supply	SM 7020 - D	Delta electronika	014604000024
Pulse Generator	33220A	AGILENT	MY44044002
Biconical Antenna	BicoLOG 30100 X	AARONIA	79479
Cables	Type	Length	Comments
Mains Supply Cable	3-wire	1m	Unshielded
Mains Supply Cable	3-wire	1.5m	Unshielded
DC Lines Cable	2-wire	1m	Unshielded
DC Lines Cable	2-wire	1.5m	Unshielded