



CE EMC TEST REPORT

for

DC /DC Power Converter

Model :

**TMDC 40-2411; TMDC 40-2412; TMDC 40-2415; TMDC 40-2418; TMDC
40-4811; TMDC 40-4812; TMDC 40-4815; TMDC 40-4818**

Brand :



Test Report Number:

T140416N04 -E2

Issued for

TRACO ELECTRONIC AG

SIHLBRUGGSTRASSE 111 CH-6340 BAAR, SWITZERLAND

Issued by

Compliance Certification Services Inc.

Tainan Laboratory

No.8,Jiucengling, Xinhua Dist., Tainan City 712,
Taiwan (R.O.C.)

TEL: 886-6-580-2201

FAX: 886-6-580-2202

Issued Date: May 13, 2014



Note: This report shall not be reproduced except in full, without the written approval of Compliance Certification Services Inc. This document may be altered or revised by Compliance Certification Services Inc. personnel only, and shall be noted in the revision section of the document. The client should not use it to claim product endorsement by TAF, NIST or any government agencies. The test results in the report only apply to the tested sample.



RREVISION HISTORY

| Rev. | Issue Date | Revisions | Effect Page | Revised By |
|------|--------------|---------------|-------------|-------------|
| 00 | May 13, 2014 | Initial Issue | ALL | Sunny Chang |
| | | | | |
| | | | | |



TABLE OF CONTENTS

| | | |
|----------|---|-----------|
| 1 | TEST CERTIFICATION..... | 4 |
| 2 | TEST RESULT SUMMARY | 5 |
| 3 | EUT DESCRIPTION..... | 6 |
| 4 | TEST METHODOLOGY..... | 8 |
| 4.1. | DECISION OF FINAL TEST MODE..... | 8 |
| 4.2. | EUT SYSTEM OPERATION | 8 |
| 5 | SETUP OF EQUIPMENT UNDER TEST | 9 |
| 5.1. | DESCRIPTION OF SUPPORT UNITS..... | 9 |
| 5.2. | CONFIGURATION OF SYSTEM UNDER TEST | 9 |
| 6 | FACILITIES AND ACCREDITATIONS | 10 |
| 6.1. | FACILITIES..... | 10 |
| 6.2. | ACCREDITATIONS | 10 |
| 6.3. | MEASUREMENT UNCERTAINTY..... | 11 |
| 7 | EMISSION TEST..... | 12 |
| 7.1. | CONDUCTED EMISSION MEASUREMENT..... | 12 |
| 7.2. | RADIATED EMISSION MEASUREMENT..... | 31 |
| 7.3. | HARMONICS CURRENT MEASUREMENT..... | 51 |
| 7.4. | VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT | 54 |
| 8 | IMMUNITY TEST | 56 |
| 8.1. | GENERAL DESCRIPTION | 56 |
| 8.2. | GENERAL PERFORMANCE CRITERIA DESCRIPTION..... | 57 |
| 8.3. | ELECTROSTATIC DISCHARGE (ESD) | 58 |
| 8.4. | RADIATED, RADIO-FREQUENCY, ELECTROMAGNETIC FIELD (RS) | 64 |
| 8.5. | ELECTRICAL FAST TRANSIENT (EFT) | 67 |
| 8.6. | SURGE IMMUNITY TEST | 70 |
| 8.7. | CONDUCTED RADIO FREQUENCY DISTURBANCES (CS)..... | 73 |
| 8.8. | VOLTAGE DIP & VOLTAGE INTERRUPTIONS..... | 77 |
| 9 | PHOTOGRAPHS OF THE TEST CONFIGURATION | 79 |
| | APPENDIX 1 - PHOTOGRAPHS OF EUT | A1 |



1 TEST CERTIFICATION

Product: DC /DC Power Converter

Model: TMDC 40-2411; TMDC 40-2412; TMDC 40-2415; TMDC 40-2418;
TMDC 40-4811; TMDC 40-4812; TMDC 40-4815; TMDC 40-4818

Brand:



Applicant: TRACO ELECTRONIC AG

SIHLBRUGGSTASSE 111 CH-6340 BAAR, SWITZERLAND

Tested: March 28, 2014 ~ April 01, 2014

Applicable Standards: EN 61204-3: 2000

IEC 61000-4-2:2008

IEC 61000-4-3:2010

IEC 61000-4-4:2012

IEC 61000-4-5:2005

IEC 61000-4-6:2008

| Deviation from Applicable Standard |
|------------------------------------|
| None |

The above equipment was tested by Compliance Certification Services Inc. for compliance with the requirements of technical standards specified above under the EMC Directive 2004/108/EC. The results of testing in this report apply only to the product/system, which was tested. Other similar equipment will not necessarily produce the same results due to production tolerance and measurement uncertainties.

Approved by:

Jeter Wu
Assistant Manager

Reviewed by:

Eric Huang
Assistant Section Manager



2 TEST RESULT SUMMARY


| EMISSION | | | |
|----------------------------|--------------------------------|--------|--------------------|
| Standard | Item | Result | Remarks |
| EN 61204-3: 2000 | Conducted (Main Port) | PASS | Meet Class A limit |
| | Radiated | PASS | Meet Class A limit |
| EN 61000-3-2: 2006+A2:2009 | Harmonic current emissions | N/A | No requirement |
| EN 61000-3-3:2008 | Voltage fluctuations & flicker | N/A | No requirement |

| Standard | Item | Result | Remarks |
|----------------------|-----------------------------------|--------|---|
| IEC 61000-4-2:2008 | ESD | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-3: 2010 | RS | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-4: 2012 | EFT | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-5: 2005 | Surge | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-6: 2008 | CS | PASS | Meets the requirements of Performance Criterion A |
| IEC 61000-4-11: 2004 | Voltage dips & voltage variations | N/A | Meets the requirements of Voltage Dips: 1) 30% reduction Performance Criterion N/A 2) 60% reduction Performance Criterion N/A Voltage Interruptions: 1) >95% reduction Performance Criterion N/A |

NOTE: 1. The statements of test result on the above are decided by the request of test standard only; the measurement uncertainties are not factored into this compliance determination.
2. The information of measurement uncertainty is available upon the customer's request.



3 EUT DESCRIPTION

| | |
|-------------------------|--|
| Product | DC /DC Power Converter |
| Model | TMDC 40-2411; TMDC 40-2412; TMDC 40-2415; TMDC 40-2418; TMDC 40-4811; TMDC 40-4812; TMDC 40-4815; TMDC 40-4818 |
| Brand |  |
| Applicant | TRACO ELECTRONIC AG |
| Housing material | Plastics |
| Serial Number | T140416N04 -E2 |
| Received Date | March 31, 2014 |
| Power Source | See Below |

I/O PORT

| I/O PORT TYPES | Q'TY | TESTED WITH |
|----------------|------|-------------|
| 1. DC Power | 1 | DC Source |
| 2. DC Power | 1 | Load |

NOTE:


- Client consigns only eight model samples to test (Model Number: **TMDC 40-2411; TMDC 40-2412; TMDC 40-2415; TMDC 40-2418; TMDC 40-4811; TMDC 40-4812; TMDC 40-4815; TMDC 40-4818**). Therefore, the testing Lab. just guarantees the unit, which has been tested.
- For more details, please refer to the User's manual of the EUT.
- The different of the each model is shown as below:

The different of the each model:


| Model Number | Input Voltage (Range) | Output Voltage | Output Current | Input Current | | Max. capacitive Load | Efficiency (typ.) |
|--------------|-----------------------|----------------|----------------|----------------------|-------------------|----------------------|-------------------|
| | VDC | VDC | Max. mA(typ.) | @ Max. Load mA(typ.) | @No Load mA(typ.) | | @Max. Load % |
| TMDC 40-2411 | 24 (9~36) | 5.1 | 8000 | 1889 | 90 | 13600 | 90 |
| TMDC 40-2412 | | 12 | 3330 | 1850 | 90 | 2400 | 90 |
| TMDC 40-2415 | | 24 | 1670 | 1856 | 90 | 600 | 90 |
| TMDC 40-2418 | | 48 | 835 | 1876 | 90 | 150 | 89 |
| TMDC 40-4811 | 48 (18~75) | 5.1 | 8000 | 955 | 55 | 13600 | 89 |
| TMDC 40-4812 | | 12 | 3330 | 915 | 55 | 2400 | 91 |
| TMDC 40-4815 | | 24 | 1670 | 908 | 55 | 600 | 92 |
| TMDC 40-4818 | | 48 | 835 | 928 | 55 | 150 | 90 |



1) Radiation Solution:



| | L1 | C1 | C2 | C3 |
|-------------|-------------|------------|-------|-------|
| TMDC40-24XX | 175uH/175uH | 4.7uF 50V | 220pF | 220pF |
| TMDC40-48XX | | 3.3uF 100V | | |



| Connections | |
|-------------|---------------|
| Pin | Function |
| 1 | Remote On/Off |
| 2 | -Vin |
| 3 | +Vin |
| 4 | +Vout |
| 5 | NC |
| 6 | -Vout |
| 7 | NC |
| 8 | NC |

NC: No Connection

2) Surge Solution:

Add a electrolytic capacitor 330uF/80V at input port.



4 TEST METHODOLOGY

4.1. DECISION OF FINAL TEST MODE

The EUT was tested together with the above additional components, and a configuration, which produced the worst emission levels, was selected and recorded in this report.

The test configuration/ mode is as the following:

Conduction (Main Port) Modes: (Full Load)

| | | | |
|----|--------------|----|--------------|
| 1. | TMDC 40-2411 | 5. | TMDC 40-4811 |
| 2. | TMDC 40-2412 | 6. | TMDC 40-4812 |
| 3. | TMDC 40-2415 | 7. | TMDC 40-4815 |
| 4. | TMDC 40-2418 | 8. | TMDC 40-4818 |

Radiation Modes: (Full Load)

| | | | |
|----|--------------|----|--------------|
| 1. | TMDC 40-2411 | 5. | TMDC 40-4811 |
| 2. | TMDC 40-2412 | 6. | TMDC 40-4812 |
| 3. | TMDC 40-2415 | 7. | TMDC 40-4815 |
| 4. | TMDC 40-2418 | 8. | TMDC 40-4818 |

Immunity Test Mode: (Full Load)

| | |
|----|--------------|
| 1. | TMDC 40-2411 |
|----|--------------|

4.2. EUT SYSTEM OPERATION

1. Setup a whole system for test as shown on setup diagram.
2. Turn on power and check E.U.T. function.
3. Start to test.



5 SETUP OF EQUIPMENT UNDER TEST

5.1. DESCRIPTION OF SUPPORT UNITS

The EUT has been tested as an independent unit together with other necessary accessories or support units. The following support units or accessories were used to form a representative test configuration during the tests.

Peripherals Devices:

| No. | Product | Manufacturer | Model No. | Certify No. | Signal cable |
|-----|-----------------|--------------|-----------|-------------|--------------------------|
| 1 | DC Power Supply | GW | GPR-3036D | DOC | Power cable, unshd, 1.6m |

| No. | Signal cable description | |
|-----|--------------------------|-------------------------|
| A | DC Power cable | Unshielded, 1.0m, 1pcs. |
| B | DC Power cable | Unshielded, 0.1m, 1pcs. |

Note:

- 1) All the equipment/cables were placed in the worst-case configuration to maximize the emission during the test.
- 2) Grounding was established in accordance with the manufacturer's requirements and conditions for the intended use.

5.2. CONFIGURATION OF SYSTEM UNDER TEST





6 FACILITIES AND ACCREDITATIONS

6.1. FACILITIES

All measurement facilities used to collect the measurement data are located at

☒ No.8, Jiucengling, Xinhua Dist., Tainan City 712, Taiwan (R.O.C.)

The sites are constructed in conformance with the requirements of ANSI C63.4 and CISPR Publication 11. All receiving equipment conforms to CISPR Publication 16-1, "Radio Interference Measuring Apparatus and Measurement Methods."

6.2. ACCREDITATIONS

Our laboratories are accredited and approved by the following approval agencies according to ISO/IEC 17025.

| | |
|---------------|-----------------|
| USA | FCC |
| Canada | INDUSTRY CANADA |
| Taiwan | TAF, BSMI |
| Europe | TUV NORD |

Copies of granted accreditation certificates are available for downloading from our web site, <http://www.ccsemc.com.tw>



6.3. MEASUREMENT UNCERTAINTY

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT as specified in CISPR 16-4-2:

| Measurement | | Frequency | Uncertainty |
|-------------------------------|--------------------|-------------------|-------------|
| Power Line Conducted Emission | | 9kHz~30MHz | ±1.48dB |
| Conduction Emission | ISN | 150kHz~30MHz | ±2.61dB |
| | T-ISN | 150kHz~30MHz | ±2.61dB |
| | Clamp | 30MHz ~ 300MHz | ±2.0736dB |
| Radiated Emission (10m) | Test Site : OATS-5 | 30 MHz ~200 MHz | ±3.6721dB |
| | | 200 MHz ~1000 MHz | ±2.9511dB |
| | Test Site : OATS-6 | 30 MHz ~200 MHz | ±3.7451dB |
| | | 200 MHz ~1000 MHz | ±3.2195dB |
| | Test Site : OATS-7 | 30 MHz ~200 MHz | ±3.8729dB |
| | | 200 MHz ~1000 MHz | ±3.8996dB |
| Radiated Emission (3m) | Test Site : OATS-5 | 30 MHz ~200 MHz | ±3.6303dB |
| | | 200 MHz ~1000 MHz | ±2.3764dB |
| | Test Site : OATS-6 | 30 MHz ~200 MHz | ±3.4896dB |
| | | 200 MHz ~1000 MHz | ±2.7196dB |
| | Test Site : OATS-7 | 30 MHz ~200 MHz | ±3.6570dB |
| | | 200 MHz ~1000 MHz | ±2.9825dB |

This uncertainty represents an expanded uncertainty expressed at approximately the 95% confidence level using a coverage factor of k=2.



7 EMISSION TEST

7.1. CONDUCTED EMISSION MEASUREMENT

7.1.1. LIMITS

| FREQUENCY (MHz) | Class A (dBuV) Group 1 | | Class B (dBuV) Group 1 | |
|-----------------|------------------------|---------|------------------------|---------|
| | Quasi-peak | Average | Quasi-peak | Average |
| 0.15 - 0.5 | 79 | 66 | 66 - 56 | 56 - 46 |
| 0.50 - 5.0 | 73 | 60 | 56 | 46 |
| 5.0 - 30.0 | 73 | 60 | 60 | 50 |

NOTE:

- (1) The lower limit shall apply at the transition frequencies.
- (2) The limit decreases in line with the logarithm of the frequency in the range of 0.15 to 0.50 MHz.
- (3) All emanations from a class A/B digital device or system, including any network of conductors and apparatus connected thereto, shall not exceed the level of field strengths specified above.

7.1.2. TEST INSTRUMENTS

| Conducted Emission room | | | | |
|-------------------------|------------------------------|-----------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| L.I.S.N. | SCHWARZBECK | NNLK 8130 | 8130124 | AUG. 12, 2014 |
| | Rohde & Schwarz | ESH 3-Z5 | 840062/021 | SEP. 09, 2014 |
| TEST RECEIVER | Rohde & Schwarz | ESCS 30 | 100348 | AUG. 09, 2014 |
| BNC COAXIAL CABLE | CCS | BNC50 | 11 | NOV. 19, 2014 |
| Test S/W | e-3 (5.04211c) R&S (2.27) | | | |

NOTE: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.



7.1.3. TEST PROCEDURES

Procedure of Preliminary Test


- The EUT was set up as per the test configuration to simulate typical usage per the user's manual. When the EUT is a tabletop system, a wooden table with a height of 0.8 meters is used and is placed on the ground plane as per EN 61204-3 (see Test Facility for the dimensions of the ground plane used). When the EUT is a floor-standing equipment, it is placed on the ground plane which has a 3-12 mm non-conductive covering to insulate the EUT from the ground plane.
- Support equipment, if needed, was placed as per EN 61204-3.
- All I/O cables were positioned to simulate typical actual usage as per EN 61204-3.
- The test equipment EUT installed received power source, through a Line Impedance Stabilization Network (LISN), which supplied power source and was grounded to the ground plane.
- All support equipment received power from a second LISN.
- The EUT test program was started. Emissions were measured on each current carrying line of the EUT using an EMI Test Receiver connected to the LISN powering the EUT.
- The Receiver scanned from 150kHz to 30MHz for emissions in each of the test modes.
- During the above scans, the emissions were maximized by cable manipulation.
- The test mode(s) described in Item 4.1 were scanned during the preliminary test.
- After the preliminary scan, we found the test mode described in Item 4.1 producing the highest emission level.
- The EUT configuration and cable configuration of the above highest emission levels were recorded for reference of the final test.

Procedure of Final Test

- EUT and support equipment were set up on the test bench as per the configuration with highest emission level in the preliminary test.
- A scan was taken on both power lines, Line 1 and Line 2, recording at least the six highest emissions. Emission frequency and amplitude were recorded into a computer in which correction factors were used to calculate the emission level and compare reading to the applicable limit.
- The test data of the worst-case condition(s) was recorded.



7.1.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.1.5. DATA SAMPLE

| Freq. (MHz) | LISN Factor (dB) | Cable Loss (dB) | Meter Reading (dBuV) | Measured Level (dBuV) | Limits (dBuV) | Over Limits (dBuV) | Detector |
|-------------|------------------|-----------------|----------------------|-----------------------|---------------|--------------------|----------|
| x.xx | 9.6 | 0.1 | 15.7 | 25.4 | 46 | -20.6 | QP |

| | |
|----------------|---|
| Freq. | = Emission frequency in MHz |
| LISN Factor | = Insertion loss of LISN and Pulse Limiter |
| Cable Loss | = Insertion loss of Cable (LISN to EMI Tester Receiver) |
| Meter Reading | = Uncorrected Analyzer/Receiver reading |
| Measured Level | = Read Level + Factor |
| Limit | = Limit stated in standard |
| Over Limit | = Reading in reference to limit |
| Peak | = Peak Reading |
| QP | = Quasi-peak Reading |
| AV | = Average Reading |

Calculation Formula

1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)




7.1.6. TEST RESULTS

| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2411 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2411 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




- Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2412 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2412 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Sam Shen | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2415 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2415 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Sam Shen | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2418 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2418 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Sam Shen | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4811 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

LINE

(The chart below shows the highest readings taken from the final data.)




- Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4811 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Sam Shen | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4812 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4812 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Sam Shen | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4815 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

LINE

(The chart below shows the highest readings taken from the final data.)




- Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4815 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Sam Shen | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)




- Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4818 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by | Sam Shen | | |

LINE

(The chart below shows the highest readings taken from the final data.)




Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4818 | Test Mode | Full Load |
| Environmental Conditions | 23.1 , 60% RH | Resolution Bandwidth | 9 kHz |
| Tested by: | Sam Shen | | |

NEUTRAL

(The chart below shows the highest readings taken from the final data.)



Note: 1. Level (dBuV) = Read Level (dBuV) + LISN Factor (dB) + Cable Loss (dB)
2. Over Limit value (dB) = Level (dBuV) – Limit Line (dBuV)

**7.2. RADIATED EMISSION MEASUREMENT****7.2.1. LIMITS**

| FREQUENCY (MHz) | dBuV/m (At 10m) | |
|-----------------|-----------------|---------|
| | Class A | Class B |
| 30 ~ 230 | 40 | 30 |
| 230 ~ 1000 | 47 | 37 |

NOTE: (1) The lower limit shall apply at the transition frequencies.

(2) Emission level (dBuV/m) = 20 log Emission level (uV/m).

7.2.2. TEST INSTRUMENTS

| Open Area Test Site # 5 | | | | |
|-------------------------|----------------------------|-------------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| TEST RECEIVER | Rohde & Schwarz | ESCS 30 | 100294 | JUN. 24, 2014 |
| TYPE N COAXIAL CABLE | SUHNER | RG_214_U/2X | 5 | NOV. 18, 2014 |
| BILOG ANTENNA | Sunol sciences | JB1 | A070506-1 | SEP. 11, 2014 |
| Test Software | EMI e-3 / AUDIX (5.04211c) | | | |

| Open Area Test Site # 7 | | | | |
|-------------------------|----------------------------|-------------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| TEST RECEIVER | Rohde & Schwarz | ESCS30 | 100343 | FEB. 26, 2015 |
| EMI Test Receiver | Rohde & Schwarz | ESCI3 | 101336 | JAN. 17, 2015 |
| TYPE N COAXIAL CABLE | SUHNER | RG_214_U/2X | 7 | NOV. 18, 2014 |
| BILOG ANTENNA | Sunol sciences | JB1 | A013105-1 | SEP. 11, 2014 |
| Test Software | EMI e-3 / AUDIX (5.04211c) | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

2. N.C.R = No Calibration Request.



7.2.3. TEST PROCEDURE

Procedure of Preliminary Test

- The equipment was set up as per the test configuration to simulate typical usage per the user's manual. When the EUT is a tabletop system, a wooden turntable with a height of 0.8 meters is used which is placed on the ground plane. When the EUT is a floor-standing equipment, it is placed on the ground plane which has a 3-12 mm non-conductive covering to insulate the EUT from the ground plane.
- Support equipment, if needed, was placed as per EN 61204-3.
- All I/O cables were positioned to simulate typical usage as per EN 61204-3.
- The EUT received power source from the outlet socket under the turntable. All support equipment power received from another socket under the turntable.
- Mains cables, telephone lines or other connections to auxiliary equipment located outside the test are shall drape to the floor, be fitted with ferrite clamps or ferrite tubes placed on the floor at the point where the cable reaches the floor and then routed to the place where they leave the turntable. No extension cords shall be used to mains receptacle.
- The antenna was placed at 10 meter away from the EUT as stated in EN 55022. The antenna connected to the Spectrum Analyzer via a cable and at times a pre-amplifier would be used.
- The Analyzer / Receiver quickly scanned from 30MHz to 1000MHz. The EUT test program was started. Emissions were scanned and measured rotating the EUT to 360 degrees and positioning the antenna 1 to 4 meters above the ground plane, in both the vertical and the horizontal polarization, to maximize the emission reading level.
- The test mode(s) described in Item 4.1 were scanned during the preliminary test:
- After the preliminary scan, we found the test mode described in Item 4.1 producing the highest emission level.
- The EUT and cable configuration, antenna position, polarization and turntable position of the above highest emission level were recorded for the final test.




Procedure of Final Test

- EUT and support equipment were set up on the turntable as per the configuration with highest emission level in the preliminary test.
- The Analyzer / Receiver scanned from 30MHz to 1000MHz. Emissions were scanned and measured rotating the EUT to 360 degrees, varying cable placement and positioning the antenna 1 to 4 meters above the ground plane, in both the vertical and the horizontal polarization, to maximize the emission reading level.
- Recorded at least the six highest emissions. Emission frequency, amplitude, antenna position, polarization and turntable position were recorded into a computer in which correction factors were used to calculate the emission level and compare reading to the applicable limit and only Q.P. reading is presented.
- The test data of the worst-case condition(s) was recorded.



7.2.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.2.5. DATA SAMPLE

| Freq. (MHz) | Reading Level (dBuV) | Antenna Factor (dB/m) | Cable Loss (dB) | Measure Level (dBuV/m) | Limit (dBuV/m) | Over Limit (dBuV/m) |
|-------------|----------------------|-----------------------|-----------------|------------------------|----------------|---------------------|
| xx.xx | 14.00 | 12 | 0.2 | 26.2 | 30 | -3.80 |

Freq. = Emission frequency in MHz
Reading = Uncorrected Analyzer/Receiver reading
Factor = Antenna Factor + Cable Loss - Amplifier Gain
Result = Reading + Factor
Limit = Limit stated in standard
Margin = Reading in reference to limit
P = Peak Reading
Q = Quasi-peak Reading
H = Antenna Polarization: Horizontal
V = Antenna Polarization: Vertical

Calculation Formula


Margin (dB) = Result (dBuV/m) – Limit (dBuV/m)



7.2.6. TEST RESULTS

| | | | |
|---------------------------------|--------------|-----------------------------|-----------|
| Model No. | TMDC 40-2411 | Test Mode | Full Load |
| Environmental Conditions | 18 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested by | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|--------------|----------------------|-----------|
| Model No. | TMDC 40-2411 | Test Mode | Full Load |
| Environmental Conditions | 18 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested by | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|--------------|----------------------|-----------|
| Model No. | TMDC 40-2412 | Test Mode | Full Load |
| Environmental Conditions | 20 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|---------------------------------|--------------|-----------------------------|-----------|
| Model No. | TMDC 40-2412 | Test Mode | Full load |
| Environmental Conditions | 20 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2415 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2415 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)
2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|---------------------------------|---------------|-----------------------------|-----------|
| Model No. | TMDC 40-2418 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-2418 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4811 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4811 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4812 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|---------------------------------|---------------|-----------------------------|-----------|
| Model No. | TMDC 40-4812 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4815 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4815 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|---------------------------------|---------------|-----------------------------|-----------|
| Model No. | TMDC 40-4818 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Vertical | Antenna Distance | 10m |
| Detector Function: | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)




Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)



| | | | |
|--------------------------|---------------|----------------------|-----------|
| Model No. | TMDC 40-4818 | Test Mode | Full load |
| Environmental Conditions | 25.9 , 57% RH | Resolution Bandwidth | 120 kHz |
| Antenna Pole | Horizontal | Antenna Distance | 10m |
| Detector Function | Quasi-peak. | Tested By | Weici Lo |

(The chart below shows the highest readings taken from the final data.)



Note: 1.Level (dBuV/m) = Read Level (dBuV) + Antenna Factor (dB/m) + Cable loss (dB)

2.Over Limit value (dB) = Level (dBuV/m)-Limit Line(dBuV/m)

**7.3. HARMONICS CURRENT MEASUREMENT****7.3.1. LIMITS OF HARMONICS CURRENT MEASUREMENT**

| Limits for Class A equipment | | Limits for Class D equipment | | |
|------------------------------|--------------------------------------|------------------------------|--|--------------------------------------|
| Harmonics Order n | Max. permissible harmonics current A | Harmonics Order n | Max. permissible harmonics current per watt mA/W | Max. permissible harmonics current A |
| Odd harmonics | | Odd Harmonics only | | |
| 3 | 2.30 | 3 | 3.4 | 2.30 |
| 5 | 1.14 | 5 | 1.9 | 1.14 |
| 7 | 0.77 | 7 | 1.0 | 0.77 |
| 9 | 0.40 | 9 | 0.5 | 0.40 |
| 11 | 0.33 | 11 | 0.35 | 0.33 |
| 13 | 0.21 | 13 | 0.30 | 0.21 |
| 15<=n<=39 | 0.15x15/n | 15<=n<=39 | 3.85/n | 0.15x15/n |
| Even harmonics | | | | |
| 2 | 1.08 | | | |
| 4 | 0.43 | | | |
| 6 | 0.30 | | | |
| 8<=n<=40 | 0.23x8/n | | | |

NOTE: 1. Class A and Class D are classified according to item 7.3.3.
2. According to section 7 of EN 61000-3-2, the above limits for all equipment except for lighting equipment having an active input power > 75 W and no limits apply for equipment with an active input power up to and including 75 W.

7.3.2. TEST INSTRUMENTS

| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
|--------------------|------------------------------------|--------|---------------|-----------------|
| Harmonics Analyzer | TTI | HA1600 | 198202 | MAY. 12, 2014 |
| Test S/W | H/F HA 1600 PC LINK Field Probe | | | |

NOTE: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.



7.3.3. TEST PROCEDURE

- The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the maximum harmonic components under normal operating conditions for each successive harmonic component in turn.
- The classification of EUT is according to section 5 of EN 61000-3-2.
- The EUT is classified as follows:

Class A: Balanced three-phase equipment, Household appliances excluding equipment as Class D, Tools excluding portable tools, Dimmers for incandescent lamps, audio equipment, equipment not specified in one of the three other classes.


Class B: Portable tools; Arc welding equipment which is not professional equipment.

Class C: Lighting equipment.

Class D: Equipment having a specified power less than or equal to 600 W of the following types: Personal computers and personal computer monitors and television receivers.

- The correspondent test program of test instrument to measure the current harmonics emanated from EUT is chosen. The measure time shall be not less than the time necessary for the EUT to be exercised.

7.3.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

**7.3.5. TEST RESULTS**

| | | | |
|--------------------------|-----|--------------|--|
| Power Consumption | N/A | Test Results | N/A |
| Environmental Conditions | N/A | Limits | Class <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C <input type="checkbox"/> D |
| Test Mode | N/A | Tested By | N/A |
| Tested Date | N/A | | |

NOTE: 1. Limits classified according to item 7.3.3.

2. According to section 7 of EN 61000-3-2, the above limits for all equipment except for lighting equipment having an active input power > 75 W and no limits apply for equipment with an active input power up to and including 75 W.

Test Result

This EUT is not connected to AC Source directly. Not applicable for this test.

**7.4. VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT****7.4.1. LIMITS OF VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT**

| TEST ITEM | LIMIT | REMARK |
|---------------|-------|--|
| P_{st} | 1.0 | P_{st} means short-term flicker indicator. |
| P_{lt} | 0.65 | P_{lt} means long-term flicker indicator. |
| T_{dt} (ms) | 500 | T_{dt} means maximum time that dt exceeds 3 %. |
| d_{max} (%) | 4% | d_{max} means maximum relative voltage change. |
| dc (%) | 3.3% | dc means relative steady-state voltage change |

7.4.2. TEST INSTRUMENTS

| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
|--------------------|------------------------------------|--------|---------------|-----------------|
| Harmonics Analyzer | TTI | HA1600 | 198202 | MAY. 12, 2014 |
| Test S/W | H/F HA 1600 PC LINK Field Probe | | | |


NOTE: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.



7.4.3. TEST PROCEDURE

- The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the most unfavorable sequence of voltage changes under normal operating conditions.
- During the flick measurement, the measure time shall include that part of whole operation cycle in which the EUT produce the most unfavorable sequence of voltage changes. The observation period for short-term flicker indicator is 10 minutes and the observation period for long-term flicker indicator is 2 hours.

7.4.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.4.5. TEST RESULTS

| | | | |
|--------------------------|---------------------------------|-----------|-----|
| Observation Period (Tp) | --- Seconds | Test Mode | --- |
| Environmental Conditions | --- deg.C, ---% RH, --- mbar | Tested by | --- |

Test Result

This EUT do not connect to AC Source directly. Not applicability for this test.



8 IMMUNITY TEST

8.1. GENERAL DESCRIPTION

| Product Standard | Test Type | Minimum Requirement |
|--|----------------|--|
| Basic Standard, Specification, and Performance Criterion required | IEC 61000-4-2 | Electrostatic Discharge – ESD: 8kV Air discharge, 4kV Contact discharge, Performance Criterion B |
| | IEC 61000-4-3 | Radio-Frequency Electromagnetic Field Susceptibility Test – RS: 80 ~1000 MHz, 3V/m, 900 MHz, 3V/m, 80% AM(1kHz), Performance Criterion A |
| | IEC 61000-4-4 | Electrical Fast Transient/Burst - EFT, Power line: 1kV, Performance Criterion B |
| | IEC 61000-4-5 | Surge Immunity Test: 1.2/50 us Open Circuit Voltage, 8 /20 us Short Circuit Current, Power Port ~ Line to line: 1 kV, Line to ground: 2kV Performance Criterion B |
| | IEC 61000-4-6 | Conducted Radio Frequency Disturbances Test –CS: 0.15 ~ 80 MHz, 3Vrms, 80% AM, 1kHz, Performance Criterion B |
| | IEC 61000-4-11 | Voltage Dips: i) 30% reduction for reduction 10ms, Performance Criterion B ii) 60% reduction for reduction 100ms, Performance Criterion B Voltage Interruptions: >95% reduction for reduction 5000 ms Performance Criterion C |



8.2. GENERAL PERFORMANCE CRITERIA DESCRIPTION

| | |
|--------------------|--|
| Criteria A: | The apparatus shell continues to operate as intended without operator intervention. No degradation of performance or loss of function is allowed below a performance level specified by the manufacturer, when the apparatus is used as intended. The performance level may be replaced by a permissible loss of performance. If the manufacturer does not specify the minimum performance level or the permissible performance loss, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended. |
| Criteria B: | <p>After test, the apparatus shell continues to operate as intended without operator intervention. No degradation of performance or loss of function is allowed, after the application of the phenomenon below a performance level specified by the manufacturer, when the apparatus is used as intended. The performance level may be replaced by a permissible loss of performance.</p> <p>During the test, degradation of performance is however allowed. However, no change of operating state if stored data is allowed to persist after the test. If the manufacturer does not specify the minimum performance level or the permissible performance loss, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.</p> |
| Criteria C: | <p>Temporary loss of function is allowed, provided the functions is self-recoverable or can be restored by the operation of controls by the user in accordance with the manufacturer instructions.</p> <p>Functions, and/or information stored in non-volatile memory, or protected by a battery backup, shall not be lost.</p> |



8.3. ELECTROSTATIC DISCHARGE (ESD)

8.3.1. TEST SPECIFICATION

Basic Standard: EN 61000-4-2

Discharge Impedance: 330 ohm / 150 pF

Discharge Voltage: Air Discharge: 2 ; 4 ; 8 kV (Direct)
Contact Discharge: 4 kV (Indirect)

Polarity: Positive & Negative

Number of Discharge: 10 Discharges / Sensitive Polarity for Air Discharge.
25 Discharges / Sensitive Polarity for Contact, HCP and VCP Discharge.

Discharge Mode: Single Discharge
1 second minimum

8.3.2. TEST INSTRUMENT

| IMMUNITY SHIELDED ROOM | | | | |
|------------------------|--------------|----------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| ESD Simulator | NoiseKen | ESS-2002 | ESS04Z3762 | MAR. 16, 2015 |

NOTE: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.



8.3.3. TEST PROCEDURE

The discharges shall be applied in two ways:

a) Contact discharges to the conductive surfaces and coupling planes:

The EUT shall be exposed to at least 200 discharges, 100 each at negative and positive polarity, at a minimum of four test points. One of the test points shall be subjected to at least 50 indirect discharges to the center of the front edge of the **Horizontal Coupling Plane (HCP)**. The remaining three test points shall each receive at least 50 direct contact discharges. If no direct contact test points are available, then at least 200 indirect discharges shall be applied in the indirect mode. Test shall be performed at a maximum repetition rate of one discharge per second.

b) Air discharges at slots and apertures and insulating surfaces:


On those parts of the EUT where it is not possible to perform contact discharge testing, the equipment should be investigated to identify user accessible points where breakdown may occur. Such points are tested using the air discharge method. This investigation should be restricted to those area normally handled by the user. A minimum of 10 single air discharges shall be applied to the selected test point for each such area.

The basic test procedure was in accordance with IEC 61000-4-2:

- a) The EUT was located 0.1 m minimum from all side of the **HCP** (dimensions 1.6m x 0.8m).
- b) The support units were located another table 30 cm away from the EUT, but direct support unit was/were located at same location as EUT on the HCP and keep at a distance of 10 cm with EUT.
- c) The time interval between two successive single discharges was at least 1 second.
- d) Contact discharges were applied to the non-insulating coating, with the pointed tip of the generator penetrating the coating and contacting the conducting substrate.
- e) Air discharges were applied with the round discharge tip of the discharge electrode approaching the EUT as fast as possible (without causing mechanical damage) to touch the EUT. After each discharge, the ESD generator was removed from the EUT and re-triggered for a new single discharge. The test was repeated until all discharges were complete.
- f) At least ten single discharges (in the most sensitive polarity) were applied at the front edge of each **HCP** opposite the center point of each unit of the EUT and 0.1 meters from the front of the EUT. The long axis of the discharge electrode was in the plane of the **HCP** and perpendicular to its front edge during the discharge.
- g) At least ten single discharges (in the most sensitive polarity) were applied to the center of one vertical edge of the **Vertical Coupling Plane (VCP)** in sufficiently different positions that the four faces of the EUT were completely illuminated. The **VCP** (dimensions 0.5m x 0.5m) was placed vertically to and 0.1 meters from the EUT.



8.3.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

TABLE-TOP EQUIPMENT

The configuration consisted of a wooden table 0.8 meters high standing on the **Ground Reference Plane**. The **GRP** consisted of a sheet of aluminum at least 0.25 mm thick, and 2.5 meters square connected to the protective grounding system. A **Horizontal Coupling Plane** (1.6m x 0.8m) was placed on the table and attached to the **GRP** by means of a cable with 940k Ω total impedance. The equipment under test, was installed in a representative system as described in section 7 of EN 61000-4-2, and its cables were placed on the **HCP** and isolated by an insulating support of 0.5 mm thickness. A distance of 1 meter minimum was provided between the EUT and the walls of the laboratory and any other metallic structure.

FLOOR-STANDING EQUIPMENT

The equipment under test was installed in a representative system as described in section 7 of IEC 61000-4-2, and its cables were isolated from the Ground Reference Plane by an insulating support of 0.1 meter thickness. The GRP consisted of a sheet of aluminum that is at least 0.25 mm thick, and 2.5 meters square connected to the protective grounding system and extended at least 0.5 meters from the EUT on all sides.



8.3.5. TEST RESULTS

| | | | |
|------------------------------|----------|-------------|----------|
| Temperature | 24°C | Humidity | 43% RH |
| Pressure | 1028mbar | Tested By | Rock Guo |
| Required Passing Performance | | Criterion B | |

| Air Discharge | | | | | | | | | |
|---------------|-------------------------------------|-------------------------------------|-------------------------------------|--------------------------|--------------------------|-------------------------------------|--------------------------|---|-------------|
| Test Points | Test Levels | | | | | Results | | | |
| | ± 2 kV | ± 4 kV | ± 8 kV | ± 12 kV | ± 15 kV | Pass | Fail | Performance Criterion | Observation |
| Front | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Back | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Left | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Right | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Top | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Bottom | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |

| Contact Discharge | | | | | | | | | |
|-------------------|--------------------------|-------------------------------------|--------------------------|--------------------------|--------------------------|-------------------------------------|--------------------------|---|-------------|
| Test Points | Test Levels | | | | | Results | | | |
| | ± 2 kV | ± 4 kV | ± 6 kV | ± 8 kV | ± 12 kV | Pass | Fail | Performance Criterion | Observation |
| Front | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Back | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Left | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Right | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Top | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Bottom | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |



Please refer to ESD test photo on next page for detail discharge point

| Discharge To Horizontal Coupling Plane | | | | | | | | |
|--|--------------------------|-------------------------------------|--------------------------|--------------------------|-------------------------------------|--------------------------|---|-------------|
| Side of EUT | Test Levels | | | | Results | | | |
| | ± 2 kV | ± 4 kV | ± 6kV | ± 8 kV | Pass | Fail | Performance Criterion | Observation |
| Front | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Back | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Left | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Right | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |

| Discharge To Vertical Coupling Plane | | | | | | | | |
|--------------------------------------|--------------------------|-------------------------------------|--------------------------|--------------------------|-------------------------------------|--------------------------|---|-------------|
| Side of EUT | Test Levels | | | | Results | | | |
| | ± 2 kV | ± 4 kV | ± 6 kV | ± 8 kV | Pass | Fail | Performance Criterion | Observation |
| Front | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Back | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Left | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |
| Right | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | |




The Photo for Discharge Points of EUT



'A' Mark — Air Discharged ;



The Photo for Discharge Points of EUT



'A' Mark — Air Discharged ;

**8.4. RADIATED, RADIO-FREQUENCY, ELECTROMAGNETIC FIELD (RS)****8.4.1. TEST SPECIFICATION**

| | |
|--|---------------------------------------|
| Basic Standard: | EN 61000-4-3 |
| Frequency Range/ Field Strength | 80 ~1000 MHz, 3V/m, 900 MHz, 3V/m, |
| Modulation: | 1kHz Sine Wave, 80%, AM Modulation |
| Frequency Step: | 1 % of preceding frequency value |
| Polarity of Antenna: | Horizontal and Vertical |
| Test Distance: | 3 m |
| Antenna Height: | 1.5m |

8.4.2. TEST INSTRUMENT

| RS Chamber | | | | |
|--|----------------|-------------------|----------------------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | SYNNEX | BTO -LMIW300 - GB | A41202-0031 | N.C.R. |
| LCD Monitor | Acer | AL1715sm | ETL130719944302 366RH01 | N.C.R. |
| Keyboard | SYNNEX | 5211A | G4430091266 | N.C.R. |
| Amplifier Freq. Range :80MHz 1GHz | AR | 150W1000M3 | 310037 | N.C.R. |
| Amplifier Freq. Range :0.8MHz 3GHz | AR | 60S1G3M3 | 310102 | N.C.R. |
| Digital SIGNAL GENERATOR | HP | ESG-D3000A | US36260655 | JUN. 08, 2014 |
| RF Power Meter | BOONTON | 4232A-01-02 | 122202 | MAY. 27, 2014 |
| Log – Periodic Antenna | AR | AT5080 | 309817 | N.C.R. |
| Test S/W | RS SW1005 R1_4 | | | |

NOTE: 1.The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R.= No Calibration Required.

'A' Mark — Air Discharged ;
'C' Mark —Contact Discharged




8.4.3. TEST PROCEDURE

The test procedure was in accordance with EN 61000-4-3

- The testing was performed in a fully anechoic chamber. The transmit antenna was located at a distance of 3 meters from the EUT.
- The frequency range is swept from 80 MHz to 1000 MHz, with the signal 80% amplitude modulated with a 1kHz sine-wave. The rate of sweep did not exceed 1.5×10^{-3} decade/s, where the frequency range is swept incrementally, the step size was 1% of preceding frequency value.
- The dwell time at each frequency shall be not less than the time necessary for the EUT to be able to respond.
- The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

8.4.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

**NOTE:****TABLETOP EQUIPMENT**

The EUT installed in a representative system as described in section 7 of EN 61000-4-3 was placed on a non-conductive table 0.8 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

FLOOR STANDING EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-3 was placed on a non-conductive wood support 0.1 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

8.4.5. TEST RESULTS

| | | | |
|-------------------------------------|--------------------|------------------|----------|
| Temperature | 26 °C | Humidity | 51 % RH |
| Pressure | 1032 mbar | Tested By | Rock Guo |
| Dwell Time | 3 sec. | | |
| Required Passing Performance | Criterion A | | |

| Frequency (MHz) | Polarity | Azimuth | Field Strength (V/m) | Result | Observation |
|-----------------|----------|---------|----------------------|--------|-------------|
| 80 ~ 1000 | V&H | 0 | 3 | A PASS | |
| 80 ~ 1000 | V&H | 90 | 3 | A PASS | |
| 80 ~ 1000 | V&H | 180 | 3 | A PASS | |
| 80 ~ 1000 | V&H | 270 | 3 | A PASS | |

Repetition frequency at 900±5MHz

| | |
|-----------------------|-------|
| Duty cycle | 50% |
| Rep. Frequency | 200Hz |

| Frequency (MHz) | Polarity | Azimuth | Field Strength (V/m) | Result | Observation |
|-----------------|----------|---------|----------------------|--------|-------------|
| 900±5MHz | V&H | 0 | 3 | A PASS | |
| 900±5MHz | V&H | 90 | 3 | A PASS | |
| 900±5MHz | V&H | 180 | 3 | A PASS | |
| 900±5MHz | V&H | 270 | 3 | A PASS | |



8.5. ELECTRICAL FAST TRANSIENT (EFT)

8.5.1. TEST SPECIFICATION

Basic Standard: EN 61000-4-4

Test Voltage: Power Line: 0.5 kV

Polarity: Positive & Negative

Repetition Rate: 5 kHz

Impulse Wave-shape: 5/50 ns

Burst Duration: 15 ms / 300ms.

Burst Period: 300 ms

Test Duration: Not less than 1 min.

8.5.2. TEST INSTRUMENT

| Immunity Shield Room | | | | |
|------------------------------|---------------|----------------|--------------------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | IBM | M/T 8183 - ICV | 99BG137 | N.C.R. |
| VGA Monitor | Acer | 1555 | 917160230584200572P5C431 | N.C.R. |
| Keyboard | HP | KB - 0133 | B69360MGAPEOK5 | N.C.R. |
| EMC Pro IMMUNITY TEST SYSTEM | KeyTek | EMCpro | 0312231 | APR. 07, 2015 |
| Test S/W | CE Ware 3.00b | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.


2. N.C.R.= No Calibration Required.

8.5.3. TEST PROCEDURE

- Both positive and negative polarity discharges were applied.
- The length of the "hot wire" from the coaxial output of the EFT generator to the terminals on the EUT should not exceed 1 meter.
- The duration time of each test sequential was 1 minute.
- The transient/burst waveform was in accordance with EN 61000-4-4, 5/50ns.



8.5.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

TABLETOP EQUIPMENT

The configuration consisted of a wooden table (0.8 m high) standing on the Ground Reference Plane. The GRP consisted of a sheet of aluminum (at least 0.25 mm thick and 2.5 m square) connected to the protective grounding system. A minimum distance of 0.5 m was provided between the EUT and the walls of the laboratory or any other metallic structure.

FLOOR STANDING EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-4 and its cables, were isolated from the Ground Reference Plane by an insulating support that is 0.1-meter thick. The GRP consisted of a sheet of aluminum (at least 0.25 mm thick and 2.5 m square) connected to the protective grounding system.

**8.5.5. TEST RESULTS**

| | | | |
|-------------------------------------|-----------|--------------------|----------|
| Temperature | 25 °C | Humidity | 48% RH |
| Pressure | 1028 mbar | Tested By | Rock Guo |
| Required Passing Performance | | Criterion B | |

POWER

| Test Point | Polarity | Test Level (kV) | Performance Criterion | Result | Observation |
|------------|----------|-----------------|---|--------|-------------|
| L1 | +/- | 0.5kV | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | A PASS | |
| L2 | +/- | 0.5kV | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | A PASS | |
| L1 + L2 | +/- | 0.5kV | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | A PASS | |

SIGNAL

| Test Point | Polarity | Test Level (kV) | Performance Criterion | Observation | Result |
|------------|----------|-----------------|-----------------------|-------------|--------|
| N/A | | | | | |

Characteristics of the fast transient/burst generator

| Burst duration | Burst Period | Repetition Rate | Rise time | Duration |
|------------------------------------|-------------------------------------|-----------------|-----------------------------------|------------------------------------|
| 15 ms ⁺ _{-20%} | 300 ms ⁺ _{-20%} | 5 kHz | 5 ns ⁺ _{-30%} | 50 ns ⁺ _{-30%} |

**8.6. SURGE IMMUNITY TEST****8.6.1. TEST SPECIFICATION****Basic Standard:** EN 61000-4-5**Wave-Shape:** Combination Wave
1.2/50 us Open Circuit Voltage
8/20 us Short Circuit Current**Test Voltage:** Power line ~ line to line: 0.5 kV;
line to ground: 2 kV**Surge Input/Output:** Power Line: L1-L2**Generator Source Impedance:** 2 ohm between networks
12 ohm between network and ground**Polarity:** Positive/Negative**Phase Angle:** 0 / 90 / 180 / 270**Pulse Repetition Rate:** 30 sec**Number of Tests:** 5 positive and 5 negative at selected points**8.6.2. TEST INSTRUMENT**

| Immunity Shield Room | | | | |
|------------------------------|---------------|----------------|--------------------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | IBM | M/T 8183 - ICV | 99BG137 | N.C.R. |
| VGA Monitor | Acer | 1555 | 917160230584200572P5C431 | N.C.R. |
| Keyboard | HP | KB - 0133 | B69360MGAPEOK5 | N.C.R. |
| EMC Pro IMMUNITY TEST SYSTEM | KeyTek | EMCpro | 0312231 | APR. 07, 2015 |
| Switzerland | CDN | CDN-UTP8 | See headline | MAR. 06, 2015 |
| Test S/W | CE Ware 3.00b | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R. = No Calibration Required.



8.6.3. TEST PROCEDURE

a) For EUT power supply:

The surge is applied to the EUT power supply terminals via the capacitive coupling network. Decoupling networks are required in order to avoid possible adverse effects on equipment not under test that may be powered by the same lines, and to provide sufficient decoupling impedance to the surge wave. The power cord between the EUT and the coupling/decoupling networks was shorter than 2 meters in length.


b) For test applied to unshielded un-symmetrically operated interconnection lines of EUT:

The surge was applied to the lines via the capacitive coupling. The coupling / decoupling networks didn't influence the specified functional conditions of the EUT. The interconnection line between the EUT and the coupling/decoupling networks was shorter than 2 meters in length.

c) For test applied to unshielded symmetrically operated interconnection / telecommunication lines of EUT:

The surge was applied to the lines via gas arrestors coupling. Test levels below the ignition point of the coupling arrestor were not specified. The interconnection line between the EUT and the coupling/decoupling networks was shorter than 2 meters in length.

8.6.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

**8.6.5. TEST RESULTS**

| | | | |
|-------------------------------------|-----------|--------------------|----------|
| Temperature | 25 °C | Humidity | 48 % RH |
| Pressure | 1028 mbar | Tested By | Rock Guo |
| Required Passing Performance | | Criterion B | |

| Test Point | Polarity | Test Level (kV) | Performance Criterion | Result | Observation |
|------------|----------|-----------------|---|--------|-------------|
| L1 – L2 | +/- | 0.5kV | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | A PASS | |

| Phase shifting | Repetition Rate | Waveform parameter | Coupling Rate |
|---------------------|-----------------|---|-------------------------|
| 0°、 90°、 180°、 270° | 30 sec | Combine Wave 1.2μs/50μs 8μs /20μs | 5 times |
| | | Impedance 2 / 12 | Each Angle and Polarity |

**8.7. CONDUCTED RADIO FREQUENCY DISTURBANCES (CS)****8.7.1. TEST SPECIFICATION**

Basic Standard: EN 61000-4-6
Frequency Range: 0.15 MHz ~ 80 MHz
Field Strength: 3 Vrms
Modulation: 1kHz Sine Wave, 80%, AM Modulation
Frequency Step: 1 % of preceding frequency value
Coupling device: CDN-M2 (2 wires)

8.7.2. TEST INSTRUMENT

| Immunity Shield Room | | | | |
|--|----------------|-------------|---------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | HP | d330 uT | SGH3480LTH | N.C.R. |
| VGA Monitor | NEC | JC-1572VMA | 6600645RA | N.C.R. |
| Keyboard | IBM | KB - 8923 | 1021424 | N.C.R. |
| CS Frankonia EMVMess-System GmbH | FRANKONIA | CIT-10/75 | 102C3220 | JUN 10, 2014 |
| FCC Coupling Decoupling Network Freq. range : 150KHz~230MHz | FRANKONIA | CDN M2+M3 | A3011095 | JUN. 09, 2014 |
| FCC EM Injection Clamp | ----- | F-203I-23mm | 449 | NOV. 17, 2014 |
| Test S/W | CS-EN61000-4-6 | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R. = No Calibration Required.



8.7.3. TEST PROCEDURE

The EUT shall be tested within its intended operating and climatic conditions.

The test shall be performed with the test generator connected to each of the coupling and decoupling devices in turn, while the other non-excited RF input ports of the coupling devices are terminated by a 50-ohm load resistor.


The frequency range was swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80 % amplitude. The signal was modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. The sweep rate was 1.5×10^{-3} decades/s. Where the frequency range is swept incrementally, the step size was 1 % of preceding frequency value from 150 kHz to 80 MHz.

The dwell time at each frequency was less than the time necessary for the EUT to be exercised, and able to respond. Sensitive frequencies such as clock frequency(ies) and harmonics or frequencies of dominant interest, was analyzed separately.

Attempts were made to fully exercise the EUT during testing, and to fully interrogate all exercise modes selected for susceptibility.



8.7.4. TEST SETUP



- Note:** 1. The EUT is setup 0.1m above Ground Reference Plane
2. The CDNs and / or EM clamp used for real test depends on ports and cables configuration of EUT.

- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

TABLE-TOP AND FLOOR-STANDING EQUIPMENT

The equipment to be tested is placed on an insulating support of 0.1 meters height above a ground reference plane. All relevant cables shall be provided with the appropriate coupling and decoupling devices at a distance between 0.1 meters and 0.3 meters from the projected geometry of the EUT on the ground reference plane.



8.7.5. TEST RESULTS

| | | | |
|-------------------------------------|-----------|--------------------|----------|
| Temperature | 25 °C | Humidity | 46% RH |
| Pressure | 1028 mbar | Tested By | Rock Guo |
| Required Passing Performance | | Criterion B | |

POWER

| Frequency Band (MHz) | Field Strength (Vrms) | Cable | Injection Method | Performance Criterion | Result | Observation |
|-----------------------------|------------------------------|--------------|--|---|---------------|--------------------|
| 0.15 ~ 80 | 3 | DC Power | CDN- <input checked="" type="checkbox"/> M2 <input type="checkbox"/> M3 | <input checked="" type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | PASS | |

SIGNAL

| Frequency Band (MHz) | Field Strength (Vrms) | Cable | Injection Method | Performance Criterion | Observation | Result |
|-----------------------------|------------------------------|--------------|-------------------------|------------------------------|--------------------|---------------|
| N/A | | | | | | |

**8.8. VOLTAGE DIP & VOLTAGE INTERRUPTIONS****8.8.1. TEST SPECIFICATION****Basic Standard:** EN 61000-4-11**Test duration time:** Minimum three test events in sequence**Interval between event:** Minimum 10 seconds**Phase Angle:** 0 / 45 / 90 / 135 / 180 / 225 / 270 / 315 / 360**Test cycle:** Voltage Dips:i) 30% reduction for reduction 10ms,
Performance Criterion Bii) 60% reduction for reduction 100ms,
Performance Criterion C

Voltage Interruptions:

>95% reduction for reduction 5000 ms
Performance Criterion C**8.8.2. TEST INSTRUMENT**

| Immunity shielded room | | | | |
|------------------------------|---------------|----------------|--------------------------|-----------------|
| Name of Equipment | Manufacturer | Model | Serial Number | Calibration Due |
| Computer | IBM | M/T 8183 - ICV | 99BG137 | N.C.R. |
| VGA Monitor | Acer | 1555 | 917160230584200572P5C431 | N.C.R. |
| Keyboard | HP | KB - 0133 | B69360MGAPEOK5 | N.C.R. |
| EMC Pro IMMUNITY TEST SYSTEM | KeyTek | EMCpro | 0312231 | APR. 07, 2015 |
| Test S/W | CE Ware 3.00b | | | |

NOTE: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.


2. N.C.R.= No Calibration Required

8.1.1 TEST PROCEDURE

- The EUT and support units were located on a wooden table, 0.8 m away from ground floor.
- Setting the parameter of tests and then perform the test software of test simulator.
- Conditions changes to occur at 0 degree crossover point of the voltage waveform.
- Recording the test result in test record form.



8.8.3. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

8.8.4. TEST RESULTS

| | | | |
|------------------------------|--|-----------|----------|
| Temperature | --- °C | Humidity | --- % RH |
| Pressure | ---mbar | Tested By | --- |
| Required Passing Performance | Criterion B: 30% reduction 10ms & 60% reduction 100ms Criterion C: >95% reduction 5000 ms | | |

| Test Power: 230Vac, 50Hz | | | | |
|--------------------------|---------------|--|-------------|-------------|
| Voltage (% Reduction) | Duration (ms) | Performance Criterion | Test Result | Observation |
| 30 | 0.5 | <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | --- | |
| 60 | 5 | <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | --- | |
| >95 | 250 | <input type="checkbox"/> A <input type="checkbox"/> B <input type="checkbox"/> C | --- | |

This EUT do not connect to AC Source directly. Not applicability for this test.




9 PHOTOGRAPHS OF THE TEST CONFIGURATION CONDUCTED EMISSION TEST






RADIATED EMISSION TEST





ESD Test



RS Test





EFT Test



Surge Test





CS Test

