

Test report

CO344_02.DOC

EUT: Industrial Power Supply
Type: TCL 060-112C
Tested type: TCL 060-112C, 12VDC/4A

Production level: 10/07/2003
S/N: xx

Manufacturer: Convertec Ltd.
Whitemill Industrial Estate
Wexford
Republic of Ireland

Measurement procedure: EMC review of the EUT according the conformity with the provisions of 89/336/EEC Directive related standards:
EN 55011:1998 + A1:1999
EN 61000-3-2:2000
EN 61000-3-3:1995 + A1:2001
EN 61000-6-2:2001

The standards were: ☒ kept
☐ not kept

Applicant: Convertec Ltd.
Whitemill Industrial Estate
Wexford
Republic of Ireland

Contact person: Mr. Hinterleitner


Arrival of EUT: 10/21/2003

ID of EUT: PR343_06

Date(s) of test of EUT: 10/22/2003, 10/24/2003

Remark:

The test results effects only to the relate items tested. The test report shall not be reproduced except in full without the written approval of the testing laboratory



Test laboratory: EMCE GmbH Ingenieurbüro für EMV-Prüfungen
 und Schaltungsentwicklung
 Laupheimer-Str. 25d
 88483 Burgrieden / Germany
DAR-Registrierungsummer: TTI-P-G164/98
FCC Registration No. 90568

Test engineer: Mr. Hauser
 EMCE GmbH Ingenieurbüro für EMV-Prüfungen
 und Schaltungsentwicklung

EUT description: Industrial power supply with fixed output voltage $12V_{dc}$ at max.
 output current 4A. Input supply range 100-240VAC 50/60 Hz.
 “DC OK” voltage threshold 9...11V_{dc}.

EUT size: 45x100x75 mm (LxWxH)

Used accessories:

Designation	Type	Manufacturer	S/N
Variable resistor	13Ω/650W	Frizlen	Inv.Nr. 541
Multimeter	Fluke 77A	Fluke	Inv.Nr. 506
Multimeter	Protek 506	Protek	Inv.Nr. 573

EUT configuration:


Harness	Type	Length	Remarks
Mains leads	3-Wire	1.3 m	xx
DC-Output leads	2-Wire	2.0 m	xx

Additional information: The corresponding German edition of the regulations were used
 for the test procedures.

List of valid equipment

<input checked="" type="checkbox"/>	Inv-Nr.	Designation	Type	Manufacturer	S/N
<input checked="" type="checkbox"/>	001	Test receiver	ESS 5Hz - 1000 MHz	Rohde & Schwarz	833776/008
	002	Probe	ESH2-Z3	Rohde & Schwarz	-
	003	LISN 1	ESH3-Z5	Rohde & Schwarz	835268/007
	004	LISN 2	ESH3-Z5	Rohde & Schwarz	835268/003
<input checked="" type="checkbox"/>	005	LISN 3	NNB 4/32T	Rolf Heine HF-Technik	4/32T-96015
	006	LISN	NNBM 8125	Schwarzbeck	8125371
	007	Absorbing clamp	MDS 21	Schwarzbeck	942436
	008	Antenna 9kHz - 30MHz	HFH2-Z2	Rohde & Schwarz	835776/0002
	009	Antenna 30 - 300MHz	VHBA9123 / BBA9106	Schwarzbeck	435
<input checked="" type="checkbox"/>	010	Antenna 250 -1200MHz	UHALP 9108A	Schwarzbeck	108
<input checked="" type="checkbox"/>	011	Antenna 30 - 300MHz	VHBA9123 / BBA9106	Schwarzbeck	0408/94
	012	Antenna 250 -1200MHz	UHALP 9108A	Schwarzbeck	166
	013	Antenna 9kHz - 30MHz	Loop antenna 1.5m	EMCE GmbH	-
	014	Open area test site	3m	EMCE GmbH	-
<input checked="" type="checkbox"/>	015	Open area test site	10m	EMCE GmbH	-
	019	Burst generator	PEFT / PHV 41.2	Haefely	082948-50
<input checked="" type="checkbox"/>	020	Coupling clamp	IP4A	Haefely	082672-13
<input checked="" type="checkbox"/>	022	ESD-Gun	NSG 435	Schaffner	577
<input checked="" type="checkbox"/>	024	HF-Generator	SMY01	Rohde & Schwarz	844146/046
	025	Current clamp BCI	F-120-2	FCC	47
<input checked="" type="checkbox"/>	026	Coupling device network	CDN 801-M3-25	FCC	92
	027	Surge Generator	Transient 1000	EMC-Partner AG	TRA1000-85
	029	HF Amplifier	10W1000	Amplifier Research	10576
	030	Coupling device network	CDN-S9	EMCE GmbH	-
	031	Coupling device network	CDN-S9	EMCE GmbH	-

<input checked="" type="checkbox"/>	Inv-Nr.	Designation	Type	Manufacturer	S/N
<input checked="" type="checkbox"/>	032	HF Amplifier	75A250	Amplifier Research	22789
<input checked="" type="checkbox"/>	033	Coupling device network	CDN-AF2	EMCE GmbH	
<input checked="" type="checkbox"/>	034	Coupling device network	CDN-AF2	EMCE GmbH	
	035	3-Phase Coupling network	CDN-1000	EMC-Partner AG	CDN-1000-45
	036	Coupling device network	CDN-M5-25	EMCE GmbH	
	037	Coupling device network	CDN-S1	EMCE GmbH	
	038	Helmholtz coil	Rectangular 1x1m	EMCE GmbH	
	039	Helmholtz coil	Rectangular 1x1m	EMCE GmbH	
	040	Current transformer		EMCE GmbH	
	041	HZ-10	Shielded coil	Rohde & Schwarz	849788/020
<input checked="" type="checkbox"/>	042	AC-Source / Analyser / Norm impedance	EMV D5000/PAS	Spitzenberger + Spies	A274700/0 0501
<input checked="" type="checkbox"/>	xx	Susceptibility test equipment according EN 61000-4-3	Full anechoic chamber 3m test site	Siemens	xx
	043	Receiver	3DH/E Field meter ESM-100	Maschek	971521
<input checked="" type="checkbox"/>	044	CDN	CN-U	EMC-Partner AG	86
	045	CDN	DN-HF	EMC-Partner AG	86
	046	CDN	DN-LF2	EMC-Partner AG	86
	047	CDN	DN-LF1	EMC-Partner AG	86
<input checked="" type="checkbox"/>	048	ESD-/Burst-/Surge- Generator	Transient 2000	EMC-Partner AG	561
	049	ESD-Gun	ESD 2000	EMC-Partner AG	012



Scope:

1	EMC - Test(s).....	7
1.1	Emission according DIN EN 55011 (VDE 0875 Teil 11) / 05.2000.....	7
1.1.1	Conducted emission according DIN EN 55011 (VDE 0875 Teil 11) / 05.2000.....	7
1.1.1.1	Test setup.....	7
1.1.1.2	Test.....	8
1.1.2	Radio disturbances according DIN EN 55011 (VDE 0875 Teil 11) / 05.2000.....	14
1.1.2.1	Test setup.....	14
1.1.2.2	Test.....	15
1.2	Harmonic current emissions according DIN EN 61000-3-2 (VDE 0838 Teil 2) / 12.2001.....	21
1.2.1	Test set up.....	21
1.2.2	Test.....	22
1.3	Voltage fluctuations and flicker according DIN EN 61000-3-3 (VDE 0838 Teil 3) / 05.2002.....	25
1.3.1	Test set up.....	25
1.3.2	Test.....	26
1.4	Electrostatic discharge immunity test according DIN EN 61000-4-2 (VDE 0847 Teil 4-2) / 12.2001.....	29
1.4.1	Test set up.....	29
1.4.2	Test.....	32
1.5	Radiated, radio-frequency, electromagnetic field immunity test according DIN EN 61000-4-3 (VDE 0847 Teil 4-3) / 12.2001.....	34
1.5.1	Test set up.....	34
1.5.2	Test.....	35
1.6	Electrical fast transient / burst immunity test according DIN EN 61000-4-4 (VDE 0847 Teil 4-4) / 12.2001.....	38
1.6.1	Test set up.....	38
1.6.2	Test.....	40
1.7	Surge immunity test according DIN EN 61000-4-5 (VDE 0847 Teil 4-5) / 12.2001.....	42
1.7.1	Test set up.....	42
1.7.2	Test.....	44
1.8	Immunity to conducted disturbances, induced by radio-frequency fields according DIN EN 61000-4-6 (VDE 0847 Teil 4-6) / 12.2001.....	46
1.8.1	Test set up.....	46
1.8.2	Test.....	47
1.9	Immunity against low frequency magnetic fields according DIN EN 61000-4-8 (VDE 0847 Teil 4-8) / 12.2001.....	50
1.10	Voltage dips, short interruptions and voltage variations immunity tests according DIN EN 61000-4-11 (VDE 0847 Teil 4-11) / 12.2001.....	51



	1.10.1 Test set up.....	51
	1.10.2 Test.....	52
2	Summary.....	54



1 EMC - Test(s)

1.1 *Emission according DIN EN 55011 (VDE 0875 Teil 11) / 05.2000*


1.1.1 Conducted emission according DIN EN 55011 (VDE 0875 Teil 11) / 05.2000


1.1.1.1 *Test setup*

According DIN EN 55011 (VDE 0875 Teil 11) /05.2000

Test location: ☒ Shielded room ☐ Laboratory
☐ —

☒ The test equipment was checked and complied to the requirements.





1.1.1.2 Test

Regulation:

DIN EN 55011 (VDE 0875 Teil 11) /05.2000

☐ 9kHz - 30MHz
 ☒ 150kHz - 30MHz

ISM-Classification ☒ Group 1* ☐ Group 2**
 Limits: ☒ Class B ☐ Class A

*Group 1 comprises all ISM appliances, which use rf energy for internal functions.

**Group 2 comprises all ISM appliances, which use rf energy for tooling material.

Operation mode:

EUT arrangement: ☒ Tabletop ☐ Floor standing

Port #	Lead	Remarks
#1	Mains leads	L1/N/PE
#2		
#3		

Continuous operation at max. load*.

Environmental conditions:

Temperature: 15 - 35 °C
 Humidity: 30 - 60 %
 Air pressure: 860 - 1060 hPa

The environmental conditions during the test: ☒ were kept
☐ were not kept

Test results:

Measurements are made with a CISPR receiver. If the emanation is closer than 6dB to the limits or more, the receiver will stop and measure the exact value with quasipeak or average. The frequency, the maximum quasipeak value and the limit will be printed out.



Summary:

Limits for continuous disturbances:

☒
☐

kept
not kept

Remarks: * This mode met “worst case” operation.

Protocol scope:

☒
☒

Readings
Diagram continuous emanations

EMCE GmbH Ing_buero fuer EMV_Pruefungen Terminal voltage

21. Oct 03 10:39

EUT: SMPS TCL060-112C
Manuf: Convertec Ltd.
Op Cond: Max. load, 12V/4A
Operator: Mr. Hauser
Test Spec: EN 55011 ISM-Appliances Class B
Comment: TestID_EUT PR343_06
CO343_01, Phase L1


Scan Settings (1 Range)

Frequencies				Receiver Settings			
Start	Stop	Step	IF BW	Detector	M-Time	Atten	Preamp OpRge
150k	30M	5k	10k	PK+AV	20ms	AUTO	LN OFF 60dB

Final Measurement: x QP / + AV

Meas Time: 1 s
Subranges: 50
Acc Margin: 6dB

Transducer No.	Start	Stop	Name
2	1Hz	1000M	Kabel_6m





EMCE GmbH Ing_buero fuer EMV_Pruefungen

Terminal voltage

21. Oct 03 10:39

EUT: SMPS TCL060-112C
 Manuf: Convertec Ltd.
 Op Cond: Max. load, 12V/4A
 Operator: Mr. Hauser
 Test Spec: EN 55011 ISM-Appliances Class B
 Comment: TestID_EUT PR343_06
 CO343_01, Phase L1

Scan Settings (1 Range)

Frequencies				Receiver Settings				
Start	Stop	Step	IF BW	Detector	M-Time	Atten	Preamp	OpRge
150k	30M	5k	10k	PK+AV	20ms	AUTO	LN OFF	60dB

Final Measurement Results:


Frequency	QP Level	QP Limit
MHz	dBuV	dBuV

no Results

Frequency	AV Level	AV Limit
MHz	dBuV	dBuV

0.15000	52.2	56.0
0.29500	44.7	50.3

* limit exceeded



EMCE GmbH Ing_buero fuer EMV_Pruefungen Terminal voltage

21. Oct 03 10:51


EUT: SMPS TCL060-112C
Manuf: Convertec Ltd.
Op Cond: Max. load, 12V/4A
Operator: Mr. Hauser
Test Spec: EN 55011 ISM-Appliances Class B
Comment: TestID_EUT PR343_06
CO343_02, Phase N

Scan Settings (1 Range)

Frequencies				Receiver Settings					
Start	Stop	Step	IF BW	Detector	M-Time	Atten	Preamp	OpRge	
150k	30M	5k	10k	PK+AV	20ms	AUTO	LN	OFF 60dB	

Final Measurement: x QP / + AV
Meas Time: 1 s
Subranges: 50
Acc Margin: 6dB

Transducer No.	Start	Stop	Name
2	1Hz	1000M	Kabel_6m





EMCE GmbH Ing_buero fuer EMV_Pruefungen

Terminal voltage

21. Oct 03 10:51

EUT: SMPS TCL060-112C
 Manuf: Convertec Ltd.
 Op Cond: Max. load, 12V/4A
 Operator: Mr. Hauser
 Test Spec: EN 55011 ISM-Appliances Class B
 Comment: TestID_EUT PR343_06
 CO343_02, Phase N

Scan Settings (1 Range)


Frequencies				Receiver Settings				
Start	Stop	Step	IF BW	Detector	M-Time	Atten	Preamp	OpRge
150k	30M	5k	10k	PK+AV	20ms	AUTO	LN OFF	60dB

Final Measurement Results:

Frequency	QP Level	QP Limit
MHz	dBuV	dBuV
0.15000	61.3	66.0
0.30500	52.6	60.1

Frequency	AV Level	AV Limit
MHz	dBuV	dBuV
0.15000	54.8	56.0
0.30000	48.6	50.2

* limit exceeded



1.1.2.2 Test

Regulation:

DIN EN 55011 (VDE 0875 Teil 11) / 05.2000

☐

9kHz - 30MHz

☒

30MHz - 1000MHz

☐

150kHz - 30MHz

☐

11,7 – 12,7GHz

ISM-Classification

☒

Group 1*

☐

Group 2**

Limits:

☒

Class B

☐

Class A

*Group 1 comprises all ISM appliances, which use rf energy for internal functions.

**Group 2 comprises all ISM appliances, which use rf energy for tooling material.

Operation mode:

EUT arrangement:

☒

Tabletop

☐

Floor standing

Continuous operation at max. load*.

Environmental conditions:

Temperature: 15 - 35 °C

Humidity: 30 - 60 %

Air pressure: 860 - 1060 hPa

The environmental conditions during the test:

☒

were kept

☐

were not kept

Test results:

Measurements are made with a CISPR receiver. If the emanation is closer than 6dB to the limits or more, the receiver will stop and measure the exact value with quasipeak or average. The frequency, the maximum quasipeak value and the limit will be printed out.



Summary:

Limits for continuous disturbances:

☒
☐

kept
not kept

Remarks: * This mode met “worst case” operation.

Protocol scope:

- ☒ Readings - Antenna horizontal polarized.
- ☒ Diagram radio disturbances - Antenna horizontal polarized.
- ☒ Readings - Antenna vertical polarized.
- ☒ Diagram radio disturbances - Antenna vertical polarized.
- ☐ Precompliance measuerment(s).

Readings - Antenna horizontal polarized


Frequency	Measured	+ AF	+ KF	Emission	Limit	Difference	Ant.-	Ant.-
MHz	value	dB/m	dB		dB μ V/m	dB μ V	Height	Polar.
	dB μ V	Antenna	Cable	dB μ V/m			meter	H/V
110.000	7.7	10.5	2.2	20.3	30.0	9.7	4.0	H
143.000	6.9	12.1	2.5	21.5	30.0	8.5	4.0	H
144.000	7.4	12.2	2.5	22.1	30.0	7.9	3.5	H
188.000	4.0	14.4	2.9	21.3	30.0	8.7	3.5	H




Diagram radio disturbances - Antenna horizontal polarized

Limits according DIN EN 55011 (VDE 0875 Teil 11) / 05.2000

☐ Class A
☒ Class B





Readings - Antenna vertical polarized

Frequency	Measured	+ AF	+ KF	Emission	Limit	Difference	Ant.-	Ant.-
MHz	value	dB/m	dB		dB μ V/m	dB μ V	Height	Polar.
	dB μ V	Antenna	Cable	dB μ V/m			meter	H/V
56.000	11.9	8.2	1.4	21.6	30.0	8.4	1.0	V
89.000	18.3	9.4	1.9	29.6	30.0	0.4	1.0	V
96.100	13.3	9.7	2.0	25.0	30.0	5.0	1.0	V
107.100	15.6	10.3	2.1	28.0	30.0	2.0	1.0	V
110.000	15.8	10.5	2.2	28.4	30.0	1.6	1.0	V
111.000	16.0	10.5	2.2	28.7	30.0	1.3	1.0	V
117.000	16.0	10.8	2.2	29.0	30.0	1.0	1.0	V
118.000	16.2	10.8	2.2	29.3	30.0	0.7	1.0	V
119.000	16.4	10.9	2.3	29.6	30.0	0.4	1.0	V
120.000	15.6	10.9	2.3	28.8	30.0	1.2	1.0	V
121.000	14.4	11.0	2.3	27.7	30.0	2.3	1.0	V
128.000	13.9	11.3	2.4	27.6	30.0	2.4	1.0	V
129.000	14.0	11.4	2.4	27.8	30.0	2.2	1.0	V
130.000	14.8	11.4	2.4	28.6	30.0	1.4	1.0	V
131.000	15.4	11.5	2.4	29.3	30.0	0.7	1.0	V
132.000	15.8	11.5	2.4	29.7	30.0	0.3	1.0	V
133.000	15.6	11.6	2.4	29.6	30.0	0.4	1.0	V
134.000	14.1	11.6	2.4	28.2	30.0	1.8	1.0	V
135.000	14.6	11.7	2.4	28.7	30.0	1.3	1.0	V
136.000	14.8	11.7	2.4	29.0	30.0	1.0	1.0	V
137.000	15.0	11.8	2.4	29.2	30.0	0.8	1.0	V
138.000	15.5	11.8	2.5	29.8	30.0	0.2	1.0	V
139.000	15.3	11.9	2.5	29.7	30.0	0.3	1.0	V
140.000	15.4	12.0	2.5	29.8	30.0	0.2	1.0	V
141.000	14.9	12.0	2.5	29.4	30.0	0.6	1.0	V
142.000	14.6	12.1	2.5	29.1	30.0	0.9	1.0	V
143.000	14.4	12.1	2.5	29.0	30.0	1.0	1.0	V
144.000	14.7	12.2	2.5	29.4	30.0	0.6	1.0	V
145.000	12.9	12.2	2.5	27.6	30.0	2.4	1.0	V
146.000	11.5	12.3	2.5	26.3	30.0	3.7	1.0	V
186.000	8.3	14.3	2.9	25.5	30.0	4.5	1.0	V
187.000	8.1	14.4	2.9	25.4	30.0	4.6	1.0	V





Diagram radio disturbances - Antenna vertical polarized

Limits according DIN EN 55011 (VDE 0875 Teil 11) / 05.2000



Class A
 Class B




1.2 Harmonic current emissions according DIN EN 61000-3-2 (VDE 0838 Teil 2) / 12.2001

1.2.1 Test set up

According DIN EN 61000-3-2 (VDE 0838 Teil 2) / 12.2001

Test location: ☐ Shielded room ☒ Laboratory
☐ Open field ☐ _





1.2.2 Test

Regulation:

DIN EN 61000-3-2 (VDE 0838 Teil 2) / 12.2001

100Hz - 2000Hz

Limit:

☐ Constant Harmonics

☒ Fluctuating Harmonics

☒ Class A

☐ Class B

☐ Class C

☐ Class D

Operation mode:

EUT arrangement:



Tabletop



Floor standing

The EUT was supplied via an AC-Source.

Continuous operation at maximum load*.

Environmental conditions:

Temperature: 15 - 35 °C

Humidity: 30 - 60 %

Air pressure: 860 - 1060 hPa

The environmental conditions during the test:



were kept



were not kept

Test results:

Limits:



kept



not kept



not relevant

Remarks: *This mode met “worst case” operation. No limits applicable if the input power is less or equal than 75 Watts.

Diagrams:



Harmonic test table



Bar chart – Window #1



Diagram margin

Name: Mr. Hauser
Department: EMC Testing
Company: EMCE GmbH
Test report no: xx
Device: SMPS
Specimen: Class A
Manufacturer: Convertec Ltd
Type: TCL 060-112C

Serial no: xx
Operating modes: Max. load 4A
Comment1: EUT ID / PR343_06
Comment2: 230V/50Hz
Comment3: --
Comment4: --
Date: 29.10.2003
Test date: 21.10.2003

Maximum RMS current and corresponding values in timewindow 469:

Voltage: 230.37 Vrms THD=0.02 % THV=0.038 V POHV=0.017 V PWHD=0.04 %
Current: 0.537 Arms THD=183.32 % THC=0.472 A POHC=0.047 A PWHD=177.87 %
Power: 57.9 W P1=57.9 W 123.6 VA
Powerfactor: 0.468 CosPhi1: 0.988




Testconditions: EN 61000-3-2 / A14, f=50 Hz, Phase=L1, Range=0.80 A
Time window cycles=16, Grouping of harmonics=off

HARMONIC ANALYSIS: Test PASS

Tobs = worst 2.5 min: tw 1.469 POHC: avg=0.047 A, limits=0.251 A

Ha	Entire measurement (2.5 min = 469 time windows)						Worst 2.5 min		Worst 2.5 min avg		P A S S	F A I L
	Maximum	Window	EN61000-3-2 Class A	Margin in MaxWin	100 to 150%	Ex- ceeded	100 to 150%	Ex- ceeded	Value	Ex- ceeded		
DC	0.0017 A	76	----	----	0	0	0	0	-0.0015 A	0	X	
1	0.2551 A	1	----	----	0	0	0	0	0.2546 A	0	X	
2	0.0007 A	130	1.0800 A	-99.9 %	0	0	0	0	0.0005 A	0	X	
3	0.2424 A	1	2.3000 A	-89.5 %	0	0	0	0	0.2421 A	0	X	
4	0.0007 A	409	0.4300 A	-99.8 %	0	0	0	0	0.0005 A	0	X	
5	0.2256 A	244	1.1400 A	-80.2 %	0	0	0	0	0.2254 A	0	X	
6	0.0006 A	408	0.3000 A	-99.8 %	0	0	0	0	0.0005 A	0	X	
7	0.2016 A	469	0.7700 A	-73.8 %	0	0	0	0	0.2011 A	0	X	
8	0.0006 A	449	0.2300 A	-99.7 %	0	0	0	0	0.0005 A	0	X	
9	0.1730 A	469	0.4000 A	-56.7 %	0	0	0	0	0.1722 A	0	X	
10	0.0006 A	449	0.1840 A	-99.7 %	0	0	0	0	0.0005 A	0	X	
11	0.1412 A	469	0.3300 A	-57.2 %	0	0	0	0	0.1400 A	0	X	
12	0.0005 A	449	0.1533 A	-99.7 %	0	0	0	0	0.0004 A	0	X	
13	0.1087 A	469	0.2100 A	-48.3 %	0	0	0	0	0.1072 A	0	X	
14	0.0004 A	449	0.1314 A	-99.7 %	0	0	0	0	0.0003 A	0	X	
15	0.0773 A	469	0.1500 A	-48.5 %	0	0	0	0	0.0757 A	0	X	
16	0.0003 A	458	0.1150 A	-99.7 %	0	0	0	0	0.0003 A	0	X	
17	0.0493 A	469	0.1324 A	-62.8 %	0	0	0	0	0.0476 A	0	X	
18	0.0002 A	459	0.1022 A	-99.8 %	0	0	0	0	0.0002 A	0	X	
19	0.0265 A	469	0.1184 A	-77.6 %	0	0	0	0	0.0251 A	0	X	
20	0.0002 A	109	0.0920 A	-99.8 %	0	0	0	0	0.0002 A	0	X	
21	0.0129 A	469	0.1071 A	-88.0 %	0	0	0	0	0.0124 A	0	X	
22	0.0002 A	112	0.0836 A	-99.7 %	0	0	0	0	0.0002 A	0	X	
23	0.0159 A	1	0.0978 A	-83.8 %	0	0	0	0	0.0151 A	0	X	
24	0.0002 A	119	0.0767 A	-99.7 %	0	0	0	0	0.0002 A	0	X	
25	0.0208 A	1	0.0900 A	-76.9 %	0	0	0	0	0.0203 A	0	X	
26	0.0003 A	450	0.0708 A	-99.6 %	0	0	0	0	0.0002 A	0	X	
27	0.0221 A	175	0.0833 A	-73.4 %	0	0	0	0	0.0221 A	0	X	
28	0.0002 A	448	0.0657 A	-99.6 %	0	0	0	0	0.0002 A	0	X	
29	0.0207 A	469	0.0776 A	-73.3 %	0	0	0	0	0.0204 A	0	X	
30	0.0002 A	449	0.0613 A	-99.6 %	0	0	0	0	0.0002 A	0	X	
31	0.0168 A	469	0.0726 A	-76.8 %	0	0	0	0	0.0163 A	0	X	
32	0.0002 A	450	0.0575 A	-99.7 %	0	0	0	0	0.0001 A	0	X	
33	0.0116 A	469	0.0682 A	-83.0 %	0	0	0	0	0.0109 A	0	X	
34	0.0001 A	409	0.0541 A	-99.8 %	0	0	0	0	0.0001 A	0	X	
35	0.0063 A	469	0.0643 A	-90.2 %	0	0	0	0	0.0058 A	0	X	
36	0.0001 A	110	0.0511 A	-99.8 %	0	0	0	0	0.0001 A	0	X	
37	0.0043 A	2	0.0608 A	-93.0 %	0	0	0	0	0.0040 A	0	X	
38	0.0001 A	113	0.0484 A	-99.7 %	0	0	0	0	0.0001 A	0	X	
39	0.0068 A	2	0.0577 A	-88.3 %	0	0	0	0	0.0062 A	0	X	
40	0.0002 A	418	0.0460 A	-99.7 %	0	0	0	0	0.0001 A	0	X	

Tested with EMC test software V2.3h / PAS1000 by Spitzenberger + Spies GmbH & Co. KG, Schmidstr. 32-34, D-94234 Viechtach, 21.10.2003




1.3 Voltage fluctuations and flicker according DIN EN 61000-3-3 (VDE 0838 Teil 3) / 05.2002

1.3.1 Test set up

According DIN EN 61000-3-3 (VDE 0838 Teil 3) / 05.2002

Test location: ☐ Shielded room ☒ Laboratory
☐ Open field ☐ —





1.3.2 Test

Regulations:

DIN EN 61000-3-3 (VDE 0838 Teil 3) / 05.2002

☒ Voltage changes measured at a norm impedance according the „Voltage Method“

$R_A = 0.24\Omega$ / $X_A = 0.15\Omega$ at 50Hz

$R_N = 0.16\Omega$ / $X_N = 0.10\Omega$ at 50Hz

☐ Voltage changes measured according with the „Current Method“ - Precompliant.

☒ Voltage changes caused by hand.

- dc < 3.3%

- dmax < 4.0%

- d(t) < 500ms

The observation time for one cycle is 1 minute.

☐ Voltage changes, flicker caused by program

- dc < 3.3%

- dmax < 6.0%

- d(t) < 500ms

- Pst < 1

- Plt < 0.65

The observation time for one cycle is 10 minutes.

Operation mode:

EUT arrangement: ☒ Tabletop ☐ Floor standing


To get the voltage dips, the power supply was switched on / off at maximum load current. This procedure was repeated 24 times to get the maximum values.

Environmental conditions:

Temperature: 15 - 35 °C

Humidity: 30 - 60 %

Air pressure: 860 - 1060 hPa



The environmental conditions during the test:

☒
☐

were kept
were not kept

Test results:

Limits: ☒ kept
☐ not kept
☒ Pst, Plt – not relevant

| Remarks: xx

Name:	Mr. Hauser	Serial no:	xx
Department:	EMC Testing	Operating modes:	Max. load 4A
Company:	EMCE GmbH	Comment1:	EUT ID / PR343_06
Test report no:	xx	Comment2:	230V/50Hz
Device:	SMPS	Comment3:	--
Specimen:	Manual switching	Comment4:	--
Manufacturer:	Convertec Ltd	Date:	05.11.2003
Type:	TCL 060-112C	Test date:	21.10.2003

Testconditions: 230 V / 50 Hz / Phase: L1 / Observations: 24 x 1 min / Ztest: (0.40+j0.25) Ohm

FLICKER: Test PASS!

Time	Pmax	Pst	Sliding Plt	d(t)>3.30% [s]	dmax [%]	dc [%]	PASS	FAIL
12:40:38	0.173	0.1690	- .----	0.000	0.484	0.038	X	
12:41:38	0.202	0.1710	- .----	0.000	0.523	0.038	X	
12:42:38	0.293	0.1800	- .----	0.000	0.636	0.013	X	
12:43:38	0.337	0.1850	- .----	0.000	0.685	0.012	X	
12:44:37	0.155	0.1670	- .----	0.000	0.455	0.007	X	
12:45:37	0.613	0.2110	- .----	0.000	0.514	0.008	X	
12:46:37	0.139	0.1660	- .----	0.000	0.434	0.008	X	
12:47:37	0.143	0.1660	- .----	0.000	0.440	0.004	X	
12:48:37	0.190	0.1710	- .----	0.000	0.508	0.011	X	
12:49:37	0.151	0.1670	- .----	0.000	0.454	0.011	X	
12:50:37	0.209	0.1720	- .----	0.000	0.478	0.006	X	
12:51:37	0.379	0.1890	0.1771	0.000	0.728	0.006	X	
12:52:37	0.134	0.1650	0.1768	0.000	0.428	0.010	X	
12:53:37	0.144	0.1660	0.1765	0.000	0.442	0.010	X	
12:54:37	0.539	0.2040	0.1788	0.000	0.825	0.008	X	
12:55:37	0.492	0.2000	0.1802	0.000	0.510	0.008	X	
12:56:37	0.190	0.1710	0.1805	0.000	0.471	0.002	X	
12:57:37	0.330	0.1840	0.1778	0.000	0.516	0.011	X	
12:58:37	0.154	0.1670	0.1779	0.000	0.460	0.011	X	
12:59:37	0.267	0.1780	0.1788	0.000	0.504	0.004	X	
13:00:37	0.328	0.1840	0.1799	0.000	0.669	0.005	X	
13:01:37	0.144	0.1660	0.1798	0.000	0.432	0.005	X	
13:02:37	0.554	0.2050	0.1828	0.000	0.477	0.007	X	
13:03:37	0.626	0.2110	0.1849	0.000	0.727	0.007	X	
Limits:		1.000	0.650	0.500	4.000	3.300		
Plt: 0.181114								
Evaluated: dc, dmax average (0.525 %), d(t)								

FLICKER: Source test PASS!

Time	Pmax	Pst	Sliding Plt	d(t)>3.30% [s]	dmax [%]	dc [%]	PASS	FAIL
12:40:38	0.000	0.0040	- .----	0.000	0.011	- .----	X	
12:41:38	0.000	0.0050	- .----	0.000	0.017	- .----	X	
12:42:38	0.000	0.0070	- .----	0.000	0.017	- .----	X	
12:43:38	0.000	0.0050	- .----	0.000	0.020	- .----	X	
12:44:37	0.000	0.0030	- .----	0.000	0.021	- .----	X	
12:45:37	0.000	0.0080	- .----	0.000	0.021	- .----	X	
12:46:37	0.000	0.0030	- .----	0.000	0.021	- .----	X	
12:47:37	0.000	0.0030	- .----	0.000	0.022	- .----	X	
12:48:37	0.000	0.0040	- .----	0.000	0.022	- .----	X	
12:49:37	0.000	0.0030	- .----	0.000	0.022	- .----	X	
12:50:37	0.000	0.0030	- .----	0.000	0.022	- .----	X	
12:51:37	0.000	0.0070	- .----	0.000	0.029	- .----	X	
12:52:37	0.000	0.0020	- .----	0.000	0.029	- .----	X	
12:53:37	0.000	0.0030	- .----	0.000	0.029	- .----	X	
12:54:37	0.000	0.0090	- .----	0.000	0.029	- .----	X	
12:55:37	0.000	0.0070	- .----	0.000	0.029	- .----	X	
12:56:37	0.000	0.0040	- .----	0.000	0.029	- .----	X	
12:57:37	0.000	0.0040	- .----	0.000	0.029	- .----	X	
12:58:37	0.000	0.0030	- .----	0.000	0.029	- .----	X	
12:59:37	0.000	0.0040	- .----	0.000	0.029	- .----	X	
13:00:37	0.000	0.0070	- .----	0.000	0.029	- .----	X	
13:01:37	0.000	0.0030	- .----	0.000	0.029	- .----	X	
13:02:37	0.000	0.0070	- .----	0.000	0.029	- .----	X	
13:03:37	0.000	0.0080	- .----	0.000	0.029	- .----	X	
Plt: 0.005621								
Evaluated: PST <= 0.4 dmax < 20% dmax1								

Tested with EMC test software V2.3h / PAS1000 by Spitzenberger + Spies GmbH & Co. KG, Schmidstr 32-34, D-94234 Viechtach, 21.10.2003






1.4 Electrostatic discharge immunity test according DIN EN 61000-4-2 (VDE 0847 Teil 4-2) / 12.2001


1.4.1 Test set up


According DIN EN 61000-4-2 (VDE 0847 Teil 4-2) / 12.2001

Test location:
☐ Shielded room
 ☒ Laboratory
☐ Open field
 ☐ —









1.4.2 Test

Regulation:

DIN EN 61000-4-2 (VDE 0847 Teil 4-2) /12.2001

Number of discharges:	<input checked="" type="checkbox"/> 10 positive	<input checked="" type="checkbox"/> 10 negative
Repetition rate:	<input checked="" type="checkbox"/> < 1 Pulse/s	<input type="checkbox"/> ___ Pulse/s
Test level Contact Discharge:	<input checked="" type="checkbox"/> ±2kV	<input checked="" type="checkbox"/> ±4kV
	<input type="checkbox"/> ±6kV	<input type="checkbox"/> ±___kV
Test level Air Discharge:	<input checked="" type="checkbox"/> ±2kV	<input checked="" type="checkbox"/> ±4kV
	<input checked="" type="checkbox"/> ±8kV	<input type="checkbox"/> ±___kV

Contact Discharge:

Port #	Discharge location	Test level ±2kV	Test level ±3kV	Test level ±4kV	Test level ±6kV	Test level ±8kV
1	Horizontal coupling plate	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
2	Vertical coupling plate	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
3	Output terminals	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

Air Discharge:


Port #	Discharge location	Test level ±2kV	Test level ±4kV	Test level ±6kV	Test level ±8kV	Test level ±15kV
4	Air cooling ducts - housing	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>
5	DC ON LED / O/P Adj.	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>

The test level was increased step by step, starting from the lowest up to the given severity level, to evaluate the fault level. Minimum 10 discharges, with the most critical polarisation and level, were applied to the selected locations
All used test equipment are calibrated periodically.

Operation mode:

EUT arrangement: ☒ Tabletop ☐ Floor standing

Continuous operation at 2A load. During the test the output voltage and the “DC OK” voltage were observed.



Environmental conditions:

Temperature: 15 - 35 °C
Humidity: 30 - 60 %
Air pressure: 860 - 1060 hPa

The environmental conditions during the test: ☒ were kept
☐ were not kept


Criterion B:

After the immunity test the EUT must work as intended. During the immunity test, there is some degradation of the performance allowed, but no change of the given working mode. The output voltage must be kept in the range of $\pm 5\%$.

Test results:

Immunity: ☒ Met criterion B
☐ Met not criterion B

Remarks: xx



1.5 Radiated, radio-frequency, electromagnetic field immunity test according DIN EN 61000-4-3 (VDE 0847 Teil 4-3) / 12.2001

1.5.1 Test set up

According DIN EN 61000-4-3 (VDE 0847 Teil 4-3) / 12.2001

Location:

Precompliance

☐

Shielded room

☐

Laboratory


Full compliance

☒

Full anechoic chamber

☒ The test equipment was checked and complied to the requirements.





1.5.2 Test

Regulation:

DIN EN 61000-4-3 (VDE 0847 Teil 4-3) / 12.2001

Frequency range:	<input checked="" type="checkbox"/>	80MHz - 1000MHz	<input type="checkbox"/>	26MHz - 1000MHz
Test level:	<input type="checkbox"/>	1V/m	<input type="checkbox"/>	3V/m
	<input checked="" type="checkbox"/>	10V/m	<input type="checkbox"/>	__ V/m
Modulation:	<input checked="" type="checkbox"/>	AM: 80%		
	<input checked="" type="checkbox"/>	AF: 1000Hz		
	<input type="checkbox"/>	not modulated		
	<input checked="" type="checkbox"/>	900MHz pulsed - duty cycle 50% / f _{rep} 200Hz		
Frequency step:	<input checked="" type="checkbox"/>	1% of the preceding frequency		
Sweep rate:	<input checked="" type="checkbox"/>	0.0015 Decades/s	<input type="checkbox"/>	__ Decades/s
Antenna – EUT:	<input type="checkbox"/>	1m	<input checked="" type="checkbox"/>	3m
Antenna polarisation:	<input checked="" type="checkbox"/>	horizontal	<input checked="" type="checkbox"/>	vertical

All used test equipment are calibrated periodically.

Operation mode:

EUT arrangement:	<input checked="" type="checkbox"/>	Tabletop	<input type="checkbox"/>	Floor standing
EUT Position:	<input checked="" type="checkbox"/>	Front	<input type="checkbox"/>	Backside
	<input checked="" type="checkbox"/>	Side / 90°	<input type="checkbox"/>	Side / 270°

Continuous operation at 2A load. During the test the output voltage and the “DC OK” voltage were observed.

Environmental conditions:

Temperature:	15 - 35 °C
Humidity:	30 - 60 %
Air pressure:	860 - 1060 hPa

The environmental conditions during the test:	<input checked="" type="checkbox"/>	were kept
	<input type="checkbox"/>	were not kept



Criterion A:

During the immunity test the EUT must work as intended. There is no degradation of the performance allowed and no change of the given working mode. The output voltage must be kept in the range of $\pm 2\%$.

Test results:

Frequency	Ant.-Polarization	Test parameter / max. deviation	Remarks

Immunity:


☒
☐

Met criterion A



Met not criterion A

Remarks:

xx



Test level: 10V/m






1.6 Electrical fast transient / burst immunity test according DIN EN 61000-4-4 (VDE 0847 Teil 4-4) / 12.2001


1.6.1 Test set up

According DIN EN 61000-4-4 (VDE 0847 Teil 4-4) / 12.2001

Test location:
☒ Shielded room
 ☐ Laboratory
☐ Open field
 ☐ —







1.6.2 Test

Regulation:

DIN EN 61000-4-4 (VDE 0847 Teil 4-4) / 12.2001

Burst frequency:	<input checked="" type="checkbox"/>	5kHz	<input type="checkbox"/>	__ kHz
Burst duration:	<input checked="" type="checkbox"/>	15ms	<input type="checkbox"/>	__ ms
Burst repetition freq.:	<input checked="" type="checkbox"/>	3Hz	<input type="checkbox"/>	__ Hz
Test duration:	<input checked="" type="checkbox"/>	>120s		
Polarity	<input checked="" type="checkbox"/>	positive	<input checked="" type="checkbox"/>	negative

Coupling ports:

Port #1: Mains leads

Coupled to: L, N, PE, L-N, L-PE, N-PE, L-N-PE

Coupling device:	<input checked="" type="checkbox"/>	CDN	<input type="checkbox"/>	Coupling clamp
Test level:	<input type="checkbox"/>	± 0.5kV	<input type="checkbox"/>	± 1kV
	<input checked="" type="checkbox"/>	± 2kV	<input type="checkbox"/>	± 4kV

Port #2: DC – Output leads

Coupled to: + / -

Coupling device:	<input type="checkbox"/>	CDN	<input checked="" type="checkbox"/>	Coupling clamp
Test level:	<input type="checkbox"/>	± 0.5kV	<input type="checkbox"/>	± 1kV
	<input checked="" type="checkbox"/>	± 2kV	<input type="checkbox"/>	± 4kV

Port #3: “DC OK” leads

Coupled to: DC OK / -


Coupling device:	<input type="checkbox"/>	CDN	<input checked="" type="checkbox"/>	Coupling clamp
Test level:	<input type="checkbox"/>	± 0.5kV	<input checked="" type="checkbox"/>	± 1kV
	<input type="checkbox"/>	± 2kV	<input type="checkbox"/>	± 4kV

All used test equipment are calibrated periodically.

Operation mode:

EUT arrangement: ☒ Tabletop ☐ Floor standing

Continuous operation at 2A load. During the test the output voltage and the “DC OK” voltage were observed.



Environmental conditions:

Temperature: 15 - 35 °C
Humidity: 30 - 60 %
Air pressure: 860 - 1060 hPa

The environmental conditions during the test: ☒ were kept
☐ were not kept


Criterion B:

After the immunity test the EUT must work as intended. During the immunity test, there is some degradation of the performance allowed, but no change of the given working mode. The output voltage must be kept in the range of $\pm 5\%$.

Test results:

Immunity: ☒ Met criterion B
☐ Met not criterion B

Remarks: xx





1.7 Surge immunity test according DIN EN 61000-4-5 (VDE 0847 Teil 4-5) / 12.2001


1.7.1 Test set up

According DIN EN 61000-4-5 (VDE 0847 Teil 4-5) / 12.2001

Test location: ☒ Shielded room ☐ Laboratory
☐ Open field ☐ _







1.7.2 Test

Regulation:

DIN EN 61000-4-5 (VDE 0847 Teil 4-5) / 12.2001

Number of surges:	<input checked="" type="checkbox"/>	5 positive	<input checked="" type="checkbox"/>	5 negative
Angle:	<input checked="" type="checkbox"/>	0 Degree	<input checked="" type="checkbox"/>	90 Degree
	<input checked="" type="checkbox"/>	270 Degree	<input type="checkbox"/>	___ Degree
Repetition rate:	<input checked="" type="checkbox"/>	1 Surge / min	<input type="checkbox"/>	___ Surge / min

Coupling ports:

Port #1: Mains leads


Type of lines: PE applied

Coupling device:	<input checked="" type="checkbox"/>	CDN	<input type="checkbox"/>	
Coupled to:	<input checked="" type="checkbox"/>	L - N	<input type="checkbox"/>	L/N - PE <input type="checkbox"/>
Test level:	<input checked="" type="checkbox"/>	± 0.5kV	<input checked="" type="checkbox"/>	± 1kV
	<input type="checkbox"/>	± 2kV	<input type="checkbox"/>	± 4kV
Source impedance:	<input checked="" type="checkbox"/>	2Ω+18μF	<input type="checkbox"/>	12Ω+9μF
	<input type="checkbox"/>	42Ω+0.1μF	<input type="checkbox"/>	42Ω+0.5μF
Coupled to:	<input checked="" type="checkbox"/>	L - PE	<input checked="" type="checkbox"/>	N - PE <input type="checkbox"/>
Test level:	<input checked="" type="checkbox"/>	± 0.5kV	<input checked="" type="checkbox"/>	± 1kV
	<input checked="" type="checkbox"/>	± 2kV	<input type="checkbox"/>	± 4kV
Source impedance:	<input type="checkbox"/>	2Ω+18μF	<input checked="" type="checkbox"/>	12Ω+9μF
	<input type="checkbox"/>	42Ω+0.1μF	<input type="checkbox"/>	42Ω+0.5μF

Port #2: DC leads

Type of lines: PE applied

Coupling device:	<input checked="" type="checkbox"/>	CDN	<input type="checkbox"/>	
Coupled to:	<input checked="" type="checkbox"/>	+ / -	<input type="checkbox"/>	
Test level:	<input checked="" type="checkbox"/>	± 0.5kV	<input type="checkbox"/>	± 1kV
	<input type="checkbox"/>	± 2kV	<input type="checkbox"/>	± 4kV
Source impedance:	<input type="checkbox"/>	2Ω+18μF	<input type="checkbox"/>	12Ω+9μF
	<input type="checkbox"/>	42Ω+0.1μF	<input checked="" type="checkbox"/>	42Ω+0.5μF
Coupled to:	<input checked="" type="checkbox"/>	+ / PE	<input checked="" type="checkbox"/>	- / PE <input type="checkbox"/>
Test level:	<input checked="" type="checkbox"/>	± 0.5kV	<input type="checkbox"/>	± 1kV
	<input type="checkbox"/>	± 2kV	<input type="checkbox"/>	± 4kV
Source impedance:	<input type="checkbox"/>	2Ω+18μF	<input type="checkbox"/>	12Ω+9μF
	<input type="checkbox"/>	42Ω+0.1μF	<input checked="" type="checkbox"/>	42Ω+0.5μF



All used test equipment are calibrated periodically.

Operation mode:

EUT arrangement: ☒ Tabletop ☐ Floor standing

Continuous operation at 2A load. During the test the output voltage and the “DC OK” voltage were observed.

Environmental conditions:

Temperature: 15 - 35 °C
Humidity: 30 - 60 %
Air pressure: 860 - 1060 hPa

The environmental conditions during the test: ☒ were kept
☐ were not kept


Criterion B:

After the immunity test the EUT must work as intended. During the immunity test, there is some degradation of the performance allowed, but no change of the given working mode. The output voltage must be kept in the range of $\pm 5\%$.

Test results:

Immunity: ☒ Met criterion B
☐ Met not criterion B

Remarks: The “DC OK” leads were not tested, it is supposed that they are shorter than 30m.




1.8 Immunity to conducted disturbances, induced by radio-frequency fields according DIN EN 61000-4-6 (VDE 0847 Teil 4-6) / 12.2001

1.8.1 Test set up

According DIN EN 61000-4-6 (VDE 0847 Teil 4-6) / 12.2001

Test location: ☒ Shielded room ☐ Laboratory
☐ Open field ☐ _

☒ The test equipment was checked and complied to the requirements.



1.8.2 Test

Regulation:

DIN EN 61000-4-6 (VDE 0847 Teil 4-6) / 12.2001

Frequency range:	<input checked="" type="checkbox"/>	150kHz - 80MHz	<input type="checkbox"/>	150kHz - 230MHz
Test level:	<input type="checkbox"/>	1V	<input type="checkbox"/>	3V
	<input checked="" type="checkbox"/>	10V	<input type="checkbox"/>	__V
Modulation	<input checked="" type="checkbox"/>	AM: 80%		
	<input checked="" type="checkbox"/>	AF: 1000Hz		
	<input type="checkbox"/>	not modulated		
Frequency step:	<input checked="" type="checkbox"/>	1% of the preceding frequency		
Sweep rate:	<input checked="" type="checkbox"/>	0.0015 Decades/s	<input type="checkbox"/>	__ Decades/s


Coupling ports:

Port #1: Mains leads

Type of line:	<input checked="" type="checkbox"/>	unshielded	<input type="checkbox"/>	shielded
Signal type:	<input checked="" type="checkbox"/>	analogous	<input type="checkbox"/>	digital
Status of lines:	<input checked="" type="checkbox"/>	active	<input type="checkbox"/>	passive
Cable length EUT –CDN:		20cm		
Coupling device network:	<input type="checkbox"/>	CDN-AF2	<input checked="" type="checkbox"/>	CDN-M3
	<input type="checkbox"/>	CDN-M5	<input type="checkbox"/>	CDN-S9
Clamp:	<input type="checkbox"/>	F-120-2		

Port #2: DC-leads

Type of line:	<input checked="" type="checkbox"/>	unshielded	<input type="checkbox"/>	shielded
Signal type:	<input checked="" type="checkbox"/>	analogous	<input type="checkbox"/>	digital
Status of lines:	<input checked="" type="checkbox"/>	active	<input type="checkbox"/>	passive
Cable length EUT –CDN:		20cm		
Coupling device network:	<input checked="" type="checkbox"/>	CDN-AF2	<input type="checkbox"/>	CDN-M3
	<input type="checkbox"/>	CDN-M5	<input type="checkbox"/>	CDN-S9
Clamp:	<input type="checkbox"/>	F-120-2		



Port #3: “DC OK” leads

Type of line: ☒ unshielded
 Signal type: ☒ analogous
 Status of lines: ☒ active
 Cable length EUT –CDN: 20cm
 Coupling device network: ☒ CDN-AF2
 ☐ CDN-M5
 Clamp: ☐ F-120-2

☐ shielded
☐ digital
☐ passive

☐ CDN-M3
☐ CDN-S9

All used test equipment are calibrated periodically.

Operation mode:

EUT arrangement: ☒ Tabletop ☐ Floor standing

Continuous operation at 2A load. During the test the output voltage and the DC OK voltage were observed.

Coupling- / Decoupling- Network	CDN-AF2 Inv. Nr. 033	CDN-AF2 Inv. Nr. 034	CDN-M3 Inv. Nr. 026	CDN-M5 Inv. Nr. 036	CDN-S1 Inv. Nr. 037	CDN-S9 Inv. Nr. 030	CDN-S9 Inv. Nr. 031	CDN-F-120-2 Inv. Nr. 025
Port								
#1	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
#2	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
#3	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

Environmental conditions:

Temperature: 15 - 35 °C
 Humidity: 30 - 60 %
 Air pressure: 860 - 1060 hPa

The environmental conditions during the test: ☒ were kept
 ☐ were not kept



Criterion A:

During the immunity test the EUT must work as intended. There is no degradation of the performance allowed and no change of the given working mode. The output voltage must be kept in the range of $\pm 2\%$.

Immunity:




Met criterion A



Met not criterion A


| Remarks:

xx



1.9 Immunity against low frequency magnetic fields according DIN EN 61000-4-8 (VDE 0847 Teil 4-8) / 12.2001

Not tested, there are no parts inside which are sensitive to low frequency magnetic fields.



1.10.2 Test

Regulation:

DIN EN 61000-4-11 (VDE 0847 Teil 4-11) / 12.2001

Nominal mains voltage UN: ☒ 230V ☐ V
 Nominal mains frequency: f: ☒ 50Hz ☐ Hz

All used test equipment are calibrated periodically.

Name:	Mr. Hauser	Serial no:	xx
Department:	EMC Testing	Operating modes:	Max. load 4A
Company:	EMCE GmbH	Comment1:	EUT ID / PR343_06
Test report no:	xx	Comment2:	230V/50Hz
Device:	SMPS	Comment3:	--
Specimen:	xx	Comment4:	--
Manufacturer:	Convertec Ltd	Date:	29.10.2003
Type:	TCL 060-112C	Test date:	21.10.2003

Test conditions: EN 61000-4-11 voltage dips, short interruptions and variations test
 Voltage / frequency: 230.0 V / 50.0 Hz
 Test phase: 1
 Executed test: Dip example 1: Total drop out
 Test description: Total drop out, time increasing from 1 period up to 100 periods
 Disturbances per step: 3 (per phase angle) / 10.5 sec delay between

Step	Disturbance	TestLevel	Duration	Phase angle(s) (Ref.Ph.1)
1	Voltage dip / short interruption	70 %	0.5 periods	0°
2	Voltage dip / short interruption	40 %	5 periods	0°
3	Voltage dip / short interruption	40 %	50 periods	0°
4	Voltage dip / short interruption	0 %	250 periods	0°


Operation mode:

EUT arrangement: ☒ Tabletop ☐ Floor standing

Continuous operation at 4A load. During the test the output voltage and the “DC OK” voltage were observed.

Environmental conditions:

Temperature: 15 - 35 °C
 Humidity: 30 - 60 %
 Air pressure: 860 - 1060 hPa



The environmental conditions during the test:

☒
☐

were kept
were not kept

Criterion B:

After the immunity test the EUT must work as intended. During the immunity test, there is some degradation of the performance allowed, but no change of the given working mode. The output voltage must be kept in the range of $\pm 5\%$.

Test results - Step #1:

Immunity:

☒
☐

Met criterion B
Met not criterion B

Remarks: xx

Criterion C:

A function degradation is allowed, but not a permanent failure.


Test results – Step #2, #3, #4:

Immunity:

☒
☐


Met criterion C
Met not criterion C

Remarks: xx



2 Summary

Regulation	Class / Test level	Result	Remark(s)
DIN EN 55011 VDE 0875 Teil 11 / 05.2000			
Conducted emission [0.15-30MHz]	B	Limits kept	
Radiated emission [30-1000MHz]	B	Limits kept	
DIN EN 61000-3-2 VDE 0838 Teil 2 / 12.2001			
Harmonic current emissions	A	Limits kept	
DIN EN 61000-3-3 VDE 0838 Teil 3/ 05.2002			
Flicker, Voltage fluctuations	Manual switching	Limits kept	
DIN EN 61000-4-2 VDE 0847 Teil 4-2/ 12.2001			
Electrostatic discharge			
- Air discharge	±2/4/8kV	Met criterion B	
- Contact discharge	±2/4kV	Met criterion B	
DIN EN 61000-4-3 VDE 0847 Teil 4-3/ 12.2001			
Radiated, radio-frequency, electromagnetic field [80 – 1000MHz]	10V/m	Met criterion A	
DIN EN 61000-4-4 VDE 0847 Teil 4-4 / 12.2001			
Electrical fast transient / burst			
- AC-Supply I / O	±2kV	Met criterion B	
- DC I / O	±2kV	Met criterion B	
- Signal-, Data-, Control I/O	±1kV	Met criterion B	
DIN EN 61000-4-5 VDE 0847 Teil 4-5 / 12.2001			
Surge			
- AC-Supply I / O	±1kV L – N ±2kV L – PE ±2kV N – PE	Met criterion B Met criterion B Met criterion B	
- DC I / O	±0.5kV + - Gnd ±0.5kV + - PE ±0.5kV Gnd - PE	Met criterion B Met criterion B Met criterion B	




Regulation	Class / Test level	Result	Remark(s)
DIN EN 61000-4-6 VDE 0847 Teil 4-6 / 12.2001			
Conducted disturbances, induced by radio-frequency fields [0.15 – 80MHz]			
- AC-Supply I / O	10V	Met criterion A	
- DC I / O	10V	Met criterion A	
- Signal-, Data-, Control I/O	10V	Met criterion A	
DIN EN 61000-4-8 VDE 0847 Teil 4-8 / 12.2001			
Low frequency magnetic fields			n. r.
DIN EN 61000-4-11 VDE 0847 Teil 4-11 / 12.2001			
Voltage dips, short interruptions and voltage variations			
- AC-Supply I / O	Step #1 Step #2,#3,#4	Met criterion B Met criterion C	

Burgrieden, 11/05/2003



Responsible Tester – Peter Hauser



Principal engineer - Christian Vogelmann