

## CE EMC Test Report

**Report No.:** CE190823C26

**Test Model:** TMDC 06-7211H, TMDC 06-7218H, TMDC 06-7222H, TMDC 06-7225H

**Series Model:** TMDC 06-7211H-B1, TMDC 06-7211H, TMDC 06-7212H, TMDC 06-7213H,  
TMDC 06-7215H, TMDC 06-7218H, TMDC 06-7222H, TMDC 06-7223H,  
TMDC 06-7225H

**Received Date:** Sep. 7, 2018

**Test Date:** Sep. 11 to 18, 2018

**Issued Date:** Aug. 27, 2019

**Applicant:** TRACO ELECTRONIC AG

**Address:** SIHLBRUGGSTRASSE 111 CH-6340 BAAR, SWITZERLAND

**Issued By:** Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch  
Lin Kou Laboratories

**Lab Address:** No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan

**Test Location (1):** No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan

**Test Location (2):** No. 49, Ln. 206, Wende Rd., Shangshan Tsuen, Chiung Lin Hsiang, Hsin  
Chu Hsien 307, Taiwan



This report is for your exclusive use. Any copying or replication of this report to or for any other person or entity, or use of our name or trademark, is permitted only with our prior written permission. This report sets forth our findings solely with respect to the test samples identified herein. The results set forth in this report are not indicative or representative of the quality or characteristics of the lot from which a test sample was taken or any similar or identical product unless specifically and expressly noted. Our report includes all of the tests requested by you and the results thereof based upon the information that you provided to us. You have 60 days from date of issuance of this report to notify us of any material error or omission caused by our negligence, provided, however, that such notice shall be in writing and shall specifically address the issue you wish to raise. A failure to raise such issue within the prescribed time shall constitute your unqualified acceptance of the completeness of this report, the tests conducted and the correctness of the report contents. Unless specific mention, the uncertainty of measurement has been explicitly taken into account to declare the compliance or non-compliance to the specification. The report must not be used by the client to claim product certification, approval, or endorsement by TAF or any government agencies.

## Table of Contents

|  |           |
|--|-----------|
| <b>Release Control Record</b> .....  | <b>4</b>  |
| <b>1 Certificate of Conformity</b> .....   | <b>5</b>  |
| <b>2 Summary of Test Results</b> .....   | <b>6</b>  |
| 2.1 Measurement Uncertainty .....  | 8         |
| 2.2 Modification Record.....   | 8         |
| <b>3 General Information</b> .....   | <b>9</b>  |
| 3.1 Description of EUT .....   | 9         |
| 3.2 Features of EUT .....  | 9         |
| 3.3 Operating Modes of EUT and Determination of Worst Case Operating Mode .....    | 10        |
| 3.4 Test Program Used and Operation Descriptions.....                              | 10        |
| 3.5 Primary Clock Frequencies of Internal Source .....                             | 10        |
| 3.6 Package Specifications by Manufacturer .....                                   | 11        |
| <b>4 Configuration and Connections with EUT</b> .....                              | <b>12</b> |
| 4.1 Connection Diagram of EUT and Peripheral Devices.....                          | 12        |
| 4.2 Configuration of Peripheral Devices and Cable Connections .....                | 13        |
| <b>5 Conducted Emission from the Mains Power Port</b> .....                        | <b>14</b> |
| 5.1 Limits .....   | 14        |
| 5.2 Test Instruments .....   | 14        |
| 5.3 Test Arrangement .....   | 15        |
| 5.4 Test Results .....   | 16        |
| <b>6 Radiated Emission at Frequencies up to 1GHz</b> .....                         | <b>24</b> |
| 6.1 Limits .....   | 24        |
| 6.2 Test Instruments .....   | 25        |
| 6.3 Test Arrangement .....   | 26        |
| 6.4 Test Results .....   | 27        |
| <b>7 General Immunity Requirements</b> .....                                       | <b>35</b> |
| 7.1 Specific Immunity Requirements by Manufacturer.....                            | 37        |
| 7.2 Performance Criteria .....   | 37        |
| <b>8 Electrostatic Discharge Immunity Test (ESD)</b> .....                         | <b>38</b> |
| 8.1 Test Specification.....  | 38        |
| 8.2 Test Instruments .....   | 38        |
| 8.3 Test Arrangement .....   | 39        |
| 8.4 Supplementary Information .....  | 40        |
| 8.5 Test Results .....   | 40        |
| <b>9 Radiated, Radio-frequency, Electromagnetic Field Immunity Test (RS)</b> ..... | <b>42</b> |
| 9.1 Test Specification.....  | 42        |
| 9.2 Test Instruments .....   | 42        |
| 9.3 Test Arrangement .....   | 43        |
| 9.4 Supplementary Information .....  | 43        |
| 9.5 Test Results .....   | 44        |
| <b>10 Electrical Fast Transient/Burst Immunity Test (EFT)</b> .....                | <b>45</b> |
| 10.1 Test Specification.....   | 45        |
| 10.2 Test Instruments .....  | 45        |
| 10.3 Test Arrangement .....  | 46        |
| 10.4 Supplementary Information .....   | 46        |
| 10.5 Test Results .....  | 46        |

|           |  |           |
|-----------|--|-----------|
| <b>11</b> | <b>Surge Immunity Test.....</b>  | <b>47</b> |
| 11.1      | Test Specification.....  | 47        |
| 11.2      | Test Instruments .....   | 47        |
| 11.3      | Test Arrangement .....   | 48        |
| 11.4      | Supplementary Information .....  | 49        |
| 11.5      | Test Results .....   | 49        |
| <b>12</b> | <b>Immunity to Conducted Disturbances Induced by RF Fields (CS).....</b> | <b>50</b> |
| 12.1      | Test Specification.....  | 50        |
| 12.2      | Test Instruments .....   | 50        |
| 12.3      | Test Arrangement .....   | 51        |
| 12.4      | Supplementary Information .....  | 52        |
| 12.5      | Test Results .....   | 52        |
| <b>13</b> | <b>Power Frequency Magnetic Field Immunity Test.....</b>                 | <b>53</b> |
| 13.1      | Test Specification.....  | 53        |
| 13.2      | Test Instruments .....   | 53        |
| 13.3      | Test Arrangement .....   | 54        |
| 13.4      | Supplementary Information .....  | 54        |
| 13.5      | Test Results .....   | 55        |
| <b>14</b> | <b>Pictures of Test Arrangements .....</b>                               | <b>56</b> |
| 14.1      | Conducted Emission from the Mains Power Port .....                       | 56        |
| 14.2      | Radiated Emission at Frequencies up to 1GHz .....                        | 60        |
| 14.3      | Electrostatic Discharge Immunity Test (ESD) .....                        | 63        |
| 14.4      | Radio-frequency, Electromagnetic Field Immunity Test (RS).....           | 64        |
| 14.5      | Electrical Fast Transient/Burst Immunity Test (EFT).....                 | 65        |
| 14.6      | Surge Immunity Test.....   | 65        |
| 14.7      | Conducted Disturbances Induced by RF Fields (CS) .....                   | 66        |
| 14.8      | Power Frequency Magnetic Field Immunity Test (PFMF) .....                | 67        |
|           | <b>Appendix – Information of the Testing Laboratories .....</b>          | <b>68</b> |

### Release Control Record

| Issue No.   | Description       | Date Issued   |
|-------------|-------------------|---------------|
| CE190823C26 | Original release. | Aug. 27, 2019 |

## 1 Certificate of Conformity

**Product:** DC to DC Converter

**Brand:**



**Test Model:** TMDC 06-7211H, TMDC 06-7218H, TMDC 06-7222H, TMDC 06-7225H

**Series Model:** TMDC 06-7211H-B1, TMDC 06-7211H, TMDC 06-7212H, TMDC 06-7213H,  
TMDC 06-7215H, TMDC 06-7218H, TMDC 06-7222H, TMDC 06-7223H,  
TMDC 06-7225H

**Sample Status:** Engineering sample

**Applicant:** TRACO ELECTRONIC AG

**Test Date:** Sep. 11 to 18, 2018

**Standards:** **EN 55032:2015 +AC:2016, Class A**

**EN 61000-3-2:2014 (Not applicable)**

**EN 61000-3-3:2013 (Not applicable)**

**EN 55035:2017**

EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0

EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2

EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0

EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0

EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0

EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0

EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0 (Not applicable)

Broadband impulse noise disturbances (Not applicable)

**EN 55024:2010 / EN 55024:2010 +A1:2015**

EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0

EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2

EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0

EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0

EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0

EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0

EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0 (Not applicable)

The above equipment has been tested by **Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch**, and found compliance with the requirement of the above standards. The test record, data evaluation & Equipment Under Test (EUT) configurations represented herein are true and accurate accounts of the measurements of the sample's EMC characteristics under the conditions specified in this report.

**Prepared by :**




**Date:**

Aug. 27, 2019

Sandra Lin / Specialist

**Approved by :**



**Date:**

Aug. 27, 2019

Kenny Meng / Assistant Manager

## 2 Summary of Test Results

| Emission               |   |   |         |
|------------------------|---|---|---------|
| Standard               | Test Item   | Result/Remarks  | Verdict |
| EN 55032:2015 +AC:2016 | Conducted emission from the mains power port                                  | Minimum passing Class A margin is -3.08 dB at 7.16223 MHz | Pass    |
|                        | Asymmetric mode conducted emission at telecommunication ports and tuner ports | Without telecom port of the EUT.                          | N/A     |
|                        | Radiated emission 30-1000 MHz   | Minimum passing Class A margin is -3.06 dB at 51.02 MHz   | Pass    |
|                        | Radiated emission above 1GHz  | EUT's highest frequency is below 108MHz                   | N/A     |
|                        | Conducted differential voltage emissions                                      | Without tuner function of the EUT.                        | N/A     |
| EN 61000-3-2:2014      | Harmonic current emissions  | Test not applicable because port does not exist.          | N/A     |
| EN 61000-3-3:2013      | Voltage fluctuations and flicker  | Test not applicable because port does not exist.          | N/A     |

| EN 55035, Immunity |  |  |  |         |
|--------------------|--|--|--|---------|
| EN 55035 Clause    | Basic standard   | Test Item  | Result/Remarks                                   | Verdict |
| 4.2.1              | EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0                     | Electrostatic discharges (ESD)   | Performance Criterion A                          | Pass    |
| 4.2.2.2            | EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2   | Continuous radiated disturbances (RS)  | Performance Criterion A                          | Pass    |
| 4.2.4              | EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0                     | Electrical fast transients (EFT)   | Performance Criterion A                          | Pass    |
| 4.2.5              | EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0   | Surges   | Performance Criterion A                          | Pass    |
| 4.2.2.3            | EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0            | Continuous conducted disturbances (CS)   | Performance Criterion A                          | Pass    |
| 4.2.3              | EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0                     | Power-frequency magnetic fields (PFMF)   | Performance Criterion A                          | Pass    |
| 4.2.6              | EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0 | Voltage dips and interruptions   | Test not applicable because port does not exist. | N/A     |
| 4.2.7              | -  | Broadband impulse noise disturbances, <b>Repetitive</b> (Applicable only to xDSL ports.) | Without CPE xDSL port of the EUT.                | N/A     |

| EN 55035, Immunity |                |   |                                   |         |
|--------------------|----------------|---|-----------------------------------|---------|
| EN 55035 Clause    | Basic standard | Test Item   | Result/Remarks                    | Verdict |
| 4.2.7              | -              | Broadband impulse noise disturbances, <b>Isolated</b><br>(Applicable only to xDSL ports.) | Without CPE xDSL port of the EUT. | N/A     |

| EN 55024, Immunity |  |  |   |         |
|--------------------|--|--|---|---------|
| EN 55024 Clause    | Basic standard   | Test Item                              | Result/Remarks  | Verdict |
| 4.2.1              | EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0                     | Electrostatic discharges (ESD)         | Performance Criterion A                                   | Pass    |
| 4.2.3.2            | EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2   | Continuous radiated disturbances (RS)  | Performance Criterion A                                   | Pass    |
| 4.2.2              | EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0                     | Electrical fast transients (EFT)       | Performance Criterion A                                   | Pass    |
| 4.2.5              | EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0   | Surges                                 | Performance Criterion A                                   | Pass    |
| 4.2.3.3            | EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0            | Continuous conducted disturbances (CS) | Performance Criterion A                                   | Pass    |
| 4.2.4              | EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0                     | Power-frequency magnetic fields (PFMF) | Performance Criterion A                                   | Pass    |
| 4.2.6              | EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0 | Voltage dips and interruptions         | Test not applicable because AC power port does not exist. | N/A     |

**Note:**

1. There is no deviation to the applied test methods and requirements covered by the scope of this report.
2. Determining compliance based on the results of the compliance measurement, not taking into account measurement instrumentation uncertainty.
3. The above EN/IEC basic standards are applied with latest version if customer has no special requirement.
4. N/A: Not Applicable.

## 2.1 Measurement Uncertainty

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT as specified in CISPR 16-4-2:

| Measurement  | Expanded Uncertainty<br>(k=2) ( $\pm$ ) | Maximum allowable<br>uncertainty ( $\pm$ ) |
|--|---|--|
| Conducted emission from AC mains power port using AMN,<br>150kHz ~ 30MHz | 2.79 dB                                 | 3.4 dB ( $U_{\text{CISPR}}$ )              |
| Radiated emission, 30MHz ~ 1GHz  | 3.72 dB                                 | 6.3 dB ( $U_{\text{CISPR}}$ )              |

The other instruments specified are routine verified to remain within the calibrated levels, no measurement uncertainty is required to be calculated.


## 2.2 Modification Record

There were no modifications required for compliance.



### 3 General Information

#### 3.1 Description of EUT

|                     |  |
|---------------------|--|
| Product             | DC to DC Converter   |
| Brand               |   |
| Test Model          | TMDC 06-7211H, TMDC 06-7218H, TMDC 06-7222H, TMDC 06-7225H   |
| Series Model        | TMDC 06-7211H-B1, TMDC 06-7211H, TMDC 06-7212H, TMDC 06-7213H, TMDC 06-7215H, TMDC 06-7218H, TMDC 06-7222H, TMDC 06-7223H, TMDC 06-7225H |
| Model Difference    | Refer to note as below   |
| Operating Software  | N/A  |
| Sample Status       | Engineering sample   |
| Power Supply Rating | Refer to note as below   |
| Accessory Device    | N/A  |
| Data Cable Supplied | N/A  |

Note:

1. This report is issued as a duplicate report of BV CPS report no.: CE180907D03B. The difference compared with original report are changing applicant, brand and models for marketing purpose; therefore all test data was copied from the original test report.
2. The EUT is a DC to DC Converter; the specifications of standard models were listed as below:

| Model Number     | Input Voltage (Range) | Output Voltage |
|------------------|-----------------------|----------------|
| Standard         | VDC                   | VDC            |
| TMDC 06-7211H-B1 | 110<br>(80 ~ 160)     | 5              |
| TMDC 06-7211H    |                       | 5.1            |
| TMDC 06-7212H    |                       | 12             |
| TMDC 06-7213H    |                       | 15             |
| TMDC 06-7215H    |                       | 24             |
| TMDC 06-7218H    |                       | 48             |
| TMDC 06-7222H    |                       | ±12            |
| TMDC 06-7223H,   |                       | ±15            |
| TMDC 06-7225H    |                       | ±24            |

During the test, the Model No.: **TMDC 06-7211H, TMDC 06-7218H, TMDC 06-7222H, TMDC 06-7225H** were selected as the representative one for the test and therefore only its test data were recorded in this report.

#### 3.2 Features of EUT

The tests reported herein were performed according to the method specified by TRACO ELECTRONIC AG, for detailed feature description, please refer to the manufacturer's specifications or user's manual.

### 3.3 Operating Modes of EUT and Determination of Worst Case Operating Mode

1. The EUT was pre-tested under operating and standby condition and the worst emission level was found under **operating condition**.
2. As client's requirement, test modes are presented in the report as below.

| Mode   | Model No.     | Test Condition | Input power |
|--|---------------|----------------|-------------|
| Conducted emission test & Radiated emission test |               |                |             |
| 1  | TMDC 06-7211H | Full Load      | 110Vdc      |
| 2  | TMDC 06-7218H |                |             |
| 3  | TMDC 06-7222H |                |             |
| 4  | TMDC 06-7225H |                |             |
| Immunity tests                                   |               |                |             |
| 1  | TMDC 06-7211H | Full Load      | 110Vdc      |
| EFT, Surge tests                                 |               |                |             |
| 2  | TMDC 06-7218H | Full Load      | 110Vdc      |
| 3  | TMDC 06-7222H |                |             |
| 4  | TMDC 06-7225H |                |             |

### 3.4 Test Program Used and Operation Descriptions

#### ◆ For Conducted & Radiated tests:

Set the EUT full load.

#### ◆ For Immunity tests:


Connected a resistor load to DC output port of EUT to make EUT have maximum power consumption and a multimeter was used to monitor voltage of output.

### 3.5 Primary Clock Frequencies of Internal Source

The highest frequency generated or used within the EUT or on which the EUT operates or tunes is 280kHz, provided by TRACO ELECTRONIC AG, for detailed internal source, please refer to the manufacturer's specifications.

### 3.6 Package Specifications by Manufacturer

#### Package Specifications :




#### Physical Characteristics

|               |  |
|---------------|--|
| Case Size     | : 53.0x34.0x26.5mm (2.09x1.34x1.04 inches)       |
| Case Material | : Plastic resin (flammability to UL 94V-0 rated) |
| Weight        | : 47.8 g   |


## 4 Configuration and Connections with EUT

### 4.1 Connection Diagram of EUT and Peripheral Devices

Emission tests:



Immunity tests:



## 4.2 Configuration of Peripheral Devices and Cable Connections

### Emission tests:

| ID | Product         | Brand  | Model No.   | Serial No.   | FCC ID | Remarks            |
|----|-----------------|--------|-------------|--------------|--------|--------------------|
| A. | DUMMY LOAD      | N/A    | N/A         | N/A          | N/A    | Supplied by client |
| B. | Power supply_DC | CHROMA | 62150H-600S | 62150EC00479 | N/A    | Provided by Lab    |

| ID | Descriptions   | Qty. | Length (m) | Shielding (Yes/No) | Cores (Qty.) | Remarks         |
|----|----------------|------|------------|--------------------|--------------|-----------------|
| 1. | DC power cable | 1    | 1.0        | N                  | 0            | Provided by Lab |
| 2. | DC power cable | 1    | 10         | N                  | 0            | Provided by Lab |

Note: The core(s) is(are) originally attached to the cable(s).

### Immunity tests:

| ID | Product         | Brand  | Model No.   | Serial No.   | FCC ID | Remarks            |
|----|-----------------|--------|-------------|--------------|--------|--------------------|
| A. | DUMMY LOAD      | N/A    | N/A         | N/A          | N/A    | Supplied by client |
| B. | Power supply_DC | CHROMA | 62150H-600S | 62150EC00479 | N/A    | Provided by Lab    |
| C. | Multimeter      | YFE    | YF-370A     | N/A          | N/A    | Provided by Lab    |

Note: All power cords of the above support units are non-shielded (1.8m).

| ID | Descriptions   | Qty. | Length (m) | Shielding (Yes/No) | Cores (Qty.) | Remarks         |
|----|----------------|------|------------|--------------------|--------------|-----------------|
| 1. | DC power cable | 1    | 0.5        | N                  | 0            | Provided by Lab |
| 2. | DC power cable | 1    | 3.0        | N                  | 0            | Provided by Lab |
| 3. | Data cable     | 1    | 0.3        | N                  | 0            | Provided by Lab |

Note: The core(s) is(are) originally attached to the cable(s).

## 5 Conducted Emission from the Mains Power Port

### 5.1 Limits

| Frequency range (MHz) | Coupling device | Detector type / bandwidth | Class A limits (dBuV) |
|-----------------------|-----------------|---------------------------|-----------------------|
| 0.15 - 0.5            | AMN             | Quasi-peak / 9kHz         | 79                    |
| 0.5 - 30.0            |                 |                           | 73                    |
| 0.15 - 0.5            |                 | Average / 9kHz            | 66                    |
| 0.5 - 30.0            |                 |                           | 60                    |

| Frequency range (MHz) | Coupling device | Detector type / bandwidth | Class B limits (dBuV) |
|-----------------------|-----------------|---------------------------|-----------------------|
| 0.15 - 0.5            | AMN             | Quasi-peak / 9kHz         | 66 - 56               |
| 0.5 - 5               |                 |                           | 56                    |
| 5 - 30.0              |                 |                           | 60                    |
| 0.15 - 0.5            |                 | Average / 9kHz            | 56 - 46               |
| 0.5 - 5               |                 |                           | 46                    |
| 5 - 30.0              |                 |                           | 50                    |

### 5.2 Test Instruments


| Description & Manufacturer                                 | Model No.     | Serial No.   | Cal. Date     | Cal. Due      |
|--|---------------|--------------|---------------|---------------|
| ROHDE & SCHWARZ TEST RECEIVER                              | ESR3          | 102414       | Feb. 7, 2018  | Feb. 6, 2019  |
| ROHDE & SCHWARZ Artificial Mains Network (for EUT)         | ENV216        | 101197       | May 23, 2018  | May 22, 2019  |
| LISN With Adapter (for EUT)                                | AD10          | C10Ada-002   | May 23, 2018  | May 22, 2019  |
| ROHDE & SCHWARZ Artificial Mains Network (for peripherals) | ESH3-Z5       | 100218       | Nov. 23, 2017 | Nov. 22, 2018 |
| SCHWARZBECK Artificial Mains Network (For EUT)             | NNLK8129      | 8129229      | May 3, 2018   | May 2, 2019   |
| SCHWARZBECK Artificial Mains Network (For EUT)             | NNLK 8121     | 8121-808     | Mar. 5, 2018  | Mar. 4, 2019  |
| Software   | Cond_V7.3.7.4 | NA           | NA            | NA            |
| RF cable (JYEBAO) With 10dB PAD                            | 5D-FB         | Cable-C10.01 | Feb. 14, 2018 | Feb. 13, 2019 |
| SUHNTER Terminator (For ROHDE & SCHWARZ LISN)              | 65BNC-5001    | E1-011484    | May 8, 2018   | May 7, 2019   |
| ROHDE & SCHWARZ Artificial Mains Network (For TV EUT)      | ESH3-Z5       | 100220       | Nov. 14, 2017 | Nov. 13, 2018 |
| LISN With Adapter (for TV EUT)                             | 100220        | N/A          | Nov. 14, 2017 | Nov. 13, 2018 |

Notes: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
2. The test was performed in Shielded Room No. 10.  
3. The VCCI Site Registration No. C-1852.  
4. Tested Date: Sep. 11, 2018

### 5.3 Test Arrangement

- The EUT was placed 0.4 meters from the conducting wall of the shielded room with EUT being connected to the power mains through an Artificial Mains Network (AMN). Other support units were connected to the power mains through another AMN. The two AMNs provide 50 Ohm/ 50uH of coupling impedance for the measuring instrument.
- Both lines of the power mains connected to the EUT were checked for maximum conducted interference.
- The test results of conducted emissions at mains ports are recorded of six worst margins for quasi-peak (mandatory) [and average (if necessary)] values against the limits at frequencies of interest unless the margin is 20 dB or greater.

Note: The resolution bandwidth and video bandwidth of test receiver is 9kHz for quasi-peak detection (QP) and average detection (AV) at frequency 0.15MHz-30MHz.



- Note:**
1. Support units were connected to second AMN.
  2. The distance specified between EUT/AE and other metallic objects is  $\geq 0.8$  m in the measurement arrangement for table-top EUT.
  3. Cable on the RGP must to be insulated.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


## 5.4 Test Results

|                 |                |                               |                                      |
|-----------------|----------------|-------------------------------|--------------------------------------|
| Frequency Range | 150kHz ~ 30MHz | Detector Function & Bandwidth | Quasi-Peak (QP) / Average (AV), 9kHz |
| Input Power     | 110Vdc         | Environmental Conditions      | 23°C, 70%RH, 999mbar                 |
| Tested by       | Vic Lin        |                               |                                      |
| Test Mode       | Mode 1         |                               |                                      |

| Phase Of Power : Positive (+) |                 |                        |                      |       |                       |       |              |       |             |        |
|-------------------------------|-----------------|------------------------|----------------------|-------|-----------------------|-------|--------------|-------|-------------|--------|
| No                            | Frequency (MHz) | Correction Factor (dB) | Reading Value (dBuV) |       | Emission Level (dBuV) |       | Limit (dBuV) |       | Margin (dB) |        |
|                               |                 |                        | Q.P.                 | AV.   | Q.P.                  | AV.   | Q.P.         | AV.   | Q.P.        | AV.    |
| 1                             | 0.16173         | 9.98                   | 41.08                | 41.02 | 51.06                 | 51.00 | 79.00        | 66.00 | -27.94      | -15.00 |
| 2                             | 0.49408         | 10.02                  | 42.18                | 42.03 | 52.20                 | 52.05 | 79.00        | 66.00 | -26.80      | -13.95 |
| 3                             | 1.23508         | 10.04                  | 41.82                | 41.77 | 51.86                 | 51.81 | 73.00        | 60.00 | -21.14      | -8.19  |
| 4                             | 1.97407         | 10.09                  | 40.82                | 40.78 | 50.91                 | 50.87 | 73.00        | 60.00 | -22.09      | -9.13  |
| 5                             | 7.16223         | 10.20                  | 46.84                | 46.71 | 57.04                 | 56.91 | 73.00        | 60.00 | -15.96      | -3.09  |
| 6                             | 7.90513         | 10.22                  | 46.77                | 46.60 | 56.99                 | 56.82 | 73.00        | 60.00 | -16.01      | -3.18  |

### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value






|                 |                |                               |                                      |
|-----------------|----------------|-------------------------------|--------------------------------------|
| Frequency Range | 150kHz ~ 30MHz | Detector Function & Bandwidth | Quasi-Peak (QP) / Average (AV), 9kHz |
| Input Power     | 110Vdc         | Environmental Conditions      | 23°C, 70%RH, 999mbar                 |
| Tested by       | Vic Lin        |                               |                                      |
| Test Mode       | Mode 1         |                               |                                      |

| Phase Of Power : Negative (-) |                 |                        |                      |       |                       |       |              |       |             |        |
|-------------------------------|-----------------|------------------------|----------------------|-------|-----------------------|-------|--------------|-------|-------------|--------|
| No                            | Frequency (MHz) | Correction Factor (dB) | Reading Value (dBuV) |       | Emission Level (dBuV) |       | Limit (dBuV) |       | Margin (dB) |        |
|                               |                 |                        | Q.P.                 | AV.   | Q.P.                  | AV.   | Q.P.         | AV.   | Q.P.        | AV.    |
| 1                             | 0.16173         | 9.98                   | 41.28                | 41.09 | 51.26                 | 51.07 | 79.00        | 66.00 | -27.74      | -14.93 |
| 2                             | 0.49408         | 10.04                  | 42.11                | 41.93 | 52.15                 | 51.97 | 79.00        | 66.00 | -26.85      | -14.03 |
| 3                             | 0.98875         | 10.05                  | 41.91                | 41.89 | 51.96                 | 51.94 | 73.00        | 60.00 | -21.04      | -8.06  |
| 4                             | 1.72774         | 10.09                  | 41.26                | 41.22 | 51.35                 | 51.31 | 73.00        | 60.00 | -21.65      | -8.69  |
| 5                             | 7.16223         | 10.23                  | 46.74                | 46.69 | 56.97                 | 56.92 | 73.00        | 60.00 | -16.03      | -3.08  |
| 6                             | 7.90122         | 10.25                  | 45.80                | 44.89 | 56.05                 | 55.14 | 73.00        | 60.00 | -16.95      | -4.86  |

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




|                 |                |                               |                                      |
|-----------------|----------------|-------------------------------|--------------------------------------|
| Frequency Range | 150kHz ~ 30MHz | Detector Function & Bandwidth | Quasi-Peak (QP) / Average (AV), 9kHz |
| Input Power     | 110Vdc         | Environmental Conditions      | 23°C, 70%RH, 999mbar                 |
| Tested by       | Vic Lin        |                               |                                      |
| Test Mode       | Mode 2         |                               |                                      |

| Phase Of Power : Positive (+) |                 |                        |                      |       |                       |       |              |       |             |        |
|-------------------------------|-----------------|------------------------|----------------------|-------|-----------------------|-------|--------------|-------|-------------|--------|
| No                            | Frequency (MHz) | Correction Factor (dB) | Reading Value (dBuV) |       | Emission Level (dBuV) |       | Limit (dBuV) |       | Margin (dB) |        |
|                               |                 |                        | Q.P.                 | AV.   | Q.P.                  | AV.   | Q.P.         | AV.   | Q.P.        | AV.    |
| 1                             | 0.24920         | 10.00                  | 42.49                | 42.47 | 52.49                 | 52.47 | 79.00        | 66.00 | -26.51      | -13.53 |
| 2                             | 0.49841         | 10.02                  | 39.35                | 39.08 | 49.37                 | 49.10 | 79.00        | 66.00 | -29.63      | -16.90 |
| 3                             | 0.75024         | 10.03                  | 39.55                | 39.51 | 49.58                 | 49.54 | 73.00        | 60.00 | -23.42      | -10.46 |
| 4                             | 1.00048         | 10.03                  | 43.45                | 43.42 | 53.48                 | 53.45 | 73.00        | 60.00 | -19.52      | -6.55  |
| 5                             | 1.50096         | 10.06                  | 42.61                | 42.59 | 52.67                 | 52.65 | 73.00        | 60.00 | -20.33      | -7.35  |
| 6                             | 4.74626         | 10.14                  | 44.27                | 44.11 | 54.41                 | 54.25 | 73.00        | 60.00 | -18.59      | -5.75  |
| 7                             | 6.74777         | 10.19                  | 46.77                | 46.64 | 56.96                 | 56.83 | 73.00        | 60.00 | -16.04      | -3.17  |

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




|                 |                |                               |                                      |
|-----------------|----------------|-------------------------------|--------------------------------------|
| Frequency Range | 150kHz ~ 30MHz | Detector Function & Bandwidth | Quasi-Peak (QP) / Average (AV), 9kHz |
| Input Power     | 110Vdc         | Environmental Conditions      | 23°C, 70%RH, 999mbar                 |
| Tested by       | Vic Lin        |                               |                                      |
| Test Mode       | Mode 2         |                               |                                      |

| Phase Of Power : Negative (-) |                 |                        |                      |       |                       |       |              |       |             |        |
|-------------------------------|-----------------|------------------------|----------------------|-------|-----------------------|-------|--------------|-------|-------------|--------|
| No                            | Frequency (MHz) | Correction Factor (dB) | Reading Value (dBuV) |       | Emission Level (dBuV) |       | Limit (dBuV) |       | Margin (dB) |        |
|                               |                 |                        | Q.P.                 | AV.   | Q.P.                  | AV.   | Q.P.         | AV.   | Q.P.        | AV.    |
| 1                             | 0.24949         | 10.01                  | 41.67                | 41.66 | 51.68                 | 51.67 | 79.00        | 66.00 | -27.32      | -14.33 |
| 2                             | 0.50000         | 10.04                  | 39.61                | 39.29 | 49.65                 | 49.33 | 73.00        | 60.00 | -23.35      | -10.67 |
| 3                             | 1.00048         | 10.05                  | 43.34                | 43.31 | 53.39                 | 53.36 | 73.00        | 60.00 | -19.61      | -6.64  |
| 4                             | 1.50096         | 10.08                  | 42.76                | 42.13 | 52.84                 | 52.21 | 73.00        | 60.00 | -20.16      | -7.79  |
| 5                             | 3.49897         | 10.13                  | 43.54                | 43.51 | 53.67                 | 53.64 | 73.00        | 60.00 | -19.33      | -6.36  |
| 6                             | 6.74777         | 10.22                  | 46.38                | 46.34 | 56.60                 | 56.56 | 73.00        | 60.00 | -16.40      | -3.44  |

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




|                 |                |                               |                                      |
|-----------------|----------------|-------------------------------|--------------------------------------|
| Frequency Range | 150kHz ~ 30MHz | Detector Function & Bandwidth | Quasi-Peak (QP) / Average (AV), 9kHz |
| Input Power     | 110Vdc         | Environmental Conditions      | 23°C, 70%RH, 999mbar                 |
| Tested by       | Vic Lin        |                               |                                      |
| Test Mode       | Mode 3         |                               |                                      |

| Phase Of Power : Positive (+) |                 |                        |                      |       |                       |       |              |       |             |        |
|-------------------------------|-----------------|------------------------|----------------------|-------|-----------------------|-------|--------------|-------|-------------|--------|
| No                            | Frequency (MHz) | Correction Factor (dB) | Reading Value (dBuV) |       | Emission Level (dBuV) |       | Limit (dBuV) |       | Margin (dB) |        |
|                               |                 |                        | Q.P.                 | AV.   | Q.P.                  | AV.   | Q.P.         | AV.   | Q.P.        | AV.    |
| 1                             | 0.24775         | 10.00                  | 42.82                | 42.71 | 52.82                 | 52.71 | 79.00        | 66.00 | -26.18      | -13.29 |
| 2                             | 0.98875         | 10.03                  | 43.28                | 43.19 | 53.31                 | 53.22 | 73.00        | 60.00 | -19.69      | -6.78  |
| 3                             | 1.48517         | 10.06                  | 41.76                | 41.73 | 51.82                 | 51.79 | 73.00        | 60.00 | -21.18      | -8.21  |
| 4                             | 4.20277         | 10.13                  | 43.55                | 43.36 | 53.68                 | 53.49 | 73.00        | 60.00 | -19.32      | -6.51  |
| 5                             | 6.67348         | 10.19                  | 45.15                | 44.68 | 55.34                 | 54.87 | 73.00        | 60.00 | -17.66      | -5.13  |
| 6                             | 7.41638         | 10.21                  | 47.18                | 46.52 | 57.39                 | 56.73 | 73.00        | 60.00 | -15.61      | -3.27  |

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




|                 |                |                               |                                      |
|-----------------|----------------|-------------------------------|--------------------------------------|
| Frequency Range | 150kHz ~ 30MHz | Detector Function & Bandwidth | Quasi-Peak (QP) / Average (AV), 9kHz |
| Input Power     | 110Vdc         | Environmental Conditions      | 23°C, 70%RH, 999mbar                 |
| Tested by       | Vic Lin        |                               |                                      |
| Test Mode       | Mode 3         |                               |                                      |

| Phase Of Power : Negative (-) |                 |                        |                      |       |                       |       |              |       |             |        |
|-------------------------------|-----------------|------------------------|----------------------|-------|-----------------------|-------|--------------|-------|-------------|--------|
| No                            | Frequency (MHz) | Correction Factor (dB) | Reading Value (dBuV) |       | Emission Level (dBuV) |       | Limit (dBuV) |       | Margin (dB) |        |
|                               |                 |                        | Q.P.                 | AV.   | Q.P.                  | AV.   | Q.P.         | AV.   | Q.P.        | AV.    |
| 1                             | 0.24775         | 10.01                  | 42.06                | 41.93 | 52.07                 | 51.94 | 79.00        | 66.00 | -26.93      | -14.06 |
| 2                             | 0.49408         | 10.04                  | 39.32                | 39.04 | 49.36                 | 49.08 | 79.00        | 66.00 | -29.64      | -16.92 |
| 3                             | 0.98875         | 10.05                  | 43.20                | 43.08 | 53.25                 | 53.13 | 73.00        | 60.00 | -19.75      | -6.87  |
| 4                             | 4.20277         | 10.15                  | 43.31                | 43.21 | 53.46                 | 53.36 | 73.00        | 60.00 | -19.54      | -6.64  |
| 5                             | 6.92372         | 10.22                  | 46.14                | 45.84 | 56.36                 | 56.06 | 73.00        | 60.00 | -16.64      | -3.94  |
| 6                             | 7.41638         | 10.24                  | 46.67                | 46.63 | 56.91                 | 56.87 | 73.00        | 60.00 | -16.09      | -3.13  |

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




|                 |                |                               |                                      |
|-----------------|----------------|-------------------------------|--------------------------------------|
| Frequency Range | 150kHz ~ 30MHz | Detector Function & Bandwidth | Quasi-Peak (QP) / Average (AV), 9kHz |
| Input Power     | 110Vdc         | Environmental Conditions      | 23°C, 70%RH, 999mbar                 |
| Tested by       | Vic Lin        |                               |                                      |
| Test Mode       | Mode 4         |                               |                                      |

| Phase Of Power : Positive (+) |                 |                        |                      |       |                       |       |              |       |             |        |
|-------------------------------|-----------------|------------------------|----------------------|-------|-----------------------|-------|--------------|-------|-------------|--------|
| No                            | Frequency (MHz) | Correction Factor (dB) | Reading Value (dBuV) |       | Emission Level (dBuV) |       | Limit (dBuV) |       | Margin (dB) |        |
|                               |                 |                        | Q.P.                 | AV.   | Q.P.                  | AV.   | Q.P.         | AV.   | Q.P.        | AV.    |
| 1                             | 0.25557         | 10.01                  | 42.83                | 42.76 | 52.84                 | 52.77 | 79.00        | 66.00 | -26.16      | -13.23 |
| 2                             | 0.51173         | 10.02                  | 40.19                | 39.85 | 50.21                 | 49.87 | 73.00        | 60.00 | -22.79      | -10.13 |
| 3                             | 1.53615         | 10.06                  | 43.30                | 43.26 | 53.36                 | 53.32 | 73.00        | 60.00 | -19.64      | -6.68  |
| 4                             | 2.81472         | 10.10                  | 44.39                | 44.26 | 54.49                 | 54.36 | 73.00        | 60.00 | -18.51      | -5.64  |
| 5                             | 6.13781         | 10.18                  | 47.68                | 46.59 | 57.86                 | 56.77 | 73.00        | 60.00 | -15.14      | -3.23  |
| 6                             | 7.41638         | 10.21                  | 47.41                | 46.39 | 57.62                 | 56.60 | 73.00        | 60.00 | -15.38      | -3.40  |

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




|                 |                |                               |                                      |
|-----------------|----------------|-------------------------------|--------------------------------------|
| Frequency Range | 150kHz ~ 30MHz | Detector Function & Bandwidth | Quasi-Peak (QP) / Average (AV), 9kHz |
| Input Power     | 110Vdc         | Environmental Conditions      | 23°C, 70%RH, 999mbar                 |
| Tested by       | Vic Lin        |                               |                                      |
| Test Mode       | Mode 4         |                               |                                      |

| Phase Of Power : Negative (-) |                 |                        |                      |       |                       |       |              |       |             |        |
|-------------------------------|-----------------|------------------------|----------------------|-------|-----------------------|-------|--------------|-------|-------------|--------|
| No                            | Frequency (MHz) | Correction Factor (dB) | Reading Value (dBuV) |       | Emission Level (dBuV) |       | Limit (dBuV) |       | Margin (dB) |        |
|                               |                 |                        | Q.P.                 | AV.   | Q.P.                  | AV.   | Q.P.         | AV.   | Q.P.        | AV.    |
| 1                             | 0.25557         | 10.01                  | 42.06                | 42.01 | 52.07                 | 52.02 | 79.00        | 66.00 | -26.93      | -13.98 |
| 2                             | 1.02408         | 10.05                  | 43.87                | 43.71 | 53.92                 | 53.76 | 73.00        | 60.00 | -19.08      | -6.24  |
| 3                             | 4.09836         | 10.14                  | 45.92                | 45.91 | 56.06                 | 56.05 | 73.00        | 60.00 | -16.94      | -3.95  |
| 4                             | 4.86566         | 10.16                  | 46.73                | 46.73 | 56.89                 | 56.89 | 73.00        | 60.00 | -16.11      | -3.11  |
| 5                             | 6.14824         | 10.20                  | 47.42                | 46.71 | 57.62                 | 56.91 | 73.00        | 60.00 | -15.38      | -3.09  |
| 6                             | 7.42551         | 10.24                  | 47.35                | 46.30 | 57.59                 | 56.54 | 73.00        | 60.00 | -15.41      | -3.46  |

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value



## 6 Radiated Emission at Frequencies up to 1GHz

### 6.1 Limits

For Class A Equipment

| Frequency range (MHz) | Distance (m) | Limits (dBuV/m) |
|-----------------------|--------------|-----------------|
| 30 - 230              | 10           | 40              |
| 230 - 1000            |              | 47              |
| 30 - 230              | 3            | 50              |
| 230 - 1000            |              | 57              |

For Class B Equipment

| Frequency range (MHz) | Distance (m) | Limits (dBuV/m) |
|-----------------------|--------------|-----------------|
| 30 - 230              | 10           | 30              |
| 230 - 1000            |              | 37              |
| 30 - 230              | 3            | 40              |
| 230 - 1000            |              | 47              |

For FM Receivers

| Frequency range (MHz) | Measurement  |                             | Class B limits (dBuV/m) |           |
|-----------------------|--------------|-----------------------------|-------------------------|-----------|
|                       | Distance (m) | Detector type/<br>bandwidth | Fundamental             | Harmonics |
| 30 - 230              | 10           | Quasi peak/<br>120 kHz      | 50                      | 42        |
| 230 - 300             |              |                             |                         | 42        |
| 300 - 1000            |              |                             |                         | 46        |
| 30 - 230              | 3            |                             | 60                      | 52        |
| 230 - 300             |              |                             |                         | 52        |
| 300 - 1000            |              |                             |                         | 56        |

These relaxed limits apply only to emissions at the fundamental and harmonic frequencies of the local oscillator. Signals at all other frequencies shall be compliant with the limits given in Table A4.1 & A4.2 of EN 55032.



## 6.2 Test Instruments

| Description & Manufacturer      | Model No.        | Serial No.      | Cal. Date     | Cal. Due      |
|---------------------------------|------------------|-----------------|---------------|---------------|
| Sonoma Preamplifier             | 310N             | 352922          | Feb. 20, 2018 | Feb. 19, 2019 |
| Sonoma Preamplifier             | 310N             | 352921          | Feb. 20, 2018 | Feb. 19, 2019 |
| Agilent Test Receiver           | N9038A           | MY50010158      | Jun. 27, 2018 | Jun. 26, 2019 |
| Agilent Test Receiver           | N9038A           | MY51210114      | Jul. 2, 2018  | Jul. 1, 2019  |
| Schwarzbeck Antenna             | VULB9168         | 9168-316        | Dec. 11, 2017 | Dec. 10, 2018 |
| Schwarzbeck Antenna             | VULB9168         | 9168-317        | Dec. 11, 2017 | Dec. 10, 2018 |
| Max Full. Turn Table & Tower    | MF7802           | MF7802121       | NA            | NA            |
| Max Full. Tower                 | MF7802           | MF780208105     | NA            | NA            |
| Software                        | Radiated_V8.7.08 | NA              | NA            | NA            |
| JYEBAO RF cable<br>With 5dB PAD | LMR-600          | CABLE-CH8-01.V  | Jun. 25, 2018 | Jun. 24, 2019 |
| JYEBAO RF cable<br>With 5dB PAD | LMR-600          | CABLE-CH8-02.H  | Jun. 25, 2018 | Jun. 24, 2019 |
| WOKEN RF cable<br>With 5dB PAD  | 8D               | CABLE-CH8-03.3M | Jun. 25, 2018 | Jun. 24, 2019 |


- Notes: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in Chamber No. 8.
3. The Industry Canada Reference No. IC 7450E-8.
4. The VCCI Site Registration No. R-12946.
5. Tested Date: Sep. 12, 2018

### 6.3 Test Arrangement

- The EUT was placed on the top of a rotating table 0.8 meters above the ground at an accredited test facility. The table was rotated 360 degrees to determine the position of the highest radiation.
- The EUT was set 10 meters away from the interference-receiving antenna, which was mounted on the top of a variable-height antenna tower.
- The antenna is a broadband antenna, and its height is varied from one meter to four meters above the ground to determine the maximum value of the field strength. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- For each suspected emission, the EUT was arranged to its worst case and then the antenna was tuned to heights from 1 meter to 4 meters and the rotatable table was turned from 0 degrees to 360 degrees to find the maximum reading.
- The test-receiver system was set to quasi-peak detect function and specified bandwidth with maximum hold mode when the test frequency is up to 1 GHz.

Note:

- The resolution bandwidth and video bandwidth of test receiver/spectrum analyzer is 120kHz for quasi-peak detection (QP) at frequency up to 1GHz.
- The measurement distance is the shortest horizontal distance between an imaginary circular periphery just encompassing this arrangement and the calibration point of the antenna.



**Note: Cable on the RGP must be insulated.**

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


## 6.4 Test Results

|                 |              |                               |                         |
|-----------------|--------------|-------------------------------|-------------------------|
| Frequency Range | 30MHz ~ 1GHz | Detector Function & Bandwidth | Quasi-Peak (QP), 120kHz |
| Input Power     | 110Vdc       | Environmental Conditions      | 20°C, 68%RH, 999mbar    |
| Tested by       | Jary Huang   |                               |                         |
| Test Mode       | Mode 1       |                               |                         |

| Antenna Polarity & Test Distance : Horizontal at 10 m |                 |                         |                |             |                    |                      |                  |                          |
|---|-----------------|-------------------------|----------------|-------------|--------------------|----------------------|------------------|--------------------------|
| No  | Frequency (MHz) | Emission Level (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Antenna Height (m) | Table Angle (Degree) | Raw Value (dBuV) | Correction Factor (dB/m) |
| 1   | 33.42           | 18.64 QP                | 40.00          | -21.36      | 3.51 H             | 74                   | 33.10            | -14.46                   |
| 2   | 51.15           | 23.71 QP                | 40.00          | -16.29      | 2.64 H             | 201                  | 37.25            | -13.54                   |
| 3   | 55.34           | 23.65 QP                | 40.00          | -16.35      | 3.85 H             | 188                  | 37.33            | -13.68                   |
| 4   | 177.39          | 29.75 QP                | 40.00          | -10.25      | 3.13 H             | 212                  | 43.47            | -13.72                   |
| 5   | 322.55          | 26.41 QP                | 47.00          | -20.59      | 3.00 H             | 148                  | 37.43            | -11.02                   |
| 6   | 377.36          | 25.41 QP                | 47.00          | -21.59      | 2.89 H             | 331                  | 35.03            | -9.62                    |

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




|                 |              |                               |                         |
|-----------------|--------------|-------------------------------|-------------------------|
| Frequency Range | 30MHz ~ 1GHz | Detector Function & Bandwidth | Quasi-Peak (QP), 120kHz |
| Input Power     | 110Vdc       | Environmental Conditions      | 20°C , 68%RH, 999mbar   |
| Tested by       | Jary Huang   |                               |                         |
| Test Mode       | Mode 1       |                               |                         |

| Antenna Polarity & Test Distance : Vertical at 10 m |                 |                         |                |             |                    |                      |                  |                          |
|---|-----------------|-------------------------|----------------|-------------|--------------------|----------------------|------------------|--------------------------|
| No  | Frequency (MHz) | Emission Level (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Antenna Height (m) | Table Angle (Degree) | Raw Value (dBuV) | Correction Factor (dB/m) |
| 1   | 51.02           | 36.94 QP                | 40.00          | -3.06       | 1.06 V             | 79                   | 51.33            | -14.39                   |
| 2   | 58.06           | 36.70 QP                | 40.00          | -3.30       | 1.57 V             | 195                  | 51.28            | -14.58                   |
| 3   | 79.64           | 24.37 QP                | 40.00          | -15.63      | 2.11 V             | 2                    | 42.98            | -18.61                   |
| 4   | 119.41          | 24.72 QP                | 40.00          | -15.28      | 1.32 V             | 165                  | 40.94            | -16.22                   |
| 5   | 177.17          | 34.02 QP                | 40.00          | -5.98       | 1.08 V             | 102                  | 47.87            | -13.85                   |
| 6   | 323.89          | 29.95 QP                | 47.00          | -17.05      | 1.00 V             | 260                  | 41.30            | -11.35                   |

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




|                 |              |                               |                         |
|-----------------|--------------|-------------------------------|-------------------------|
| Frequency Range | 30MHz ~ 1GHz | Detector Function & Bandwidth | Quasi-Peak (QP), 120kHz |
| Input Power     | 110Vdc       | Environmental Conditions      | 20°C, 68%RH, 999mbar    |
| Tested by       | Jary Huang   |                               |                         |
| Test Mode       | Mode 2       |                               |                         |

| Antenna Polarity & Test Distance : Horizontal at 10 m |                 |                         |                |             |                    |                      |                  |                          |
|---|-----------------|-------------------------|----------------|-------------|--------------------|----------------------|------------------|--------------------------|
| No  | Frequency (MHz) | Emission Level (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Antenna Height (m) | Table Angle (Degree) | Raw Value (dBuV) | Correction Factor (dB/m) |
| 1   | 33.44           | 18.86 QP                | 40.00          | -21.14      | 3.19 H             | 297                  | 33.33            | -14.47                   |
| 2   | 56.12           | 25.19 QP                | 40.00          | -14.81      | 3.95 H             | 172                  | 38.94            | -13.75                   |
| 3   | 119.29          | 16.96 QP                | 40.00          | -23.04      | 3.67 H             | 200                  | 32.37            | -15.41                   |
| 4   | 178.24          | 31.77 QP                | 40.00          | -8.23       | 3.83 H             | 204                  | 45.59            | -13.82                   |
| 5   | 266.87          | 24.66 QP                | 47.00          | -22.34      | 3.00 H             | 280                  | 37.79            | -13.13                   |
| 6   | 303.30          | 28.36 QP                | 47.00          | -18.64      | 2.96 H             | 328                  | 39.90            | -11.54                   |

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




|                 |              |                               |                         |
|-----------------|--------------|-------------------------------|-------------------------|
| Frequency Range | 30MHz ~ 1GHz | Detector Function & Bandwidth | Quasi-Peak (QP), 120kHz |
| Input Power     | 110Vdc       | Environmental Conditions      | 20°C , 68%RH, 999mbar   |
| Tested by       | Jary Huang   |                               |                         |
| Test Mode       | Mode 2       |                               |                         |

| Antenna Polarity & Test Distance : Vertical at 10 m |                 |                         |                |             |                    |                      |                  |                          |
|---|-----------------|-------------------------|----------------|-------------|--------------------|----------------------|------------------|--------------------------|
| No  | Frequency (MHz) | Emission Level (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Antenna Height (m) | Table Angle (Degree) | Raw Value (dBuV) | Correction Factor (dB/m) |
| 1   | 50.73           | 36.68 QP                | 40.00          | -3.32       | 1.03 V             | 97                   | 51.08            | -14.40                   |
| 2   | 57.86           | 36.79 QP                | 40.00          | -3.21       | 2.00 V             | 102                  | 51.37            | -14.58                   |
| 3   | 79.57           | 26.03 QP                | 40.00          | -13.97      | 1.54 V             | 142                  | 44.62            | -18.59                   |
| 4   | 119.12          | 26.19 QP                | 40.00          | -13.81      | 1.32 V             | 124                  | 42.46            | -16.27                   |
| 5   | 177.42          | 36.36 QP                | 40.00          | -3.64       | 1.11 V             | 98                   | 50.25            | -13.89                   |
| 6   | 305.31          | 27.52 QP                | 47.00          | -19.48      | 2.31 V             | 241                  | 39.53            | -12.01                   |

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




|                 |              |                               |                         |
|-----------------|--------------|-------------------------------|-------------------------|
| Frequency Range | 30MHz ~ 1GHz | Detector Function & Bandwidth | Quasi-Peak (QP), 120kHz |
| Input Power     | 110Vdc       | Environmental Conditions      | 20°C, 68%RH, 999mbar    |
| Tested by       | Jary Huang   |                               |                         |
| Test Mode       | Mode 3       |                               |                         |

| Antenna Polarity & Test Distance : Horizontal at 10 m |                 |                         |                |             |                    |                      |                  |                          |
|---|-----------------|-------------------------|----------------|-------------|--------------------|----------------------|------------------|--------------------------|
| No  | Frequency (MHz) | Emission Level (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Antenna Height (m) | Table Angle (Degree) | Raw Value (dBuV) | Correction Factor (dB/m) |
| 1   | 33.13           | 18.23 QP                | 40.00          | -21.77      | 3.23 H             | 267                  | 32.69            | -14.46                   |
| 2   | 50.42           | 22.40 QP                | 40.00          | -17.60      | 3.89 H             | 174                  | 35.95            | -13.55                   |
| 3   | 55.90           | 22.65 QP                | 40.00          | -17.35      | 3.10 H             | 181                  | 36.38            | -13.73                   |
| 4   | 177.54          | 30.44 QP                | 40.00          | -9.56       | 3.79 H             | 207                  | 44.18            | -13.74                   |
| 5   | 302.81          | 29.42 QP                | 47.00          | -17.58      | 2.97 H             | 333                  | 40.96            | -11.54                   |
| 6   | 379.44          | 25.46 QP                | 47.00          | -21.54      | 3.13 H             | 328                  | 35.04            | -9.58                    |

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




|                 |              |                               |                         |
|-----------------|--------------|-------------------------------|-------------------------|
| Frequency Range | 30MHz ~ 1GHz | Detector Function & Bandwidth | Quasi-Peak (QP), 120kHz |
| Input Power     | 110Vdc       | Environmental Conditions      | 20°C , 68%RH, 999mbar   |
| Tested by       | Jary Huang   |                               |                         |
| Test Mode       | Mode 3       |                               |                         |

| Antenna Polarity & Test Distance : Vertical at 10 m |                 |                         |                |             |                    |                      |                  |                          |
|---|-----------------|-------------------------|----------------|-------------|--------------------|----------------------|------------------|--------------------------|
| No  | Frequency (MHz) | Emission Level (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Antenna Height (m) | Table Angle (Degree) | Raw Value (dBuV) | Correction Factor (dB/m) |
| 1   | 50.93           | 34.70 QP                | 40.00          | -5.30       | 1.03 V             | 153                  | 49.10            | -14.40                   |
| 2   | 58.15           | 36.57 QP                | 40.00          | -3.43       | 1.92 V             | 84                   | 51.15            | -14.58                   |
| 3   | 79.76           | 24.43 QP                | 40.00          | -15.57      | 1.44 V             | 154                  | 43.08            | -18.65                   |
| 4   | 120.06          | 24.22 QP                | 40.00          | -15.78      | 1.12 V             | 146                  | 40.33            | -16.11                   |
| 5   | 177.66          | 34.44 QP                | 40.00          | -5.56       | 1.68 V             | 90                   | 48.36            | -13.92                   |
| 6   | 303.95          | 29.10 QP                | 47.00          | -17.90      | 1.00 V             | 270                  | 41.17            | -12.07                   |

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value






|                 |              |                               |                         |
|-----------------|--------------|-------------------------------|-------------------------|
| Frequency Range | 30MHz ~ 1GHz | Detector Function & Bandwidth | Quasi-Peak (QP), 120kHz |
| Input Power     | 110Vdc       | Environmental Conditions      | 20°C, 68%RH, 999mbar    |
| Tested by       | Jary Huang   |                               |                         |
| Test Mode       | Mode 4       |                               |                         |

| Antenna Polarity & Test Distance : Horizontal at 10 m |                 |                         |                |             |                    |                      |                  |                          |
|---|-----------------|-------------------------|----------------|-------------|--------------------|----------------------|------------------|--------------------------|
| No  | Frequency (MHz) | Emission Level (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Antenna Height (m) | Table Angle (Degree) | Raw Value (dBuV) | Correction Factor (dB/m) |
| 1   | 50.71           | 22.91 QP                | 40.00          | -17.09      | 3.16 H             | 210                  | 36.46            | -13.55                   |
| 2   | 55.61           | 24.79 QP                | 40.00          | -15.21      | 3.59 H             | 147                  | 38.49            | -13.70                   |
| 3   | 119.46          | 17.00 QP                | 40.00          | -23.00      | 3.10 H             | 2                    | 32.38            | -15.38                   |
| 4   | 178.00          | 32.25 QP                | 40.00          | -7.75       | 3.19 H             | 203                  | 46.04            | -13.79                   |
| 5   | 305.16          | 29.91 QP                | 47.00          | -17.09      | 2.94 H             | 329                  | 41.43            | -11.52                   |
| 6   | 374.86          | 22.95 QP                | 47.00          | -24.05      | 3.00 H             | 227                  | 32.59            | -9.64                    |

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




|                 |              |                               |                         |
|-----------------|--------------|-------------------------------|-------------------------|
| Frequency Range | 30MHz ~ 1GHz | Detector Function & Bandwidth | Quasi-Peak (QP), 120kHz |
| Input Power     | 110Vdc       | Environmental Conditions      | 20°C, 68%RH, 999mbar    |
| Tested by       | Jary Huang   |                               |                         |
| Test Mode       | Mode 4       |                               |                         |

| Antenna Polarity & Test Distance : Vertical at 10 m |                 |                         |                |             |                    |                      |                  |                          |
|---|-----------------|-------------------------|----------------|-------------|--------------------|----------------------|------------------|--------------------------|
| No  | Frequency (MHz) | Emission Level (dBuV/m) | Limit (dBuV/m) | Margin (dB) | Antenna Height (m) | Table Angle (Degree) | Raw Value (dBuV) | Correction Factor (dB/m) |
| 1   | 50.83           | 35.89 QP                | 40.00          | -4.11       | 1.07 V             | 121                  | 50.29            | -14.40                   |
| 2   | 58.27           | 36.92 QP                | 40.00          | -3.08       | 1.45 V             | 82                   | 51.51            | -14.59                   |
| 3   | 79.95           | 28.43 QP                | 40.00          | -11.57      | 1.63 V             | 139                  | 47.15            | -18.72                   |
| 4   | 120.26          | 26.34 QP                | 40.00          | -13.66      | 1.03 V             | 121                  | 42.42            | -16.08                   |
| 5   | 178.00          | 36.90 QP                | 40.00          | -3.10       | 1.18 V             | 50                   | 50.86            | -13.96                   |
| 6   | 303.86          | 29.11 QP                | 47.00          | -17.89      | 1.00 V             | 272                  | 41.19            | -12.08                   |

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value



## 7 General Immunity Requirements

| EN 55035:2017, Immunity requirements |   |                       |
|--------------------------------------|---|-----------------------|
| Reference standard                   | Test specification  | Performance Criterion |
| EN/IEC 61000-4-2<br>ESD              | Enclosure port:<br>$\pm 8\text{kV}$ Air discharge, $\pm 4\text{kV}$ Contact discharge   | B                     |
| EN/IEC 61000-4-3<br>RS               | Enclosure port:<br>Swept freq. test :<br>80-1000 MHz, 3V/m, 80% AM (1kHz),<br>Spot freq. test :<br>1800, 2600, 3500, 5000 MHz ( $\pm 1\%$ ),<br>3V/m, 80% AM (1kHz)   | A                     |
| EN/IEC 61000-4-4<br>EFT              | Analogue/digital data ports (cable length > 3m):<br>xDSL equipment: $\pm 0.5\text{kV}$ , 5/50 ( $T_r/T_h$ ) ns, 100kHz<br>others: $\pm 0.5\text{kV}$ , 5/50 ( $T_r/T_h$ ) ns, 5kHz  | B                     |
|                                      | DC network power port (cable length > 3m):<br>$\pm 0.5\text{kV}$ , 5/50 ( $T_r/T_h$ ) ns, 5kHz  |                       |
|                                      | AC mains power ports:<br>$\pm 1.0\text{kV}$ , 5/50 ( $T_r/T_h$ ) ns, 5kHz   |                       |
| EN/IEC 61000-4-5<br>Surge            | Analogue/digital data ports (direct to outdoor cables):<br>Port type: unshielded symmetrical<br>10/700(5/320) ( $T_r/T_h$ ) $\mu\text{s}$ ,<br>w/o primary protectors (line to ground): $\pm 1.0\text{kV}$ , or<br>with primary protectors (line to ground): $\pm 1.0\text{kV}$ , $\pm 4.0\text{kV}$<br>Port type: coaxial or shielded<br>1.2/50 (8/20) ( $T_r/T_h$ ) $\mu\text{s}$ ,<br>shield to ground: $\pm 0.5\text{kV}$ | C                     |
|                                      | DC network power port (direct to outdoor cables):<br>1.2/50(8/20) ( $T_r/T_h$ ) $\mu\text{s}$ ,<br>Line to ground: $\pm 0.5\text{kV}$   | B                     |
|                                      | AC mains power ports: 1.2/50(8/20) ( $T_r/T_h$ ) $\mu\text{s}$ ,<br>Line to line: $\pm 1\text{kV}$ ,<br>Line to ground: $\pm 2\text{kV}$  | B                     |
| EN/IEC 61000-4-6<br>CS               | Analogue/digital data ports (cable length > 3m) ;<br>DC network power ports (cable length > 3m) ;<br>AC mains power ports<br>0.15-10 MHz, 3V, 80% AM (1kHz),<br>10-30 MHz, 3V-1V, 80% AM (1kHz),<br>30-80 MHz, 1V, 80% AM (1kHz)  | A                     |
| EN/IEC 61000-4-8<br>PFMF             | Enclosure port:<br>50 or 60 Hz, 1A/m  | A                     |

**EN 55024:2010 / EN 55024:2010 +A1:2015, Immunity requirements**

| Clause  | Reference standard        | Table | Test specification   | Performance Criterion |
|---------|---------------------------|-------|--|-----------------------|
| 4.2.1   | EN/IEC 61000-4-2<br>ESD   | 1.3   | Enclosure port:<br>±8kV Air discharge, ±4kV Contact discharge  | B                     |
| 4.2.3.2 | EN/IEC 61000-4-3<br>RS    | 1.2   | Enclosure port:<br>80-1000 MHz, 3V/m, 80% AM (1kHz)  | A                     |
| 4.2.2   | EN/IEC 61000-4-4<br>EFT   | 2.3   | Signal ports and telecommunication ports:<br>xDSL equipment: ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 100kHz<br>others: ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz      | B                     |
|         |                           | 3.3   | Input DC power port: ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz   |                       |
|         |                           | 4.5   | Input AC Power ports: ±1kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz  |                       |
| 4.2.5   | EN/IEC 61000-4-5<br>Surge | 2.2   | Signal and telecommunication ports (direct to outdoor cables): 10/700 (5/320) (T <sub>r</sub> /T <sub>h</sub> ) µs<br>w/o primary protectors: ±1kV, or<br>with primary protectors fitted: ±4kV | C                     |
|         |                           | 3.2   | Input DC power port (direct to outdoor cables):<br>1.2/50 (8/20) (T <sub>r</sub> /T <sub>h</sub> ) µs<br>Line to earth: ±0.5kV   | B                     |
|         |                           | 4.4   | Input AC Power ports: 1.2/50 (8/20) (T <sub>r</sub> /T <sub>h</sub> ) µs,<br>Line to line: ±1kV<br>Line to earth: ±2kV   |                       |
| 4.2.3.3 | EN/IEC 61000-4-6<br>CS    | 2.1   | Signal and telecommunication ports(cable length > 3m): 0.15-80 MHz, 3V, 80% AM (1kHz)  | A                     |
|         |                           | 3.1   | Input DC power port: 0.15-80 MHz, 3V, 80% AM (1kHz)  |                       |
|         |                           | 4.1   | Input AC Power ports: 0.15-80 MHz, 3V, 80% AM (1kHz)   |                       |
| 4.2.4   | EN/IEC 61000-4-8<br>PFMF  | 1.1   | Enclosure port:<br>50 or 60 Hz, 1A/m   | A                     |

## 7.1 Specific Immunity Requirements by Manufacturer

| Additional Test           |  |                       |
|---------------------------|--|-----------------------|
| Reference standard        | Test specification   | Performance Criterion |
| EN/IEC 61000-4-2<br>ESD   | Enclosure port:<br>±6kV Indirect Contact discharge   | A                     |
| EN/IEC 61000-4-3<br>RS    | Enclosure port:<br>Swept freq. test :<br>80-1000 MHz, 10V/m, 80% AM (1kHz),<br>Spot freq. test :<br>1800, 2600, 3500, 5000 MHz (±1 %),<br>10V/m, 80% AM (1kHz) | A                     |
| EN/IEC 61000-4-4<br>EFT   | DC network power port (cable length > 3m):<br>±2kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz  | A                     |
| EN/IEC 61000-4-5<br>Surge | DC network power port (direct to outdoor cables):<br>1.2/50(8/20) (T <sub>r</sub> /T <sub>h</sub> ) μs,<br>Line to line: ±2kV                                  | A                     |
| EN/IEC 61000-4-6<br>CS    | Input DC Power ports: 0.15-80 MHz, 10V, 80% AM (1kHz)  | A                     |
| EN/IEC 61000-4-8<br>PFMF  | Enclosure port:<br>50 Hz, 1000A/m  | A                     |

## 7.2 Performance Criteria

### General Performance Criteria

#### Performance criterion A

The equipment shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed below a performance level specified by the manufacturer when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.

#### Performance criterion B

After the test, the equipment shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed, after the application of the phenomena below a performance level specified by the manufacturer, when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. During the test, degradation of performance is allowed. However, no change of operating state or stored data is allowed to persist after the test. If the minimum performance level (or the permissible performance loss) is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.

#### Performance criterion C

Loss of function is allowed, provided the function is self-recoverable, or can be restored by the operation of the controls by the user in accordance with the manufacturer's instructions. Functions, and/or information stored in non-volatile memory, or protected by a battery backup, shall not be lost.

### Product Specific Performance Criteria

The particular performance criteria which are specified in the normative annexes of EN 55035 / EN 55024 take precedence over the corresponding parts of the general performance criteria. Where particular performance criteria for specific functions are not given, then the general performance criteria shall apply.

## 8 Electrostatic Discharge Immunity Test (ESD)

### 8.1 Test Specification

|                             |  |
|-----------------------------|--|
| <b>Basic Standard:</b>      | EN/IEC 61000-4-2   |
| <b>Discharge Impedance:</b> | 330 ohm / 150 pF   |
| <b>Discharge Voltage:</b>   | Air Discharge: $\pm 2\text{kV}$ , $\pm 4\text{kV}$ , $\pm 8\text{kV}$ (Direct)<br>Contact Discharge: $\pm 2\text{kV}$ , $\pm 4\text{kV}$ , $\pm 6\text{kV}$ (Indirect) |
| <b>Number of Discharge:</b> | Air – Direct: 10 discharges per location (each polarity)<br>Contact – Direct & Indirect: 10 discharges per location (each polarity)                                    |
| <b>Discharge Mode:</b>      | Single Discharge   |
| <b>Discharge Period:</b>    | 1-second minimum   |

### 8.2 Test Instruments


| Description & Manufacturer | Model No. | Serial No.  | Cal. Date     | Cal. Due      |
|----------------------------|-----------|-------------|---------------|---------------|
| EM Test ESD Simulator      | Dito      | V0707102251 | Apr. 12, 2018 | Apr. 11, 2019 |

Notes: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
2. The test was performed in ESD Room No. 3.  
3. Tested Date: Sep. 17, 2018

### 8.3 Test Arrangement

The basic test procedure was in accordance with EN/IEC 61000-4-2:

- Electrostatic discharges were applied only to those points and surfaces of the EUT that are accessible to users during normal operation.
- The test was performed with at least ten single discharges on the pre-selected points in the most sensitive polarity.
- The time interval between two successive single discharges was at least 1 second.
- The ESD generator was held perpendicularly to the surface to which the discharge was applied and the return cable was at least 0.2 meters from the EUT.
- Contact discharges were applied to the non-insulating coating, with the pointed tip of the generator penetrating the coating and contacting the conducting substrate.
- Air discharges were applied with the round discharge tip of the discharge electrode approaching the EUT as fast as possible (without causing mechanical damage) to touch the EUT. After each discharge, the ESD generator was removed from the EUT and re-triggered for a new single discharge. The test was repeated until all discharges were complete.
- At least ten single discharges (in the most sensitive polarity) were applied to the **Horizontal Coupling Plane** at points on each side of the EUT. The ESD generator was positioned at a distance of 0.1 meters from the EUT with the discharge electrode touching the **HCP**.
- At least ten single discharges (in the most sensitive polarity) were applied to the center of one vertical edge of the **Vertical Coupling Plane** in sufficiently different positions that the four faces of the EUT were completely illuminated. The **VCP** (dimensions 0.5m x 0.5m) was placed vertically to and 0.1 meters from the EUT.



#### TABLE-TOP EQUIPMENT

The configuration consisted of a wooden table 0.8 meters high standing on the **Ground Reference Plane**. The **GRP** consisted of a sheet of aluminum at least 0.25mm thick, and 2.5 meters square connected to the protective grounding system. A **Horizontal Coupling Plane** (1.6m x 0.8m) was placed on the table and attached to the **GRP** by means of a cable with 940kΩ total impedance. The equipment under test, was installed in a representative system as described in section 7 of EN/IEC 61000-4-2, and its cables were placed on the **HCP** and isolated by an insulating support of 0.5mm thickness. A distance of 1-meter minimum was provided between the EUT and the walls of the laboratory and any other metallic structure.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

#### 8.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

#### 8.5 Test Results

|                          |                            |           |              |
|--------------------------|----------------------------|-----------|--------------|
| Input Power              | 110Vdc                     | Tested by | Thomas Cheng |
| Environmental Conditions | 24 °C, 41% RH<br>1003 mbar | Test mode | Mode 1       |

| Test Results of Direct Application |                |            |                   |               |                       |
|------------------------------------|----------------|------------|-------------------|---------------|-----------------------|
| Discharge Level (kV)               | Polarity (+/-) | Test Point | Contact Discharge | Air Discharge | Performance Criterion |
| 2, 4, 8                            | +/-            | 1-2        | NA                | Note          | A                     |

Description of test points of direct application: Please refer to following page for representative mark only.

| Test Results of Indirect Application |                |            |                           |                         |                       |
|--------------------------------------|----------------|------------|---------------------------|-------------------------|-----------------------|
| Discharge Level (kV)                 | Polarity (+/-) | Test Point | Horizontal Coupling Plane | Vertical Coupling Plane | Performance Criterion |
| 2, 4, 6                              | +/-            | Four Sides | Note                      | Note                    | A                     |



Description of test points of indirect application:

1. Front side
2. Rear side
3. Right side
4. Left side

Note: The EUT function was correct during the test.



## Description of Test Points



## 9 Radiated, Radio-frequency, Electromagnetic Field Immunity Test (RS)

### 9.1 Test Specification

|                        |   |
|------------------------|---|
| Basic Standard:        | EN/IEC 61000-4-3                        |
| Swept Frequency Range: | 80 MHz - 1000 MHz                       |
| Spot Frequencies:      | 1800, 2600, 3500, 5000 MHz ( $\pm 1$ %) |
| Field Strength:        | 3 V/m, 10 V/m                           |
| Modulation:            | 1kHz Sine Wave, 80%, AM Modulation      |
| Frequency Step:        | 1 % of preceding frequency value        |
| Polarity of Antenna:   | Horizontal and Vertical                 |
| Antenna Height:        | 1.5m                                    |
| Dwell Time:            | 3 seconds                               |

### 9.2 Test Instruments


| Description & Manufacturer                 | Model No.   | Serial No. | Cal. Date     | Cal. Due      |
|--|-------------|------------|---------------|---------------|
| Agilent Signal Generator                   | E8257D      | MY48050465 | Jun. 6, 2018  | Jun. 5, 2019  |
| PRANA RF Amplifier                         | AP32DP280   | 0811-894   | NA            | NA            |
| TESEQ RF Amplifier                         | CBA1G-150   | T44220     | NA            | NA            |
| AR RF Amplifier                            | 35S4G8AM4   | 0326094    | NA            | NA            |
| AR RF Amplifier                            | 100S1G4M3   | 0329249    | NA            | NA            |
| AR Controller                              | SC1000M3    | 305910     | NA            | NA            |
| ETS Electric Field Sensor                  | HI-6105     | 00217912   | Nov. 27, 2017 | Nov. 26, 2018 |
| BOONTON RF Voltage Meter                   | 4232A       | 10180      | May 23, 2018  | May 22, 2019  |
| BOONTON Power Sensor                       | 51013-4E    | 34870      | Jun. 4, 2018  | Jun. 3, 2019  |
| BOONTON Power Sensor                       | 51013-4E    | 34873      | Jun. 4, 2018  | Jun. 3, 2019  |
| AR Log-Periodic Antenna                    | AT6080      | 0329465    | NA            | NA            |
| EMCO BiconiLog Antenna                     | 3141        | 1001       | NA            | NA            |
| AR High Gain Antenna                       | AT4010      | 0329800    | NA            | NA            |
| Schwarzbeck LOG ANTENNA                    | Stlp 9149   | 9149-260   | NA            | NA            |
| CHANCE MOST Full Anechoic Chamber (9x5x3m) | Chance Most | RS-002     | Feb. 6, 2018  | Feb. 5, 2019  |
| Software                                   | RS_V7.6     | NA         | NA            | NA            |

- Notes:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  2. The test was performed in RS Room No.2.
  3. Tested Date: Sep. 17, 2018

### 9.3 Test Arrangement

The test procedure was in accordance with EN/IEC 61000-4-3.

- The testing was performed in a fully anechoic chamber.
- The swept frequency range is from 80 MHz to 1000 MHz and the spot frequencies are 1800, 2600, 3500, 5000 MHz ( $\pm 1\%$ ), with the signal 80% amplitude modulated with a 1kHz sine wave.
- The dwell time of the amplitude modulated carrier was applied in 3 s at each of the frequencies during the scan. The sensitive frequencies (e.g. clock frequencies or frequencies identified by the manufacturer or obtained as outcome of the test) shall be analyzed in addition to the stepped frequencies.
- The field strength level was 3 V/m, 10 V/m.
- The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.



#### Table-top Equipment

The EUT installed in a representative system as described in section 7 of EN/IEC 61000-4-3 was placed on a non-conductive table 0.8 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

### 9.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

## 9.5 Test Results

|                          |               |           |              |
|--------------------------|---------------|-----------|--------------|
| Input Power              | 110Vdc        | Tested by | Thomas Cheng |
| Environmental Conditions | 27 °C, 68% RH | Test mode | Mode 1       |

| Frequency (MHz)                      | Polarity | Azimuth(°) | Applied Field Strength |               | Observation | Performance Criterion |
|--------------------------------------|----------|------------|------------------------|---------------|-------------|-----------------------|
|                                      |          |            | (V/m)                  | Modulation    |             |                       |
| 80 - 1000                            | V&H      | 0          | 3, 10                  | 80% AM (1kHz) | Note        | A                     |
|                                      |          | 90         | 3, 10                  | 80% AM (1kHz) | Note        | A                     |
|                                      |          | 180        | 3, 10                  | 80% AM (1kHz) | Note        | A                     |
|                                      |          | 270        | 3, 10                  | 80% AM (1kHz) | Note        | A                     |
| 1800, 2600, 3500,<br>5000 MHz (±1 %) | V&H      | 0          | 3, 10                  | 80% AM (1kHz) | Note        | A                     |
|                                      |          | 90         | 3, 10                  | 80% AM (1kHz) | Note        | A                     |
|                                      |          | 180        | 3, 10                  | 80% AM (1kHz) | Note        | A                     |
|                                      |          | 270        | 3, 10                  | 80% AM (1kHz) | Note        | A                     |

Note: The EUT function was correct during the test.

## 10 Electrical Fast Transient/Burst Immunity Test (EFT)

### 10.1 Test Specification

|                               |   |
|-------------------------------|---|
| Basic Standard:               | EN/IEC 61000-4-4  |
| Test Voltage:                 | Analogue/digital data port (cable length > 3m): N/A<br>DC network power port (cable length > 3m): $\pm 0.5\text{kV}$ , $\pm 2\text{kV}$<br>AC mains power port: N/A |
| Impulse Repetition Frequency: | 100kHz : applicable only to xDSL port<br>5kHz : others  |
| Impulse Wave Shape :          | 5/50 ns   |
| Burst Duration:               | 0.75 ms for 100kHz Repetition Frequency<br>15 ms for 5kHz Repetition Frequency,   |
| Burst Period:                 | 300 ms  |
| Test Duration:                | 1 min.  |

### 10.2 Test Instruments

| Description & Manufacturer | Model No. | Serial No. | Cal. Date     | Cal. Due      |
|----------------------------|-----------|------------|---------------|---------------|
| TESEQ, EFT Simulator       | NSG 3060  | 1572       | May 28, 2018  | May 27, 2019  |
| Haefely, Capacitive Clamp  | IP4A      | 155173     | Apr. 25, 2018 | Apr. 24, 2019 |

- Notes:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  2. The test was performed in EMS Room No. 2.
  3. Tested Date: Sep. 15, 2018



## 11 Surge Immunity Test

### 11.1 Test Specification

|                          |  |
|--------------------------|--|
| Basic Standard:          | EN/IEC 61000-4-5   |
| Wave-Shape:              | Analogue/digital data ports (direct to outdoor cables*):<br>Port type: unshielded symmetrical<br>10/700 $\mu$ s Open Circuit Voltage<br>5/320 $\mu$ s Short Circuit Current<br><br>Port type: coaxial or shielded<br>1.2/50 $\mu$ s Open Circuit Voltage<br>8/20 $\mu$ s Short Circuit Current<br><br>DC network power port (direct to outdoor cables*):<br>1.2/50 $\mu$ s Open Circuit Voltage<br>8/20 $\mu$ s Short Circuit Current<br><br>AC mains power port:<br>1.2/50 $\mu$ s Open Circuit Voltage<br>8/20 $\mu$ s Short Circuit Current |
| Test Voltage:            | Analogue/digital data ports:<br>Port type: unshielded symmetrical**<br>w/o primary protectors (line to ground): NA<br>with primary protectors (line to ground): NA<br>Port type: coaxial or shielded<br>shield to ground: NA<br><br>DC network power port: $\pm 0.5$ kV, $\pm 1$ kV, $\pm 2$ kV<br><br>AC mains power ports:<br>Line to line : NA<br>Line to ground : NA   |
| AC Phase Angle (degree): | 90° / 270°   |
| Pulse Repetition Rate:   | 1 time / 20 sec.   |
| Number of Tests:         | 5 positive and 5 negative at selected points   |

\* This test is only applicable only to ports, which according to the manufacturer's specification, may connect directly to outdoor cables.

\*\* For ports where primary protection is intended, surges are applied at voltages up to 4 kV with the primary protectors. Otherwise the 1 kV test level is applied without primary protection in place.

### 11.2 Test Instruments

| Description & Manufacturer        | Model No. | Serial No. | Cal. Date     | Cal. Due      |
|-----------------------------------|-----------|------------|---------------|---------------|
| TESEQ, Surge Simulator            | NSG 3060  | 1572       | May 28, 2018  | May 27, 2019  |
| Coupling Decoupling Network       | CDN-UTP8  | 045        | Aug. 27, 2018 | Aug. 26, 2019 |
| TESEQ Coupling Decoupling Network | CDN HSS-2 | 41009      | May 23, 2018  | May 22, 2019  |

Notes: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
 2. The test was performed in EMS Room No. 2.  
 3. Tested Date: Sep. 15, 2018

### 11.3 Test Arrangement

#### a. AC mains /DC network power ports:

The surge is to be applied to the EUT power supply terminals via the capacitive coupling network. Decoupling networks are required in order to avoid possible adverse effects on equipment not under test that may be powered by the same lines, and to provide sufficient decoupling impedance to the surge wave. The power cord between the EUT and the coupling/decoupling networks shall be 2 meters in length (or shorter).

For double-insulated products without PE or external earth connections, the test shall be done in a similar way as for grounded products but without adding any additional external grounded connections. If there are no other possible connections to earth, line-to-ground tests may be omitted.

#### b. Analogue/digital data ports,

- Port type: unshielded symmetrical (line to ground)

The surge is applied to the lines via the capacitive coupling. The coupling / decoupling networks shall not influence the specified functional conditions of the EUT. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length.

- Port type: coaxial or shielded (shield to ground)

The surge is applied to the lines via gas arrestors coupling. Test levels below the ignition point of the coupling arrestor cannot be specified. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length.

- High speed communications lines

Prior to the test, the correct operation of the port shall be verified; the external connection shall then be removed and the surge applied directly to the port's terminals with no coupling /decoupling network. After the surge, the correct operation of the port shall again be verified.

- Shielded lines:

- Direct application,

The EUT is isolated from ground and the surge is applied to its metallic enclosure; the termination (or auxiliary equipment) at the port(s) under test is grounded. This test applies to equipment with single or multiple shielded cables.

Rules for application of the surge to shielded lines:

##### a) Shields grounded at both ends

- The surge injection on the shield.

##### b) Shields grounded at one end


- If in the installation the shield is connected only at the auxiliary equipment, test shall be done in that configuration but with the generator still connected to the EUT side. If cable lengths allow, the cables shall be on insulated supports 0,1 m above the ground plane or cable tray.

For products which do not have metallic enclosures, the surge is applied directly to the shielded cable.

- Alternative coupling method for testing single cables in a multi-shield configuration,

Surges are applied in close proximity to the interconnection cable under test by a wire. The length of the cable between the port(s) under test and the device attached to the other end of the cable shall be the lesser of: the maximum length permitted by the EUT's specification, or 20 m. Where the length exceeds 1 m, excess lengths of cables shall be bundled at the approximate centre of the cables with the bundles 30 cm to 40 cm in length.





For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

#### 11.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

#### 11.5 Test Results

|                          |               |           |                 |
|--------------------------|---------------|-----------|-----------------|
| Input Power              | 110Vdc        | Tested by | Thomas Cheng    |
| Environmental Conditions | 27 °C, 61% RH | Test mode | Mode 1, 2, 3, 4 |

Input DC power port

| Voltage (kV) | Test Point | Polarity (+/-) | Observation | Performance Criterion |
|--------------|------------|----------------|-------------|-----------------------|
| 0.5, 1, 2    | (+)-(-)    | +/-            | Note        | A                     |

Note: The EUT function was correct during the test.

## 12 Immunity to Conducted Disturbances Induced by RF Fields (CS)

### 12.1 Test Specification

|                  |   |
|------------------|---|
| Basic Standard:  | EN/IEC 61000-4-6  |
| Frequency Range: | 0.15 MHz - 80 MHz   |
| Voltage Level:   | 0.15 MHz - 80 MHz: 10V<br>0.15 MHz - 10 MHz: 3V<br>10 MHz - 30 MHz: 3-1V<br>30 MHz - 80 MHz: 1V |
| Modulation:      | 1kHz Sine Wave, 80%, AM Modulation  |
| Frequency Step:  | 1 % of preceding frequency value  |
| Dwell Time       | 3 seconds   |


### 12.2 Test Instruments

| Description & Manufacturer                                  | Model No.      | Serial No. | Cal. Date     | Cal. Due      |
|---|----------------|------------|---------------|---------------|
| ROHDE & SCHWARZ<br>Signal Generator                         | SML03          | 101801     | Jan. 8, 2018  | Jan. 7, 2019  |
| Digital Sweep Function Generator                            | 8120           | 984801     | NA            | NA            |
| AR Power Amplifier  | 75A250AM1      | 306331     | NA            | NA            |
| FCC Coupling Decoupling Network                             | FCC-801-M2-16A | 01047      | Jun. 20, 2018 | Jun. 19, 2019 |
| FISCHER CUSTOM<br>COMMUNICATIONS<br>EM Injection Clamp      | F-203I-23mm    | 455        | NA            | NA            |
| FISCHER CUSTOM<br>COMMUNICATIONS<br>Current Injection Clamp | F-120-9A       | 361        | Jul. 24, 2018 | Jul. 23, 2019 |
| B&K Ear Simulator   | 4185           | 2553594    | NA            | NA            |
| EM TEST Coupling<br>Decoupling Network                      | CDN M1/32A     | 306508     | Jun. 20, 2018 | Jun. 19, 2019 |
| TESEQ Coupling Decoupling Network                           | CDN T800       | 34428      | Jun. 20, 2018 | Jun. 19, 2019 |
| FCC Coupling Decoupling Network                             | FCC-801-T4     | 02031      | Jun. 20, 2018 | Jun. 19, 2019 |
| EM TEST Coupling Decoupling Network                         | CDN T2         | 306509     | Jun. 20, 2018 | Jun. 19, 2019 |
| R&S Power Sensor  | NRV-Z5         | 837878/039 | Oct. 30, 2017 | Oct. 29, 2018 |
| R&S Power Meter   | NRVD           | 837794/040 | Oct. 30, 2017 | Oct. 29, 2018 |
| TESEQ Coupling Decoupling Network                           | CDN M232       | 37702      | Jun. 20, 2018 | Jun. 19, 2019 |
| TESEQ Coupling Decoupling Network                           | CDN M332       | 41258      | Jun. 20, 2018 | Jun. 19, 2019 |
| TESEQ Coupling Decoupling Network                           | CDN M332       | 41256      | Jun. 20, 2018 | Jun. 19, 2019 |
| TESEQ Coupling Decoupling Network                           | CDN T400A      | 28569      | Jun. 20, 2018 | Jun. 19, 2019 |
| TESEQ Coupling Decoupling Network                           | CDN T8-10      | 40376      | Jun. 20, 2018 | Jun. 19, 2019 |
| TESEQ Coupling Decoupling Network                           | ISN ST08       | 41212      | Jun. 20, 2018 | Jun. 19, 2019 |
| FCC Coupling Decoupling Network                             | FCC-801-M5-50A | 100018     | Jan. 24, 2018 | Jan. 23, 2019 |
| Software  | CS_V7.4.2      | NA         | NA            | NA            |

- Notes:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  2. The test was performed in CS Room No. 1.
  3. Tested Date: Sep. 15, 2018

### 12.3 Test Arrangement

- The EUT shall be tested within its intended operating and climatic conditions.
- An artificial hand was placed on the hand-held accessory and connected to the ground reference plane.
- One of the CDNs not used for injection was terminated with 50 ohm, providing only one return path. All other CDNs were coupled as decoupling networks.
- The frequency range is swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80 % amplitude. The signal is modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. Where the frequency is swept incrementally, the step size shall not exceed 1 % of the preceding frequency value.
- The dwell time of the amplitude modulated carrier was applied in 3s at each of the frequencies during the scan. The sensitive frequencies (e.g. clock frequencies or frequencies identified by the manufacturer or obtained as outcome of the test) shall be analyzed in addition to the stepped frequencies.
- Attempts should be made to fully exercise the EUT during testing, and to fully interrogate all exercise modes selected for susceptibility.



IEC 2606/13

- Note:**
- The EUT clearance from any metallic obstacles shall be at least 0,5 m.
  - Interconnecting cables ( $\leq 1$  m) belonging to the EUT shall remain on the insulating support.
  - The equipment to be tested is placed on an insulating support of 0.1 meters height above a ground reference plane. All relevant cables shall be provided with the appropriate coupling and decoupling devices at a distance between 0.1 meters and 0.3 meters from the projected geometry of the EUT on the ground reference plane.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

## 12.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

## 12.5 Test Results

|                          |               |           |              |
|--------------------------|---------------|-----------|--------------|
| Input Power              | 110Vdc        | Tested by | Thomas Cheng |
| Environmental Conditions | 28 °C, 60% RH | Test mode | Mode 1       |

| Frequency (MHz) | Level (Vrms) | Tested Line | Injection Method | Return Path | Observation | Performance Criterion |
|-----------------|--------------|-------------|------------------|-------------|-------------|-----------------------|
| 0.15 – 80       | 10           | DC power    | CDN-M2           | N/A         | Note        | A                     |
| 0.15 – 10       | 3            | DC power    | CDN-M2           | N/A         | Note        | A                     |
| 10 – 30         | 3 – 1        | DC power    | CDN-M2           | N/A         | Note        | A                     |
| 30 – 80         | 1            | DC power    | CDN-M2           | N/A         | Note        | A                     |

Note: The EUT function was correct during the test.

### 13 Power Frequency Magnetic Field Immunity Test

#### 13.1 Test Specification

|                   |   |
|-------------------|---|
| Basic Standard:   | EN/IEC 61000-4-8  |
| Frequency Range:  | 50Hz  |
| Field Strength:   | 1A/m, 100A/m, 1000A/m   |
| Observation Time: | 1 minute for Field Strength 1A/m, 100A/m<br>1 second for Field Strength 1000A/m |
| Inductance Coil:  | Rectangular type, 1 m x 1 m   |

#### 13.2 Test Instruments

##### For Field Strength 1A/m, 100A/m

| Description & Manufacturer     | Model No. | Serial No. | Cal. Date     | Cal. Due      |
|--------------------------------|-----------|------------|---------------|---------------|
| HAEFELY Magnetic Field Tester  | MAG 100   | 083794-06  | NA            | NA            |
| COMBINOVA Magnetic Field Meter | MFM10     | 224        | Apr. 24, 2018 | Apr. 23, 2019 |
| F.W.BELL 4190 Gaussmeter       | 4190      | 0743043    | Mar. 12, 2018 | Mar. 11, 2019 |

- Notes:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  2. The test was performed in EMS Room No. 1
  3. Tested Date: Sep. 15, 2018


##### For Field Strength 1000A/m

| Description & Manufacturer                      | Model no.  | Serial No. | Calibrated DATE | Calibrated Until |
|---|------------|------------|-----------------|------------------|
| Triaxial Elf Magnetic Field Meter BELL          | 4090       | NA         | Feb. 08, 2018   | Feb. 07, 2019    |
| Power frequency magnetic filed coil 3ctest      | TCX30      | EC1281401  | Mar. 05, 2018   | Mar. 04, 2019    |
| Power frequency magnetic filed generator 3ctest | PFMF-1200G | EC0111401  | Mar. 05, 2018   | Mar. 04, 2019    |

- Notes:
1. The calibration interval of the above test instruments are 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  2. The test was performed in Hsin Chu EMS-1 room. (TAF code: 2022)
  3. Tested Date: Sep. 18, 2018

### 13.3 Test Arrangement

- The equipment is configured and connected to satisfy its functional requirements.
- The power supply, input and output circuits shall be connected to the sources of power supply, control and signal.
- The cables supplied or recommended by the equipment manufacturer shall be used. 1 meter of all cables used shall be exposed to the magnetic field.



#### TABLETOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

### 13.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

### 13.5 Test Results

|                          |               |           |              |
|--------------------------|---------------|-----------|--------------|
| Input Power              | 110Vdc        | Tested by | Thomas Cheng |
| Environmental Conditions | 28 °C, 64% RH | Test mode | Mode 1       |

| Application | Frequency (Hz) | Test Duration | Field Strength (A/m) | Observation | Performance Criterion |
|-------------|----------------|---------------|----------------------|-------------|-----------------------|
| X - Axis    | 50             | 1 min.        | 1, 100               | Note        | A                     |
| Y - Axis    | 50             | 1 min.        | 1, 100               | Note        | A                     |
| Z - Axis    | 50             | 1 min.        | 1, 100               | Note        | A                     |

Note: The EUT function was correct during the test.

|                          |               |           |            |
|--------------------------|---------------|-----------|------------|
| Input Power              | 110Vdc        | Tested by | Terry Liao |
| Environmental Conditions | 25 °C, 66% RH | Test mode | Mode 1     |

| Application | Frequency (Hz) | Test Duration | Field Strength (A/m) | Observation | Performance Criterion |
|-------------|----------------|---------------|----------------------|-------------|-----------------------|
| X - Axis    | 50             | 1 sec.        | 1000                 | Note        | A                     |
| Y - Axis    | 50             | 1 sec.        | 1000                 | Note        | A                     |
| Z - Axis    | 50             | 1 sec.        | 1000                 | Note        | A                     |

Note: The EUT function was correct during the test.

Remark: The test, calibration and test results are compliance with the TAF (TAF code: 2022).

## 14 Pictures of Test Arrangements

### 14.1 Conducted Emission from the Mains Power Port

Mode 1






Mode 2



Mode 3




Mode 4




## 14.2 Radiated Emission at Frequencies up to 1GHz

Mode 1 & Mode 2







Mode 3




Mode 4



### 14.3 Electrostatic Discharge Immunity Test (ESD)



#### 14.4 Radio-frequency, Electromagnetic Field Immunity Test (RS)






#### 14.5 Electrical Fast Transient/Burst Immunity Test (EFT)



#### 14.6 Surge Immunity Test



#### 14.7 Conducted Disturbances Induced by RF Fields (CS)



#### 14.8 Power Frequency Magnetic Field Immunity Test (PFMF)

For Field Strength 1A/m, 100A/m



For Field Strength 1000A/m



## Appendix – Information of the Testing Laboratories

We, Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch, were founded in 1988 to provide our best service in EMC, Radio, Telecom and Safety consultation. Our laboratories are accredited and approved according to ISO/IEC 17025.

If you have any comments, please feel free to contact us at the following:

**Lin Kou EMC/RF Lab**

Tel: 886-2-26052180

Fax: 886-2-26051924

**Hsin Chu EMC/RF/Telecom Lab**

Tel: 886-3-6668565

Fax: 886-3-6668323

**Hwa Ya EMC/RF/Safety Lab**

Tel: 886-3-3183232

Fax: 886-3-3270892

**Email:** [service.adt@tw.bureauveritas.com](mailto:service.adt@tw.bureauveritas.com)

**Web Site:** [www.bureauveritas-adt.com](http://www.bureauveritas-adt.com)

The address and road map of all our labs can be found in our web site also.

--- END ---