

EMC TEST REPORT

for

Power

MODEL:

TPP100-112A	TPP100-112U	TPP100-112	TPP100-112D	TPP100-112BA	TPP100-112BU	TPP100-112B	TPP100-112BD
TPP100-115A	TPP100-115U	TPP100-115	TPP100-115D	TPP100-115BA	TPP100-115BU	TPP100-115B	TPP100-115BD
TPP100-124A	TPP100-124U	TPP100-124	TPP100-124D	TPP100-124BA	TPP100-124BU	TPP100-124B	TPP100-124BD
TPP100-128A	TPP100-128U	TPP100-128	TPP100-128D	TPP100-128BA	TPP100-128BU	TPP100-128B	TPP100-128BD
TPP100-136A	TPP100-136U	TPP100-136	TPP100-136D	TPP100-136BA	TPP100-136BU	TPP100-136B	TPP100-136BD
TPP100-148A	TPP100-148U	TPP100-148	TPP100-148D	TPP100-148BA	TPP100-148BU	TPP100-148B	TPP100-148BD

Test Report Number:

T170214E01-E-1

Issued for

TRACO ELECTRONIC AG

Sihlbruggstrasse 111 CH-6340 Baar Switzerland

Issued By:

Compliance Certification Services Inc.

Wugu Laboratory

No.11, Wugong 6th Rd., Wugu Dist.,
New Taipei City 24891, Taiwan. (R.O.C.)

TEL: 886-2-2299-9720

FAX: 886-2-2299-9721

Issued Date: February 16, 2017



Note: This report shall not be reproduced except in full, without the written approval of Compliance Certification Services Inc. This document may be altered or revised by Compliance Certification Services Inc. personnel only, and shall be noted in the revision section of the document. The client should not use it to claim product endorsement by TAF, A2LA, NIST or any government agencies. The test results in the report only apply to the tested sample.

Revision History

Rev.	Issue Date	Revisions	Effect Page	Revised By
00	February 16, 2017	Initial Issue	ALL	Angel Cheng

TABLE OF CONTENTS

1 TEST CERTIFICATION4

2 TEST RESULT SUMMARY5

3 EUT DESCRIPTION6

4 TEST METHODOLOGY8

4.1. DECISION OF FINAL TEST MODE 8

4.2. EUT SYSTEM OPERATION 8

5 SETUP OF EQUIPMENT UNDER TEST9

5.1. DESCRIPTION OF SUPPORT UNITS..... 9

5.2. CONFIGURATION OF SYSTEM UNDER TEST 10

6 FACILITIES AND ACCREDITATIONS..... 11

6.1. FACILITIES 11

6.2. ACCREDITATIONS 11

6.3. MEASUREMENT UNCERTAINTY 12

7 EMISSION TEST13

7.1. CONDUCTED EMISSION MEASUREMENT 13

7.2. RADIATED EMISSION MEASUREMENT 19

7.3. HARMONICS CURRENT MEASUREMENT 26

7.4. VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT 29

8 IMMUNITY TEST32

8.1. GENERAL DESCRIPTION..... 32

8.2. GENERAL PERFORMANCE CRITERIA DESCRIPTION 33

8.3. ELECTROSTATIC DISCHARGE (ESD) 34

8.4. RADIATED, RADIO-FREQUENCY, ELECTROMAGNETIC FIELD (RS) 39

8.5. ELECTRICAL FAST TRANSIENT (EFT) 47

8.6. SURGE IMMUNITY TEST 50

8.7. CONDUCTED RADIO FREQUENCY DISTURBANCES (CS) 53

8.8. POWER FREQUENCY MAGNETIC FIELD 57

8.9. VOLTAGE DIP & VOLTAGE INTERRUPTIONS..... 60

9 PHOTOGRAPHS OF THE TEST CONFIGURATION.....63

1 TEST CERTIFICATION

Product: Power

Model:

TPP100-112A	TPP100-124U	TPP100-136	TPP100-112BA	TPP100-124BU	TPP100-136B
TPP100-115A	TPP100-128U	TPP100-148	TPP100-115BA	TPP100-128BU	TPP100-148B
TPP100-124A	TPP100-136U	TPP100-112D	TPP100-124BA	TPP100-136BU	TPP100-112BD
TPP100-128A	TPP100-148U	TPP100-115D	TPP100-128BA	TPP100-148BU	TPP100-115BD
TPP100-136A	TPP100-112	TPP100-124D	TPP100-136BA	TPP100-112B	TPP100-124BD
TPP100-148A	TPP100-115	TPP100-128D	TPP100-148BA	TPP100-115B	TPP100-128BD
TPP100-112U	TPP100-124	TPP100-136D	TPP100-112BU	TPP100-124B	TPP100-136BD
TPP100-115U	TPP100-128	TPP100-148D	TPP100-115BU	TPP100-128B	TPP100-148BD

Brand: TRACO POWER

Applicant: **TRACO ELECTRONIC AG**
Sihlbruggstrasse 111 CH-6340 Baar Switzerland

Manufacturer: **TRACO ELECTRONIC AG**
Sihlbruggstrasse 111 CH-6340 Baar Switzerland

Tested: February 06, 2013 ~ January 24, 2017

Applicable Standards: **EN 60601-1-2:2015**
EN 55011: 2009/A1:2010
CISPR 11: 2009/A1:2010
IEC 61000-4-2:2008
IEC 61000-4-3:2006+A1:2007+A2:2010
IEC 61000-4-4:2012
IEC 61000-4-5:2005
IEC 61000-4-6:2013
IEC 61000-4-8:2009
IEC 61000-4-11:2004
IEC 61000-3-2:2005+A1:2008+A2:2009
IEC 61000-3-3:2013

Deviation from Applicable Standard


None

The above equipment has been tested by Compliance Certification Services Inc., and found compliance with the requirements set forth in the technical standards mentioned above. The results of testing in this report apply only to the product/system, which was tested. Other similar equipment will not necessarily produce the same results due to production tolerance and measurement uncertainties.

Approved by:



Reviewed by:



Tony Hsu
Asst. Manager

Rex Chen
Engineer

2 TEST RESULT SUMMARY

EMISSION			
Standard	Item	Result	Remarks
(Group 1, Class B) EN 55011: 2009/A1:2010 CISPR 11: 2009/A1:2010	Conducted (Power Port)	PASS	Meet Class B limit
	Radiated	PASS	Meet Class A limit
IEC 61000-3-2:2005+A1:2008+A2:2009	Harmonic current emissions	PASS	Meet Class D limit
IEC 61000-3-3:2013	Voltage fluctuations & flicker	PASS	Meets the requirements

IMMUNITY			
Standard	Item	Result	Remarks
IEC 61000-4-2:2008	ESD	PASS	See Item 8.3 of this report
IEC 61000-4-3:2006+A1:2007+A2:2010	RS	PASS	See Item 8.4 of this report
IEC 61000-4-4:2012	EFT	PASS	See Item 8.5 of this report
IEC 61000-4-5:2005	Surge	PASS	See Item 8.6 of this report
IEC 61000-4-6:2013	CS	PASS	See Item 8.7 of this report
IEC 61000-4-8:2009	PFMF	PASS	See Item 8.8 of this report
IEC 61000-4-11:2004	Voltage dips & short interruptions	PASS	See Item 8.9 of this report

- Note:**
1. The statements of test result on the above are decided by the request of test standard only; the measurement uncertainties are not factored into this compliance determination.
 2. The information of measurement uncertainty is available upon the customer's request.

3 EUT DESCRIPTION

Product	Power					
Brand Name	TRACO POWER					
Model	TPP100-112A	TPP100-124U	TPP100-136	TPP100-112BA	TPP100-124BU	TPP100-136B
	TPP100-115A	TPP100-128U	TPP100-148	TPP100-115BA	TPP100-128BU	TPP100-148B
	TPP100-124A	TPP100-136U	TPP100-112D	TPP100-124BA	TPP100-136BU	TPP100-112BD
	TPP100-128A	TPP100-148U	TPP100-115D	TPP100-128BA	TPP100-148BU	TPP100-115BD
	TPP100-136A	TPP100-112	TPP100-124D	TPP100-136BA	TPP100-112B	TPP100-124BD
	TPP100-148A	TPP100-115	TPP100-128D	TPP100-148BA	TPP100-115B	TPP100-128BD
	TPP100-112U	TPP100-124	TPP100-136D	TPP100-112BU	TPP100-124B	TPP100-136BD
	TPP100-115U	TPP100-128	TPP100-148D	TPP100-115BU	TPP100-128B	TPP100-148BD
Applicant	TRACO ELECTRONIC AG					
Housing material	Plastic					
Identify Number	T170214E01					
Received Date	February 14, 2017					
EUT Power Rating	48VDC 2.09A					
Power Adapter Manufacturer	TRACO ELECTRONIC AG			Model	TPP100-148BA	
Power Adapter Power Rating	I/P: 85-264VAC, 50-60Hz, 2.09A O/P: 48VDC, 2.09A					
AC Power Cord Type	Shielded, 1.8m (Non-Detachable) to Power Adapter					

Note:1. The difference of the model.

Model Name		Input Range	Output Voltage	Output Current
TPP100-112BA	TPP100-112A	85 – 264 VAC	12 VDC	8.34A
TPP100-115BA	TPP100-115A	85 – 264 VAC	15 VDC	6.67A
TPP100-124A	TPP100-124BA	85 – 264 VAC	24 VDC	4.17A
TPP100-128BA	TPP100-128A	85 – 264 VAC	28 VDC	3.58A
TPP100-136BA	TPP100-136A	85 – 264 VAC	36 VDC	2.78A
TPP100-148BA	TPP100-148A	85 – 264 VAC	48 VDC	2.09A
TPP100-112BU	TPP100-112U	85 – 264 VAC	12 VDC	8.34A
TPP100-115BU	TPP100-115U	85 – 264 VAC	15 VDC	6.67A
TPP100-124BU	TPP100-124U	85 – 264 VAC	24 VDC	4.17A
TPP100-128BU	TPP100-128U	85 – 264 VAC	28 VDC	3.58A
TPP100-136BU	TPP100-136U	85 – 264 VAC	36 VDC	2.78A
TPP100-148BU	TPP100-148U	85 – 264 VAC	48 VDC	2.09A
TPP100-112B, TPP100-112BD	TPP100-112, TPP100-112D	85 – 264 VAC	12 VDC	8.34A
TPP100-115B, TPP100-115BD	TPP100-115, TPP100-115D	85 – 264 VAC	15 VDC	6.67A
TPP100-124B, TPP100-124BD	TPP100-124, TPP100-124D	85 – 264 VAC	24 VDC	4.17A
TPP100-128B, TPP100-128BD	TPP100-128, TPP100-128D	85 – 264 VAC	28 VDC	3.58A
TPP100-136B, TPP100-136BD	TPP100-136, TPP100-136D	85 – 264 VAC	36 VDC	2.78A
TPP100-148B, TPP100-148BD	TPP100-148, TPP100-148D	85 – 264 VAC	48 VDC	2.09A

1. For more details, please refer to the User's manual of the EUT.
2. The model TPP100-148BA was considered the main model for testing.

I/O PORT

I/O PORT TYPES	Q'TY	TESTED WITH
1. DC Port	1	1
2. AC Port	1	1

4 TEST METHODOLOGY

4.1. DECISION OF FINAL TEST MODE

The EUT was tested together with the above additional components, and a configuration, which produced the worst emission levels, was selected and recorded in this report.

The test configuration / modes are as the following:

1. The following test mode was scanned during the preliminary test:

Pre-Test Mode	
Mode 1: Full Load (TPP100-148BA)	

2. After the preliminary scan, the following test mode was found to produce the highest emission level.

Final Test Mode		
Emission	Conducted Emission	Mode 1
	Radiated Emission	Mode 1
Immunity		Mode 1

Then, the above highest emission mode of the configuration of the EUT and cable was chosen for all final test items.

4.2. EUT SYSTEM OPERATION

- | |
|---|
| <ol style="list-style-type: none"> 1. Setup the EUT and simulators as shown on 5.2. 2. Turn on the power of all equipment. 3. Adjust to the test mode, and begin the test. |
|---|

Note: Test program is self-repeating throughout the test.

5 SETUP OF EQUIPMENT UNDER TEST

5.1. DESCRIPTION OF SUPPORT UNITS

The EUT has been tested as an independent unit together with other necessary accessories or support units. The following support units or accessories were used to form a representative test configuration during the tests.

Peripherals Devices:


No.	Equipment	Model No.	Serial No.	FCC ID / BSMI ID	Trade Name	Power Cord
1.	Load	10W1.2KJ*3 20W10RJ*8	N/A	N/A	N/A	N/A
2.	Ammeter	DM-3000	N/A	N/A	HOLA	N/A

No.	Cable Name	Unit	Shielded	Length	With Core
(A)	Signal Cable	1	<input type="checkbox"/> Shielded, <input checked="" type="checkbox"/> Non	1.8 m	<input type="checkbox"/> With Core, <input checked="" type="checkbox"/> Non
(B)	Signal Cable	1	<input type="checkbox"/> Shielded, <input checked="" type="checkbox"/> Non	0.2 m	<input type="checkbox"/> With Core, <input checked="" type="checkbox"/> Non

Note:

1. All the equipment/cables were placed in the worst-case configuration to maximize the emission during the test.
2. Grounding was established in accordance with the manufacturer's requirements and conditions for the intended use.

5.2. CONFIGURATION OF SYSTEM UNDER TEST



6 FACILITIES AND ACCREDITATIONS

6.1. FACILITIES

All measurement facilities used to collect the measurement data are located at:

- No.11, Wugong 6th Rd., Wugu Dist., New Taipei City 24891, Taiwan. (R.O.C.)
- No.139, Wugong Rd., Wugu Dist., New Taipei City 24886, Taiwan. (R.O.C.)
- No.163-1, Jhongsheng Rd. Sindian City, Taipei County 23151, Taiwan.

The sites are constructed in conformance with the requirements of ANSI C63.4 and CISPR Publication 22. All receiving equipment conforms to CISPR 16-1-1, CISPR 16-1-2, CISPR 16-1-3, CISPR 16-1-4 and CISPR 16-1-5.

6.2. ACCREDITATIONS

Our laboratories are accredited and approved by the following accreditation body according to ISO/IEC 17025.

Taiwan	TAF (TAF 1309)
USA	A2LA (0824.01)

The measuring facility of laboratories has been authorized or registered by the following approval agencies.

Canada	Industry Canada (3M Semi Anechoic Chamber: IC 2324G-1 / IC 2324G-2 / 2324J-1 / 2324J-2 to perform)
Norway	Nemko
Japan	VCCI Radiated emissions: 30 MHz -1000 MHz: R-3283 / Above 1GHz: G-147 Conducted Emission B: C-3700 / T-1839
USA	FCC (3M Semi Anechoic Chamber (FCC MRA: TW1039) to perform FCC Part 15 measurements)

Copies of granted accreditation certificates are available for downloading from our web site,

<http://www.ccsrf.com>

6.3. MEASUREMENT UNCERTAINTY

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT as specified in CISPR 16-4-2:

Measurement	Frequency	Uncertainty
Conducted emissions	0.15MHz ~ 30MHz	±1.2575 dB
Radiated emissions	30MHz ~ 200MHz	±3.9163 dB
	200MHz ~1000MHz	±3.9030 dB

This uncertainty represents an expanded uncertainty expressed at approximately the 95% confidence level using a coverage factor of k=2.

Consistent with industry standard (e.g. CISPR 22:2008, clause 11, Measurement Uncertainty) determining compliance with the limits shall be base on the results of the compliance measurement. Consequently the measure emissions being less than the maximum allowed emission result in this be a compliant test or passing test.

The acceptable measurement uncertainty value without requiring revision of the compliance statement is base on conducted and radiated emissions being less than U_{CISPR} which is 3.6dB and 5.2dB respectively. CCS values (called U_{Lab} in CISPR 16-4-2) is less than U_{CISPR} as shown in the table above. Therefore, MU need not be considered for compliance.

7 EMISSION TEST

7.1. CONDUCTED EMISSION MEASUREMENT

7.1.1. LIMITS

CLASS A

FREQUENCY (MHz)	Group 1		Group 2		Group 2*	
	Quasi-peak (dBuV)	Average (dBuV)	Quasi-peak (dBuV)	Average (dBuV)	Quasi-peak (dBuV)	Average (dBuV)
0.15 - 0.5	79	66	100	90	130	120
0.50 - 5.0	73	60	86	76	125	115
5.0 - 30.0	73	60	90-70	80-60	115	105
			Decreasing linearly with logarithm of frequency			

* Mains supply currents in excess of 100 A per phase when using the CISPR voltage probe or a suitable V-network (LISN or AMN).

Note:

1. The lower limit shall apply at the transition frequency
2. Care should be taken to comply with leakage current requirements.

CLASS B

FREQUENCY (MHz)	Group 1 & 2	
	Quasi-peak (dBuV)	Average (dBuV)
0.15 - 0.5	66-56 Decreasing linearly with logarithm of frequency	56-46 Decreasing linearly with logarithm of frequency
0.50 - 5.0	56	46
5.0 - 30.0	60	50

Note:

1. The lower limit shall apply at the transition frequency
2. Care should be taken to comply with leakage current requirements.

7.1.2. TEST INSTRUMENTS

Conducted Emission Room # B				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
EMI Test Receiver	R&S	ESCI	101073	07/31/2013
LISN	R&S	ENV216	101054	06/06/2013
LISN	EMCO	3825/2	9106-1809	07/03/2013
ISN	FCC	FCC-TLISN-T2-02-09	100105	07/30/2013
ISN	FCC	FCC-TLISN-T4-02-09	20395	05/24/2013
ISN	FCC	FCC-TLISN-T8-02-09	100106	07/31/2013
Capacitive Voltage Probe	FCC	F-CVP-1	100185	03/25/2013
Test S/W	CCS-3A1-CE			

Note:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.


7.1.3. TEST PROCEDURES (please refer to measurement standard or CCS SOP PA-031)**Procedure of Preliminary Test**

- The EUT was set up as per the test configuration to simulate typical usage per the user's manual. When the EUT is a tabletop system, a wooden table with a height of 0.8 meters is used and is placed on the ground plane as per CISPR 11 (see Test Facility for the dimensions of the ground plane used). When the EUT is a floor-standing equipment, it is placed on the ground plane which has a 3-12 mm non-conductive covering to insulate the EUT from the ground plane.
- Support equipment, if needed, was placed as per CISPR 11.
- All I/O cables were positioned to simulate typical actual usage as per CISPR 11.
- The test equipment EUT installed received AC power, 230VAC/50Hz, through a Line Impedance Stabilization Network (LISN), which supplied power source and was grounded to the ground plane.
- All support equipment received power from a second LISN.
- The EUT test program was started. Emissions were measured on each current carrying line of the EUT using an EMI Test Receiver connected to the LISN powering the EUT.
- The Receiver scanned from 150 kHz to 30MHz for emissions in each of the test modes.
- During the above scans, the emissions were maximized by cable manipulation.
- The test mode(s) described in Item 3.2 were scanned during the preliminary test.
- After the preliminary scan, we found the test mode described in Item 3.2 producing the highest emission level.
- The worst configuration of EUT and cable of the above highest emission level were recorded for reference of the final test.

Procedure of Final Test

- EUT and support equipment were set up on the test bench as per the configuration with highest emission level in the preliminary test.
- A scan was taken on both power lines, Line 1 and Line 2, recording at least the six highest emissions. Emission frequency and amplitude were recorded into a computer in which correction factors were used to calculate the emission level and compare reading to the applicable limit. If EUT emission level was less -2dB to the Average limit in Q.P. mode, then the emission signal was re-checked using an Average detector.
- The test data of the worst-case condition(s) was recorded.

7.1.4. TEST SETUP



- For the actual test configuration, please refer to the related item - Photographs of the Test Configuration.

7.1.5. DATA SAMPLE

Freq. (MHz)	Read Level (dBuV)	Factor (dB)	Level (dBuV)	Limit Line (dBuV)	Over Limit (dB)	Remark (P/Q/A)	Line (L1/L2)
x.xx	42.95	0.55	43.50	56	-12.50	Q	L1


- Freq. = Emission frequency in MHz
- Read Level = Uncorrected Analyzer/Receiver reading
- Factor = Insertion loss of LISN + Cable Loss
- Level = Read Level + Factor
- Limit Line = Limit stated in standard
- Over Limit = Reading in reference to limit
- P = Peak Reading
- Q = Quasi-peak Reading
- A = Average Reading
- L1 = Hot side
- L2 = Neutral side

Calculation Formula

Over Limit (dB) = Level (dBuV) – Limit Line (dBuV)

7.1.6. TEST RESULTS


Model No.	TPP100-148BA	Line:	L1
Environmental Conditions	24°C, 50% RH	Test Date	2013/02/08
Tested by	Moore Cheng	Test Mode	Mode 1



NO	Frequency (MHz)	Quasi Peak reading (dBuV)	Average reading (dBuV)	Correction factor (dB)	Quasi Peak result (dBuV)	Average result (dBuV)	Quasi Peak limit (dBuV)	Average limit (dBuV)	Quasi Peak margin (dB)	Average margin (dB)	Remark
1*	0.1500	55.09	45.69	9.87	64.96	55.56	65.99	56.00	-1.03	-0.44	Pass
2	0.1581	53.40	43.81	9.87	63.27	53.68	65.56	55.56	-2.29	-1.88	Pass
3	0.1718	50.32	40.43	9.87	60.19	50.30	64.87	54.87	-4.68	-4.57	Pass
4	0.2171	45.66	36.49	9.87	55.53	46.36	62.93	52.93	-7.40	-6.57	Pass
5	0.2311	44.17	35.03	9.87	54.04	44.90	62.41	52.41	-8.37	-7.51	Pass
6	0.3875	36.89	24.59	9.88	46.77	34.47	58.12	48.12	-11.35	-13.65	Pass
7	3.5716	33.49	27.04	10.00	43.49	37.04	56.00	46.00	-12.51	-8.96	Pass
8	3.9963	33.10	27.09	10.01	43.11	37.10	56.00	46.00	-12.89	-8.90	Pass
9	14.0196	34.37	29.09	10.24	44.61	39.33	60.00	50.00	-15.39	-10.67	Pass

REMARKS: L1 = Line One (Live Line)

Model No.	TPP100-148BA	Line:	L2
Environmental Conditions	24°C, 50% RH	Test Date	2013/02/08
Tested by	Moore Cheng	Test Mode	Mode 1



NO	Frequency (MHz)	Quasi Peak reading (dBuV)	Average reading (dBuV)	Correction factor (dB)	Quasi Peak result (dBuV)	Average result (dBuV)	Quasi Peak limit (dBuV)	Average limit (dBuV)	Quasi Peak margin (dB)	Average margin (dB)	Remark
1*	0.1540	55.47	45.79	9.63	65.10	55.42	65.78	55.78	-0.68	-0.36	Pass
2	0.1588	53.11	44.01	9.63	62.74	53.64	65.53	55.53	-2.79	-1.89	Pass
3	0.1757	50.32	40.86	9.64	59.96	50.50	64.69	54.69	-4.73	-4.19	Pass
4	0.1904	48.68	39.56	9.64	58.32	49.20	64.02	54.02	-5.70	-4.82	Pass
5	0.2313	44.11	35.63	9.64	53.75	45.27	62.40	52.40	-8.65	-7.13	Pass
6	0.3630	35.95	25.46	9.66	45.61	35.12	58.66	48.66	-13.05	-13.54	Pass
7	3.7014	34.50	28.66	9.79	44.29	38.45	56.00	46.00	-11.71	-7.55	Pass
8	4.3790	32.62	26.66	9.82	42.44	36.48	56.00	46.00	-13.56	-9.52	Pass
9	12.8945	34.62	29.34	10.06	44.68	39.40	60.00	50.00	-15.32	-10.60	Pass

REMARKS: L2 = Line Two (Neutral Line)

7.2. RADIATED EMISSION MEASUREMENT

7.2.1. LIMITS

FREQUENCY (MHz)	Measured on a test site		Measured in situation
	Group 1, class A	Group 1, class B	Group 1, class A Limits with measuring distance 30 m from exterior wall outside the building in which the equipment is situated
	Quasi-peak (dBuV/m)	Quasi-peak (dBuV/m)	
0.15 - 30	Under consideration	Under consideration	Under consideration
30 - 230	40	30	30
230 - 1000	47	37	37

Note:

1. The lower limit shall apply at the transition frequencies.
2. Emission level (dBuV/m) = 20 log Emission level (uV/m).

7.2.2. TEST INSTRUMENTS

Wugu 10M Chamber				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
Bilog Antenna	TESEQ	CBL 6112D	31674	03/20/2017
Bilog Antenna	TESEQ	CBL 6112D	31675	03/20/2017
Coaxial Cable	Huber+Suhner	104	330026	05/02/2017
Coaxial Cable	Huber+Suhner	SUCOFLEX 104PEA	330028	05/02/2017
Coaxial Cable	Huber+Suhner	SUCOFLEX 104PEA	329383	05/02/2017
Coaxial Cable	Huber+Suhner	104PEA	33948/4PEA	05/02/2017
Coaxial Cable	Huber+Suhner	104PEA	33949/4PEA	05/02/2017
EMI Test Receiver	R&S	ESCI	100961	08/03/2017
EMI Test Receiver	R&S	ESCI	100962	08/12/2017
Horn Antenna	EMCO	3117	00055167	01/08/2018
Horn Antenna	ETS LINDGREN	3116	00026370	01/11/2018
Pre-Amplifier	HP	8447D	2944A07754	05/02/2017
Pre-Amplifier	HP	8447D	2944A08150	05/02/2017
Pre-Amplifier	EMC	EMC051845	980040	05/02/2017
Pre-Amplifier	MITEQ	AMF-6F-260400-40-8P	985646	01/09/2018
Spectrum Analyzer	Agilent	E4446A	MY48250297	09/08/2017
Thermo-Hygro Meter	ROTRONIC	M800	0GYJ	11/14/2017
AC POWER SOURE	APE	AFC-130	991259	N.C.R
Antenna Tower	CCS	CC-A-1F	N/A	N.C.R
Antenna Tower	Sunol Sciences	TLT2	031010-5	N.C.R
Coaxial Cable	Huber+Suhner	104	330029/4	N.C.R
Coaxial Cable	Huber+Suhner	SF104PEA	33946	N.C.R
Coaxial Cable	Huber+Suhner	SF104PEA	33947	N.C.R
Controller	CCS	CC-C-1F	N/A	N.C.R
Controller	Sunol Sciences	SC104V	031010-1	N.C.R
Turn Table	CCS	CC-T-1F	N/A	N.C.R
Software	EZ-EMC (CCS-3A1RE)			

Note:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R. = No Calibration Required.


7.2.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-031)**Frequency range 30MHz ~ 1GHz**

1. The EUT was placed on the top of a rotating table 0.8 meters above the ground at a 10 meter semi-anechoic chamber room. The table was rotated 360 degrees to determine the position.
2. The EUT was set 10 meters away from the interference-receiving antenna, which was mounted on the top of a variable-height antenna tower.
3. The height of antenna is varied from one meter to four meter above the ground to determine the maximum value of the field strength. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
4. For each suspected emission, the EUT was arranged to its worst case and then the antenna was turned to heights for 1 meter to 4 meters and the turn table was turned from 0 degrees to 360 degrees to find the maximum reading.
5. The test-receiver system was set to quasi-peak detect function and specified bandwidth with maximum hold mode when the test frequency is below 1GHz.

NOTE: The resolution bandwidth of test receiver/spectrum analyzer is 120 kHz for Quasi-peak detection (QP) at frequency below 1GHz.

7.2.4. TEST SETUP

Below 1GHz



- For the actual test configuration, please refer to the related item - Photographs of the Test Configuration.

7.2.5. DATA SAMPLE

Below 1GHz


Frequency (MHz)	Reading (dBuV)	Correction Factor (dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Height (cm)	Degree (°)	Remark
xx.xx	16.49	9.86	26.35	30.00	-3.65	116.00	101.00	QP

- Frequency (MHz) = Emission frequency in MHz
- Reading (dBuV) = Uncorrected Analyzer / Receiver reading
- Correction Factor (dB/m) = Antenna factor + Cable loss – Amplifier gain
- Result (dBuV/m) = Reading (dBuV) + Corr. Factor (dB/m)
- Limit (dBuV/m) = Limit stated in standard
- Margin (dB) = Result (dBuV/m) – Limit (dBuV/m)
- Q.P. = Quasi-Peak

7.2.6. TEST RESULTS

Below 1GHz

Model No.	TPP100-148BA	Test Mode	Mode 1
Environmental Conditions	26°C, 60% RH	Test Date	2017/1/24
Antenna Pole	Vertical	Antenna Distance	10m
Detector Function	Quasi-peak.	Tested by	Ming Fan




No.	Frequency (MHz)	Reading (dBuV)	Correction Factor(dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Height (cm)	Degree (°)	Remark
1	32.9100	37.55	-4.22	33.33	40.00	-6.67	110	353	peak
2	63.9500	51.88	-14.18	37.70	40.00	-2.30	252	96	QP
3	93.0500	43.61	-10.51	33.10	40.00	-6.90	100	353	QP
4	148.3400	42.60	-8.60	34.00	40.00	-6.00	399	1	QP
5	207.5100	40.74	-9.44	31.30	40.00	-8.70	211	34	QP
6	407.3300	29.01	-2.28	26.73	47.00	-20.27	100	0	peak

Note:

1. PK= Peak Reading; QP= Quasi-peak Reading.
2. The other emission levels were very low against the limit.

Model No.	TPP100-148BA	Test Mode	Mode 1
Environmental Conditions	26°C, 60% RH	Test Date	2017/1/24
Antenna Pole	Horizontal	Antenna Distance	10m
Detector Function	Quasi-peak.	Tested by	Ming Fan



No.	Frequency (MHz)	Reading (dBuV)	Correction Factor(dB/m)	Result (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Height (cm)	Degree (°)	Remark
1	59.1000	40.88	-15.11	25.77	40.00	-14.23	400	105	peak
2	88.2000	39.86	-12.67	27.19	40.00	-12.81	286	96	peak
3	150.2800	36.34	-9.97	26.37	40.00	-13.63	143	114	peak
4	200.7200	44.55	-10.86	33.69	40.00	-6.31	400	105	peak
5	285.1100	31.96	-6.49	25.47	47.00	-21.53	299	96	peak
6	368.5300	30.43	-4.59	25.84	47.00	-21.16	125	114	peak

Note:

1. PK= Peak Reading; QP= Quasi-peak Reading.
2. The other emission levels were very low against the limit.

Above 1GHz

Model No.	N/A	Test Mode	N/A
Environmental Conditions	N/A	6dB Bandwidth	N/A
Antenna Pole	N/A	Antenna Distance	N/A
Highest frequency generated or used	60kHz	Upper frequency	1000MHz
Detector Function	N/A	Tested by	N/A

Note: No applicable, when the highest frequency of the internal sources of the EUT is less than 108MHz, the measurement shall only be made up to 1 GHz.

7.3. HARMONICS CURRENT MEASUREMENT

7.3.1. LIMITS OF HARMONICS CURRENT MEASUREMENT

Limits for Class A equipment		Limits for Class D equipment		
Harmonics Order n	Max. permissible harmonics current A	Harmonics Order n	Max. permissible harmonics current per watt mA/W	Max. permissible harmonics current A
Odd harmonics		Odd Harmonics only		
3	2.30	3	3.4	2.30
5	1.14	5	1.9	1.14
7	0.77	7	1.0	0.77
9	0.40	9	0.5	0.40
11	0.33	11	0.35	0.33
13	0.21	13	0.30	0.21
15<=n<=39	0.15x15/n	15<=n<=39	3.85/n	0.15x15/n
Even harmonics				
2	1.08			
4	0.43			
6	0.30			
8<=n<=40	0.23x8/n			

Note:

1. Class A and Class D are classified according to item 7.4.3.
2. According to section 7 of IEC 61000-3-2, the above limits for all equipment except for lighting equipment having an active input power > 75 W and no limits apply for equipment with an active input power up to and including 75 W.

7.3.2. TEST INSTRUMENTS


Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
HARMONICS SYSTEM	EMC-PARTNER	HARMONICS-1000	107	08/27/2013
Test S/W	HARCS Immunity (4.10)			

Note: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

7.3.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-029)

- The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the maximum harmonic components under normal operating conditions for each successive harmonic component in turn.
- The classification of EUT is according to section 5 of EN 61000-3-2.
- The EUT is classified as follows:
Class A: Balanced three-phase equipment, Household appliances excluding equipment as Class D, Tools excluding portable tools, Dimmers for incandescent lamps, audio equipment, equipment not specified in one of the three other classes.
Class B: Portable tools; Arc welding equipment which is not professional equipment.
Class C: Lighting equipment.
Class D: Equipment having a specified power less than or equal to 600 W of the following types: Personal computers and personal computer monitors and television receivers.
- The correspondent test program of test instrument to measure the current harmonics emanated from EUT is chosen. The measure time shall be not less than the time necessary for the EUT to be exercised.

7.3.4. TEST SETUP




- For the actual test configuration, please refer to the related item - Photographs of the Test Configuration.

7.3.5. TEST RESULTS

Power Consumption	94.71W	Test Mode	Operating
Environmental Conditions	25°C, 49% RH	Tested by	Michael Chen

Test result of EN 61000-3-2

Operator : Michael Chen
 EUT : Power
 Model : TPP100-148BA
 Remarks : Temp: 25°C;Hum: 49% RH;Press 999mbar



Harmonic Emission - IEC 61000-3-2 , EN 61000-3-2 , (EN60555-2)

2013/2/7 PM 02:16:56

U_{rms} = 229.3 V P = 94.71 W THC = 0.084 A Range: 1 A
 I_{rms} = 0.429 A pf = 0.963 P_{max} = 94.69 W V_{nom}: 230 V
 TestTime: 5 min (100%)

Power **Test completed, Result: PASSED**

Temp: 25°C; Hum: 49% ; Press 999mbar

HAR-1000 EMC-Reter

Full Bar : Actual Values
 Empty Bar : Maximum Values
 Blue : Current , Green : Voltage , Red : Failed

Note:

- Limits classified according to item 7.3.3.
- According to clause 7 of IEC 61000-3-2:2005+A1:2008+A2:2009, equipment with a rated power of 75W or less, no limits apply. The test result is only for reference.

7.4. VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT

7.4.1. LIMITS OF VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT

TEST ITEM	LIMIT	REMARK
P_{st}	1.0	P_{st} means short-term flicker indicator.
P_{lt}	0.65	P_{lt} means long-term flicker indicator.
T_{dt} (ms)	500	T_{dt} means maximum time that dt exceeds 3.3 %.
d_{max} (%)	4%	d_{max} means maximum relative voltage change.
dc (%)	3.3%	dc means relative steady-state voltage change

7.4.2. TEST INSTRUMENTS


IMMUNITY SHIELDED ROOM				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
HARMONICS SYSTEM	EMC-PARTNER	HARMONICS-1000	107	08/27/2013
Test S/W	HARCS Immunity (4.10)			

Note: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

7.4.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-030)

- The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the most unfavorable sequence of voltage changes under normal operating conditions.
- During the flick measurement, the measure time shall include that part of whole operation cycle in which the EUT produce the most unfavorable sequence of voltage changes. The observation period for short-term flicker indicator is 10 minutes and the observation period for long-term flicker indicator is 2 hours.

7.4.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

7.4.5. TEST RESULTS

Observation Period (Tp)	12mins	Test Mode	Operating
Environmental Conditions	24°C, 45% RH, 999mbar	Tested by	Michael Chen


TEST PARAMETER	MEASUREMENT VALUE	LIMIT	REMARK
P _{st}	0.07	1.0	Pass
P _{lt}	0.07	0.65	Pass
T _{dt} (ms)	0.00	500	Pass
d _{max} (%)	0.00	4%	Pass
dc (%)	0.00	3.3%	Pass

Note: None.

Test result of EN 61000-3-3

Operator : Michael Chen
 EUT : Power
 Model : TPP100-148BA
 Remarks : Temp: 24°C; Hum: 45% RH; Press 999mbar

Flickermeter 1000-4-15 for 230V/50Hz



Actual Flicker (Fli): 0.00
Short-term Flicker (Pst): 0.07
 Limit (Pst): 1.00
Long-term Flicker (Plt): 0.07
 Limit (Plt): 0.65
Maximum Relative Volt. Change (dmax): 0.00%
 Limit (dmax): 4.00%
Relative Steady-state Voltage Change (dc): 0.00%
 Limit (dc): 3.00%
Maximum Interval exceeding 3.30% (dt): 0.00ms
 Limit (dt>Lim): 500ms

Flicker Emission - IEC 61000-3-3 , EN 61000-3-3 , (EN60555-3)

2013/2/7 PM 02:32:39

U_{rms} = 229.1 V P = 95.71 W
 I_{rms} = 0.433 A pf = 0.965

Range: 1 A
 V_{nom}: 230 V
 TestTime: 12 min (100%)

Power

Test completed, Result: PASSED

Temp: 24°C; Hum: 45% ; Press 999mbar

HAR-1000 BMC-Reter

Full Bar : Actual Values
 Empty Bar : Maximum Values
 Circles : Average Values
 Blue : Current , Green : Voltage , Red : Failed

8 IMMUNITY TEST

8.1. GENERAL DESCRIPTION

Product Standard	Immunity	
	Test Type	Minimum Requirement
Basic Standard, Specification, and Performance Criterion required	IEC 61000-4-2	Electrostatic Discharge - ESD: 15kV air discharge, 8kV Contact discharge Criterion required please see 8.2
	IEC 61000-4-3	3 V/m at 80 - 2,700MHz, (10V/m Home Healthcare) AM Modulation. And 9-28V/m at 385-6000MHz, Pulse Mode and other Modulation Criterion required please see 8.2
	IEC 61000-4-4	Electrical Fast Transient/Burst - EFT, AC Power Port: 2kV Signal cable greater than 3 meters: 1kV Criterion required please see 8.2 Interconnect Lines at 100kHz rate
	IEC 61000-4-5	Surge Immunity Test: 1.2/50 us Open Circuit Voltage, 8 /20 us Short Circuit Current, AC Power Port ~ line to line: 1kV, line to earth (ground): 2kV Criterion required please see 8.2
	IEC 61000-4-6	3V at 0.15 – 80MHz & 6V at ISM Home Healthcare: Freq 3V at 0.15 – 80MHz, and 6V at ISM & Radio Amateur Freq Criterion required please see 8.2
	IEC 61000-4-8	Power frequency magnetic field immunity test 50 Hz/60Hz, 30A/m Criterion required please see 8.2
	IEC 61000-4-11	Voltage Dips: 0% Ut for 0.5 Cycle 0% Ut for 1 cycle; 70% Ut for 25 cycles Voltage Interruptions: 0% for 5 sec. Criterion required please see 8.2

8.2. GENERAL PERFORMANCE CRITERIA DESCRIPTION

Compliance Criteria:

Under the test conditions specified in 6.2.1.10 of EN 60601-1-2, the ME EQUIPMENT or ME SYSTEM shall be able to provide the BASIC SAFETY and ESSENTIAL PERFORMANCE. The following DEGRADATIONS, if associated with BASIC SAFETY and ESSENTIAL PERFORMANCE, shall not be allowed:

- Component failures
- Changes in programmable parameters
- Reset to factory defaults (manufacturer's presets)
- Chang of operating mode
- False alarms
- Cessation or interruption of any intended operation, even if accompanied by an alarm
- Initiation of any unintended operation, including unintended or uncontrolled motion, even if accompanied by an alarm
- Error of a displayed numerical value sufficiently large to affect diagnosis or treatment
- Noise on a waveform in which the noise would interfere with diagnosis, treatment or monitoring;
- Artefact or distortion in an image in which the artefact would interfere with diagnosis, treatment or monitoring
- Failure of automatic diagnosis or treatment ME EQUIPMENT and ME SYSTEMS to diagnose or treat, even if accompanied by an alarm.

For ME EQUIPMENT and ME SYSTEMS with multiple FUNCTIONS, the criteria apply to each FUNCTION, parameter and channel.

The ME EQUIPMENT or ME SYSTEMS may exhibit DEGRADATION of performance (e.g. deviation from MANUFACTURER'S specifications) that does not affect BASIC SAFETY and ESSENTIAL PERFORMANCE.

8.3. ELECTROSTATIC DISCHARGE (ESD)

8.3.1. TEST SPECIFICATION

Basic Standard:	IEC 61000-4-2
Discharge Impedance:	330 ohm / 150 pF
Discharge Voltage:	Air Discharge: 2 ; 4 ; 8 ; 15 kV (Direct) Contact Discharge: 2 ; 4 ; 8kV (Direct/Indirect)
Polarity:	Positive & Negative
Number of Discharge:	Minimum 10 times at each test point
Discharge Mode:	Single Discharge 1 second minimum

8.3.2. TEST INSTRUMENT

IMMUNITY SHIELDED ROOM				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
ESD gun	SCHAFFNER	NSG 438	170	10/14/2017
Software	N/A			

Note: The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

8.3.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-022)

The discharges shall be applied in two ways:

a) Contact discharges to the conductive surfaces and coupling planes:

The EUT shall be exposed to at least 200 discharges, 100 each at negative and positive polarity, at a minimum of four test points. One of the test points shall be subjected to at least 50 indirect discharges to the center of the front edge of the **Horizontal Coupling Plane (HCP)**. The remaining three test points shall each receive at least 50 direct contact discharges. If no direct contact test points are available, then at least 200 indirect discharges shall be applied in the indirect mode. Test shall be performed at a maximum repetition rate of one discharge per second.


b) Air discharges at slots and apertures and insulating surfaces:

On those parts of the EUT where it is not possible to perform contact discharge testing, the equipment should be investigated to identify user accessible points where breakdown may occur. Such points are tested using the air discharge method. This investigation should be restricted to those area normally handled by the user. A minimum of 10 single air discharges shall be applied to the selected test point for each such area.

The basic test procedure was in accordance with IEC 61000-4-2:

- a) The EUT was located 0.1 m minimum from all side of the **HCP** (dimensions 1.6m x 0.8m).
- b) The support units were located another table 30 cm away from the EUT, but direct support unit was/were located at same location as EUT on the HCP and keep at a distance of 10 cm with EUT.
- c) The time interval between two successive single discharges was at least 1 second.
- d) Contact discharges were applied to the non-insulating coating, with the pointed tip of the generator penetrating the coating and contacting the conducting substrate.
- e) Air discharges were applied with the round discharge tip of the discharge electrode approaching the EUT as fast as possible (without causing mechanical damage) to touch the EUT. After each discharge, the ESD generator was removed from the EUT and re-triggered for a new single discharge. The test was repeated until all discharges were complete.
- f) At least ten single discharges (in the most sensitive polarity) were applied at the front edge of each **HCP** opposite the center point of each unit of the EUT and 0.1 meters from the front of the EUT. The long axis of the discharge electrode was in the plane of the **HCP** and perpendicular to its front edge during the discharge.
- g) At least ten single discharges (in the most sensitive polarity) were applied to the center of one vertical edge of the **Vertical Coupling Plane (VCP)** in sufficiently different positions that the four faces of the EUT were completely illuminated. The **VCP** (dimensions 0.5m x 0.5m) was placed vertically to and 0.1 meters from the EUT.

8.3.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

Note:

TABLETOP EQUIPMENT

The configuration consisted of a wooden table 0.8 meters high standing on the **Ground Reference Plane**. The **GRP** consisted of a sheet of aluminum at least 0.25mm thick, and 2.5 meters square connected to the protective grounding system. A **Horizontal Coupling Plane** (1.6m x 0.8m) was placed on the table and attached to the **GRP** by means of a cable with 940k Ω total impedance. The equipment under test, was installed in a representative system as described in section 7 of IEC 61000-4-2, and its cables were placed on the **HCP** and isolated by an insulating support of 0.5mm thickness. A distance of 1-meter minimum was provided between the EUT and the walls of the laboratory and any other metallic structure.

FLOOR-STANDING EQUIPMENT

The equipment under test was installed in a representative system as described in section 7 of IEC 61000-4-2, and its cables were isolated from the Ground Reference Plane by an insulating support of 0.1-meter thickness. The GRP consisted of a sheet of aluminum that is at least 0.25mm thick, and 2.5 meters square connected to the protective grounding system and extended at least 0.5 meters from the EUT on all sides.

8.3.5. TEST RESULTS

Temperature	25°C	Humidity	52% RH
Pressure	1001mbar	Tested by	Rex Chen
Test Date	2016/12/29		
Required Passing Performance	The ME Equipment or ME System shall be able to provide the basic safety and essential performance.		

Air Discharge												
Test Points	Test Levels						Results					
	± 2 kV	Performance Criterion		± 4 kV	Performance Criterion		± 8 kV	Performance Criterion		Pass	Fail	Observation
Front	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Back	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Left	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Right	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Top	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Bottom	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Contacts	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2

Air Discharge					
Test Points	Test Levels		Results		
	± 15 kV	Performance Criterion	Pass	Fail	Observation
Front	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 3
Back	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 3
Left	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 3
Right	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 3
Top	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 3
Bottom	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 3

Contact Discharge												
Test Points	Test Levels						Results					
	± 2 kV	Performance Criterion		± 4 kV	Performance Criterion		± 6 kV	Performance Criterion		Pass	Fail	Observation
Front	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Back	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Left	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Right	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Top	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Bottom	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/> A	<input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2

Contact Discharge					
Test Points	Test Levels		Results		
	± 8 kV	Performance Criterion	Pass	Fail	Observation
Front	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Back	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Left	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Right	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Top	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2
Bottom	<input checked="" type="checkbox"/>	<input type="checkbox"/> A <input type="checkbox"/> B	<input checked="" type="checkbox"/>	<input type="checkbox"/>	Note 2

Contact Discharge To Horizontal Coupling Plane								
Side of EUT	Test Levels				Results			
	± 2 kV	± 4 kV	± 6 kV	± 8 kV	Pass	Fail	Performance Criterion	Observation
Front	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/> A <input type="checkbox"/> B	Note 1				
Back	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/> A <input type="checkbox"/> B	Note 1				
Left	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/> A <input type="checkbox"/> B	Note 1				
Right	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/> A <input type="checkbox"/> B	Note 1				

Contact Discharge To Vertical Coupling Plane								
Side of EUT	Test Levels				Results			
	± 2 kV	± 4 kV	± 6 kV	± 8 kV	Pass	Fail	Performance Criterion	Observation
Front	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/> A <input type="checkbox"/> B	Note 1				
Back	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/> A <input type="checkbox"/> B	Note 1				
Left	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/> A <input type="checkbox"/> B	Note 1				
Right	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/> A <input type="checkbox"/> B	Note 1				

Note:

1. There was no change compared with initial operation during the test.
2. Means that no discharge point had been occurred during that particular coupling method.
3. During the test at air 15kV, no discharge point.

8.4. RADIATED, RADIO-FREQUENCY, ELECTROMAGNETIC FIELD (RS)

8.4.1. TEST SPECIFICATION

Basic Standard:	IEC 61000-4-3
Frequency Range:	80 MHz ~2700 MHz, 385 MHz ~ 6GHz
Field Strength:	3 V/m, 9~28 V/m
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Polarity of Antenna:	Horizontal and Vertical
Test Distance:	3 m
Antenna Height:	1.5 m

8.4.2. TEST INSTRUMENT

RS Chamber				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
AVG Power Sensor	R&S	NRP-Z21	101860	09/21/2017
AVG Power Sensor	R&S	NRP-Z21	101861	09/21/2017
Rs Probe	narda	NBM-520/EF-1891	D-0924/E-0005	12/04/2017
Signal Generator	R&S	SMJ100A	101258	09/18/2017
Bilog Antenna	AR	ATL80M1G	044851	N.C.R
Dual Directional Coupler	AR	DC6180A	433803	N.C.R
Dual Directional Coupler	RD Microswaves	C1-A47NFNF	31	N.C.R
Horn Antenna	SCHWARZBECK	STLP 9149	9149-261	N.C.R
Power Amplifier	AR	50S1G6M1	0433952	N.C.R
Power Amplifier	AR	250W1000BM1	0579919	N.C.R
RF Test System Controller	AR	SC1000M3	0433953	N.C.R
Test S/W	SW1006 (V1.13)			

Note:


1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R.= No Calibration required.

8.4.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-023)

The test procedure was in accordance with IEC 61000-4-3

- a) The testing was performed in a fully anechoic chamber. The transmit antenna was located at a distance of 3 meters from the EUT.
- b) The frequency range is swept from 80 MHz to 2500 MHz, with the signal 80% amplitude modulated with a 1 kHz sine-wave. The rate of sweep did not exceed 1.5×10^{-3} decade/s, where the frequency range is swept incrementally, the step size was 1% of preceding frequency value.
- c) The dwell time at each frequency shall be not less than the time necessary for the EUT to be able to respond.
- e) The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

8.4.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

Note:

TABLETOP EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-3 was placed on a non-conductive table 0.8 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

FLOOR-STANDING EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-3 was placed on a non-conductive wood support 0.1 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

8.4.5. TEST RESULTS

Temperature	25°C	Humidity	52% RH
Pressure	1001mbar	Dwell Time	3 sec.
Tested by	Rex Chen	Test Date	2016/12/29
Required Passing Performance	The ME Equipment or ME System shall be able to provide the basic safety and essential performance.		

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Observation	Result
80 ~ 2700	V&H	0	10	Note 1	PASS
80 ~ 2700	V&H	90	10	Note 1	PASS
80 ~ 2700	V&H	180	10	Note 1	PASS
80 ~ 2700	V&H	270	10	Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Temperature	25°C	Humidity	52% RH
Pressure	1001mbar	Dwell Time	60 sec.
Tested by	Rex Chen	Test Date	2016/12/29
Required Passing Performance	The ME Equipment or ME System shall be able to provide the basic safety and essential performance.		

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
385	V&H	0	27	Pulse Modulation 18HZ	Note 1	PASS
385	V&H	90	27		Note 1	PASS
385	V&H	180	27		Note 1	PASS
385	V&H	270	27		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
450	V&H	0	28	FM ±5 kHz deviation 1 kHz sine	Note 1	PASS
450	V&H	90	28		Note 1	PASS
450	V&H	180	28		Note 1	PASS
450	V&H	270	28		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
710	V&H	0	9	Pulse Modulation 217Hz	Note 1	PASS
710	V&H	90	9		Note 1	PASS
710	V&H	180	9		Note 1	PASS
710	V&H	270	9		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
745	V&H	0	9	Pulse Modulation 217Hz	Note 1	PASS
745	V&H	90	9		Note 1	PASS
745	V&H	180	9		Note 1	PASS
745	V&H	270	9		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
780	V&H	0	9	Pulse Modulation 217Hz	Note 1	PASS
780	V&H	90	9		Note 1	PASS
780	V&H	180	9		Note 1	PASS
780	V&H	270	9		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
810	V&H	0	28	Pulse Modulation 18HZ	Note 1	PASS
810	V&H	90	28		Note 1	PASS
810	V&H	180	28		Note 1	PASS
810	V&H	270	28		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
870	V&H	0	28	Pulse Modulation 18HZ	Note 1	PASS
870	V&H	90	28		Note 1	PASS
870	V&H	180	28		Note 1	PASS
870	V&H	270	28		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
930	V&H	0	28	Pulse Modulation 18HZ	Note 1	PASS
930	V&H	90	28		Note 1	PASS
930	V&H	180	28		Note 1	PASS
930	V&H	270	28		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
1720	V&H	0	28	Pulse Modulation 217Hz	Note 1	PASS
1720	V&H	90	28		Note 1	PASS
1720	V&H	180	28		Note 1	PASS
1720	V&H	270	28		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
1845	V&H	0	28	Pulse Modulation 217Hz	Note 1	PASS
1845	V&H	90	28		Note 1	PASS
1845	V&H	180	28		Note 1	PASS
1845	V&H	270	28		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
1970	V&H	0	28	Pulse Modulation 217Hz	Note 1	PASS
1970	V&H	90	28		Note 1	PASS
1970	V&H	180	28		Note 1	PASS
1970	V&H	270	28		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
2450	V&H	0	28	Pulse Modulation 217Hz	Note 1	PASS
2450	V&H	90	28		Note 1	PASS
2450	V&H	180	28		Note 1	PASS
2450	V&H	270	28		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
5240	V&H	0	9	Pulse Modulation 217Hz	Note 1	PASS
5240	V&H	90	9		Note 1	PASS
5240	V&H	180	9		Note 1	PASS
5240	V&H	270	9		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
5500	V&H	0	9	Pulse Modulation 217Hz	Note 1	PASS
5500	V&H	90	9		Note 1	PASS
5500	V&H	180	9		Note 1	PASS
5500	V&H	270	9		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Modulation	Observation	Result
5785	V&H	0	9	Pulse Modulation 217Hz	Note 1	PASS
5785	V&H	90	9		Note 1	PASS
5785	V&H	180	9		Note 1	PASS
5785	V&H	270	9		Note 1	PASS

Note: There was no change compared with the initial operation during the test.

8.5. ELECTRICAL FAST TRANSIENT (EFT)

8.5.1. TEST SPECIFICATION

Basic Standard:	IEC 61000-4-4
Test Voltage:	Power Line: 2 kV Signal/Control Line: 1 kV
Polarity:	Positive & Negative
Impulse Frequency:	5 kHz
Impulse Wave-shape:	5/50 ns
Burst Duration:	15 ms
Burst Period:	300ms
Test Duration:	Not less than 1 min.

8.5.2. TEST INSTRUMENT

Immunity Shield Room				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
CDN	EMC Partner	CDN-UTP8	046	12/21/2017
Clamp	EMC Partner	CN-EFT1000	683	09/09/2017
EMC Immunity Tester	EMC Partner	TRA2006	1144	11/30/2017
Test S/W	Genecs (3.03)			


Note:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R.= No Calibration required

8.5.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-024)

- a) Both positive and negative polarity discharges were applied.
- b) The length of the “hot wire” from the coaxial output of the EFT generator to the terminals on the EUT should not exceed 0.5 meter.
- c) The duration time of each test sequential was 1 minute.
- d) The transient/burst waveform was in accordance with IEC 61000-4-4, 5/50ns.

8.5.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

Note:

TABLETOP EQUIPMENT

The configuration consisted of a wooden table (0.1m high) standing on the Ground Reference Plane. The GRP consisted of a sheet of aluminum (at least 0.25mm thick and 2.5m square) connected to the protective grounding system. A minimum distance of 0.5m was provided between the EUT and the walls of the laboratory or any other metallic structure.

FLOOR-STANDING EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-4 and its cables, were isolated from the Ground Reference Plane by an insulating support that is 0.1-meter thick. The GRP consisted of a sheet of aluminum (at least 0.25mm thick and 2.5m square) connected to the protective grounding system.

8.5.5. TEST RESULTS

Temperature	23°C	Humidity	44% RH
Pressure	998mbar	Tested by	Rex Chen
Test Date	2016/12/29		
Required Passing Performance	The ME Equipment or ME System shall be able to provide the basic safety and essential performance.		

Test Point	Polarity	Test Level (kV)	Inject Method	Observation	Result
L	+/-	2	Direct	Note 1	PASS
N	+/-	2	Direct	Note 1	PASS
L + N	+/-	2	Direct	Note 1	PASS

Note: There was no change compared with initial operation during the test.

8.6. SURGE IMMUNITY TEST

8.6.1. TEST SPECIFICATION

Basic Standard:	IEC 61000-4-5
Wave-Shape:	Combination Wave 1.2/50 us Open Circuit Voltage 8/20 us Short Circuit Current
Test Voltage:	AC Power Port ~ line to line: 1kV, line to earth (ground): 2kV
Surge Input/Output:	AC Power Port: L1-L2 / L1-PE / L2-PE
Generator Source Impedance:	2 ohm between networks 12 ohm between network and ground
Polarity:	Positive/Negative
Phase Angle:	0° / 90° / 180° / 270°
Pulse Repetition Rate:	1 time / min. (maximum)
Number of Tests:	5 positive and 5 negative at selected points

8.6.2. TEST INSTRUMENT

Immunity Shield Room				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
EMC Immunity Tester	EMC Partner	TRA2000IN6	1144	01/03/2014
CDN	EMC Partner	CDCN-UTP8	046	01/09/2014
Clamp	EMC Partner	CN-EFT1000	683	N.C.R.
Test S/W	Genecs (3.03)			

Note:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R.= No Calibration required

8.6.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-025)

a) For EUT power supply:

The surge is applied to the EUT power supply terminals via the capacitive coupling network. Decoupling networks are required in order to avoid possible adverse effects on equipment not under test that may be powered by the same lines, and to provide sufficient decoupling impedance to the surge wave. The power cord between the EUT and the coupling/decoupling networks was shorter than 2 meters in length.


b) For test applied to unshielded un-symmetrically operated interconnection lines of EUT:

The surge was applied to the lines via the capacitive coupling. The coupling / decoupling networks didn't influence the specified functional conditions of the EUT. The interconnection line between the EUT and the coupling/decoupling networks was shorter than 2 meters in length.

c) For test applied to unshielded symmetrically operated interconnection / telecommunication lines of EUT:

The surge was applied to the lines via gas arrestors coupling. Test levels below the ignition point of the coupling arrestor were not specified. The interconnection line between the EUT and the coupling/decoupling networks was shorter than 2 meters in length.

8.6.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

8.6.5. TEST RESULTS

Temperature	22°C	Humidity	50% RH
Pressure	999mbar	Tested by	Moore Cheng
Required Passing Performance	The ME Equipment or ME System shall be able to provide the basic safety and essential performance.		

Test Point	Polarity	Test Level (kV)	Coupling Method	Observation	Result
L - N	+/-	1	Capacitive	Note 1	PASS
L - PE	+/-	2	Capacitive	Note 1	PASS
N - PE	+/-	2	Capacitive	Note 1	PASS

Note:

1. There was no change compared with initial operation during the test.

8.7. CONDUCTED RADIO FREQUENCY DISTURBANCES (CS)

8.7.1. TEST SPECIFICATION

Basic Standard:	IEC 61000-4-6
Frequency Range:	0.15 MHz ~ 80 MHz
Field Strength:	3 Vrms 6 Vrms
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Coupled cable:	Power Mains, Unshielded; RJ45 Line, Unshielded
Coupling device:	<input checked="" type="checkbox"/> CDN-M2 (2 wires) <input type="checkbox"/> CDN-M3 (3 wires) <input type="checkbox"/> CDN-T2 for Line <input type="checkbox"/> CDN-T4 for LAN

8.7.2. TEST INSTRUMENT

CS Room				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
CDN	FCC	FCC-801-M2-16A	121695	09/28/2017
CDN	FCC	FCC-801-M3-16A	03027	09/28/2017
CDN	EM TEST	CDN M2/M3	P1325119693	09/28/2017
CDN	EM TEST	CDN T2-3A	P1336124265	09/28/2017
CDN	EM TEST	CDN T4-3A	P1339124699	09/28/2017
CDN	EM TEST	CDN T8 RJ45	P1320118639	09/28/2017
EM Injection Clamp	FCC	F-2031-23mm	421	09/28/2017
S.G.	R&S	SMY02	100094	09/20/2017
CDN	FCC	FCC-801-T8-RJ45	4024	N.C.R
CDN	FCC	FCC-801-T4	3017	N.C.R
CDN	FCC	FCC-801-T2	3016	N.C.R
Clamp	FCC	F-2031-23mm	421	N.C.R
Power Amplifier	AR	150A100B	41657	N.C.R
Test S/W	SW1006 (V1.22)			

Note:

- The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
- N.C.R.= No Calibration required

8.7.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-026)

The EUT shall be tested within its intended operating and climatic conditions.


The test shall be performed with the test generator connected to each of the coupling and decoupling devices in turn, while the other non-excited RF input ports of the coupling devices are terminated by a 50-ohm load resistor.

The frequency range was swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80 % amplitude. The signal was modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. The sweep rate was 1.5×10^{-3} decades/s. Where the frequency range is swept incrementally, the step size was 1 % of preceding frequency value from 150 kHz to 80 MHz.

The dwell time at each frequency was less than the time necessary for the EUT to be exercised, and able to respond. Sensitive frequencies such as clock frequency(ies) and harmonics or frequencies of dominant interest, was analyzed separately.

Attempts were made to fully exercise the EUT during testing, and to fully interrogate all exercise modes selected for susceptibility.

8.7.4. TEST SETUP



Note:

1. The EUT is setup 0.1m above Ground Reference Plane
2. The CDNs and / or EM clamp used for real test depends on ports and cables configuration of EUT.

- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

Note:

TABLETOP AND FLOOR-STANDING EQUIPMENT

The equipment to be tested was placed on an insulating support of 0.1 meters height above a ground reference plane. All relevant cables shall be provided with the appropriate coupling and decoupling devices at a distance between 0.1 meters and 0.3 meters from the projected geometry of the EUT on the ground reference plane.

8.7.5. TEST RESULTS

Temperature	25°C	Humidity	52% RH
Pressure	1001mbar	Tested by	Rex Chen
Test Date	2016/12/29		
Required Passing Performance	The ME Equipment or ME System shall be able to provide the basic safety and essential performance.		

Frequency Band (MHz)	Field Strength (Vrms)	Cable	Injection Method	Observation	Result
0.15 ~ 80	3V & 6V	DC Power Line	CDN-M2	Note 1	PASS

Note: There was no change compared with initial operation during the test.

8.8. POWER FREQUENCY MAGNETIC FIELD

8.8.1. TEST SPECIFICATION

Basic Standard:	IEC 61000-4-8
Frequency Range:	50Hz, 60Hz
Field Strength:	30 A/m
Observation Time:	1 minute
Inductance Coil:	Rectangular type, 1mx1m

8.8.2. TEST INSTRUMENT

Immunity Shield Room				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
Triax Elf Magnetic Field Meter	F.W.BELL	4190	0845014	07/10/2017
Magnetic field Tester	HAEFFLY	MAG 100.1	081436-02	N.C.R.
Software	N/A			

Note:


1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. N.C.R.= No Calibration required.

8.8.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-027)

- a) The equipment is configured and connected to satisfy its functional requirements. It shall be placed on the GRP with the interposition of a 0.1m-thick insulating support.
- b) The equipment cabinets shall be connected to the safety earth directly on the GRP via the earth terminal of the EUT.
- c) The power supply, input and output circuits shall be connected to the sources of power supply, control and signal.
- d) The cables supplied or recommended by the equipment manufacturer shall be used. 1 meter of all cables used shall be exposed to the magnetic field.

8.8.4. TEST SETUP

- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.



Note:

TABLETOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

FLOOR-STANDING EQUIPMENT

The equipment shall be subjected to the test magnetic field by using induction coils of suitable dimensions. The test shall be repeated by moving and shifting the induction coils, in order to test the whole volume of the EUT for each orthogonal direction. The test shall be repeated with the coil shifted to different positions along the side of the EUT, in steps corresponding to 50 % of the shortest side of the coil. The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

8.8.5. TEST RESULTS

Temperature	25°C	Humidity	52% RH
Pressure	1001mbar	Tested by	Rex Chen
Test Date	2016/12/29		
Required Passing Performance	The ME Equipment or ME System shall be able to provide the basic safety and essential performance.		

Direction	Field Strength (A/m)	Observation	Results
X	30	Note 1	Pass
Y	30	Note 1	Pass
Z	30	Note 1	Pass

Note: There was no change compared with the initial operation during the test.

8.9. VOLTAGE DIP & VOLTAGE INTERRUPTIONS

8.9.1. TEST SPECIFICATION

Basic Standard:	IEC 61000-4-11
Test duration time:	Minimum three test events in sequence
Interval between event:	Voltage Dips:
	0% Ut for 0.5 Cycle
	0% Ut for 1 cycle
	70% Ut for 25 cycles
	Voltage Interruptions:
	0% for 5 sec.
Angle:	0~360 degree
Step:	45 degree

8.9.2. TEST INSTRUMENT

Immunity Shield Room				
Name of Equipment	Manufacturer	Model	Serial Number	Calibration Due
CDN	EMC Partner	CDN-UTP8	046	12/21/2017
Clamp	EMC Partner	CN-EFT1000	683	09/09/2017
EMC Immunity Tester	EMC Partner	TRA2006	1144	11/30/2017
Test S/W	Genecs (3.03)			


Note:

- The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
- N.C.R.= No Calibration required

8.9.3. TEST PROCEDURE (please refer to measurement standard or CCS SOP PA-028)

- The EUT and support units were located on a wooden table, 0.8 m away from ground floor.
- Setting the parameter of tests and then perform the test software of test simulator.
- Conditions changes to occur at 0 degree crossover point of the voltage waveform.
- Recording the test result in test record form.

8.9.4. TEST SETUP



- For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

8.9.5. TEST RESULTS

Temperature	23°C	Humidity	44% RH
Pressure	998mbar	Tested by	Rex Chen
Test Date	2016/12/29		
Required Passing Performance	The ME Equipment or ME System shall be able to provide the basic safety and essential performance.		

Voltage Dips:

Test Power: 100/240Vac, 50Hz				
Test Level % U_T	Reduction (%)	Duration (periods)	Observation	Result
0	100	0.5	Note 1	PASS
0	100	1	Note 1	PASS
70	30	25	Note 1	PASS


Voltage Interruptions:

Test Power: 100/240Vac, 50Hz				
Test Level % U_T	Reduction (%)	Duration (seconds)	Observation	Result
0	100	5	Note 2	PASS

Note:


1. *There was no change compared with initial operation during and after the test. No unintentional response was found during the test.*
2. *EUT disturbance voltage drop test is completed automatically reply.*

9 PHOTOGRAPHS OF THE TEST CONFIGURATION CONDUCTED EMISSION TEST




RADIATED EMISSION TEST

Below 1GHz



HARMONIC & FLICKER TEST




ESD TEST




RS TEST



EFT TEST



SURGE TEST



CS TEST



POWER FREQUENCY MAGNETIC FIELD



VOLTAGE DIPS / INTERRUPTIONS TEST

