

**TEST REPORT****FOR****DC to DC Converter****BRAND :** **MODEL : TEQ 300-7212WIR-B1****SERIES MODEL : Refer to item 5.1 for more details****REPORT NUMBER: 4790893561A-EN-E0-V0****ISSUE DATE: Jul. 6, 2023****Prepared for****TRACO ELECTRONIC AG****Sihlbruggstrasse 111 CH-6340 Baar****Prepared by****Underwriters Laboratories Taiwan Co., Ltd.,****Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township,  
Hsinchu County, Taiwan****Tel: +886.2.2896.7790****Fax: +886.3.583.7948****Website: www.ul.com**

The results reported herein have been performed in accordance with the laboratory's terms of accreditation. This report shall not be reproduced except in full without the written approval of the Laboratory. The results in this report are responsible of the test sample(s) provided by the client only and are not to be used to indicate applicability to other similar products.

### **Revision History**

<b>Rev.</b>	<b>Issue Date</b>	<b>Revisions</b>	<b>Revised By</b>
--	Jul. 6, 2023	Initial Issue	Sally Lu

Summary of Test Results				
EMISSION				
Standard	Test Item	Limit	Result	Remark
EN 55032:2015 / A11: 2020	Conducted disturbance at mains terminals ports	Class A	PASS	Note 4
	Conducted common mode (asymmetric mode) disturbance telecommunication ports	Class A/B	N/A	Note 1
	Radiated disturbance below 1GHz	Class A	PASS	Note 4
	Radiated disturbance above 1 GHz	Class A	N/A	Note 2
EN IEC 61000-3-2: 2019 / A1: 2021	Harmonic current disturbance	Class A~D	N/A	Note 3
EN 61000-3-3: 2013 / A2: 2021	Voltage Fluctuations & Flicker	Refer to 6.5.1	N/A	Note 3

**Note 1 :** Since the EUT does not contain asymmetric port, the test is unnecessary.

**Note 2 :** Since the highest frequency of EUT is less than 108 MHz, the measurement above 1 GHz is unnecessary.

**Note 3 :** Since the EUT does not connect to mains power network directly, the test is unnecessary.

**Note 4 :** All test data are copied from 4790653020A-EN-E0-V0 report.

Summary of Test Results				
IMMUNITY				
Basic Standard	Test Item	Class / Severity	Require Performance Criteria	Result
EN 61000-4-2: 2009	Electrostatic discharge immunity	Contact $\pm 4$ kV Air $\pm 8$ kV	B	PASS (Note 5)
EN IEC 61000-4-3: 2020	Continuous RF electromagnetic field disturbances, swept test	80-1000MHz 3V/m 80%, 1kHz, AM	A	PASS (Note 5)
	Continuous RF electromagnetic field disturbances, spot test	1800 ;2600 ;3500 5000 MHz ( $\pm 1\%$ ) 3V/m 80%, 1kHz, AM (Note 2)	A	PASS (Note 5)
	immunity levels to common wireless communication devices	See Table I.1	A	PASS (Note 5)
EN 61000-4-4: 2012	Electrical fast transient/burst immunity	1kV(AC Mains) 5/50ns, 5kHz	B	N/A (Note 3)
		0.5kV(DC Ports) 5/50ns, 5kHz	B	PASS (Note 5)
		0.5kV(Signal Lines) 5/50ns, 5kHz	B	N/A (Note 4)
EN 61000-4-5: 2014 / A1: 2017	Surge immunity	AC Mains 2.0kV(Common) 1.0kV(Differential) 1.2/50us	B	N/A (Note 3)
		DC Ports 0.5kV Line to Ground	B	PASS (Note 5)
		Signal port 1.0kV (w/o primary protector) 4.0kV (w primary protector) 1.2/50us or 10/700us (Note 1)	C	N/A (Note 4)
		0.5kV Coaxial or shielded to ground 1.2/50 (8/20) us	B	N/A (Note 4)

Summary of Test Results				
IMMUNITY				
Basic Standard	Test Item	Class / Severity	Require Performance Criteria	Result
EN 61000-4-6: 2014 / AC:2015	Continuous induced RF disturbances	AC Mains 0.15~10MHz, 3V 10~30MHz, 3~1V 30-80MHz, 1V with 1kHz 80% AM (Note 2)	A	N/A (Note 3)
		DC Ports 0.15~10MHz, 3V 10~30MHz, 3~1V 30-80MHz, 1V with 1kHz 80% AM (Note 2)	A	PASS (Note 5)
		Signal Line 0.15~10MHz, 3V 10~30MHz, 3~1V 30-80MHz, 1V with 1kHz 80% AM (Note 2)	A	N/A (Note 4)
EN 61000-4-8: 2010	Power frequency magnetic field immunity (Continuous)	50 Hz, 1 A/m(r.m.s) 50 Hz, 3,10,30,100 A/m (r.m.s) by client request	A	PASS (Note 5)
	Power frequency magnetic field immunity (Short duration)	50Hz, 1000A/m, 1~3s (r.m.s) by client request	A	PASS (Note 5)
EN IEC 61000-4-11: 2020	Voltage dips, short interruptions and voltage variations immunity	Voltage dips, <5% residual with 0.5cycles	B	N/A (Note 3)
		Voltage dips, 70% residual with 25 cycles	C	
		Voltage interruptions, <5% residual with 250 cycles	C	

**Note 1:** Where the coupling network for the 10/700  $\mu$ s waveform affects the functioning of high speed data ports, the test shall be carried out using a 1,2/50 (8/20)  $\mu$ s waveform and appropriate coupling network.

**Note 2:** The frequency range is scanned as specified. However, when specified in EN 55035, an additional EUT contains telephony functional test shall be carried out at a limited number of frequencies. The selected frequencies for conducted immunity tests are: 0,2; 1; 7,1; 13,56; 21; 27,12 and 40,68 MHz ( $\pm 1$  %) and radiated immunity tests are 80; 120; 160; 230; 434; 460; 600; 863 and 900MHz ( $\pm 1$  %).

**Note 3:** Since the EUT does not connect to mains power network directly, the test is unnecessary.

**Note 4:** Since the EUT does not contain signal port, the test is unnecessary.

**Note 5 :** All test data are copied from 4790653020A-EN-E0-V0 report.

**Table I.1 – Guidance on the selection of immunity levels  
to common wireless communication devices**

Table clause	Approximate protection distance (m)	Calculated RF field strength in V/m for frequencies and protection distances simulating different radio transmission types, assuming a given ERP						
		LTE/UMTS (0,2 W)	GSM		WiMAX/3 G (1,26 W)	WiMAX (1,26 W)	Wi-Fi (1 W)	Maximum RF field strength at any frequency
			(2 W)	(1 W)				
		800 MHz	900 MHz	1,8 GHz	2,6 GHz	3,5 GHz	5 GHz	
I.1.1	3,0	0,6	1,8	1,3	1,5	1,5	1,3	3
I.1.2	1,5	1,2	3,7	2,6	2,9	2,9	2,6	4
I.1.3	1,0	1,7	5,5	3,9	4,4	4,4	3,9	6
I.1.4	0,5	3,3	10,5	10,5	11,8	11,8	10,5	12
I.1.5	0,2	8,3	26,4	26,4	29,6	29,6	26,4	30
The protection distance is not the test distance as defined in IEC 61000-4-3:2006/AMD1:2007/AMD2:2010, but the shortest expected operating distance between the EUT and the interfering wireless communication device at which the immunity performance criteria will be satisfied.								

## TABLE OF CONTENTS

<b>1. ATTESTATION OF TEST RESULTS.....</b>	<b>9</b>
<b>2. TEST METHODOLOGY .....</b>	<b>10</b>
<b>3. FACILITIES AND ACCREDITATION.....</b>	<b>10</b>
<b>4. CALIBRATION AND UNCERTAINTY .....</b>	<b>11</b>
4.1. Measuring Instrument Calibration .....	11
4.2. Measurement Uncertainty .....	11
<b>5. EQUIPMENT UNDER TEST .....</b>	<b>13</b>
5.1. Description of EUT .....	13
5.2. Test Mode .....	15
5.3. EUT Operation Test Setup.....	15
5.4. Monitoring of EUT for All Immunity Test .....	15
5.5. Accessory .....	15
5.6. Block diagram showing the configuration of system tested .....	16
5.7. Description of support units.....	18
5.8. Measuring Instrument List.....	19
<b>6. EMISSION TEST .....</b>	<b>22</b>
6.1. Conducted Disturbance Measurement.....	22
6.1.1. Limits of conducted disturbance voltage and common mode disturbance. ....	22
6.1.2. Test Procedure .....	23
6.1.3. Test Setup .....	23
6.1.4. Test Result .....	24
6.2. Radiated Disturbance Measurement(below 1GHz).....	26
6.2.1. Limits of radiated disturbance measurement .....	26
6.2.2. Test Procedure .....	27
6.2.3. Test Setup .....	28
6.2.4. Test Result .....	29
<b>7. IMMUNITY TEST .....</b>	<b>31</b>
7.1. Performance Criteria .....	31
7.2. Electrostatic Discharge Immunity Test.....	32
7.2.1. Test Specification .....	32
7.2.2. Test Procedure .....	32
7.2.3. Test Setup .....	33
7.2.4. Test Result .....	34
7.3. Radio Frequency Electromagnetic Field Immunity Test.....	41
7.3.1. Test Specification .....	41
7.3.2. Test Procedure .....	41

7.3.3. Test Setup .....	42
7.3.4. Test Result .....	43
7.4. Electrical Fast Transient/Burst Immunity Test.....	45
7.4.1. Test Specification .....	45
7.4.2. Test Procedure .....	45
7.4.3. Test Setup .....	46
7.4.4. Test Result .....	47
7.5. Surge Immunity Test .....	48
7.5.1. Test Specification .....	48
7.5.2. Test Procedure .....	48
7.5.3. Test Setup .....	49
7.5.4. Test Result .....	50
7.6. Immunity to Conducted Disturbances Induced by RF Fields .....	51
7.6.1. Test Specification .....	51
7.6.2. Test Procedure .....	51
7.6.3. Test Setup .....	52
7.6.4. Test Result .....	53
7.7. Power frequency magnetic field immunity Test.....	54
7.7.1. Test Specification .....	54
7.7.2. Test Procedure .....	54
7.7.3. Test Setup .....	55
7.7.4. Test Results .....	56
<b>Appendix I: Photographs of EMC Test Configuration .....</b>	<b>57</b>
<b>Appendix II: Photographs of the EUT .....</b>	<b>63</b>
<b>Annex : Additional test request by client. ....</b>	<b>64</b>



## 1. ATTESTATION OF TEST RESULTS

**COMPANY NAME:** TRACO ELECTRONIC AG  
Sihlbruggstrasse 111 CH-6340 Baar

**MANUFACTURER:** TRACO ELECTRONIC AG  
Sihlbruggstrasse 111 CH-6340 Baar

**EUT DESCRIPTION:** DC to DC Converter

**BRAND:**



**MODEL:** TEQ 300-7212WIR-B1

**SERIES MODEL :** Refer to item 5.1 for more details


**DATE of TESTED:** May 19, 2023 ~ Jun. 9, 2023

APPLICABLE STANDARDS	
STANDARDS	TEST RESULTS
EN 55032 :2015 / A11: 2020 EN 55035: 2017 / A11: 2020	PASS

Underwriters Laboratories Taiwan Co., Ltd. Tested the above equipment in accordance with the requirements set forth in the above standards. All indications of Pass/Fail in this report are opinions expressed by Underwriters Laboratories Taiwan Co., Ltd. Based on interpretations and/or observations of test results. The test results show that the equipment tested is capable of demonstrating compliance with the requirements as documented in this report.


**Note:** The results documented in this report apply only to the tested sample, under the conditions and modes of operation as described herein. This document may not be altered or revised in any way unless done so by Underwriters Laboratories Taiwan Co., Ltd. And all revisions are duly noted in the revisions section. Any alteration of this document not carried out by Underwriters Laboratories Taiwan Co., Ltd. Will constitute fraud and shall nullify the document. This report must not be used by the client to claim product certification, approval, or endorsement by NVLAP, NIST, any agency of the Federal Government, or any agency of any government.

Prepared By:

  
\_\_\_\_\_  
Sally Lu  
Project Handler

Date : Jul. 6, 2023

Approve and Authorized By:

  
\_\_\_\_\_  
Roy Chen  
Laboratory Manager

Date : Jul. 6, 2023

## 2. TEST METHODOLOGY

All tests were performed in accordance with the correspond to each test item's procedure of this report and refer to each standard.

## 3. FACILITIES AND ACCREDITATION

Test Location	Underwriters Laboratories Taiwan Co., Ltd.,
Address	Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township, Hsinchu County, Taiwan
Description	All measurement facilities use to collect the measurement data are located at Building B and Building E, No. 372-7, Sec. 4, Zhongxing Rd., Zhudong Township, Hsinchu County, Taiwan

## 4. CALIBRATION AND UNCERTAINTY

### 4.1. Measuring Instrument Calibration

The measuring equipment utilized to perform the tests documented in this report has been calibrated in accordance with the manufacturer's recommendations, and is traceable to recognized national standards.

### 4.2. Measurement Uncertainty

The decision rule refer to CISPR 16-4-2 clause 4.2 accordingly. If  $U_{lab}$  is less than  $U_{cisp}$ , then :

- compliance is deemed to occur if no measured disturbance level exceeds the disturbance limit ;
- non-compliance is deemed to occur if any measured disturbance level exceeds the disturbance limit.

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the apparatus:

The following uncertainties have been calculated to provide a confidence level of 95 % using a coverage factor  $k=2$ .

Electromagnetic interference:

Test Item	Measurement Frequency Range	K	U(dB)
Conducted disturbance at mains terminals ports	0.15MHz ~ 30MHz	2	3.2
966-1 Test Site			
Radiated disturbance below 1 GHz	30MHz ~ 1000MHz	2	5.9

Electromagnetic sensitivity:

Test Item	Measurement Frequency Range	K	U(dB)
Radiated, radio frequency electromagnetic field immunity	80MHz ~ 6000MHz	2	2.1
Immunity to conducted disturbances, induced by radio-frequency fields (CDN)	0.15MHz ~ 80MHz	2	2.4

Test Item	K	Voltage(%)	Rise Time(%)	First Peak Current (%)	Current @ 30ns (%)	Current @ 60ns (%)
Electrostatic discharge immunity	2	2.8	7.2	3.4	3.1	3.7


Test Item	K	Peak Voltage(%)	Rise Time(%)	Pulse width(%)	Burst Period (%)	Burst duration (%)	Repetition rate (%)
Electrical fast transient/burst immunity	2	3.6	3.7	1.7	0.94	0.47	0.29

Test Item	K	Phase Shifting (%)	Voltage (%)	Current (%)	Front Time (For waveform of the surge voltage)(%)	Duration (For waveform of the surge voltage)(%)	Front Time (For waveform of the surge current)(%)	Duration (For waveform of the surge current)(%)
Surge immunity	2	1.1	3.6	2.7	1.2	0.43	5.9	0.79

Test Item	K	Magnetic field Strength(%)
Power Frequency Magnetic Field Immunity Test	2	4.9%

## 5. EQUIPMENT UNDER TEST

### 5.1. Description of EUT

<b>EUT Name:</b>	DC to DC Converter
<b>Brand:</b>	
<b>Model:</b>	TEQ 300-7212WIR-B1
<b>Series Model:</b>	TEQ 300-4812WIR(a), TEQ 300-4813WIR(a), TEQ 300-4815WIR(a), TEQ 300-4816WIR(a), TEQ 300-4818WIR(a), TEQ 300-7212WIR(a), TEQ 300-7213WIR(a), TEQ 300-7215WIR(a), TEQ 300-7216WIR(a), TEQ 300-7218WIR(a), TEQ 300-4812WIR-B1(a), TEQ 300-4813WIR-B1(a), TEQ 300-4815WIR-B1(a), TEQ 300-4816WIR-B1(a), TEQ 300-4818WIR-B1(a), TEQ 300-7212WIR-B1(a), TEQ 300-7213WIR-B1(a), TEQ 300-7215WIR-B1(a), TEQ 300-7216WIR-B1(a), TEQ 300-7218WIR-B1(a)
<b>Power Rating:</b>	110Vdc from DC source
<b>Highest Frequency within EUT:</b>	less than 108MHz
<b>Condition of EUT:</b>	Mass-Production Test sample
<b>Sample ID:</b>	5567216
<b>Date Of Receipt Of Sample:</b>	Nov. 24, 2022

Note :

1. This supplemental report was issued based on the original report with report number 4790653020A-EN-E0-V0, the differences were as below:
  - Change model, series model, brand, the applicant and manufacturer
2. According to above conditions, there is no addition test has to be performed. All test data are copied from the original test report (Report No.: 4790653020A-EN-E0-V0), and all data are verified to meet the requirements
3. The models difference table as below:

Model Number	Input Range(VDC)	Output Voltage(VDC)
TEQ 300-4812WIR(a)	18 ~ 75	12
TEQ 300-4813WIR(a)	18 ~ 75	15
TEQ 300-4815WIR(a)	18 ~ 75	24
TEQ 300-4816WIR(a)	18 ~ 75	28
TEQ 300-4818WIR(a)	18 ~ 75	48
TEQ 300-7212WIR(a)	43 ~ 160	12
TEQ 300-7213WIR(a)	43 ~ 160	15
TEQ 300-7215WIR(a)	43 ~ 160	24
TEQ 300-7216WIR(a)	43 ~ 160	28
TEQ 300-7218WIR(a)	43 ~ 160	48
TEQ 300-4812WIR-B1(a)	18 ~ 75	12
TEQ 300-4813WIR-B1(a)	18 ~ 75	15
TEQ 300-4815WIR-B1(a)	18 ~ 75	24
TEQ 300-4816WIR-B1(a)	18 ~ 75	28
TEQ 300-4818WIR-B1(a)	18 ~ 75	48
TEQ 300-7212WIR-B1(a)	43 ~ 160	12
TEQ 300-7213WIR-B1(a)	43 ~ 160	15
TEQ 300-7215WIR-B1(a)	43 ~ 160	24
TEQ 300-7216WIR-B1(a)	43 ~ 160	28
TEQ 300-7218WIR-B1(a)	43 ~ 160	48
(a)" can be 6 variables, each variable may be any alphanumeric, "-", any punctuation mark or blank for marketing purpose and no impact to safety.		

## 5.2. Test Mode

Mode	Description
Mode 1	Full Load

Test Items		Test Mode
Emission	Conducted Emission	Mode 1
	Radiated Emission	Mode 1
Immunity	Electrostatic Discharge	Mode 1
	Radio Frequency Electromagnetic Field	Mode 1
	Electrical Fast Transient	Mode 1
	Surge Immunity	Mode 1
	Immunity to conducted disturbances, induced by radio-frequency fields	Mode 1
	Power frequency magnetic field immunity	Mode 1

Note

1. The customer only provided TEQ 300-7212WIR-B1 for the EMC test.
2. The customer requested to test "Conducted Emission".

## 5.3. EUT Operation Test Setup

Mode 1: (For Emission)

- a. The EUT was linked to resistance load with full load during the testing.
- b. Power on the EUT and run test.

Mode 1: (For Immunity)

- a. The EUT was linked to resistance load with full load and the resistance load was connected with a meter during the testing.
- b. Power on the EUT and run test.

## 5.4. Monitoring of EUT for All Immunity Test


Audio	N/A
Visual	Monitor the output voltage through the meter.

## 5.5. Accessory


N/A

## 5.6. Block diagram showing the configuration of system tested

For Radiated Emission test:  
Mode 1




For Conducted Emission test





For Immunity



## 5.7. Description of support units

The EUT has been tested as an independent unit together with other necessary accessories or support units. The following support units or accessories were used to form a representative test configuration during the tests.

Item	Equipment	Mfr/Brand	Model/Type No.	Series No.	FCC ID	Note
A	Power supply	GW INSTEK	GPC-60300	N/A	N/A	Provided by customer
B	Meter	N/A	SD-670	N/A	N/A	N/A
C	Resistance load	N/A	N/A	N/A	N/A	Provided by customer

Item	Connection	Shielded Type	Note
1	DC Power Wire	Non-shield	Provided by customer
2	DC Power Wire	Non-shield	Provided by customer
3	DC Power Wire	Non-shield	N/A
4	DC Power Wire	Non-shield	N/A

## 5.8. Measuring Instrument List

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
<b>Conducted Disturbance</b>					
EMI Test Receiver	Rohde & Schwarz	ESR7	101753	2022/11/10	2023/11/9
Two-Line V-Network	Rohde & Schwarz	ENV216	102136	2022/8/29	2023/8/28
Two-Path V-LISN	SCHWARZBECK	NSLK 8127	8127-946	2022/11/10	2023/11/9
RF Current Probe	FCC	F-52	171502	2023/2/8	2024/2/7
Coupling and Decoupling Network	TESEQ	ISN ST08	45105	2023/2/8	2024/2/7
Impedance Stabilization Network	TESEQ	ISN T800	42830	2023/4/7	2024/4/6
Capacitive Voltage Probe	TESEQ	CVP 2200A	44922	2023/2/18	2024/2/17
Impuls-Begrenzer Pulse Limiter	Rohde & Schwarz	ESH3-Z2	102219-Qt	2022/8/30	2023/8/29
Cable	TITAN	CFD200	T0732ACFD20020A300-2	2023/5/23	2024/5/22
Measurement Software	Farad	EZ-EMC Ver: UL-3A1.2	N/A	N/A	N/A
<b>Radiated Disturbance</b>					
<b>966-1</b>					
EMI Test Receiver	Rohde & Schwarz	ESR7	101755	2022/12/7	2023/12/6
Trilog-Broadband Antena with 5dB Attenuator	SCHWARZBECK	VULB 9168 & N-6-05	774 & AT-N0538	2023/2/13	2024/2/12
Double Ridged Guide Horn Antenna	SCHWARZBECK	BBHA 9120 D	1686	2022/12/9	2023/12/8
Preamplifier	EMC Instrument	EMC330E	060655	2023/3/13	2024/3/12
Preamplifier	EMC Instrument	EMC051835BE	980407	2023/1/6	2024/1/5
Cables	UltraPhase&EMC Instrument&Huber+Suhner	A1K50-UP0358-A1K50-1500& EMC106-NM-SM-2500	170111-3&170104	2023/2/6	2024/2/5
Cables	Huber+Suhner	EMC104-SM-SM-15000	230215	2023/3/22	2024/3/21
Measurement Software	Farad	EZ-EMC Ver: UL-3A1	N/A	N/A	N/A

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
<b>Electrostatic discharge</b>					
ESD Generator	TESEQ	NSG 437	1125	2022/11/23	2023/11/22
Barometer	TFA	DIVA PLUS	35.1078.10.IT	2022/6/7	2023/6/6
<b>Radio frequency electromagnetic field immunity</b>					
RF and Microwave Signal Generator	Rohde & Schwarz	SMB100A	113793	2023/3/10	2024/3/9
Power amplifier	Milmega	80RF1000-300	1077558	N/A	N/A
Power amplifier	Milmega	AS0860B	1077559	N/A	N/A
Directional coupler	Werlatone	C10117-10	111786	N/A	N/A
Directional coupler	Werlatone	C8719-20	111759	N/A	N/A
Antenna	AR	ATR80M6G	346008	N/A	N/A
Antenna	SCHWARZBECK	STLP 9149	00441	N/A	N/A
RF switch	OSP	OSP	N/A	N/A	N/A
Power Meter	Rohde & Schwarz	NRP2	105524	2022/9/13	2023/9/12
Power Sensor	Rohde & Schwarz	NRP-Z91	103732	2022/9/13	2023/9/12
Power Sensor	Rohde & Schwarz	NRP-Z91	103733	2022/9/13	2023/9/12
Measurement Software	Rohde & Schwarz	EMC32, VER.10.60.20	N/A	N/A	N/A
<b>Electrical fast transient</b>					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1623180275	2022/11/24	2023/11/23
Capacitive Coupling Clamp	EM TEST	HFK	P1642185790	2022/11/25	2023/11/24
Measurement Software	TESEQ	IEC.control, VER.7.1.5	N/A	N/A	N/A

Instrument					
Equipment	Manufacturer	Model No.	Serial No.	Last Cal.	Expired date
<b>Surge</b>					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1623180275	2022/11/24	2023/11/23
Telecom Surge Generator	EM TEST	TSurge7	P1620180015	2022/11/23	2023/11/22
Coupling and Decoupling Network	EM TEST	CNV 508T5	P1637184038	2022/11/23	2023/11/22
Coupling and Decoupling Network	TESEQ	CDN HSS-2	45091	2022/11/23	2023/11/22
Measurement Software	TESEQ	IEC.control, VER.7.1.5	N/A	N/A	N/A
<b>Immunity to conducted disturbances, induced by radio-frequency fields</b>					
Signal Generator	Rohde & Schwarz	SMC100A	105811	2022/9/26	2023/9/25
Power amplifier	Rohde & Schwarz	BBA150-A125B125	102340	N/A	N/A
Coupling and Decoupling Network	TESEQ	CDN M016	45073	2023/3/13	2024/3/12
Coupling and Decoupling Network	TESEQ	CDN T2-10	45003	2023/3/13	2024/3/12
Coupling and Decoupling Network	TESEQ	CDN T4-10	44939	2023/3/13	2024/3/12
Coupling and Decoupling Network	TESEQ	CDN T8-10	49203	2022/12/12	2023/12/11
Coupling and Decoupling Network	TESEQ	CDN ST08A	57417	2022/6/27	2023/6/26
EM Injection Clamp	TESEQ	CAL 801A & KEMZ 801A	75454.1, 75454.2 & 45181	2023/4/13	2024/4/12
Power - Sensor	Rohde & Schwarz	NRP-Z91	103730	2022/12/9	2023/12/8
Power - Sensor	Rohde & Schwarz	NRP-Z91	103731	2022/12/9	2023/12/8
Measurement Software	Rohde & Schwarz	EMC32, VER.10.20.01	N/A	N/A	N/A
<b>Power frequency magnetic field immunity</b>					
Ultra Compact Simulator	EM TEST	UCS 500N7	P1623180275	2022/11/24	2023/11/23
Current Transformer	EM TEST	MC 2630	P1644186773	2022/8/22	2023/8/21
Magnetic Field Test Antenna	EM TEST	MS 100N	P1627181324	2022/8/22	2023/8/21
Current Transformer	EM TEST	MFT100	P2025241594	2022/8/22	2023/8/21
Motorized Variac	EM TEST	MV 2616 (varic NX1-260-16)	P1643186426	2022/11/25	2023/11/24

## 6. EMISSION TEST

### 6.1. Conducted Disturbance Measurement

#### 6.1.1. Limits of conducted disturbance voltage and common mode disturbance.

AC mains port:

FREQUENCY (MHz)	<input checked="" type="checkbox"/> Class A (dB $\mu$ V)		<input type="checkbox"/> Class B (dB $\mu$ V)	
	Quasi-peak	Average	Quasi-peak	Average
0.15 -0.5	79.00	66.00	66 - 56 *	56 - 46*
0.50 -5.0	73.00	60.00	56.00	46.00
5.0 -30.0	73.00	60.00	60.00	50.00

Telecommunications/network port:

FREQUENCY (MHz)	<input type="checkbox"/> Class A			
	Voltage limit (dB $\mu$ V)		Current limit(dB $\mu$ A)	
	Quasi-peak	Average	Quasi-peak	Average
0.15 -0.5	97 - 87 *	84 - 74*	53 - 43 *	40 - 30*
0.50 -30.0	87.00	74.00	43.00	30.00
FREQUENCY (MHz)	<input type="checkbox"/> Class B			
	Voltage limit (dB $\mu$ V)		Current limit(dB $\mu$ A)	
	Quasi-peak	Average	Quasi-peak	Average
0.15 -0.5	84 - 74 *	74 - 64*	40 - 30 *	30 - 20*
0.50 -30.0	74.00	64.00	30.00	20.00

Note:

- (1) The tighter limit applies at the band edges.
- (2) The limit of " \* " marked band means the limitation decreases linearly with the logarithm of the frequency in the range.
- (3) The test result calculated as following:  
Measurement Value = Reading Level + Correct Factor  
Correct Factor = Insertion Loss + Cable Loss + Attenuator Factor(if use)  
Margin Level = Measurement Value - Limit Value

The following table is the setting of the receiver


Receiver Parameters	Setting
Attenuation	10 dB
Start Frequency	0.15 MHz
Stop Frequency	30 MHz
IF Bandwidth	9 kHz



#### 6.1.4. Test Result

Mode 1 ; LISN (150k-30MHz)

Test Mode:	Mode 1	Temperature:	23℃
Test Voltage:	110Vdc from DC source	Humidity:	66%RH
Tested By:	Duncan Wang	Test Date:	May 25, 2023



No.	Frequency (MHz)	Reading (dBuV)	Correct (dB)	Result (dBuV)	Limit (dBuV)	Margin (dB)	Remark
1	0.1655	25.59	9.96	35.55	79.00	-43.45	QP
2	0.1655	17.79	9.96	27.75	66.00	-38.25	AVG
3	0.2102	49.46	9.96	59.42	79.00	-19.58	QP
4	0.2102	48.87	9.96	58.83	66.00	-7.17	AVG
5	0.4172	34.86	9.96	44.82	79.00	-34.18	QP
6	0.4172	34.92	9.96	44.88	66.00	-21.12	AVG
7	14.8062	32.63	10.39	43.02	73.00	-29.98	QP
8	14.8062	32.48	10.39	42.87	60.00	-17.13	AVG
9	27.7327	44.47	10.63	55.10	73.00	-17.90	QP
10	27.7327	43.56	10.63	54.19	60.00	-5.81	AVG
11	28.5808	47.21	10.63	57.84	73.00	-15.16	QP
12	28.5808	45.77	10.63	56.40	60.00	-3.60	AVG

Remark:


Result = Reading +Correct.

Correct = Insertion Loss + Cable Loss + Attenuator Factor.

Margin = Result - Limit.



Test Mode:	Mode 1	Temperature:	23℃
Test Voltage:	110Vdc from DC source	Humidity:	66%RH
Tested By:	Duncan Wang	Test Date:	May 25, 2023



No.	Frequency (MHz)	Reading (dBuV)	Correct (dB)	Result (dBuV)	Limit (dBuV)	Margin (dB)	Remark
1	0.2084	49.75	9.94	59.69	79.00	-19.31	QP
2	0.2084	49.78	9.94	59.72	66.00	-6.28	AVG
3	2.0832	33.11	10.01	43.12	73.00	-29.88	QP
4	2.0832	33.19	10.01	43.20	60.00	-16.80	AVG
5	3.7496	33.09	10.07	43.16	73.00	-29.84	QP
6	3.7496	33.16	10.07	43.23	60.00	-16.77	AVG
7	8.3315	30.46	10.21	40.67	73.00	-32.33	QP
8	8.3315	30.48	10.21	40.69	60.00	-19.31	AVG
9	14.5849	34.63	10.41	45.04	73.00	-27.96	QP
10	14.5849	34.43	10.41	44.84	60.00	-15.16	AVG
11	28.5472	47.84	10.70	58.54	73.00	-14.46	QP
12	28.5472	46.98	10.70	57.68	60.00	-2.32	AVG

Remark:

Result = Reading +Correct.

Correct = Insertion Loss + Cable Loss + Attenuator Factor.

Margin = Result - Limit.

## 6.2. Radiated Disturbance Measurement(below 1GHz)

### 6.2.1. Limits of radiated disturbance measurement

FREQUENCY (MHz)	<input checked="" type="checkbox"/> Class A		<input type="checkbox"/> Class B	
	<input type="checkbox"/> At 10m	<input checked="" type="checkbox"/> At 3m	<input type="checkbox"/> At 10m	<input type="checkbox"/> At 3m
	dBμV/m	dBμV/m	dBμV/m	dBμV/m
30 – 230	40	50	30	40
230 – 1000	47	57	37	47

#### NOTE:

- (1) The limit for radiated test was performed according to EN55032, CISPR 32.
- (2) The tighter limit applies at the band edges.
- (3) The test result calculated as following:

Measurement Value = Reading Level + Correct Factor,


Correct Factor = Antenna Factor + Cable Loss - Amplifier Gain(if use),

Margin Level = Measurement Value - Limit Value.


### **6.2.2. Test Procedure**

- a. The measuring distance of at 3m shall be used for measurements at frequency from 30 to 1000MHz.
- b. The EUT was placed on the top of a rotating table 0.8 meters above the ground at a 3 meter chamber. The table was rotated 360 degrees to determine the position of the highest radiation.
- c. The height of the equipment shall be set at 0.8 m; the height of the test antenna shall vary between 1 m to 4 m. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- d. The initial step in collecting radiated emission data is a spectrum analyzer peak detector mode pre-scanning the measurement frequency range. Significant peaks are then marked and then Quasi Peak detector mode re-measured.
- e. If the Peak Mode measured value compliance with and lower than Quasi Peak Mode Limit, the EUT shall be deemed to meet QP Limits and then no additional QP Mode measurement performed.
- f. For the actual test configuration, please refer to the related Item:EUT Test Photos.

### 6.2.3. Test Setup




For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.



## 6.2.4. Test Result

Mode 1 ; 30M-1GHz

Test Mode:	Mode 1	Temperature:	25°C
Test Voltage:	110Vdc from DC source	Humidity:	64%RH
Tested By:	Duncan Wang	Test Date:	May 19, 2023



No.	Frequency (MHz)	Reading (dBuV/m)	Correct dB/m	Result (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Remark
1	68.0887	65.78	-21.22	44.56	50.00	-5.44	PK
2	95.3780	66.75	-25.59	41.16	50.00	-8.84	PK
3	141.2267	65.70	-20.92	44.78	50.00	-5.22	PK
4	266.7123	72.30	-21.00	51.30	57.00	-5.70	PK
5	305.6417	68.13	-19.19	48.94	57.00	-8.06	PK
6	327.3697	66.08	-18.62	47.46	57.00	-9.54	PK


Remark:

Result = Reading +Correct.

Correct Factor = Antenna Factor + Cable Loss - Amplifier Gain.

Margin = Result - Limit.

Test Mode:	Mode 1	Temperature:	25°C
Test Voltage:	110Vdc from DC source	Humidity:	64%RH
Tested By:	Duncan Wang	Test Date:	May 19, 2023



No.	Frequency (MHz)	Reading (dBuV/m)	Correct dB/m	Result (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Remark
1	40.7023	66.01	-20.91	45.10	50.00	-4.90	PK
2	67.3450	65.97	-21.25	44.72	50.00	-5.28	PK
3	138.0257	59.02	-20.95	38.07	50.00	-11.93	PK
4	263.2527	69.46	-21.20	48.26	57.00	-8.74	PK
5	302.2467	62.72	-19.35	43.37	57.00	-13.63	PK
6	321.0970	61.95	-18.90	43.05	57.00	-13.95	PK

Remark:

Result = Reading +Correct.

Correct Factor = Antenna Factor + Cable Loss - Amplifier Gain.

Margin = Result - Limit.

## 7. IMMUNITY TEST

### 7.1. Performance Criteria

According to EN 55035 standard, the general performance criteria as following:

<b>Criteria A</b>	<p>The equipment shall continue to operate as intended without operator intervention. No degradation of performance, loss of function or change of operating state is allowed below a performance level specified by the manufacturer when the equipment is used as intended.</p> <p>The performance level may be replaced by a permissible loss of performance. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.</p>
<b>Criteria B</b>	<p>During the application of the disturbance, degradation of performance is allowed. However, no unintended change of actual operating state or stored data is allowed to persist after the test.</p> <p>After the test, the equipment shall continue to operate as intended without operator intervention; no degradation of performance or loss of function is allowed, below a performance level specified by the manufacturer, when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance.</p> <p>If the minimum performance level (or the permissible performance loss), or recovery time, is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.</p>
<b>Criteria C</b>	<p>Loss of function is allowed, provided the function is self-recoverable, or can be restored by the operation of the controls by the user in accordance with the manufacturer's instructions. A reboot or re-start operation is allowed.</p> <p>Information stored in non-volatile memory, or protected by a battery backup, shall not be lost.</p>

## 7.2. Electrostatic Discharge Immunity Test

### 7.2.1. Test Specification

<b>Standard:</b>	EN 55035(refer to IEC/EN 61000-4-2)
<b>Discharge Impedance:</b>	330(1±10%)Ω / 150(1±10%)pF
<b>Discharge Voltage:</b> <b>Polarity:</b>	Air Discharge: ±2kV/±4kV/±8kV (Direct)
	Contact Discharge: ±2kV/±4kV (Direct/Indirect)
	Positive and Negative
<b>Discharge Mode of Operation:</b>	Single discharges
<b>Discharge Period:</b>	1 second minimum

### 7.2.2. Test Procedure

The test generator necessary to perform direct and indirect application of discharges to the EUT in the following manner:

- a. Contact discharge was applied to conductive surfaces and coupling planes of the EUT. During the test, it was performed with single discharges. For the single discharge time between successive single discharges was at least 1 second. On each pre-selected point at least 10 single discharges (at each polarity) shall be applied. Test shall be performed at a maximum repetition rate of one discharge per second.

Vertical Coupling Plane (VCP):

The coupling plane, of dimensions 0.5m x 0.5m, is placed parallel to, and positioned at a distance 0.1m from, the EUT, with the Discharge Electrode touching the coupling plane. The four faces of the EUT will be performed with electrostatic discharge.

Horizontal Coupling Plane (HCP):

The coupling plane is placed under to the EUT. The generator shall be positioned vertically at a distance of 0.1m from the EUT, with the Discharge Electrode touching the coupling plane. The four faces of the EUT will be performed with electrostatic discharge.


- b. Air discharges at insulation surfaces of the EUT.

It was at least 10 single discharges with positive and negative at the same selected point.

- c. For the actual test configuration, please refer to the related Item :EUT Test Photos.



### 7.2.3. Test Setup



IEC 2209/08

A distance of 0,8 m minimum shall be provided between the EUT and the walls of the laboratory and any other metallic structure.

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

#### 7.2.4. Test Result


Test Mode:	Mode 1					Temperature:				24℃						
Test Voltage:	110Vdc from DC source					Humidity:				45%RH						
Discharge of times:	Air: 10 times Contact: 10 times					ATM pressure				1019 hpa						
Tested By:	Duncan Wang					Test Date:				Jun. 9, 2023						
Mode	Air Discharge								Contact Discharge							
	2kV		4kV		8kV		-kV		2kV		4kV		-kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
1~5	-	-	-	-	-	-	-	-	A	A	A	A	-	-	-	-
6~10	A	A	A	A	A	A	-	-	-	-	-	-	-	-	-	-
Criterion	B								B							
Results	A								A							
Judgment	PASS															
Note	There was no abnormal situation during the test compared with initial operation.															

Mode	HCP Discharge								VCP Discharge							
	2kV		4kV		-kV		-kV		2kV		4kV		-kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
front	A	A	A	A	-	-	-	-	A	A	A	A	-	-	-	-
rear	A	A	A	A	-	-	-	-	A	A	A	A	-	-	-	-
left	A	A	A	A	-	-	-	-	A	A	A	A	-	-	-	-
right	A	A	A	A	-	-	-	-	A	A	A	A	-	-	-	-
Criterion	B				-				B				-			
Results	A				-				A				-			
Judgment	PASS															
Note	There was no abnormal situation during the test compared with initial operation.															



**Customer Request:**


Mode	Air Discharge								Contact Discharge							
	2kV		4kV		6kV		-kV		2kV		4kV		6kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
1~5	-	-	-	-	-	-	-	-	-	-	-	-	A	A	-	-
Criterion	A								A							
Results	-								A							
Judgment	PASS															
Note	There was no abnormal situation during the test compared with initial operation.															

Mode	HCP Discharge								VCP Discharge							
	2kV		4kV		6kV		-kV		2kV		4kV		6kV		-kV	
Location	+	-	+	-	+	-	+	-	+	-	+	-	+	-	+	-
front	-	-	-	-	A	A	-	-	-	-	-	-	A	A	-	-
rear	-	-	-	-	A	A	-	-	-	-	-	-	A	A	-	-
left	-	-	-	-	A	A	-	-	-	-	-	-	A	A	-	-
right	-	-	-	-	A	A	-	-	-	-	-	-	A	A	-	-
Criterion	-				A				-				A			
Results	-				A				-				A			
Judgment	PASS															
Note	There was no abnormal situation during the test compared with initial operation.															







Test point	<div><div></div>Air Discharge</div>	<div><div></div>Contact Discharge</div>
 <p>A photograph of a black, multi-layered electronic component, likely a DC to DC converter, resting on a metallic surface. Two red arrows originate from a red-bordered box containing the number '2'. One arrow points to the top surface of the component, and the other points to a small circular feature on the bottom surface. A red cable is visible on the right side of the component.</p>		
Test point	<div><div></div>Air Discharge</div>	<div><div></div>Contact Discharge</div>
 <p>A photograph of the same black, multi-layered electronic component, resting on a metallic surface. Two blue arrows originate from a blue-bordered box containing the number '7'. One arrow points to the top surface of the component, and the other points to a small circular feature on the bottom surface. A red cable is visible on the right side of the component.</p>		











## 7.3. Radio Frequency Electromagnetic Field Immunity Test

### 7.3.1. Test Specification


<b>Standard:</b>	EN 55035(refer to IEC/EN 61000-4-3)
<b>Frequency Range:</b>	80 MHz to 1000MHz
<b>Spot Frequency:</b>	1800, 2600, 3500, 5000 ( $\pm 1\%$ )
<b>Field Strength:</b>	3V/m (unmodulated)
<b>Immunity level to common wireless communication:</b>	See Table I.1 for test frequency and level
<b>Modulation:</b>	80%, AM(1kHz)
<b>Frequency Step:</b>	1%
<b>Polarity of Antenna</b>	Vertical and Horizontal
<b>Test Distance:</b>	3 meters
<b>Antenna Height:</b>	1.55 meters
<b>Dwell Time:</b>	3 s

### 7.3.2. Test Procedure

The test procedure was in accordance with IEC/EN IEC 61000-4-3.

- The testing was performed in a fully anechoic chamber. The transmit antenna was located at a distance of 3 meters from the EUT.
- The frequency range is swept from 80 MHz to 1000MHz with the signal 80% amplitude modulated with a 1kHz sine wave. The rate of sweep did not exceed  $1.5 \times 10^{-3}$  decade/s. Where the frequency range is swept incrementally, the step size was 1% of fundamental.
- The dwell time at each frequency shall be not less than the time necessary for the EUT to be able to respond.
- The field strength level from 80 MHz to 1000MHz was 3V/m.
- A special spot frequency test point are 1800, 2600, 3500 and 5000MHz ( $\pm 1\%$ )
- Immunity level to common wireless communication test distance is base on client requirement.
- The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

### 7.3.3. Test Setup



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

### 7.3.4. Test Result

Test Mode:	Mode 1	Temperature:	24°C
Test Voltage:	110Vdc from DC source	Humidity:	71%RH
Tested By:	Duncan Wang	Test Date:	May 26, 2023

Freq. Range (MHz)	Position ( Face )	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgement
80-1000	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
1800(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
2600(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
3500(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
5000(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

Immunity Level to common wireless communication						
Freq. Range (MHz)	Position ( Face )	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgement
800(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
900(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
1800(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
2600(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
3500(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
5000(±1%)	Front / Left / Right / Rear	H / V	3V/m	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

**Customer request:**

Freq. Range (MHz)	Position ( Face )	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgement
80-1000	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
1800(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
2600(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
3500(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
5000(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

Immunity Level to common wireless communication						
Freq. Range (MHz)	Position ( Face )	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgement
800(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
900(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
1800(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
2600(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
3500(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
5000(±1%)	Front / Left / Right / Rear	H / V	10V/m	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

## 7.4. Electrical Fast Transient/Burst Immunity Test


### 7.4.1. Test Specification

<b>Standard:</b>	EN 55035(refer to IEC/EN 61000-4-4)
<b>Test Voltage:</b>	0.5,1 kV(Peak)
<b>Polarity:</b>	Positive and Negative
<b>Impulse Frequency:</b>	5 kHz
<b>Impulse wave shape:</b>	5/50 Tr/Th ns
<b>Burst Duration:</b>	15ms
<b>Burst Period:</b>	300ms
<b>Test Duration:</b>	1 Minute

### 7.4.2. Test Procedure

- The EUT was tested with 1000 volt discharges to the AC power input leads, 500 volt discharges to the signal/control ports.
- Both positive and negative polarity discharges were applied.
- Table-top equipment and equipment normally mounted on ceilings or walls as well as built-in equipment shall be tested with the EUT located  $(0,1 \pm 0,01)$  m above the ground reference plane.
- The EUT and the auxiliary equipment were placed on a table of 0.8 m heights above a metal ground reference plane. The size of ground plane is greater than 0.8mx1m and project beyond the EUT by at least 0.1m on all sides. The ground plane is connected to the protective earth. The minimum distance between the EUT and all other conductive structures (including the generator, AE and the walls of a shielded room), except the ground reference plane, shall be more than 0,5 m.
- The duration time of each test sequential was 1 minute.
- The transient/burst waveform was in accordance with IEC/EN 61000-4-4, 5/50ns.

### 7.4.3. Test Setup



IEC 645/12

- (A) location for supply line coupling
- (B) location for signal lines coupling

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

#### 7.4.4. Test Result

Test Mode:	Mode 1	Temperature:	24°C
Test Voltage:	110Vdc from DC source	Humidity:	65%RH
Tested By:	Duncan Wang	Test Date:	Jun. 9, 2023

Repetition Frequency					5kHz					
Test Port		Test Levels (kV)						Criterion	Results	Judgment
		+0.5	-0.5	+1.0	-1.0	-	-			
DC Port	+	A	A	-	-	-	-	B	A	PASS
	-	A	A	-	-	-	-			
	+ & -	A	A	-	-	-	-			
Note		There was no abnormal situation during the test compared with initial operation.								

#### Customer Request:

Repetition Frequency								5kHz		
Test Port		Test Levels (kV)						Criterion	Results	Judgment
		+0.5	-0.5	+1.0	-1.0	+2.0	-2.0			
DC Port	+	-	-	-	-	A	A	B	A	PASS
	-	-	-	-	-	A	A			
	+ & -	-	-	-	-	A	A			
Note		There was no abnormal situation during the test compared with initial operation.								

## 7.5. Surge Immunity Test

### 7.5.1. Test Specification


<b>Standard:</b>	EN 55035(refer to IEC/EN 61000-4-5)
<b>Waveform:</b>	1.2/50 (8/20) Tr/Th $\mu$ s , 10/700 Tr/Th $\mu$ s
<b>Test Voltage:</b>	0.5,1 kV(Line to Line) 0.5,1,2 kV(Line to Earth)
<b>Polarity:</b>	Positive and Negative
<b>Phase Angle:</b>	90°/270°
<b>Repetition Rate:</b>	1 per minute
<b>Times:</b>	5 times each polarity

### 7.5.2. Test Procedure

- The EUT and the auxiliary equipment were placed on a table of 0.8m heights above a metal ground reference plane. The size of ground plane is greater than 1m×1m and project beyond the EUT by at least 0.1m on all sides. The ground plane is connected to the protective earth. The length of power cord between the coupling device and the EUT shall not exceed 2 meters (provided by the manufacturer).
- The EUT was connected to the power mains through a coupling device that directly couples the surge interference signal. The surge noise was applied synchronized to the voltage phase at the zero crossing and the peak value of the AC voltage wave (positive and negative).
- The surges were applied line to line and line(s) to earth. When testing line to earth the test voltage was applied successively between each of the lines and earth. Steps up to the test level specified increased the test voltage. All lower levels including the selected test level were tested. The polarity of each surge level included positive and negative test pulses.
- If EUT was included telecom port and connected to outdoor directly, test shall be applied to line to earth test using 10/700 surge wave form. If the wave form affects the functioning of high speed data port, the test shall be carried out using 1.2/50 wave form do the test.



### 7.5.3. Test Setup



For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

#### 7.5.4. Test Result

Test Mode:	Mode 1	Temperature:	24°C
Test Voltage:	110Vdc from DC source	Humidity:	65%RH
Tested By:	Duncan Wang	Test Date:	Jun. 9, 2023

Wave Form EUT Ports Tested	1.2/50(8/20)Ti/Th us						Criterion	Results	Judgement
	Polarity	Phase	Voltage						
			0.5kV	1kV	2kV	-kV			
DC power port + to -	+	-	A	-	-	-	B	A	PASS
	-	-	A	-	-	-			
Note	There was no abnormal situation during the test compared with initial operation.								

#### Customer request:

Wave Form EUT Ports Tested	1.2/50(8/20)Ti/Th us						Criterion	Results	Judgement
	Polarity	Phase	Voltage						
			0.5kV	1kV	2kV	-kV			
DC power port + to -	+	-	-	A	-	-	B	A	PASS
	-	-	-	A	-	-			
Note	There was no abnormal situation during the test compared with initial operation.								

## 7.6. Immunity to Conducted Disturbances Induced by RF Fields


### 7.6.1. Test Specification

<b>Standard:</b>	EN 55035(refer to IEC/EN 61000-4-6)
<b>Frequency Range:</b>	0.15-10; 10-30; 30-80MHz
<b>Field Strength:</b>	3V; 3 to 1V; 1V (unmodulated, r.m.s.)
<b>Modulation:</b>	80% AM (1 kHz)
<b>Frequency Step:</b>	1%
<b>Dwell Time:</b>	3s

### 7.6.2. Test Procedure

- a. The EUT shall be tested within its intended operating and climatic conditions.
- b. The test shall be performed with the test generator connected to each of the coupling and decoupling devices in turn, while the other non-excited RF input ports of the coupling devices are terminated by a 50-ohm load resistor.
- c. The frequency range is swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80% amplitude. The signal is modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. The step size shall not exceed 1% of the start and thereafter 1% of the preceding frequency value where the frequency is swept incrementally.
- d. The dwell time at each frequency shall not be less than the time necessary for the EUT to be exercised, and able to respond. Sensitive frequencies such as clock frequencies and harmonics or frequencies of dominant interest, shall be analyzed separately.
- e. Attempts should be made to fully exercise the EUT during test, and to fully interrogate all exercise modes selected for susceptibility.

### 7.6.3. Test Setup



- a) The EUT clearance from any metallic objects other than test equipment shall be at least 0,5 m.
- b) Only one of the CDNs not used for injection shall be terminated with  $50 \Omega$ , providing only a return path. All other CDNs shall be configured as decoupling networks.

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

#### 7.6.4. Test Result

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	110Vdc from DC source	Humidity:	65%RH
Tested By:	Duncan Wang	Test Date:	May 24, 2023

Test Ports (Mode)	Freq. Range (MHz)	Field Strength	CDN	Criterion	Results	Judgement
DC Power Port	0.15 --- 10	3V	M016(M2)	A	A	PASS
	10 --- 30	3 to 1V		A	A	PASS
	30 --- 80	1V		A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

#### Customer Request:

Test Ports (Mode)	Freq. Range (MHz)	Field Strength	CDN	Criterion	Results	Judgement
DC Power Port	0.15 --- 80	10V	M016(M2)	A	A	PASS
Note	There was no abnormal situation during the test compared with initial operation.					

## 7.7. Power frequency magnetic field immunity Test


### 7.7.1. Test Specification

<b>Standard:</b>	EN 55035(refer to IEC/EN 61000-4-8)
<b>Frequency Range:</b>	50 Hz
<b>Field Strength:</b>	1 A/m 100 A/m for Continuous (Client request) 1000 A/m for short duration (Client request)
<b>Observation Time:</b>	1 minute for continuous 1s to 3s for short duration
<b>Inductance Coil:</b>	Rectangular type, 1mx1m

### 7.7.2. Test Procedure

- The EUT and support equipment, are placed on a table that is 0.8 meter above a metal ground plane measured 1m\*1m min. and 0.65mm thick min.
- The equipment cabinets shall be connected to the safety earth directly on the GRP via the earth terminal of the EUT.
- The cables supplied or recommended by the equipment manufacturer shall be used 1 meter of all cables used shall be exposed to the magnetic field.
- The EUT with coil shall be leave all magnetic material and wall 1m away in any axis during the test.
- The cable length from generator to coil shall be less than 2m
- The background noise shall be 20dB less than test field strength.
- Test shall be applied to three axis X, Y, Z and disturbance over 1 minute and short term disturbance over 1 to 3 seconds.
- All cables shall be exposed to the magnetic field for 1m of their length.
- For magnetic field strength less than or equal to 30A/m the transformer shall be used MC 2630, for magnetic strength greater than 30A/m, the transformer shall be used MFT 100.

### 7.7.3. Test Setup



Note:

#### TABLE-TOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

#### FLOOR-STANDING EQUIPMENT

The equipment shall be subjected to the test magnetic field by using induction coils of suitable dimensions. The test shall be repeated by moving and shifting the induction coils, in order to test the whole volume of the EUT for each orthogonal direction. The test shall be repeated with the coil shifted to different positions along the side of the EUT, in steps corresponding to 50% of the shortest side of the coil. The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

For the actual test configuration, please refer to Appendix I: Photographs of the Test Configuration.

#### 7.7.4. Test Results

Test Mode:	Mode 1	Temperature:	22°C
Test Voltage:	110Vdc from DC source	Humidity:	60%RH
Tested By:	Rupert Huang	Test Date:	May 22, 2023

Level	Magnetic Field Strength (A/m)	Criterion	Results			Judgement
			X	Y	Z	
1	1	A	A	A	A	PASS
2	3	/	/	/	/	
3	10	/	/	/	/	
4	30	/	/	/	/	
5	100	/	/	/	/	
X	Special	/	/	/	/	
Note	There was no abnormal situation during the test compared with initial operation.					

#### Customer Request:

Level	Magnetic Field Strength (A/m)	Criterion	Results			Judgement
			X	Y	Z	
1	1	/	/	/	/	PASS
2	3	/	/	/	/	
3	10	/	/	/	/	
4	30	/	/	/	/	
5	100	A	A	A	A	
X	Special	/	/	/	/	
Note	There was no abnormal situation during the test compared with initial operation.					



#### Test Results (Short Term: 1 s):

Level	Magnetic Field Strength (A/m)	Criterion	Results			Judgement
			X	Y	Z	
4	300	/	/	/	/	PASS
5	1000	A	A	A	A	
X	Special	/	/	/	/	
Note	There was no abnormal situation during the test compared with initial operation.					




## Appendix I: Photographs of EMC Test Configuration

Conducted Disturbance: Mode 1, LISN





**Radiated Disturbance: Mode 1, 30M-1GHz**






### Electrostatic Discharge Immunity: Mode 01




**Radio Frequency Field Immunity: Mode 01**







### Electrical Fast Transient Immunity: Mode 01



### Surge Immunity: Mode 01



**Immunity to conducted disturbance induced by RF fields: Mode 01**



**Power Frequency Magnetic Immunity: Mode 01**



## **Appendix II: Photographs of the EUT**

Please see the photographs of EUT in the test report no.: 4790893561-EP.

---

**END OF REPORT**

## Annex : Additional test request by client.

### RS TEST RESULT FORM

Project No.: 4790653020

Applicant	TRACO	Product Name	DC to DC Converter
Model Name	TEQ 300-7212WIR-B1	Standard	EN 55035

Test Mode:	Mode 1	Temperature:	24°C
Test Voltage:	DC 110V from DC source	Humidity:	71%RH
Tested By:	Duncan Wang	Test Date:	May. 26, 2023

Customer request: H: Horizontal V: Vertical

Freq. Range (MHz)	Position ( Face )	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgment
80-1000	Front	H / V	20	A	A	Pass
	Left	H / V	20	A	A	
	Right	H / V	20	A	A	
	Rear	H / V	20	A	A	
1800(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
2600(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
3500(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
5000(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
Note	There was no abnormal situation during the test compared with initial operation.					

Immunity Level to common wireless communication						
Freq. Range (MHz)	Position ( Face )	Polarity (H or V)	Field Strength (V/m)	Criterion	Results	Judgment
800	Front / Left / Right / Rear	H / V	20	A	A	Pass
900	Front / Left / Right / Rear	H / V	20	A	A	Pass
1800(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
2600(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
3500(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
5000(±1%)	Front / Left / Right / Rear	H / V	20	A	A	Pass
Note	There was no abnormal situation during the test compared with initial operation.					