



# CAL-TECH Technology Co.,Ltd.

2F., No.2, Ln. 295, Sinming Rd., Neihs Dist., Taipei City 114, Taiwan (R.O.C.)  
TEL: 886-2-2796-5371 / FAX: 886-3-2794-3091 / www.cal-tehc.com.tw

## REPORT OF PERFORMANCE OF EN 55022 / EN 55024

Applicant's company	Traco Electronic AG <b>TRACO POWER</b>
Applicant Address	Jenatschstrasse 1 CH-8002 Zurich
Manufacturers	
Survey By	Cal-Tech Technology Co.,Ltd.

Product Name	AC-DC Switching Power Supply
Brand Name	<b>TRACO POWER</b>
Model Name	TXH 240-124
Receive Date	Jun. 12, 2008~Dec. 22, 2010
Test Date	Jul. 03, 2008~Dec. 22, 2010
Submission Type	Original Equipment
Multiple Listing	TXH 240-112, TXH 240-148
Test Standard	EN 61000-6-3:2001/A11:2004 EN 55024:1999/A1:2001/A2:2003 EN 55022:2006 EN 61000-3-2:2006 EN 61000-3-3:1995/A2:2005 EN 61000-4-2:1995/A2:2001 EN 61000-4-3:2006 EN 61000-4-4:2004 EN 61000-4-5:2006 EN 61000-4-6:1996/A1:2001 EN 61000-4-8:1993/A1:2001 EN 61000-4-5:2006

### Statement

The testing described in this report has been carried out to the best of our knowledge and ability, and our responsibility is limited to the exercise of reasonable care. This certification is not intended to believe the sellers from their legal and/or contractual obligations

## Table of Contents

<b>1. TEST OF COMPLIANCE .....</b>	<b>2</b>
<b>2. SUMMARY OF THE TEST RESULT .....</b>	<b>3</b>
2.1. Test program according to EN55022 & EN55024 & EN 61000-6-3 .....	3
<b>3. HISTORY OF THIS TEST REPORT .....</b>	<b>4</b>
<b>4. GENERAL INFORMATION.....</b>	<b>5</b>
4.1. Test Conditions.....	5
4.2. Standard for Methods of Measurement.....	5
4.3. Deviation Record.....	5
4.4. Table for Supporting Units .....	5
4.5. TEST SETUP .....	6
4.6. Performance Criteria Description .....	6
<b>5. IMMUNITY TESTS RESULT .....</b>	<b>7</b>
5.1. Electrostatic discharge .....	7
5.2. Electromagnetic field .....	8
5.3. Conducted radio frequency .....	9
5.4. Burst/fast transients .....	10
5.5. Surge/show transient .....	11
5.6. Power Frequency Magnetic Field.....	12
5.7. Power supply Interruptions / Power supply Dips .....	13
<b>6. EMISSION TESTS RESULT .....</b>	<b>14</b>
6.1. Radiated emission .....	14
6.2. Conducted emission .....	17
6.3. Harmonics Current Emissions Test .....	20
6.4. Voltage Fluctuations and Flicker Test.....	22
<b>7. PHOTOGRAPHS OF TEST CONFIGURATION.....</b>	<b>24</b>
7.1. Radiated Emissions .....	24
7.2. Conducted Emissions .....	25
7.3. Harmonics Current Emissions Test Setup Photos .....	26
7.4. Voltage Fluctuations and Flicker Test Setup Photos .....	27
7.5. Electrostatic Discharge Immunity Test Setup Photo.....	28
7.6. RF Radiated Fields Immunity Test Setup Photo.....	29
7.7. EFT/Burst Immunity Test Setup Photo .....	30
7.8. Surge Immunity Test Setup Photo .....	31
7.9. RF Common Mode Immunity Test Setup Photo .....	32
7.10. Power Frequency Magnetic Field.....	33
7.11. Voltage Interruptions and Voltage Dips Immunity Test Setup Photo.....	34
<b>8. PHOTOGRAPHS OF EUT .....</b>	<b>35</b>
<b>9. TEST EQUIPMENT AND ANCILLARIES USED FOR TESTS.....</b>	<b>40</b>

## 1. TEST OF COMPLIANCE

Product Name : AC-DC Switching Power Supply  
Brand Name : **TRACO  
POWER**  
Model Name : TXH 240-124  
Applicant : Traco Electronic AG  
**TRACO  
POWER**  
Test Standard : EN 61000-6-3:2001/A11:2004  
EN 55024:1999/A1:2001/A2:2003  
EN 55022:2006  
EN 61000-3-2:2006  
EN 61000-3-3:1995/A2:2005

The AC-DC Switching Power Supply is tested for Information technology equipment according EN55024 Test Requirements for electromagnetic immunity. EN 61000-6-3 & EN55022 for emission for Information technology equipment.

Test program according EN55022 & EN55024 is performed Information technology equipment model is TXH 240-124. The tests were passed.



2010/12/21

Jam Cheng / Checker  
Engineering Manager

## 2. SUMMARY OF THE TEST RESULT

### 2.1. Test program according to EN55022 & EN55024 & EN 61000-6-3

Item	TEST	EN 55022 & EN 61000-6-3	Result
1	Conducted Emissions	EN 55022	Pass
2	Radiated Emissions	EN 55022	Pass
3	Harmonics Current Emissions	EN 61000-3-2	Pass
4	Voltage Fluctuations and Flicker	EN 61000-3-3	Pass
5	TEST	EN 55024	
6	Electrostatic Discharge Immunity	EN 61000-4-2:1995/A2:2005	Pass
7	RF Radiated Fields Immunity	EN 61000-4-3: 2006	Pass
8	EFT/Burst Immunity	EN 61000-4-4:2004	Pass
9	Surge Immunity	EN 61000-4-5:2006	Pass
10	RF Common Mode Immunity	EN 61000-4-6:1996/A1:2001	Pass
11	Power Frequency Magnetic Field	EN 61000-4-8:1993/A1:2001	Pass
11	Voltage Interruptions and Voltage Dips Immunity	IEC 61000-4-11:2004	Pass

### 3. HISTORY OF THIS TEST REPORT

Original Report Issue Date: Jul. 07, 2008

☐ No additional attachment.

☒ additional attachment were issued as following record

Attachment No.	Issue Date	Description
RE-V01-CE-97041	2008/06/07	Original CE Test Report
101112004T	2010/12/22	Modification of CE Test Report Changes the Applicant's company.

## 4. GENERAL INFORMATION

### 4.1. Test Conditions

Normal Voltage	:	90-264 VAC, 47-63 Hz, 3.0A max; O/P Rating: 12VDC~48VDC; 16.66A~5A, 240W max
Operating Voltage	:	230VAC, 50Hz/24VDC, 10A
Normal Temperature	:	+25± 10 °C
Relative Humidity	:	60%± 30 %

### 4.2. Standard for Methods of Measurement

The test program for the TXH 240-124 is in according with the following standards:

Here is the list of the standards followed in this test report.

Within the scope of the test program the following test categories are offered:

- EMC test program includes EN55022 、EN55024 、EN 61000-6-3 、EN 61000-3-2 、EN 61000-3-2

Items	Description
Product Type	AC-DC Switching Power Supply
Power Type	TXH 240-124, TXH 240-112, TXH 240-148
Power Line	shielded : length: 1.2m

Note:

For more detailed features description, please refer to the manufacturer's specifications or User's Manual.

### 4.3. Deviation Record


(If any deviation from additions to or exclusions from test method must be stated)

N/A

### 4.4. Table for Supporting Units

Support Unit	Brand	Model	Serial
YESO	N/A	FVR50W50OK	2K06

#### 4.5. TEST SETUP



#### 4.6. Performance Criteria Description

Criteria	Performance criteria
1.	Performance criterion A: The apparatus shall continue to operate as intended during and after the test. No degradation of performance or loss of function is allowed below a performance level specified by the manufacturer, when the apparatus is used as intended. The performance level may be replaced by a permissible loss of performance. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, either of these may be derived from the product description and documentation, and from what the user may reasonably expect from the apparatus if used as intended.
2.	Performance criterion B: The apparatus shall continue to operate as intended after the test. No degradation of performance or loss of function is allowed below a performance level specified by the manufacturer, when the apparatus is used as intended. The performance level may be replaced by a permissible loss of performance. During the test, degradation of performance is however allowed. No change of actual operating state or stored data is allowed. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, either of these may be derived from the product description and documentation, and from what the user may reasonably expect from the apparatus if used as intended.
3.	Performance criterion C: Temporary loss of function is allowed, provided the function is self-recoverable or can be restored by the operation of the controls.

## 5. IMMUNITY TESTS RESULT

### 5.1. Electrostatic discharge

#### 5.1.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 55%

#### 5.1.2. Test Requirement

According to EN55024


☒ Contact discharge:  $\pm 4$  kV

☒ Air discharge:  $\pm 8$  kV

#### 5.1.3. Test Procedures

According to IEC 61000-4-2 : 1995/A2 : 2001

#### 5.1.4. Test Setup Layout



#### 5.1.5. Test Result

PASS

EUT power: DC power port

☒ Air discharge:  $\pm 8$  Kv

Performance criterion: ☒ A ☐ B ☐ C

☒ Contact discharge:  $\pm 4$  kV

Performance criterion: ☒ A ☐ B ☐ C

☒ Indirect discharge (HCP) :  $\pm 4$  kV

Performance criterion: ☒ A ☐ B ☐ C

☒ Indirect discharge (VCP Front, Left, Back, Right) :  $\pm 4$  kV

Performance criterion: ☒ A ☐ B ☐ C



## 5.2. Electromagnetic field

### 5.2.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 60%

### 5.2.2. Test Requirement


According to EN55024

☒ Frequency range: 80 to 1000 MHz, Field strength: 3 V/m prior to modulation

### 5.2.3. Test Procedures

According to IEC 61000-4-3 : 2006

### 5.2.4. Test Setup Layout



### 5.2.5. Test Result

PASS.

☒ Frequency range: 80 to 1000 MHz · Field strength: 3 V/m prior to modulation

### 5.3. Conducted radio frequency

#### 5.3.1. Test Condition

- Ambient Temperature: 26°C
- Relative Humidity: 60%

#### 5.3.2. Test Requirement

According to IEC EN55024

Frequency range: 0.15 to 80 MHz, Field strength: 3 V, 80% AM (1kHz)


- ☒ Input power port.  
☐ Signal and telecommunication ports

The measurement has to be done between each power line and ground at the power terminal.

#### 5.3.3. Test Procedures.

According to IEC 61000-4-6 : 1996/A1 : 2001

#### 5.3.4. Test Setup Layout



#### 5.3.5. Test Result

EUT power: power port

Frequency range: 0.15 to 80 MHz, Field strength: 3 V, 80% AM (1kHz)

- ☒ Input power port  
Performance criterion: ☒ A ☐ B ☐ C

☐ Signal and telecommunication ports.

Performance criterion: ☐ A ☐ B ☐ C

The EUT was placed on the test table with essential peripherals connected. The EUT was tested on the normal function.

## 5.4. Burst/fast transients

### 5.4.1. Test Condition

- Ambient Temperature: 24°C
- Relative Humidity: 62%

### 5.4.2. Test Requirement


According to EN55024

- ☒  $\pm 1$  kV input power ports
- ☐  $\pm 0.5$  kV for Signal, telecommunication

### 5.4.3. Test Procedures

According to IEC 61000-4-4 : 2004

### 5.4.4. Test Setup Layout



### 5.4.5. Test Result

PASS.

EUT power: power port

☒  $\pm 1$  kV input power ports: Line+ Line

Performance criterion: ☒ A ☐ B ☐ C

☐  $\pm 0.5$  kV On I/O (input/output) signal, data and control ports: RJ45

Performance criterion: ☐ A ☐ B ☐ C

## 5.5. Surge/show transient

### 5.5.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 61%

### 5.5.2. Test Requirement

According to EN55024


- ☒ Input power port : ☒ Line to Line:  $\pm 1\text{ kV}$  (peak), 1.2/50 (8/20) Tr/Th us  
☒ Line (Neutral) to earth:  $\pm 2\text{ kV}$  (peak), 1.2/50 (8/20) Tr/Th us

The measurement has to be done between each power line and ground at the power terminal.

### 5.5.3. Test Procedures

According to IEC 61000-4-5 : 2006

### 5.5.4. Test Setup Layout



### 5.5.5. Test Result

PASS.

EUT power Port

☒  $\pm 1\text{ kV}$  (peak): Line to Line

Performance criterion: ☒ A ☐ B ☐ C

☒ Line (Neutral) to earth:  $\pm 2\text{ kV}$  (peak), 1.2/50 (8/20) Tr/Th us

Performance criterion: ☒ A ☐ B ☐ C

## 5.6. Power Frequency Magnetic Field

### 5.6.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 61%

### 5.6.2. Test Requirement


According to EN55024

- ☒ Power Frequency is 50Hz
- ☒ Magnetic field strength: 1A/m

### 5.6.3. Test Procedures

According to IEC 61000-4-8 : 1993/A1 : 2001

### 5.6.4. Test Setup Layout



### 5.6.5. Test Result

PASS.

EUT power Port

- ☒ Power Frequency is 50Hz

Performance criterion: ☒ A ☐ B ☐ C

- ☒ Magnetic field strength: 1A/m

Performance criterion: ☒ A ☐ B ☐ C

## 5.7. Power supply Interruptions / Power supply Dips

### 5.7.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 61%

### 5.7.2. Test Requirement


According to EN550204

- ☒ Voltage Interruptions 95% : Durations (ms) 500 ms
- ☒ Voltage dips 30 % : Durations (ms) 500 ms
- ☒ Voltage dips 95 % : Durations (ms) 10 ms

### 5.7.3. Test Procedures

According to IEC 61000-4-11 : 2004

### 5.7.4. Test Setup Layout



### 5.7.5. Test Result

PASS.

EUT power Port

- ☒ Voltage Interruptions 95% : Durations (ms) 500 ms

Performance criterion: ☐A ☐B ☒C

- ☒ Voltage dips 30% : Durations (ms) 500 ms

Performance criterion: ☐A ☐B ☒C

- ☒ Voltage dips 95 % : Durations (ms) 10 ms

Performance criterion: ☐A ☒B ☐C

## 6. EMISSION TESTS RESULT

### 6.1. Radiated emission

#### 6.1.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 62%

#### 6.1.2. Test Requirement


According to EN55022

Frequency (MHz)	Quasi-Peak dB( $\mu$ V/m)
30 ~230	30
230-1000	37

#### 6.1.3. Test Procedures.

According to EN55022

#### 6.1.4. Test Setup Layout




## 6.1.5. Test Result

PASS.

Notes

- 1) Measurement Distance: 10m
- 2) Height of table on which the EUT was placed: 0.8 m
- 3) Height of Receiving Antenna: 1 - 4 m
- 4) Example Calculation: result for 62.6442 MHz:  $16.26 + (12.55) = 28.81 \text{ dB } \mu\text{V/m}$
- 5)(a) If the data table appeared symbol of "\*\*\*" means the value was too low to be measured.  
(b) If the data table appeared symbol of "#" means the noise was low, so record the peak value.
- 6) The estimated measurement uncertainty of the result measurement is  
 $+ 4.5\text{dB} / - 4.6\text{dB} (30\text{MHz} \leq f \leq 300\text{MHz})$   
 $+ 4.3\text{dB} / - 4.3\text{dB} (300\text{MHz} \leq f \leq 1\text{GHz})$


## Full Load /Vertical



Frequency (MHz)	Reading Amplitude (dBμV)	Table Degree (°)	Antenna Height (Meter)	Correction Factor (dB/m)	Emission Level (dBμV/m)	Limit (dBμV/m)	Margin (dB)
130.1240	8.78	58.90	1.00	13.19	21.97	30.00	-8.03
138.9730	8.03	73.80	1.00	12.66	20.69	30.00	-9.31
188.5690	6.98	113.20	1.00	10.60	17.58	30.00	-12.42
***							

## Full Load /Horizontal





Frequency (MHz)	Reading Amplitude (dBμV)	Table Degree (°)	Antenna Height (Meter)	Correction Factor (dB/m)	Emission Level (dBμV/m)	Limit (dBμV/m)	Margin (dB)
130.1240	8.38	16.10	4.00	13.19	21.57	30.00	-8.43
138.9730	8.56	21.10	4.00	12.66	21.22	30.00	-8.78
188.5690	7.77	176.80	4.00	10.60	18.37	30.00	-11.63
***							

## 6.2. Conducted emission

### 6.2.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 62%

### 6.2.2. Test Requirement


According to EN55022

Frequency (MHz)	Quasi-Peak dB(μV/m)	Average dB(μV/m)
0.15– 0.50	66-56	56-46
0.50 – 5.0	56	46
5.0-30.0	60	50

### 6.2.3. Test Procedures

According to EN55022

### 6.2.4. Test Setup Layout




### 6.2.5. Test Result


PASS.

Notes :

- 1) The EUT was placed 0.8m above reference ground plane.
- 2) Example calculation: result for 0.150 MHz:  $14.2 + 10.2 = 24.4 \text{ dB } \mu\text{V}$
- 3)(a) If the data table appeared symbol of "\*\*\*\*" means the value was too low to be measured.  
(b) If the data table appeared symbol of "----" means the Q.P. value is under the limit for AVG. so, the AVG. value doesn't need to be measured.  
(c) If the data table appeared symbol of "#" means the noise was low, so record the peak value.
- 4) The estimated measurement uncertainty of the result measurement is  $\pm 2.5\text{dB}$

## Full Load

[illegible]

[illegible]

### 6.3. Harmonics Current Emissions Test

#### 6.3.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 62%


#### 6.3.2. Test Requirement

According to IEC 61000-3-2

#### 6.3.3. Test Procedures


According to IEC 61000-3-2

#### 6.3.4. Test Setup Layout



#### 6.3.5. Test Result

PASS.



### Harmonic Emission - IEC 61000-3-2, EN 61000-3-2, (EN60555-2)

2010/12/11 下午 07:1

$U_{rms} = 230.5$  V     $P = 68.57$  W     $THC = 0.087$  A  
 $I_{rms} = 0.333$  A     $pf = 0.892$      $P_{max} = 70.58$  W

Range: 1 A  
 V-nom: 230 V  
 TestTime: 10 min (100%)

Please key in

Test completed, Result: PASSED

HAR-1000 EMC-Printer

## 6.4. Voltage Fluctuations and Flicker Test

### 6.4.1. Test Condition

- Ambient Temperature: 25°C
- Relative Humidity: 62%


### 6.4.2. Test Requirement

According to IEC 61000-3-3

### 6.4.3. Test Procedures

According to IEC 61000-3-3

### 6.4.4. Test Setup Layout



EUT : equipment under test

M : measuring equipment


G : voltage source in accordance with 6.3 of IEC 61000-3-3.

S : supply source consisting of the supply voltage generator G and test impedance Z with the following elements which include the generator impedance:

### 6.4.5. Test Result

PASS.

Flickermeter 1000-4-15 for 230V/50Hz

**Actual Flicker (Fli): 0.00****Short-term Flicker (Pst): 0.07**

Limit (Pst): 1.00

**Long-term Flicker (Plt): 0.07**

Limit (Plt): 0.65

**Maximum Relative  
Volt. Change (dmax): 0.00%**

Limit (dmax): 4.00%

**Relative Steady-state  
Voltage Change (dc): 0.01%**

Limit (dc): 3.30%

**Maximum Interval  
exceeding 3.30% (dt): 0.00ms**

Limit (dt&gt;Lim): 500ms

**Flicker Emission - IEC 61000-3-3 , EN 61000-3-3 , (EN60555-3)**

2010/12/11 下午 09:1

Urms = 230.5 V P = 67.59 W

Range: 1 A

Irms = 0.331 A pf = 0.886

V-nom: 230 V

TestTime: 120 min (10000%)


*Please key in***Test completed, Result: PASSED***on view*

HAR-1000 EMC-Printer



## 7. PHOTOGRAPHS OF TEST CONFIGURATION

### 7.1. Radiated Emissions



## 7.2. Conducted Emissions



### 7.3. Harmonics Current Emissions Test Setup Photos







#### 7.4. Voltage Fluctuations and Flicker Test Setup Photos



## 7.5. Electrostatic Discharge Immunity Test Setup Photo



## 7.6. RF Radiated Fields Immunity Test Setup Photo



### 7.7. EFT/Burst Immunity Test Setup Photo





## 7.8. Surge Immunity Test Setup Photo





### 7.9. RF Common Mode Immunity Test Setup Photo



## 7.10. Power Frequency Magnetic Field



### 7.11.Voltage Interruptions and Voltage Dips Immunity Test Setup Photo



## 8. PHOTOGRAPHS OF EUT

Outside view 1 of EUT






Inside view 2 of EUT




Inside view 3 of EUT







Inside view 4 of EUT



inside view 5 of EUT





**9. TEST EQUIPMENT AND ANCILLARIES USED FOR TESTS**

No.	Instrument	Manufacture	Model	Serial No.	Last Calibrate
1	LISN (EUT)	Rolf Heine	NNB-2/16Z	99085	Jan. 09, 2008
2	LISN (AXE)	Rolf Heine	NNB-2/16Z	99086	Dec. 31, 2007
3	EMI Receiver	Rohde & Schwarz	ESI 7	830154/001	Dec. 17, 2007
4	50W Terminator	Amphenol	46650-51	N/A	May 11, 2008
5	RF Cable	Miyazaki	BNCP-50FB	N/A	Apr. 10, 2008
6	Coxial Cable	TIM MICROWAVE	LMR-400	N/A	Apr. 10, 2008
7	H/F Test System	EMC Partner	Harmonic-1000	080	May 02, 2008
8	ESD Emulator	Noiseken	ESS-100L(A)	0199C02380	Jul. 17, 2007
9	Signal Generator	HP	8648C	3623A03457	Feb. 18, 2008
10	Amplifier	IFI	CMX50	D019-0200	Apr. 19, 2008
11	Field Monitor	Amplifier Research	FM 2000	20391	Mar. 14, 2008
12	EMC Test System	EMC Partner	Transient-1000	TRA1000-341	Jul. 20, 2007
13	Absorbing Clamp	EMC Partner	Transient-1000	CNEFT1000-176	Jul. 20, 2007
14	E CLAMP	SCHAFFNER	KEMZ801	17044	Dec. 06, 2007
15	CDN	FRANKONIA	M2 + M3	A3011020	Dec. 06, 2007
16	Conducted Immunity Test System	FRANKONIA	CIT-10/75	102C3116	Dec. 06, 2007
17	Magnetic Coil	EMC Partner	MF-1000-1	MF1000-51	Sep. 07, 2007