

## CE EMC Test Report

**Report No.:** CE190819C17

**Test Model:** TEL 10-1210, TEL 10-1223, TEL 10-2410, TEL 10-2423, TEL 10-4810,  
TEL 10-2410WI, TEL 10-2423WI, TEL 10-4810WI, TEL 10-4811AWI,  
TEL 10-4823WI

**Series Model:** TEL 10-1211-B1, TEL 10-1211, TEL 10-1212, TEL 10-1213, TEL 10-1215,  
TEL 10-1222, TEL 10-2411-B1, TEL 10-2411, TEL 10-2412, TEL 10-2413,  
TEL 10-2415, TEL 10-2422, TEL 10-4811-B1, TEL 10-4811, TEL 10-4812,  
TEL 10-4813, TEL 10-4815, TEL 10-4822, TEL 10-4823, TEL 10-2411AWI,  
TEL 10-2411WI, TEL 10-2412WI, TEL 10-2413WI, TEL 10-2415WI,  
TEL 10-2422WI, TEL 10-4811WI, TEL 10-4812WI, TEL 10-4813WI,  
TEL 10-4815WI, TEL 10-4822WI

**Received Date:** Oct. 3, 2017

**Test Date:** Nov. 8 to 14, 2017 & Jun. 25 to Sep. 26, 2019

**Issued Date:** Oct. 7, 2019

**Applicant:** TRACO ELECTRONIC AG

**Address:** SIHLBRUGGSTRASSE 111 CH-6340 BAAR, SWITZERLAND

**Issued By:** Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch  
Lin Kou Laboratories

**Lab Address:** No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan

**Test Location (1):** No. 47-2, 14th Ling, Chia Pau Vil., Lin Kou Dist., New Taipei City, Taiwan

**Test Location (2):** No.19, Hwa Ya 2nd Rd., Wen Hwa Vil., Kwei Shan Dist., Taoyuan City  
33383, Taiwan

**Test Location (3):** No. 49, Lane 206, Wende Rd., Chiung Lin Township, Hsinchu County, Taiwan



This report is for your exclusive use. Any copying or replication of this report to or for any other person or entity, or use of our name or trademark, is permitted only with our prior written permission. This report sets forth our findings solely with respect to the test samples identified herein. The results set forth in this report are not indicative or representative of the quality or characteristics of the lot from which a test sample was taken or any similar or identical product unless specifically and expressly noted. Our report includes all of the tests requested by you and the results thereof based upon the information that you provided to us. You have 60 days from date of issuance of this report to notify us of any material error or omission caused by our negligence, provided, however, that such notice shall be in writing and shall specifically address the issue you wish to raise. A failure to raise such issue within the prescribed time shall constitute your unqualified acceptance of the completeness of this report, the tests conducted and the correctness of the report contents. Unless specific mention, the uncertainty of measurement has been explicitly taken into account to declare the compliance or non-compliance to the specification. The report must not be used by the client to claim product certification, approval, or endorsement by TAF or any government agencies.

## Table of Contents

<b>Release Control Record</b> .....	<b>4</b>
<b>1 Certificate of Conformity</b> .....	<b>5</b>
<b>2 Summary of Test Results</b> .....	<b>7</b>
2.1 Measurement Uncertainty .....	9
2.2 Modification Record.....	9
<b>3 General Information</b> .....	<b>10</b>
3.1 Description of EUT .....	10
3.2 Features of EUT .....	11
3.3 Operating Modes of EUT and Determination of Worst Case Operating Mode .....	12
3.4 Test Program Used and Operation Descriptions.....	12
3.5 Primary Clock Frequencies of Internal Source .....	12
3.6 Package Specifications by Manufacturer .....	13
<b>4 Configuration and Connections with EUT</b> .....	<b>15</b>
4.1 Connection Diagram of EUT and Peripheral Devices.....	15
4.2 Configuration of Peripheral Devices and Cable Connections .....	18
<b>5 Conducted Emission from the Mains Power Port</b> .....	<b>20</b>
5.1 Limits .....	20
5.2 Test Instruments .....	20
5.3 Test Arrangement .....	21
5.4 Test Results .....	22
<b>6 Radiated Emission at Frequencies up to 1GHz</b> .....	<b>42</b>
6.1 Limits .....	42
6.2 Test Instruments .....	42
6.3 Test Arrangement .....	43
6.4 Test Results (With Radiated Solution).....	44
<b>7 General Immunity Requirements</b> .....	<b>64</b>
7.1 Specific Immunity Requirements by Manufacturer.....	66
7.2 Performance Criteria .....	66
<b>8 Electrostatic Discharge Immunity Test (ESD)</b> .....	<b>67</b>
8.1 Test Specification.....	67
8.2 Test Instruments .....	67
8.3 Test Arrangement .....	67
8.4 Supplementary Information .....	68
8.5 Test Results .....	69
<b>9 Radiated, Radio-frequency, Electromagnetic Field Immunity Test (RS)</b> .....	<b>71</b>
9.1 Test Specification.....	71
9.2 Test Instruments .....	72
9.3 Test Arrangement .....	74
9.4 Supplementary Information .....	74
9.5 Test Results .....	75
<b>10 Electrical Fast Transient/Burst Immunity Test (EFT)</b> .....	<b>77</b>
10.1 Test Specification.....	77
10.2 Test Instruments .....	77
10.3 Test Arrangement .....	78
10.4 Supplementary Information .....	78
10.5 Test Results (With EFT & Surge Solution) .....	79

<b>11</b>	<b>Surge Immunity Test.....</b>	<b>80</b>
11.1	Test Specification.....	80
11.2	Test Instruments .....	81
11.3	Test Arrangement .....	82
11.4	Supplementary Information .....	83
11.5	Test Results (With EFT & Surge Solution) .....	84
<b>12</b>	<b>Immunity to Conducted Disturbances Induced by RF Fields (CS).....</b>	<b>85</b>
12.1	Test Specification.....	85
12.2	Test Instruments .....	86
12.3	Test Arrangement .....	88
12.4	Supplementary Information .....	88
12.5	Test Results .....	89
<b>13</b>	<b>Power Frequency Magnetic Field Immunity Test.....</b>	<b>90</b>
13.1	Test Specification.....	90
13.2	Test Instruments .....	90
13.3	Test Arrangement .....	91
13.4	Supplementary Information .....	91
13.5	Test Results .....	92
<b>14</b>	<b>Pictures of Test Arrangements .....</b>	<b>94</b>
14.1	Conducted Emission from the Mains Power Port .....	94
14.2	Radiated Emission at Frequencies up to 1GHz .....	95
14.3	Electrostatic Discharge Immunity Test (ESD) .....	96
14.4	Radio-frequency, Electromagnetic Field Immunity Test (RS).....	97
14.5	Electrical Fast Transient/Burst Immunity Test (EFT).....	100
14.6	Surge Immunity Test.....	100
14.7	Conducted Disturbances Induced by RF Fields (CS) .....	101
14.8	Power Frequency Magnetic Field Immunity Test (PFMF) .....	102
	<b>Appendix – Information of the Testing Laboratories .....</b>	<b>103</b>

### Release Control Record

Issue No.	Description	Date Issued
CE190819C17	Original release.	Oct. 7, 2019

## 1 Certificate of Conformity

**Product:** DC to DC Converter

**Brand:**



**Test Model:** TEL 10-1210, TEL 10-1223, TEL 10-2410, TEL 10-2423, TEL 10-4810, TEL 10-2410WI, TEL 10-2423WI, TEL 10-4810WI, TEL 10-4811AWI, TEL 10-4823WI

**Series Model:** TEL 10-1211-B1, TEL 10-1211, TEL 10-1212, TEL 10-1213, TEL 10-1215, TEL 10-1222, TEL 10-2411-B1, TEL 10-2411, TEL 10-2412, TEL 10-2413, TEL 10-2415, TEL 10-2422, TEL 10-4811-B1, TEL 10-4811, TEL 10-4812, TEL 10-4813, TEL 10-4815, TEL 10-4822, TEL 10-4823, TEL 10-2411AWI, TEL 10-2411WI, TEL 10-2412WI, TEL 10-2413WI, TEL 10-2415WI, TEL 10-2422WI, TEL 10-4811WI, TEL 10-4812WI, TEL 10-4813WI, TEL 10-4815WI, TEL 10-4822WI

**Sample Status:** Engineering sample

**Applicant:** TRACO ELECTRONIC AG

**Test Date:** Nov. 8 to 14, 2017 & Jun. 25 to Sep. 26, 2019

**Standards:** **EN 55032:2015 +AC:2016, Class A**

**EN 61000-3-2:2014 (Not applicable)**

**EN 61000-3-3:2013 (Not applicable)**

**EN 55024:2010/ EN 55024:2010 +A1:2015**

EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0

EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2

EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0

EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0

EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0

EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0

EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0 (Not applicable)

**EN 55035:2017**

EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0

EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2

EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0

EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0

EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0

EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0

EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0 (Not applicable)

Broadband impulse noise disturbances (Not applicable)

The above equipment has been tested by **Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch**, and found compliance with the requirement of the above standards.

Approval signature – on next page

**CERTIFICATION – Continued**

The test record, data evaluation & Equipment Under Test (EUT) configurations represented herein are true and accurate accounts of the measurements of the sample's EMC characteristics under the conditions specified in this report

**Prepared by :** Celia Chen , **Date:** Oct. 7, 2019  
Celia Chen / Supervisor

**Approved by :** Kenny Meng , **Date:** Oct. 7, 2019  
Kenny Meng / Assistant Manager

## 2 Summary of Test Results

Emission			
Standard	Test Item	Result/Remarks	Verdict
EN 55032:2015 +AC:2016	Conducted emission from the mains power port	Minimum passing Class A margin is -2.71 dB at 0.42484 MHz	Pass
	Asymmetric mode conducted emission at telecommunication ports	Without telecom port of the EUT	N/A
	Radiated emission 30-1000 MHz	Minimum passing Class A margin is -2.05 dB at 161.59 MHz	Pass
	Radiated emission above 1GHz	Not applicable because the EUT's highest frequency is below 108 MHz	N/A
EN 61000-3-2:2014	Harmonic current emissions	Test not applicable because port does not exist.	N/A
EN 61000-3-3:2013	Voltage fluctuations and flicker	Test not applicable because port does not exist.	N/A

Immunity				
EN 55024 Clause	Basic standard	Test Item	Result/Remarks	Verdict
4.2.1	EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0	Electrostatic discharges (ESD)	Performance Criterion A	Pass
4.2.3.2	EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2	Continuous radiated disturbances (RS)	Performance Criterion A	Pass
4.2.2	EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0	Electrical fast transients (EFT)	Performance Criterion A	Pass
4.2.5	EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0	Surges	Performance Criterion A	Pass
4.2.3.3	EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0	Continuous conducted disturbances (CS)	Performance Criterion A	Pass
4.2.4	EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0	Power-frequency magnetic fields (PFMF)	Performance Criterion A	Pass
4.2.6	EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0	Voltage dips and interruptions	EUT consumes DC power	N/A

Immunity				
EN 55035 Clause	Basic standard	Test Item	Result/Remarks	Verdict
4.2.1	EN 61000-4-2:2009 / IEC 61000-4-2:2008 ED. 2.0	Electrostatic discharges (ESD)	Performance Criterion A	Pass
4.2.2.2	EN 61000-4-3:2006 +A1:2008 +A2:2010 / IEC 61000-4-3:2010 ED. 3.2	Continuous radiated disturbances (RS)	Performance Criterion A	Pass
4.2.4	EN 61000-4-4:2012 / IEC 61000-4-4:2012 ED. 3.0	Electrical fast transients (EFT)	Performance Criterion A	Pass
4.2.5	EN 61000-4-5:2014 +A1:2017 / IEC 61000-4-5:2014 +A1:2017 ED. 3.0	Surges	Performance Criterion A	Pass
4.2.2.3	EN 61000-4-6:2014 +AC:2015 / IEC 61000-4-6:2013 ED. 4.0	Continuous conducted disturbances (CS)	Performance Criterion A	Pass
4.2.3	EN 61000-4-8:2010 / IEC 61000-4-8:2009 ED. 2.0	Power-frequency magnetic fields (PFMF)	Performance Criterion A	Pass
4.2.6	EN 61000-4-11:2004 +A1:2017 / IEC 61000-4-11:2004 +A1:2017 ED. 2.0	Voltage dips and interruptions	EUT consumes DC power	N/A
4.2.7	-	Broadband impulse noise disturbances, <b>Repetitive</b> (Applicable only to xDSL ports.)	Without CPE xDSL port of the EUT.	N/A
4.2.7	-	Broadband impulse noise disturbances, <b>Isolated</b> (Applicable only to xDSL ports.)	Without CPE xDSL port of the EUT.	N/A

Note:

1. There is no deviation to the applied test methods and requirements covered by the scope of this report.
2. Determining compliance based on the results of the compliance measurement, not taking into account measurement instrumentation uncertainty.
3. The above EN/IEC basic standards are applied with latest version if customer has no special requirement.
4. N/A: Not Applicable.



## 2.1 Measurement Uncertainty

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT as specified in CISPR 16-4-2:

Measurement	Expanded Uncertainty (k=2) ( $\pm$ )	Maximum allowable uncertainty ( $\pm$ )
Conducted disturbance at mains port using AMN, 150kHz ~ 30MHz	2.79 dB	3.4 dB ( $U_{\text{cispr}}$ )
Radiated disturbance, 30MHz ~ 1GHz	3.67 dB	6.3 dB ( $U_{\text{cispr}}$ )


The other instruments specified are routine verified to remain within the calibrated levels, no measurement uncertainty is required to be calculated.

## 2.2 Modification Record

There were no modifications required for compliance.

### 3 General Information

#### 3.1 Description of EUT

Product	DC to DC Converter
Brand	
Test Model	TEL 10-1210, TEL 10-1223, TEL 10-2410, TEL 10-2423, TEL 10-4810, TEL 10-2410WI, TEL 10-2423WI, TEL 10-4810WI, TEL 10-4811AWI, TEL 10-4823WI
Series Model	TEL 10-1211-B1, TEL 10-1211, TEL 10-1212, TEL 10-1213, TEL 10-1215, TEL 10-1222, TEL 10-2411-B1, TEL 10-2411, TEL 10-2412, TEL 10-2413, TEL 10-2415, TEL 10-2422, TEL 10-4811-B1, TEL 10-4811, TEL 10-4812, TEL 10-4813, TEL 10-4815, TEL 10-4822, TEL 10-4823, TEL 10-2411AWI, TEL 10-2411WI, TEL 10-2412WI, TEL 10-2413WI, TEL 10-2415WI, TEL 10-2422WI, TEL 10-4811WI, TEL 10-4812WI, TEL 10-4813WI, TEL 10-4815WI, TEL 10-4822WI
Model Difference	Refer to note as below
Sample Status	Engineering sample
Operating Software	N/A
Power Supply Rating	Refer to note as below
Accessory Device	N/A
Data Cable Supplied	N/A

Note:

1. This report is issued as a duplicate report of BV CPS report no.: CE171003D15B. The difference compared with original report are changing applicant, brand and models for marketing purpose; therefore all test data was copied from the original test report.
2. The EUT is a DC to DC Converter, the specifications of standard models were listed as below:

Model Number	Input Voltage (Range)	Output Voltage
Standard	VDC	VDC
<b>TEL 10-1210</b>	12 (9 ~ 18)	3.3
TEL 10-1211-B1		5
TEL 10-1211		5.1
TEL 10-1212		12
TEL 10-1213		15
TEL 10-1215		24
TEL 10-1222		±12
<b>TEL 10-1223</b>		±15
<b>TEL 10-2410</b>	24 (18 ~ 36)	3.3
TEL 10-2411-B1		5
TEL 10-2411		5.1
TEL 10-2412		12
TEL 10-2413		15
TEL 10-2415		24
TEL 10-2422		±12
<b>TEL 10-2423</b>		±15

Model Number	Input Voltage (Range)	Output Voltage
Standard	VDC	VDC
<b>TEL 10-4810</b>	48 (36 ~ 75)	3.3
TEL 10-4811-B1		5
TEL 10-4811		5.1
TEL 10-4812		12
TEL 10-4813		15
TEL 10-4815		24
TEL 10-4822		±12
TEL 10-4823		±15
<b>TEL 10-2410WI</b>	24 (18 ~ 36)	3.3
TEL 10-2411AWI		5
TEL 10-2411WI		5.1
TEL 10-2412WI		12
TEL 10-2413WI		15
TEL 10-2415WI		24
TEL 10-2422WI		±12
<b>TEL 10-2423WI</b>		±15
<b>TEL 10-4810WI</b>	48 (36 ~ 75)	3.3
<b>TEL 10-4811AWI</b>		5
TEL 10-4811WI		5.1
TEL 10-4812WI		12
TEL 10-4813WI		15
TEL 10-4815WI		24
TEL 10-4822WI		±12
<b>TEL 10-4823WI</b>		±15

During the test, the **Model No.: TEL 10-1210, TEL 10-1223, TEL 10-2410, TEL 10-2423, TEL 10-4810, TEL 10-2410WI, TEL 10-2423WI, TEL 10-4810WI, TEL 10-4811AWI, TEL 10-4823WI** were selected as the representative models for the test and therefore only their test data were recorded in this report.

### 3.2 Features of EUT

The tests reported herein were performed according to the method specified by TRACO ELECTRONIC AG, for detailed feature description, please refer to the manufacturer's specifications or user's manual.

### 3.3 Operating Modes of EUT and Determination of Worst Case Operating Mode

1. The EUT was pre-tested under operating and standby condition and the worst emission level was found under **operating condition**.
2. As client's requirement, test modes are presented in the report as below.

As per client's requirement, test mode are presented in the report as below:				
Mode	Model No.	Test Condition	Input Voltage	Output Voltage
Conducted emission, Radiated emission, EFT & Surge tests				
1	TEL 10-1210	Full Load	12Vdc	3.3Vdc
2	TEL 10-1223			±15Vdc
3	TEL 10-2410		24Vdc	3.3Vdc
4	TEL 10-2423			±15Vdc
5	TEL 10-4810		48Vdc	3.3Vdc
6	TEL 10-2410WI		24Vdc	3.3Vdc
7	TEL 10-2423WI			±15Vdc
8	TEL 10-4810WI		48Vdc	3.3Vdc
9	TEL 10-4811AWI			5Vdc
10	TEL 10-4823WI			±15Vdc
Immunity tests (EFT & Surge tests excluded)				
1	TEL 10-1210	Full Load	12Vdc	3.3Vdc
6	TEL 10-2410WI		24Vdc	3.3Vdc

### 3.4 Test Program Used and Operation Descriptions

#### ◆ For Conducted & Radiated tests:

Set the EUT under full load.

#### ◆ For Immunity tests:

Connected a resistor load to DC output port of EUT to make EUT have maximum power consumption and a multimeter was used to monitor voltage of output.


### 3.5 Primary Clock Frequencies of Internal Source

The highest frequency generated or used within the EUT or on which the EUT operates or tunes is 460kHz, provided by TRACO ELECTRONIC AG, for detailed internal source, please refer to the manufacturer's specifications.

### 3.6 Package Specifications by Manufacturer

#### (1) Radiated Solution :

External Filter meets Radiated EMI EN 55032 , class A; FCC part 15 ,level A



Model	Class A	
	L1	C1, C2
TEL 10-1210, TEL 10-1211-B1, TEL 10-1211, TEL 10-1212, TEL 10-1213, TEL 10-1215, TEL 10-1222, TEL 10-1223	30 $\mu$ H/3A 744841330	100pF/2kV 1808
TEL 10-2410, TEL 10-2411-B1, TEL 10-2411, TEL 10-2412, TEL 10-2413, TEL 10-2415, TEL 10-2422, TEL 10-2423, TEL 10-4810, TEL 10-4811-B1, TEL 10-4811, TEL 10-4812, TEL 10-4813, TEL 10-4815, , TEL 10-4822, TEL 10-4823, TEL 10-2410WI, TEL 10-2411AWI, TEL 10-2411WI, TEL 10-2412WI, TEL 10-2413WI, TEL 10-2415WI, TEL 10-2422WI, TEL 10-2423WI, TEL 10-4810WI, TEL 10-4811AWI, TEL 10-4811WI, TEL 10-4812WI, TEL 10-4813WI, TEL 10-4815WI, TEL 10-4822WI, TEL 10-4823WI	30 $\mu$ H/1.4A 744273222	100pF/2kV 1808

#### (2) Package Specifications :

## Package Specifications

### Mechanical Dimensions

### Pin Connections

Pin	Single Output	Dual Output
1	-Vin	-Vin
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin	+Vin

NC: No Connection

All dimensions in mm (inches)

Tolerance: X.X $\pm$ 0.5 (X.XX $\pm$ 0.02)

X.XX $\pm$ 0.25 (X.XXX $\pm$ 0.01)


Pin diameter  $\varnothing$  0.5  $\pm$ 0.05 (0.02 $\pm$ 0.002)

#### Physical Characteristics

Case Size	23.8x13.7x8.0 mm (0.94x0.54x0.31 inches)
Case Material	Aluminium Alloy, Black Anodized Coating
Pin Material	Tinned Copper
Weight	6.5g

### (3) EFT & Surge Solution :

#### External Filter meets EFT & Surge




Model	EFT & Surge		
	C1	L1	C2
TEL 10-1210, TEL 10-1211-B1, TEL 10-1211, TEL 10-1212, TEL 10-1213, TEL 10-1215, TEL 10-1222, TEL 10-1223, TEL 10-2410, TEL 10-2411-B1, TEL 10-2411, TEL 10-2412, TEL 10-2413, TEL 10-2415, TEL 10-2422, TEL 10-2423, TEL 10-2410WI, TEL 10-2411AWI, TEL 10-2411WI, TEL 10-2412WI, TEL 10-2413WI, TEL 10-2415WI, TEL 10-2422WI, TEL 10-2423WI	560µF/50V CHEMI-CON KY Series	10µH/2.2A 74477410	560µF/50V CHEMI-CON KY Series
TEL 10-4810, TEL 10-4811-B1, TEL 10-4811, TEL 10-4812, TEL 10-4813, TEL 10-4815, TEL 10-4822, TEL 10-4823, TEL 10-4810WI, TEL 10-4811AWI, TEL 10-4811WI, TEL 10-4812WI, TEL 10-4813WI, TEL 10-4815WI, TEL 10-4822WI, TEL 10-4823WI	---	---	560µF/100V CHEMI-CON KY Series


## 4 Configuration and Connections with EUT

### 4.1 Connection Diagram of EUT and Peripheral Devices


Conducted test:




Radiated test:



Immunity tests (RS and PFMF (Field Strength: 100A/m, 1000A/m) of EN 55024 & RS (Field Strength: 20 V/m) of EN 55035 tests excluded):




For RS and PFMF (Field Strength: 100A/m, 1000A/m) of EN 55024 tests only:





For RS (Field Strength: 20 V/m) of EN 55035 test only:



## 4.2 Configuration of Peripheral Devices and Cable Connections

### Emission tests:

ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	Fixed Board	N/A	N/A	N/A	N/A	Supplied by client
B.	Load	N/A	N/A	N/A	N/A	Supplied by client
C.	DC Power Supply	GWINSTEK	GPC-6030D	N/A	N/A	Supplied by client

ID	Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	DC power cable	1	0.03	N	0	Supplied by client
2.	DC power cable	1	0.3	N	0	Supplied by client
3.	AC power cable	1	1.8	N	0	Provided by Lab
4.	DC power cable	1	10	N	0	Provided by Lab

Note: The core(s) is(are) originally attached to the cable(s).

### Immunity tests (RS & PFMF (Field Strength: 100A/m, 1000A/m) tests excluded):

ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	Fixed Board	N/A	N/A	N/A	N/A	Supplied by client
B.	Load	N/A	N/A	N/A	N/A	Supplied by client
C.	DC Power Supply	GWINSTEK	GPC-6030D	N/A	N/A	Supplied by client
D.	Multimeter	YFE	YF-370A	N/A	N/A	Provided by Lab

ID	Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	DC power cable	1	0.03	N	0	Supplied by client
2.	DC power cable	1	0.3	N	0	Supplied by client
3.	DC power cable	1	10	N	0	Provided by Lab
4.	Data cable	1	1.0	N	0	Provided by Lab

Note: The core(s) is(are) originally attached to the cable(s).

**RS (Field Strength: 3 V/m, 10 V/m) & PFMF (Field Strength: 100A/m, 1000A/m) tests:**

ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	Fixed Board	N/A	N/A	N/A	N/A	Supplied by client
B.	Battery <only for Mode 1 >	CSB	HR 1234W F2	N/A	N/A	Provided by Lab
C.	Battery *2 <only for Mode 6 >	CSB	HR 1234W F2	N/A	N/A	Provided by Lab
D.	DUMMY LOAD	N/A	N/A	N/A	N/A	Supplied by client
E.	Multimeter	YFE	YF-370A	N/A	N/A	Provided by Lab

ID	Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	DC power cable	2	0.2	N	0	Supplied by client
2.	Data cable	1	1.0	N	0	Provided by Lab

Note: The core(s) is(are) originally attached to the cable(s).

**RS (Field Strength: 20 V/m) test:**

ID	Product	Brand	Model No.	Serial No.	FCC ID	Remarks
A.	Fixed Board	N/A	N/A	N/A	N/A	Supplied by client
B.	Load	N/A	N/A	N/A	N/A	Supplied by client
C.	DC Power Supply	TOPWARD	33010D	809414	N/A	Provided by Lab
D.	Multimeter	YFE	YF-370A	N/A	N/A	Provided by Lab

ID	Descriptions	Qty.	Length (m)	Shielding (Yes/No)	Cores (Qty.)	Remarks
1.	DC power cable	1	0.03	N	0	Supplied by client
2.	DC power cable	1	10	N	0	Provided by Lab
3.	Data cable	1	1.0	N	0	Provided by Lab

Note: The core(s) is(are) originally attached to the cable(s).

## 5 Conducted Emission from the Mains Power Port

### 5.1 Limits

Frequency range (MHz)	Coupling device	Detector type / bandwidth	Class A limits (dBuV)
0.15 - 0.5	AMN	Quasi-peak / 9kHz	79
0.5 - 30.0			73
0.15 - 0.5		Average / 9kHz	66
0.5 - 30.0			60

Frequency range (MHz)	Coupling device	Detector type / bandwidth	Class B limits (dBuV)
0.15 - 0.5	AMN	Quasi-peak / 9kHz	66 - 56
0.5 - 5			56
5 - 30.0			60
0.15 - 0.5		Average / 9kHz	56 - 46
0.5 - 5			46
5 - 30.0			50

### 5.2 Test Instruments


Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
ROHDE & SCHWARZ TEST RECEIVER	ESCS 30	100290	Dec. 18, 2018	Dec. 17, 2019
ROHDE & SCHWARZ Artificial Mains Network (for EUT)	ENV216	101197	Jun 5, 2019	Jun 4, 2020
LISN With Adapter (for EUT)	101197	NA	Jun 5, 2019	Jun 4, 2020
ROHDE & SCHWARZ Artificial Mains Network (for peripherals)	ESH3-Z5	100218	Nov. 30, 2018	Nov. 29, 2019
SCHWARZBECK Artificial Mains Network (For EUT)	NNLK8129	8129229	May 14, 2019	May 13, 2020
SCHWARZBECK Artificial Mains Network (For EUT)	NNLK 8121	8121-808	Mar. 15, 2019	Mar. 14, 2020
Software	Cond_V7.3.7.4	NA	NA	NA
RF cable (JYEBao) With 10dB PAD	5D-FB	Cable-C10.01	Feb. 13, 2019	Feb. 12, 2020
LYNICS Terminator (For ROHDE & SCHWARZ LISN)	0900510	E1-011484	May 13, 2019	May 12, 2020
ROHDE & SCHWARZ Artificial Mains Network (For TV EUT)	ENV216	101196	Apr. 16, 2019	Apr. 15, 2020
LISN With Adapter (for TV EUT)	101196	NA	Apr. 16, 2019	Apr. 15, 2020

- Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
 2. The test was performed in Shielded Room No. 10.  
 3. The VCCI Site Registration No. C-11852.  
 4. Tested Date: Jun. 25 to Jul. 2, 2019.

### 5.3 Test Arrangement

- The EUT was placed 0.4 meters from the conducting wall of the shielded room with EUT being connected to the power mains through an Artificial Mains Network (AMN). Other support units were connected to the power mains through another AMN. The two AMNs provide 50 Ohm/ 50uH of coupling impedance for the measuring instrument.
- Both lines of the power mains connected to the EUT were checked for maximum conducted interference.
- The test results of conducted emissions at mains ports are recorded of six worst margins for quasi-peak (mandatory) [and average (if necessary)] values against the limits at frequencies of interest unless the margin is 20 dB or greater.

Note: The resolution bandwidth and video bandwidth of test receiver is 9kHz for quasi-peak detection (QP) and average detection (AV) at frequency 0.15MHz-30MHz.



- Note:**
1. Support units were connected to second AMN.
  2. The distance specified between EUT/AE and other metallic objects is  $\geq 0.8$  m in the measurement arrangement for table-top EUT.
  3. Cable on the RGP must to be insulated.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


#### 5.4 Test Results

Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	12Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 1		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.40781	10.01	51.00	50.99	61.01	61.00	79.00	66.00	-17.99	-5.00
2	0.81797	10.04	40.04	37.85	50.08	47.89	73.00	60.00	-22.92	-12.11
3	1.22656	10.06	39.72	36.25	49.78	46.31	73.00	60.00	-23.22	-13.69
4	1.63417	10.06	35.20	32.00	45.26	42.06	73.00	60.00	-27.74	-17.94
5	2.04297	10.06	35.98	34.18	46.04	44.24	73.00	60.00	-26.96	-15.76
6	2.44531	10.07	31.21	26.61	41.28	36.68	73.00	60.00	-31.72	-23.32
7	2.85938	10.08	35.50	33.66	45.58	43.74	73.00	60.00	-27.42	-16.26
8	3.25781	10.09	29.59	27.06	39.68	37.15	73.00	60.00	-33.32	-22.85
9	4.08984	10.11	31.16	28.82	41.27	38.93	73.00	60.00	-31.73	-21.07
10	4.91016	10.14	31.69	28.17	41.83	38.31	73.00	60.00	-31.17	-21.69
11	29.96875	10.69	33.47	30.16	44.16	40.85	73.00	60.00	-28.84	-19.15

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	12Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 1		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.41043	10.03	47.09	47.08	57.12	57.11	79.00	66.00	-21.88	-8.89
2	1.23182	10.08	39.95	39.94	50.03	50.02	73.00	60.00	-22.97	-9.98
3	2.05095	10.08	38.42	37.64	48.50	47.72	73.00	60.00	-24.50	-12.28
4	2.87001	10.10	36.66	33.62	46.76	43.72	73.00	60.00	-26.24	-16.28
5	3.69159	10.12	33.19	28.89	43.31	39.01	73.00	60.00	-29.69	-20.99
6	4.52089	10.15	34.41	28.87	44.56	39.02	73.00	60.00	-28.44	-20.98
7	5.34012	10.17	32.41	26.57	42.58	36.74	73.00	60.00	-30.42	-23.26
8	6.96052	10.22	30.97	28.61	41.19	38.83	73.00	60.00	-31.81	-21.17

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	12Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 2		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.41287	10.01	37.84	37.83	47.85	47.84	79.00	66.00	-31.15	-18.16
2	0.82578	10.05	33.05	31.61	43.10	41.66	73.00	60.00	-29.90	-18.34
3	1.65497	10.06	28.23	27.01	38.29	37.07	73.00	60.00	-34.71	-22.93
4	2.06641	10.06	29.04	26.25	39.10	36.31	73.00	60.00	-33.90	-23.69
5	2.89852	10.08	25.23	23.64	35.31	33.72	73.00	60.00	-37.69	-26.28
6	28.93822	10.67	31.93	31.30	42.60	41.97	73.00	60.00	-30.40	-18.03

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value






Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	12Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 2		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.41337	10.03	41.25	41.24	51.28	51.27	79.00	66.00	-27.72	-14.73
2	0.82706	10.07	34.91	32.47	44.98	42.54	73.00	60.00	-28.02	-17.46
3	1.24219	10.08	37.13	34.94	47.21	45.02	73.00	60.00	-25.79	-14.98
4	1.65625	10.08	35.95	32.59	46.03	42.67	73.00	60.00	-26.97	-17.33
5	2.07031	10.08	35.37	31.62	45.45	41.70	73.00	60.00	-27.55	-18.30
6	2.89844	10.10	33.21	31.77	43.31	41.87	73.00	60.00	-29.69	-18.13
7	3.72266	10.12	32.92	32.73	43.04	42.85	73.00	60.00	-29.96	-17.15
8	29.36403	10.77	32.16	32.07	42.93	42.84	73.00	60.00	-30.07	-17.16

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	24Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 3		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42606	10.01	42.24	42.23	52.25	52.24	79.00	66.00	-26.75	-13.76
2	0.85184	10.05	35.57	35.56	45.62	45.61	73.00	60.00	-27.38	-14.39
3	1.27797	10.06	36.38	36.37	46.44	46.43	73.00	60.00	-26.56	-13.57
4	1.70400	10.06	35.24	35.23	45.30	45.29	73.00	60.00	-27.70	-14.71
5	2.55659	10.07	35.04	35.03	45.11	45.10	73.00	60.00	-27.89	-14.90
6	17.47248	10.41	40.97	40.96	51.38	51.37	73.00	60.00	-21.62	-8.63
7	20.88274	10.47	44.12	44.11	54.59	54.58	73.00	60.00	-18.41	-5.42
8	25.14581	10.59	40.24	40.23	50.83	50.82	73.00	60.00	-22.17	-9.18

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	24Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 3		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42606	10.03	43.70	43.69	53.73	53.72	79.00	66.00	-25.27	-12.28
2	1.27862	10.08	38.92	38.91	49.00	48.99	73.00	60.00	-24.00	-11.01
3	2.13044	10.08	37.07	37.06	47.15	47.14	73.00	60.00	-25.85	-12.86
4	2.98263	10.10	35.84	35.83	45.94	45.93	73.00	60.00	-27.06	-14.07
5	4.26172	10.14	35.23	35.22	45.37	45.36	73.00	60.00	-27.63	-14.64
6	20.88417	10.57	38.87	38.86	49.44	49.43	73.00	60.00	-23.56	-10.57

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	24Vdc	Environmental Conditions	25°C, 65%RH, 997mbar
Tested by	Ane Wang		
Test Mode	Mode 4		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.41866	10.01	36.43	36.42	46.44	46.43	79.00	66.00	-32.56	-19.57
2	1.67722	10.06	31.34	31.33	41.40	41.39	73.00	60.00	-31.60	-18.61
3	2.51563	10.07	31.75	31.74	41.82	41.81	73.00	60.00	-31.18	-18.19
4	10.47963	10.29	32.46	32.45	42.75	42.74	73.00	60.00	-30.25	-17.26
5	21.37644	10.49	32.20	32.19	42.69	42.68	73.00	60.00	-30.31	-17.32
6	29.34051	10.68	30.74	30.21	41.42	40.89	73.00	60.00	-31.58	-19.11

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	24Vdc	Environmental Conditions	25°C , 65%RH, 997mbar
Tested by	Ane Wang		
Test Mode	Mode 4		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.41953	10.03	42.46	42.45	52.49	52.48	79.00	66.00	-26.51	-13.52
2	2.51962	10.09	37.43	37.42	47.52	47.51	73.00	60.00	-25.48	-12.49
3	3.35946	10.11	37.14	37.13	47.25	47.24	73.00	60.00	-25.75	-12.76
4	8.39881	10.27	37.30	37.29	47.57	47.56	73.00	60.00	-25.43	-12.44
5	16.37206	10.47	36.25	36.14	46.72	46.61	73.00	60.00	-26.28	-13.39
6	27.29047	10.73	36.32	35.77	47.05	46.50	73.00	60.00	-25.95	-13.50

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	48Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 5		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42080	10.01	42.32	42.31	52.33	52.32	79.00	66.00	-26.67	-13.68
2	0.84169	10.05	33.42	33.41	43.47	43.46	73.00	60.00	-29.53	-16.54
3	2.94600	10.08	32.94	32.93	43.02	43.01	73.00	60.00	-29.98	-16.99
4	18.09491	10.42	39.14	39.13	49.56	49.55	73.00	60.00	-23.44	-10.45
5	25.23882	10.59	45.28	45.27	55.87	55.86	73.00	60.00	-17.13	-4.14
6	28.17853	10.65	42.71	42.70	53.36	53.35	73.00	60.00	-19.64	-6.65

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	48Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 5		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.41953	10.03	46.80	46.79	56.83	56.82	79.00	66.00	-22.17	-9.18
2	0.83991	10.07	37.12	37.11	47.19	47.18	73.00	60.00	-25.81	-12.82
3	1.26047	10.08	37.52	37.51	47.60	47.59	73.00	60.00	-25.40	-12.41
4	1.68019	10.08	39.02	39.01	49.10	49.09	73.00	60.00	-23.90	-10.91
5	2.52069	10.09	39.49	39.48	49.58	49.57	73.00	60.00	-23.42	-10.43
6	4.62100	10.15	39.21	39.20	49.36	49.35	73.00	60.00	-23.64	-10.65
7	25.20656	10.68	43.56	43.55	54.24	54.23	73.00	60.00	-18.76	-5.77

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	24Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 6		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42609	10.01	52.57	52.56	62.58	62.57	79.00	66.00	-16.42	-3.43
2	0.85313	10.05	40.74	40.73	50.79	50.78	73.00	60.00	-22.21	-9.22
3	1.27850	10.06	36.21	36.20	46.27	46.26	73.00	60.00	-26.73	-13.74
4	2.98378	10.08	37.40	37.39	47.48	47.47	73.00	60.00	-25.52	-12.53
5	4.26163	10.12	36.63	36.62	46.75	46.74	73.00	60.00	-26.25	-13.26
6	28.98581	10.67	36.76	36.75	47.43	47.42	73.00	60.00	-25.57	-12.58

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value






Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	24Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 6		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42484	10.03	53.27	53.26	63.30	63.29	79.00	66.00	-15.70	-2.71
2	0.85162	10.07	42.55	42.54	52.62	52.61	73.00	60.00	-20.38	-7.39
3	1.27734	10.08	38.88	38.87	48.96	48.95	73.00	60.00	-24.04	-11.05
4	2.55509	10.09	39.95	39.94	50.04	50.03	73.00	60.00	-22.96	-9.97
5	3.83319	10.13	39.44	39.43	49.57	49.56	73.00	60.00	-23.43	-10.44
6	6.81641	10.22	36.49	36.48	46.71	46.70	73.00	60.00	-26.29	-13.30

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	24Vdc	Environmental Conditions	25°C , 65%RH, 997mbar
Tested by	Ane Wang		
Test Mode	Mode 7		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.41308	10.01	42.12	42.11	52.13	52.12	79.00	66.00	-26.87	-13.88
2	0.82578	10.05	34.65	34.64	44.70	44.69	73.00	60.00	-28.30	-15.31
3	1.23964	10.06	34.06	34.05	44.12	44.11	73.00	60.00	-28.88	-15.89
4	2.89106	10.08	29.76	29.75	39.84	39.83	73.00	60.00	-33.16	-20.17
5	7.84750	10.22	28.46	28.45	38.68	38.67	73.00	60.00	-34.32	-21.33
6	28.90598	10.67	27.21	25.80	37.88	36.47	73.00	60.00	-35.12	-23.53

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	24Vdc	Environmental Conditions	25°C , 65%RH, 997mbar
Tested by	Ane Wang		
Test Mode	Mode 7		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.41187	10.03	46.01	46.00	56.04	56.03	79.00	66.00	-22.96	-9.97
2	0.82428	10.07	40.58	40.57	50.65	50.64	73.00	60.00	-22.35	-9.36
3	2.47369	10.09	37.47	37.46	47.56	47.55	73.00	60.00	-25.44	-12.45
4	6.18578	10.20	38.70	38.69	48.90	48.89	73.00	60.00	-24.10	-11.11
5	9.48494	10.30	37.12	37.11	47.42	47.41	73.00	60.00	-25.58	-12.59
6	21.85406	10.60	34.50	34.49	45.10	45.09	73.00	60.00	-27.90	-14.91

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	48Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 8		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42344	10.01	51.37	51.36	61.38	61.37	79.00	66.00	-17.62	-4.63
2	0.84531	10.05	39.13	39.12	49.18	49.17	73.00	60.00	-23.82	-10.83
3	2.95703	10.08	36.01	36.00	46.09	46.08	73.00	60.00	-26.91	-13.92
4	4.22356	10.12	34.73	34.72	44.85	44.84	73.00	60.00	-28.15	-15.16
5	25.76875	10.60	36.77	36.76	47.37	47.36	73.00	60.00	-25.63	-12.64
6	29.14744	10.67	38.06	38.05	48.73	48.72	73.00	60.00	-24.27	-11.28

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	48Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 8		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42219	10.03	51.59	51.58	61.62	61.61	79.00	66.00	-17.38	-4.39
2	0.84531	10.07	40.76	40.75	50.83	50.82	73.00	60.00	-22.17	-9.18
3	2.53681	10.09	39.26	39.25	49.35	49.34	73.00	60.00	-23.65	-10.66
4	3.80469	10.13	39.84	39.83	49.97	49.96	73.00	60.00	-23.03	-10.04
5	22.40347	10.61	36.99	36.98	47.60	47.59	73.00	60.00	-25.40	-12.41
6	28.32184	10.75	36.17	36.16	46.92	46.91	73.00	60.00	-26.08	-13.09

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	48Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 9		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42344	10.01	52.65	52.64	62.66	62.65	79.00	66.00	-16.34	-3.35
2	0.84656	10.05	40.36	40.35	50.41	50.40	73.00	60.00	-22.59	-9.60
3	1.26953	10.06	34.49	34.48	44.55	44.54	73.00	60.00	-28.45	-15.46
4	2.53947	10.07	36.01	36.00	46.08	46.07	73.00	60.00	-26.92	-13.93
5	3.81000	10.11	33.22	33.21	43.33	43.32	73.00	60.00	-29.67	-16.68
6	29.63519	10.68	31.92	31.91	42.60	42.59	73.00	60.00	-30.40	-17.41

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	48Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 9		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.42344	10.03	52.65	52.64	62.68	62.67	79.00	66.00	-16.32	-3.33
2	0.84681	10.07	40.72	40.71	50.79	50.78	73.00	60.00	-22.21	-9.22
3	1.26953	10.08	35.62	35.61	45.70	45.69	73.00	60.00	-27.30	-14.31
4	2.54122	10.09	34.16	34.15	44.25	44.24	73.00	60.00	-28.75	-15.76
5	24.56641	10.67	35.54	35.53	46.21	46.20	73.00	60.00	-26.79	-13.80
6	29.22656	10.76	29.99	29.52	40.75	40.28	73.00	60.00	-32.25	-19.72

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value




Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	48Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 10		

Phase Of Power : Positive (+)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.40653	10.01	43.63	43.62	53.64	53.63	79.00	66.00	-25.36	-12.37
2	0.81278	10.04	37.03	37.02	47.07	47.06	73.00	60.00	-25.93	-12.94
3	2.43866	10.07	34.11	34.10	44.18	44.17	73.00	60.00	-28.82	-15.83
4	11.37872	10.30	33.75	33.74	44.05	44.04	73.00	60.00	-28.95	-15.96
5	23.16244	10.54	34.01	34.00	44.55	44.54	73.00	60.00	-28.45	-15.46
6	29.66234	10.68	31.09	31.08	41.77	41.76	73.00	60.00	-31.23	-18.24

**Remarks:**

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value






Frequency Range	150kHz ~ 30MHz	Detector Function & Bandwidth	Quasi-Peak (QP) / Average (AV), 9kHz
Input Power	48Vdc	Environmental Conditions	25°C, 75%RH, 997mbar
Tested by	Vincent Lin		
Test Mode	Mode 10		

Phase Of Power : Negative (-)										
No	Frequency (MHz)	Correction Factor (dB)	Reading Value (dBuV)		Emission Level (dBuV)		Limit (dBuV)		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.40531	10.03	48.84	48.83	58.87	58.86	79.00	66.00	-20.13	-7.14
2	0.81156	10.06	41.31	41.30	51.37	51.36	73.00	60.00	-21.63	-8.64
3	1.21875	10.08	36.94	36.83	47.02	46.91	73.00	60.00	-25.98	-13.09
4	2.03125	10.08	38.15	38.14	48.23	48.22	73.00	60.00	-24.77	-11.78
5	2.43750	10.09	38.36	38.35	48.45	48.44	73.00	60.00	-24.55	-11.56
6	4.46650	10.14	37.53	37.52	47.67	47.66	73.00	60.00	-25.33	-12.34
7	6.09375	10.20	38.41	38.40	48.61	48.60	73.00	60.00	-24.39	-11.40
8	17.86800	10.50	38.32	38.31	48.82	48.81	73.00	60.00	-24.18	-11.19
9	26.39500	10.71	38.20	38.00	48.91	48.71	73.00	60.00	-24.09	-11.29

#### Remarks:

1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
2. The emission levels of other frequencies were very low against the limit.
3. Margin value = Emission level – Limit value
4. Correction factor = Insertion loss + Cable loss
5. Emission Level = Correction Factor + Reading Value



## 6 Radiated Emission at Frequencies up to 1GHz

### 6.1 Limits

For Class A Equipment

Frequency range (MHz)	Distance (m)	Limits (dBuV/m)
30 - 230	10	40
230 - 1000		47
30 - 230	3	50
230 - 1000		57

For Class B Equipment

Frequency range (MHz)	Distance (m)	Limits (dBuV/m)
30 - 230	10	30
230 - 1000		37
30 - 230	3	40
230 - 1000		47

### 6.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
EMCI Preamplifier	EMC9135	980326	Feb. 20, 2019	Feb. 19, 2020
EMCI Preamplifier	EMC9135	980327	Feb. 20, 2019	Feb. 19, 2020
Agilent Test Receiver	N9038A	MY55420137	Apr. 15, 2019	Apr. 14, 2020
Agilent Test Receiver	N9038A	MY50010135	May 29, 2019	May 28, 2020
Schwarzbeck Antenna	VULB9168	9168-316	Nov. 27, 2018	Nov. 26, 2019
Schwarzbeck Antenna	VULB9168	9168-317	Nov. 27, 2018	Nov. 26, 2019
Max Full. Turn Table & Tower	MF7802	MF7802121	NA	NA
Max Full. Tower	MF7802	MF780208105	NA	NA
Software	Radiated_V8.7.08	NA	NA	NA
JYEBAO RF cable With 5dB PAD	LMR-600	CABLE-CH8-01.V	Sep. 28, 2018	Oct. 7, 2019
JYEBAO RF cable With 5dB PAD	LMR-600	CABLE-CH8-02.H	Sep. 28, 2018	Oct. 7, 2019
WOKEN RF cable With 5dB PAD	8D	CABLE-CH8-03.3M	Sep. 28, 2018	Oct. 7, 2019


Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
 2. The test was performed in Chamber No. 8.  
 3. The VCCI Site Registration No. R-12946.  
 4. Tested Date: Jul. 1 to 7, 2019.

### 6.3 Test Arrangement

- The EUT was placed on the top of a rotating table 0.8 meters above the ground at an accredited test facility. The table was rotated 360 degrees to determine the position of the highest radiation.
- The EUT was set 10 meters away from the interference-receiving antenna, which was mounted on the top of a variable-height antenna tower.
- The antenna is a broadband antenna, and its height is varied from one meter to four meters above the ground to determine the maximum value of the field strength. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- For each suspected emission, the EUT was arranged to its worst case and then the antenna was tuned to heights from 1 meter to 4 meters and the rotatable table was turned from 0 degrees to 360 degrees to find the maximum reading.
- The test-receiver system was set to quasi-peak detect function and specified bandwidth with maximum hold mode when the test frequency is up to 1 GHz.

Note:

- The resolution bandwidth and video bandwidth of test receiver/spectrum analyzer is 120kHz for quasi-peak detection (QP) at frequency up to 1GHz.
- The measurement distance is the shortest horizontal distance between an imaginary circular periphery just encompassing this arrangement and the calibration point of the antenna.



**Note: Cable on the RGP must be insulated.**

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.


#### 6.4 Test Results (With Radiated Solution)

Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	12Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 1		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	65.02	32.03 QP	40.00	-7.97	3.98 H	242	51.16	-19.13
2	78.26	22.37 QP	40.00	-17.63	3.55 H	49	44.19	-21.82
3	103.57	26.76 QP	40.00	-13.24	3.95 H	220	47.92	-21.16
4	149.38	27.31 QP	40.00	-12.69	4.00 H	42	44.47	-17.16
5	181.22	26.41 QP	40.00	-13.59	4.00 H	231	44.91	-18.50
6	220.02	26.41 QP	40.00	-13.59	4.00 H	48	45.65	-19.24

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	12Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 1		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	33.13	27.89 QP	40.00	-12.11	1.05 V	141	47.77	-19.88
2	64.02	28.59 QP	40.00	-11.41	1.32 V	240	47.68	-19.09
3	80.54	22.69 QP	40.00	-17.31	1.24 V	332	45.03	-22.34
4	88.32	22.53 QP	40.00	-17.47	1.01 V	86	45.44	-22.91
5	139.29	20.45 QP	40.00	-19.55	1.00 V	229	37.99	-17.54
6	182.10	19.02 QP	40.00	-20.98	1.00 V	224	37.27	-18.25

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	12Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 2		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	65.53	35.50 QP	40.00	-4.50	3.96 H	246	54.71	-19.21
2	139.95	33.34 QP	40.00	-6.66	4.00 H	12	51.10	-17.76
3	148.61	32.80 QP	40.00	-7.20	3.88 H	256	50.02	-17.22
4	160.22	30.60 QP	40.00	-9.40	4.00 H	21	47.69	-17.09
5	189.18	29.62 QP	40.00	-10.38	4.00 H	222	48.82	-19.20
6	208.55	30.84 QP	40.00	-9.16	4.00 H	48	50.29	-19.45

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	12Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 2		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	42.20	24.22 QP	40.00	-15.78	1.08 V	187	42.74	-18.52
2	52.09	24.25 QP	40.00	-15.75	1.86 V	247	42.31	-18.06
3	64.73	35.57 QP	40.00	-4.43	1.28 V	226	54.77	-19.20
4	81.87	22.38 QP	40.00	-17.62	1.00 V	61	44.93	-22.55
5	140.02	25.35 QP	40.00	-14.65	1.00 V	237	42.85	-17.50
6	205.67	21.62 QP	40.00	-18.38	1.00 V	101	40.82	-19.20

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	24Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 3		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	64.73	29.88 QP	40.00	-10.12	3.91 H	256	48.96	-19.08
2	103.94	22.14 QP	40.00	-17.86	4.00 H	185	43.21	-21.07
3	151.76	34.12 QP	40.00	-5.88	3.86 H	54	51.25	-17.13
4	171.79	30.92 QP	40.00	-9.08	4.00 H	239	48.40	-17.48
5	191.77	30.03 QP	40.00	-9.97	4.00 H	20	49.35	-19.32
6	225.55	29.81 QP	40.00	-10.19	4.00 H	350	48.98	-19.17

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value






Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	24Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 3		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	33.66	20.38 QP	40.00	-19.62	1.05 V	113	40.06	-19.68
2	64.73	27.47 QP	40.00	-12.53	1.62 V	35	46.67	-19.20
3	90.04	22.15 QP	40.00	-17.85	1.53 V	314	45.03	-22.88
4	134.81	21.61 QP	40.00	-18.39	1.00 V	233	39.41	-17.80
5	148.92	22.27 QP	40.00	-17.73	1.00 V	195	39.21	-16.94
6	195.75	23.45 QP	40.00	-16.55	1.00 V	213	42.66	-19.21

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	24Vdc	Environmental Conditions	25°C, 68%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 4		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	55.39	19.51 QP	40.00	-20.49	3.96 H	241	37.54	-18.03
2	63.83	27.76 QP	40.00	-12.24	4.00 H	191	46.65	-18.89
3	139.73	32.45 QP	40.00	-7.55	4.00 H	19	50.22	-17.77
4	186.58	28.36 QP	40.00	-11.64	3.84 H	273	47.33	-18.97
5	210.78	27.43 QP	40.00	-12.57	4.00 H	359	46.86	-19.43
6	228.05	27.40 QP	40.00	-12.60	4.00 H	54	46.44	-19.04

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	24Vdc	Environmental Conditions	25°C, 68%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 4		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	44.89	23.01 QP	40.00	-16.99	2.41 V	239	41.28	-18.27
2	63.66	27.47 QP	40.00	-12.53	1.52 V	185	46.42	-18.95
3	75.49	22.80 QP	40.00	-17.20	1.32 V	11	43.99	-21.19
4	89.58	23.91 QP	40.00	-16.09	1.00 V	11	46.78	-22.87
5	135.73	24.40 QP	40.00	-15.60	1.00 V	222	42.17	-17.77
6	184.08	20.68 QP	40.00	-19.32	1.00 V	187	39.16	-18.48

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	48Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 5		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	65.91	34.77 QP	40.00	-5.23	3.26 H	255	54.03	-19.26
2	132.07	32.86 QP	40.00	-7.14	3.91 H	272	51.23	-18.37
3	161.73	36.92 QP	40.00	-3.08	4.00 H	228	53.91	-16.99
4	179.94	35.80 QP	40.00	-4.20	4.00 H	27	54.13	-18.33
5	223.66	36.69 QP	40.00	-3.31	4.00 H	359	55.90	-19.21
6	483.04	36.10 QP	47.00	-10.90	3.59 H	21	48.13	-12.03

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	48Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 5		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	33.25	25.22 QP	40.00	-14.78	1.00 V	336	45.06	-19.84
2	66.04	30.92 QP	40.00	-9.08	1.52 V	249	50.28	-19.36
3	132.43	28.87 QP	40.00	-11.13	1.00 V	136	46.88	-18.01
4	165.65	27.77 QP	40.00	-12.23	1.00 V	207	44.56	-16.79
5	210.44	26.76 QP	40.00	-13.24	1.00 V	33	45.89	-19.13
6	476.95	31.00 QP	47.00	-16.00	1.00 V	207	42.02	-11.02

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	24Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 6		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	49.38	19.42 QP	40.00	-20.58	4.00 H	227	37.32	-17.90
2	67.27	26.90 QP	40.00	-13.10	3.72 H	252	46.22	-19.32
3	77.89	22.71 QP	40.00	-17.29	3.68 H	253	44.46	-21.75
4	103.87	25.64 QP	40.00	-14.36	4.00 H	213	46.73	-21.09
5	152.58	28.64 QP	40.00	-11.36	4.00 H	225	45.79	-17.15
6	224.10	26.69 QP	40.00	-13.31	4.00 H	43	45.88	-19.19

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	24Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 6		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	34.05	22.34 QP	40.00	-17.66	1.08 V	301	41.88	-19.54
2	40.89	23.18 QP	40.00	-16.82	1.52 V	124	41.80	-18.62
3	47.24	23.55 QP	40.00	-16.45	1.63 V	166	41.70	-18.15
4	65.11	23.03 QP	40.00	-16.97	1.00 V	258	42.29	-19.26
5	79.57	22.93 QP	40.00	-17.07	1.00 V	46	45.03	-22.10
6	103.89	20.74 QP	40.00	-19.26	1.00 V	97	41.81	-21.07

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	24Vdc	Environmental Conditions	25°C, 68%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 7		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	59.37	25.82 QP	40.00	-14.18	3.96 H	44	44.14	-18.32
2	65.14	36.41 QP	40.00	-3.59	3.46 H	229	55.56	-19.15
3	100.47	26.67 QP	40.00	-13.33	4.00 H	234	48.28	-21.61
4	136.53	27.48 QP	40.00	-12.52	4.00 H	215	45.47	-17.99
5	155.93	27.26 QP	40.00	-12.74	4.00 H	218	44.29	-17.03
6	163.71	26.30 QP	40.00	-13.70	4.00 H	225	43.37	-17.07

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value






Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	24Vdc	Environmental Conditions	25°C, 68%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 7		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	44.11	24.99 QP	40.00	-15.01	2.65 V	178	43.36	-18.37
2	63.54	35.08 QP	40.00	-4.92	1.56 V	222	53.98	-18.90
3	71.73	26.99 QP	40.00	-13.01	1.00 V	32	47.38	-20.39
4	77.12	26.32 QP	40.00	-13.68	1.23 V	356	47.93	-21.61
5	100.28	21.78 QP	40.00	-18.22	1.00 V	285	43.40	-21.62
6	129.57	22.24 QP	40.00	-17.76	1.00 V	200	40.47	-18.23

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	48Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 8		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	65.50	28.96 QP	40.00	-11.04	3.55 H	252	48.17	-19.21
2	76.88	24.48 QP	40.00	-15.52	4.00 H	237	46.02	-21.54
3	156.47	36.85 QP	40.00	-3.15	3.96 H	292	53.88	-17.03
4	181.47	30.93 QP	40.00	-9.07	3.81 H	50	49.44	-18.51
5	221.62	34.77 QP	40.00	-5.23	4.00 H	16	53.99	-19.22
6	435.41	36.86 QP	47.00	-10.14	2.63 H	342	49.55	-12.69

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	48Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 8		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	33.40	25.16 QP	40.00	-14.84	1.00 V	303	44.94	-19.78
2	41.01	24.40 QP	40.00	-15.60	1.20 V	151	42.99	-18.59
3	65.11	25.84 QP	40.00	-14.16	1.63 V	230	45.10	-19.26
4	88.52	23.98 QP	40.00	-16.02	1.00 V	225	46.87	-22.89
5	158.33	25.08 QP	40.00	-14.92	1.00 V	141	41.71	-16.63
6	437.38	31.45 QP	47.00	-15.55	1.00 V	276	43.16	-11.71

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	48Vdc	Environmental Conditions	26°C, 73%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 9		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	64.41	34.62 QP	40.00	-5.38	4.00 H	213	53.64	-19.02
2	151.40	37.32 QP	40.00	-2.68	3.89 H	85	54.45	-17.13
3	<b>161.59</b>	<b>37.95 QP</b>	<b>40.00</b>	<b>-2.05</b>	<b>4.00 H</b>	<b>255</b>	<b>54.94</b>	<b>-16.99</b>
4	185.37	36.59 QP	40.00	-3.41	3.96 H	18	55.46	-18.87
5	223.15	37.35 QP	40.00	-2.65	4.00 H	358	56.56	-19.21
6	240.44	36.90 QP	47.00	-10.10	3.57 H	30	55.05	-18.15

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	48Vdc	Environmental Conditions	26°C, 73%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 9		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	64.41	32.87 QP	40.00	-7.13	1.57 V	183	52.01	-19.14
2	142.11	24.03 QP	40.00	-15.97	1.00 V	73	41.34	-17.31
3	162.91	27.08 QP	40.00	-12.92	1.00 V	200	43.84	-16.76
4	185.37	28.15 QP	40.00	-11.85	1.00 V	203	46.73	-18.58
5	223.05	25.79 QP	40.00	-14.21	1.00 V	191	44.68	-18.89
6	238.67	28.73 QP	47.00	-18.27	1.20 V	182	46.60	-17.87

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	48Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 10		

Antenna Polarity & Test Distance : Horizontal at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	64.22	30.28 QP	40.00	-9.72	3.52 H	249	49.27	-18.99
2	119.17	25.61 QP	40.00	-14.39	3.96 H	265	45.05	-19.44
3	140.87	29.95 QP	40.00	-10.05	4.00 H	210	47.67	-17.72
4	154.01	32.10 QP	40.00	-7.90	4.00 H	217	49.05	-16.95
5	211.58	36.49 QP	40.00	-3.51	3.55 H	54	55.91	-19.42
6	230.00	34.49 QP	40.00	-5.51	4.00 H	86	53.44	-18.95

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value




Frequency Range	30MHz ~ 1GHz	Detector Function & Bandwidth	Quasi-Peak (QP), 120kHz
Input Power	48Vdc	Environmental Conditions	25°C, 71%RH, 994mbar
Tested by	Chin-Wen Wang		
Test Mode	Mode 10		

Antenna Polarity & Test Distance : Vertical at 10 m								
No	Frequency (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	33.35	21.40 QP	40.00	-18.60	2.12 V	279	41.20	-19.80
2	53.67	22.00 QP	40.00	-18.00	1.39 V	312	40.20	-18.20
3	63.88	28.70 QP	40.00	-11.30	1.05 V	242	47.74	-19.04
4	86.48	22.30 QP	40.00	-17.70	1.00 V	185	45.21	-22.91
5	129.38	20.34 QP	40.00	-19.66	1.00 V	214	38.60	-18.26
6	210.91	27.23 QP	40.00	-12.77	1.00 V	29	46.36	-19.13

Remarks:

1. Emission Level(dBuV/m) = Raw Value(dBuV) + Correction Factor(dB/m)
2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)  
– Pre-Amplifier Factor (dB)
3. The other emission levels were very low against the limit.
4. Margin value = Emission level – Limit value



## 7 General Immunity Requirements

### EN 55024:2010/ EN 55024:2010 +A1:2015, Immunity requirements

Clause	Reference standard	Table	Test specification	Performance Criterion
4.2.1	EN/IEC 61000-4-2 ESD	1.3	Enclosure port: ±8kV Air discharge, ±4kV Contact discharge	B
4.2.3.2	EN/IEC 61000-4-3 RS	1.2	Enclosure port: 80-1000 MHz, 3V/m, 80% AM (1kHz)	A
4.2.2	EN/IEC 61000-4-4 EFT	2.3	Signal ports and telecommunication ports: xDSL equipment: ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 100kHz others: ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz	B
		3.3	Input DC power port: ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz	
		4.5	Input AC Power ports: ±1kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz	
4.2.5	EN/IEC 61000-4-5 Surge	2.2	Signal and telecommunication ports (direct to outdoor cables): 10/700 (5/320) (T <sub>r</sub> /T <sub>h</sub> ) µs w/o primary protectors: ±1kV, or with primary protectors fitted: ±4kV	C
		3.2	Input DC power port (direct to outdoor cables): 1.2/50 (8/20) (T <sub>r</sub> /T <sub>h</sub> ) µs Line to earth: ±0.5kV	B
		4.4	Input AC Power ports: 1.2/50 (8/20) (T <sub>r</sub> /T <sub>h</sub> ) µs, Line to line: ±1kV Line to earth: ±2kV	
4.2.3.3	EN/IEC 61000-4-6 CS	2.1	Signal and telecommunication ports(cable length > 3m): 0.15-80 MHz, 3V, 80% AM (1kHz)	A
		3.1	Input DC power port: 0.15-80 MHz, 3V, 80% AM (1kHz)	
		4.1	Input AC Power ports: 0.15-80 MHz, 3V, 80% AM (1kHz)	
4.2.4	EN/IEC 61000-4-8 PFMF	1.1	Enclosure port: 50 or 60 Hz, 1A/m	A



EN 55035:2017, Immunity requirements		
Reference standard	Test specification	Performance Criterion
EN/IEC 61000-4-2 ESD	Enclosure port: ±8kV Air discharge, ±4kV Contact discharge	B
EN/IEC 61000-4-3 RS	Enclosure port: Swept freq. test : 80-1000 MHz, 3V/m, 80% AM (1kHz), Spot freq. test : 1800, 2600, 3500, 5000 MHz (±1 %), 3V/m, 80% AM (1kHz)	A
EN/IEC 61000-4-4 EFT	Analogue/digital data ports (cable length > 3m): xDSL equipment: ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 100kHz others: ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz	B
	DC network power port (cable length > 3m): ±0.5kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz	
	AC mains power ports: ±1.0kV, 5/50 (T <sub>r</sub> /T <sub>h</sub> ) ns, 5kHz	
EN/IEC 61000-4-5 Surge	Analogue/digital data ports (direct to outdoor cables): Port type: unshielded symmetrical 10/700(5/320) (T <sub>r</sub> /T <sub>h</sub> ) μs, w/o primary protectors (line to ground): ±1.0kV, or with primary protectors (line to ground): ±1.0kV, ±4.0kV Port type: coaxial or shielded 1.2/50 (8/20) (T <sub>r</sub> /T <sub>h</sub> ) μs, shield to ground: ±0.5kV	C
	DC network power port (direct to outdoor cables): 1.2/50(8/20) (T <sub>r</sub> /T <sub>h</sub> ) μs, Line to ground: ±0.5kV	B
	AC mains power ports: 1.2/50(8/20) (T <sub>r</sub> /T <sub>h</sub> ) μs, Line to line: ±1kV, Line to ground: ±2kV	B
EN/IEC 61000-4-6 CS	Analogue/digital data ports (cable length > 3m) ; DC network power ports (cable length > 3m) ; AC mains power ports 0.15-10 MHz, 3V, 80% AM (1kHz), 10-30 MHz, 3V-1V, 80% AM (1kHz), 30-80 MHz, 1V, 80% AM (1kHz)	A
EN/IEC 61000-4-8 PFMF	Enclosure port: 50 or 60 Hz, 1A/m	A

## 7.1 Specific Immunity Requirements by Manufacturer

Additional Test		
Reference standard	Test specification	Performance Criterion
EN/IEC 61000-4-2 ESD	Enclosure port: ±6kV Contact discharge	A
EN/IEC 61000-4-3 RS	Enclosure port: 80-1000 MHz, 20V/m, 80% AM (1kHz), Spot freq. test : 1800, 2600, 3500, 5000 MHz (±1 %), 20V/m, 80% AM (1kHz)	A
EN/IEC 61000-4-4 EFT	Input DC power port: ±2kV, 5/50 ( $T_r/T_h$ ) ns, 5kHz	A
EN/IEC 61000-4-5 Surge	Input DC Power ports: 1.2/50 (8/20) ( $T_r/T_h$ ) µs, Line to line: ±2kV	A
EN/IEC 61000-4-6 CS	Input DC Power ports: 0.15-80 MHz, 10V, 80% AM (1kHz)	A
EN/IEC 61000-4-8 PFMF	Enclosure port: 50 Hz, 1000A/m	A

## 7.2 Performance Criteria

### General Performance Criteria

#### Performance criterion A

The equipment shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed below a performance level specified by the manufacturer when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.

#### Performance criterion B

After the test, the equipment shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed, after the application of the phenomena below a performance level specified by the manufacturer, when the equipment is used as intended. The performance level may be replaced by a permissible loss of performance. During the test, degradation of performance is allowed. However, no change of operating state or stored data is allowed to persist after the test. If the minimum performance level (or the permissible performance loss) is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the equipment if used as intended.

#### Performance criterion C

Loss of function is allowed, provided the function is self-recoverable, or can be restored by the operation of the controls by the user in accordance with the manufacturer's instructions. Functions, and/or information stored in non-volatile memory, or protected by a battery backup, shall not be lost.

### Product Specific Performance Criteria

The particular performance criteria which are specified in the normative annexes of EN 55024 / EN 55035 take precedence over the corresponding parts of the general performance criteria. Where particular performance criteria for specific functions are not given, then the general performance criteria shall apply.

## 8 Electrostatic Discharge Immunity Test (ESD)

### 8.1 Test Specification

Product Standard:	EN 55024
Basic Standard:	EN/IEC 61000-4-2
Discharge Impedance:	330 ohm / 150 pF
Discharge Voltage:	Air Discharge: $\pm 2, \pm 4, \pm 8$ kV (Direct) Contact Discharge: $\pm 2, \pm 4, \pm 6$ kV (Indirect/ Direct)
Number of Discharge:	Air – Direct: 10 discharges per location (each polarity) Contact – Direct & Indirect: 25 discharges per location (each polarity) and min. 200 times in total
Discharge Mode:	Single Discharge
Discharge Period:	1-second minimum

Product Standard:	EN 55035
Basic Standard:	EN/IEC 61000-4-2
Discharge Impedance:	330 ohm / 150 pF
Discharge Voltage:	Air Discharge: $\pm 2, \pm 4, \pm 8$ kV (Direct) Contact Discharge: $\pm 2, \pm 4, \pm 6$ kV (Indirect/ Direct)
Number of Discharge:	Air – Direct: 10 discharges per location (each polarity) Contact – Direct & Indirect: 10 discharges per location (each polarity)
Discharge Mode:	Single Discharge
Discharge Period:	1-second minimum

### 8.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
EM Test ESD Simulator	Dito	V0707102251	Apr. 08, 2019	Apr. 07, 2020

Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
2. The test was performed in ESD Room No. 3.  
3. Tested Date: Aug. 27, 2019.

### 8.3 Test Arrangement

The discharges shall be applied in two ways: (For EN 55024 only)

a. Contact discharges to the conductive surfaces and coupling planes:


The EUT shall be exposed to at least 200 discharges, 100 each at negative and positive polarity, at a minimum of four test points. One of the test points shall be subjected to at least 50 indirect discharges to the center of the front edge of the horizontal coupling plane. The remaining three test points shall each receive at least 50 direct contact discharges. If no direct contact test points are available, then at least 200 indirect discharges shall be applied in the indirect mode. Test shall be performed at a maximum repetition rate of one discharge per second.

b. Air discharges at slots and apertures and insulating surfaces:

On those parts of the EUT where it is not possible to perform contact discharge testing, the equipment should be investigated to identify user accessible points where breakdown may occur. Such points are tested using the air discharge method. This investigation should be restricted to those area normally handled by the user. A minimum of 10 single air discharges shall be applied to the selected test point for each such area.

The basic test procedure was in accordance with EN/IEC 61000-4-2:

- Electrostatic discharges were applied only to those points and surfaces of the EUT that are accessible to users during normal operation.
- The test was performed with at least ten single discharges on the pre-selected points in the most sensitive polarity.
- The time interval between two successive single discharges was at least 1 second.
- The ESD generator was held perpendicularly to the surface to which the discharge was applied and the return cable was at least 0.2 meters from the EUT.
- Contact discharges were applied to the non-insulating coating, with the pointed tip of the generator penetrating the coating and contacting the conducting substrate.
- Air discharges were applied with the round discharge tip of the discharge electrode approaching the EUT as fast as possible (without causing mechanical damage) to touch the EUT. After each discharge, the ESD generator was removed from the EUT and re-triggered for a new single discharge. The test was repeated until all discharges were complete.
- At least ten single discharges (in the most sensitive polarity) were applied to the **Horizontal Coupling Plane** at points on each side of the EUT. The ESD generator was positioned at a distance of 0.1 meters from the EUT with the discharge electrode touching the **HCP**.
- At least ten single discharges (in the most sensitive polarity) were applied to the center of one vertical edge of the **Vertical Coupling Plane** in sufficiently different positions that the four faces of the EUT were completely illuminated. The **VCP** (dimensions 0.5m x 0.5m) was placed vertically to and 0.1 meters from the EUT.



#### TABLE-TOP EQUIPMENT

The configuration consisted of a wooden table 0.8 meters high standing on the **Ground Reference Plane**. The **GRP** consisted of a sheet of aluminum at least 0.25mm thick, and 2.5 meters square connected to the protective grounding system. A **Horizontal Coupling Plane** (1.6m x 0.8m) was placed on the table and attached to the **GRP** by means of a cable with 940kΩ total impedance. The equipment under test, was installed in a representative system as described in section 7 of EN/IEC 61000-4-2, and its cables were placed on the **HCP** and isolated by an insulating support of 0.5mm thickness. A distance of 1-meter minimum was provided between the EUT and the walls of the laboratory and any other metallic structure.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

#### 8.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

## 8.5 Test Results

### For EN 55024 & EN 55035

Test mode	Mode 1	Input Voltage	12Vdc
Environmental Conditions	24 °C, 50% RH 999 mbar	Tested by	Michael Cheng

Test Results of Direct Application					
Discharge Level (kV)	Polarity (+/-)	Test Point	Contact Discharge	Air Discharge	Performance Criterion
2, 4, 6	+/-	1	Note	NA	A
2, 4, 8	+/-	2	NA	Note	A

Description of test points of direct application: Please refer to following page for representative mark only.

Test Results of Indirect Application					
Discharge Level (kV)	Polarity (+/-)	Test Point	Horizontal Coupling Plane	Vertical Coupling Plane	Performance Criterion
2, 4, 6	+/-	Four Sides	Note	Note	A

Description of test points of indirect application:

1. Front side                      2. Rear side                      3. Right side                      4. Left side

Note: The EUT function was correct during the test.

Test mode	Mode 6	Input Voltage	24Vdc
Environmental Conditions	24 °C, 50% RH 999 mbar	Tested by	Michael Cheng

Test Results of Direct Application					
Discharge Level (kV)	Polarity (+/-)	Test Point	Contact Discharge	Air Discharge	Performance Criterion
2, 4, 6	+/-	1	Note	NA	A
2, 4, 8	+/-	2	NA	Note	A

Description of test points of direct application: Please refer to following page for representative mark only.



Test Results of Indirect Application					
Discharge Level (kV)	Polarity (+/-)	Test Point	Horizontal Coupling Plane	Vertical Coupling Plane	Performance Criterion
2, 4, 6	+/-	Four Sides	Note	Note	A

Description of test points of indirect application:

1. Front side                      2. Rear side                      3. Right side                      4. Left side

Note: The EUT function was correct during the test.

## Description of Test Points



## 9 Radiated, Radio-frequency, Electromagnetic Field Immunity Test (RS)

### 9.1 Test Specification

Product Standard:	EN 55024
Basic Standard:	EN/IEC 61000-4-3
Frequency Range:	80 MHz - 1000 MHz
Field Strength:	3 V/m, 20 V/m
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Polarity of Antenna:	Horizontal and Vertical
Antenna Height:	1.5m
Dwell Time:	3 seconds

Product Standard:	EN 55035
Basic Standard:	EN/IEC 61000-4-3
Swept Frequency Range:	80 MHz - 1000 MHz
Spot Frequencies:	1800, 2600, 3500, 5000 MHz ( $\pm 1$ %)
Field Strength:	3 V/m, 10 V/m, 20 V/m
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Polarity of Antenna:	Horizontal and Vertical
Antenna Height:	1.5m (For Field Strength: 3 V/m, 10 V/m) 1.55m (For Field Strength: 20 V/m)
Dwell Time:	3 seconds



## 9.2 Test Instruments

### For EN 55024

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
Agilent Signal Generator	E8257D	MY48050465	Jun. 3, 2017	Jun. 2, 2018
PRANA RF Amplifier	AP32DP280	0811-894	NA	NA
TESEQ RF Amplifier	CBA1G-150	T44220	NA	NA
AR RF Amplifier	35S4G8AM4	0326094	NA	NA
AR RF Amplifier	100S1G4M3	0329249	NA	NA
AR Controller	SC1000M3	305910	NA	NA
Narda Broadband Field Meter	NBM-550	B-0872	Feb. 9, 2016	Feb. 8, 2018
BOONTON RF Voltage Meter	4232A	10180	May 19, 2017	May 18, 2018
BOONTON Power Sensor	51013-4E	34870	Jun. 2, 2017	Jun. 1, 2018
BOONTON Power Sensor	51013-4E	34873	Jun. 2, 2017	Jun. 1, 2018
AR Log-Periodic Antenna	AT6080	0329465	NA	NA
EMCO BiconiLog Antenna	3141	1001	NA	NA
AR High Gain Antenna	AT4002A	306533	NA	NA
AR High Gain Horn Antenna	AT4010	0329800	NA	NA
CHANCE MOST Full Anechoic Chamber (9x5x3m)	Chance Most	RS-002	Feb. 6, 2017	Feb. 5, 2018
Software	RS_V7.6	NA	NA	NA

Notes: 1. The calibration interval of the above test instruments is 12/24 months and the calibrations are traceable to NML/ROC and NIST/USA.

2. The test was performed in RS Room No.2.

3. The transmit antenna was located at a distance of 3 meters from the EUT.

4. Tested Date: Nov. 8, 2017



**For EN 55035 (Field Strength: 3 V/m, 10 V/m)**

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
AgilentSignal Generator	E8257D	MY48050465	Jun. 7, 2019	Jun. 6, 2020
PRANA RF Amplifier	AP32DP280	0811-894	NA	NA
TESTQAmplifier	CBA 1G-275	T44344	NA	NA
AR RF Amplifier	35S4G8AM4	0326094	NA	NA
AR RF Amplifier	100S1G4M3	0329249	NA	NA
AR Controller	SC1000M3	305910	NA	NA
ETS Electric Field Sensor	HI-6105	00086973	Dec. 4, 2018	Dec. 3, 2019
BOONTON RF Voltage Meter	4232A	10180	May 29, 2019	May 28, 2020
BOONTON Power Sensor	51011-EMC	34152	May 29, 2019	May 28, 2020
BOONTON Power Sensor	51011-EMC	34153	May 29, 2019	May 28, 2020
ARLog-Periodic Antenna	AT6080	0329465	NA	NA
EMCO BiconiLog Antenna	3141	1001	NA	NA
ARHigh Gain Antenna	AT4010	0329800	NA	NA
SchwarzbeckLOG ANTENNA	Stlp 9149	9149-260	NA	NA
CHANCE MOST Full Anechoic Chamber (9x5x3m)	Chance Most	RS-002	Feb. 6, 2019	Feb. 5, 2020
Software	RS_V7.6	NA	NA	NA

- Note:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  2. The test was performed in RS Room No.2.
  3. The transmit antenna was located at a distance of 3 meters from the EUT.
  4. Tested Date: Sep. 16, 2019.

**For EN 55035 (Field Strength: 20 V/m)**


Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
BONN Power Amp	BLMA 1060-100/50D	118694	NA	NA
BBA Power Amp	B250C125	101011	NA	NA
Power Sensor	NRP-Z91	101572	Jan. 24, 2019	Jan. 23, 2020
Power Sensor	NRP-Z91	101573	Jan. 18, 2019	Jan. 17, 2020
Signal Generator	SMB100A	105801	Jan. 17, 2019	Jan. 16, 2020
R&S Software	EMC32 Version 8.52.0	NA	NA	NA
Stacked Log-Per Antenna	STLP9149	9149-141	NA	NA
High GAIN LOG-Periodic Antenna	HL046E	100114	NA	NA

- Note:
1. The test was performed in Hwa Ya RS Room 2.
  2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  3. The transmit antenna was located at a distance of 3 meters from the EUT.
  3. Tested Date: Sep. 26, 2019.

### 9.3 Test Arrangement

The test procedure was in accordance with EN/IEC 61000-4-3.

- The testing was performed in a fully anechoic chamber.
- The frequency range is swept from 80 MHz to 1000 MHz, with the signal 80% amplitude modulated with a 1kHz sine wave. **(For EN 55024)**
- The swept frequency range is from 80 MHz to 1000 MHz and the spot frequencies are 1800, 2600, 3500, 5000 MHz ( $\pm 1\%$ ), with the signal 80% amplitude modulated with a 1kHz sine wave. **(For EN 55035)**
- The dwell time of the amplitude modulated carrier was applied in 3 s at each of the frequencies during the scan. The sensitive frequencies (e.g. clock frequencies or frequencies identified by the manufacturer or obtained as outcome of the test) shall be analyzed in addition to the stepped frequencies. **(For EN 55035)**
- The field strength level was 3 V/m, 10 V/m, 20 V/m.
- The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.



#### Table-top Equipment

The EUT installed in a representative system as described in section 7 of EN/IEC 61000-4-3 was placed on a non-conductive table 0.8 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

### 9.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

## 9.5 Test Results

### For EN 55024

Test mode	Mode 1	Input Voltage	12Vdc
Environmental Conditions	25°C, 68% RH	Tested by	Michael Cheng

Frequency (MHz)	Polarity	Azimuth (°)	Test Distance (m)	Applied Field Strength		Observation	Performance Criterion
				(V/m)	Modulation		
80 -1000	V&H	0	3	3	80% AM (1kHz)	Note	A
80 -1000	V&H	90	3	3	80% AM (1kHz)	Note	A
80 -1000	V&H	180	3	3	80% AM (1kHz)	Note	A
80 -1000	V&H	270	3	3	80% AM (1kHz)	Note	A
80 -1000	V&H	0	1.5	20	80% AM (1kHz)	Note	A
80 -1000	V&H	90	1.5	20	80% AM (1kHz)	Note	A
80 -1000	V&H	180	1.5	20	80% AM (1kHz)	Note	A
80 -1000	V&H	270	1.5	20	80% AM (1kHz)	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 6	Input Voltage	24Vdc
Environmental Conditions	25°C, 68% RH	Tested by	Michael Cheng

Frequency (MHz)	Polarity	Azimuth (°)	Test Distance (m)	Applied Field Strength		Observation	Performance Criterion
				(V/m)	Modulation		
80 -1000	V&H	0	3	3	80% AM (1kHz)	Note	A
80 -1000	V&H	90	3	3	80% AM (1kHz)	Note	A
80 -1000	V&H	180	3	3	80% AM (1kHz)	Note	A
80 -1000	V&H	270	3	3	80% AM (1kHz)	Note	A
80 -1000	V&H	0	1.5	20	80% AM (1kHz)	Note	A
80 -1000	V&H	90	1.5	20	80% AM (1kHz)	Note	A
80 -1000	V&H	180	1.5	20	80% AM (1kHz)	Note	A
80 -1000	V&H	270	1.5	20	80% AM (1kHz)	Note	A

Note: The EUT function was correct during the test.

**For EN 55035 (Field Strength: 3 V/m, 10 V/m)**

Test mode	Mode 1	Input Voltage	12Vdc
Environmental Conditions	25°C, 55% RH	Tested by	Sean Chou

**For EN 55035 (Field Strength: 20 V/m)**

Test mode	Mode 1	Input Voltage	12Vdc
Environmental Conditions	22°C, 58% RH	Tested by	Evan Liao

Frequency (MHz)	Polarity	Azimuth(°)	Applied Field Strength		Observation	Performance Criterion
			(V/m)	Modulation		
80 - 1000	V&H	0	3, 10, 20	80% AM (1kHz)	Note	A
		90	3, 10, 20	80% AM (1kHz)	Note	A
		180	3, 10, 20	80% AM (1kHz)	Note	A
		270	3, 10, 20	80% AM (1kHz)	Note	A
1800, 2600, 3500, 5000 MHz (±1 %)	V&H	0	3, 10, 20	80% AM (1kHz)	Note	A
		90	3, 10, 20	80% AM (1kHz)	Note	A
		180	3, 10, 20	80% AM (1kHz)	Note	A
		270	3, 10, 20	80% AM (1kHz)	Note	A

Note: The EUT function was correct during the test.

**For EN 55035 (Field Strength: 3 V/m, 10 V/m)**

Test mode	Mode 6	Input Voltage	24Vdc
Environmental Conditions	25°C, 55% RH	Tested by	Sean Chou

**For EN 55035 (Field Strength: 20 V/m)**

Test mode	Mode 6	Input Voltage	24Vdc
Environmental Conditions	22°C, 58% RH	Tested by	Evan Liao

Frequency (MHz)	Polarity	Azimuth(°)	Applied Field Strength		Observation	Performance Criterion
			(V/m)	Modulation		
80 - 1000	V&H	0	3, 10, 20	80% AM (1kHz)	Note	A
		90	3, 10, 20	80% AM (1kHz)	Note	A
		180	3, 10, 20	80% AM (1kHz)	Note	A
		270	3, 10, 20	80% AM (1kHz)	Note	A
1800, 2600, 3500, 5000 MHz (±1 %)	V&H	0	3, 10, 20	80% AM (1kHz)	Note	A
		90	3, 10, 20	80% AM (1kHz)	Note	A
		180	3, 10, 20	80% AM (1kHz)	Note	A
		270	3, 10, 20	80% AM (1kHz)	Note	A

Note: The EUT function was correct during the test.

## 10 Electrical Fast Transient/Burst Immunity Test (EFT)

### 10.1 Test Specification

Product Standard:	EN 55024
Basic Standard:	EN/IEC 61000-4-4
Test Voltage:	Signal / telecommunication port: N/A Input DC power port: $\pm 0.5\text{kV}$ , $\pm 1\text{kV}$ , $\pm 2\text{kV}$ Input AC power port: N/A
Impulse Repetition Frequency:	xDSL telecommunication port: 100kHz others: 5kHz
Impulse Wave Shape:	5/50 ns
Burst Duration:	0.75 ms for 100kHz Repetition Frequency 15 ms for 5kHz Repetition Frequency
Burst Period:	300 ms
Test Duration:	1 min.

Product Standard:	EN 55035
Basic Standard:	EN/IEC 61000-4-4
Test Voltage:	Analogue/digital data port (cable length > 3m): N/A DC network power port (cable length > 3m): $\pm 0.5\text{kV}$ , $\pm 1\text{kV}$ , $\pm 2\text{kV}$ AC mains power port: N/A
Impulse Repetition Frequency:	100kHz : applicable only to xDSL port 5kHz : others
Impulse Wave Shape :	5/50 ns
Burst Duration:	0.75 ms for 100kHz Repetition Frequency 15 ms for 5kHz Repetition Frequency,
Burst Period:	300 ms
Test Duration:	1 min.

### 10.2 Test Instruments


Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
TESEQ, EFT Simulator	NSG 3060	1572	May 22, 2019	May 21, 2020
TESEQ, CDN	CDN 3083-B100	303	May 22, 2019	May 21, 2020
Haefely, Capacitive Clamp	IP4A	155173	Apr. 23, 2019	Apr. 22, 2020

Note:

1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
2. The test was performed in EMS Room No. 2.
3. Tested Date: Jul. 12, 2019.

### 10.3 Test Arrangement

- Both positive and negative polarity discharges were applied.
- The distance between any coupling devices and the EUT should be 0.5 m for table-top equipment testing, and 1.0 m for floor standing equipment. **(For EN 55024)**
- The distance between any coupling devices and the EUT should be  $(0.5 - 0/+0.1)$  m for table-top equipment testing, and  $(1.0 \pm 0.1)$  m for floor standing equipment. **(For EN 55035)**
- The duration time of each test sequential was 1 minute.
- The transient/burst waveform was in accordance with EN/IEC 61000-4-4, 5/50 ns.



#### NOTE:

- location for supply line coupling
- location for signal lines coupling

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

### 10.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

## 10.5 Test Results (With EFT & Surge Solution)

### For EN 55024 & EN 55035

Test mode	Mode 1 & 2	Input Voltage	12Vdc
Environmental Conditions	23°C, 70% RH	Tested by	Chiming Li

#### Input DC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1, 2	(+)	+/-	Note	A
0.5, 1, 2	(-)	+/-	Note	A
0.5, 1, 2	(+)-(-)	+/-	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 3, 4, 6 & 7	Input Voltage	24Vdc
Environmental Conditions	23°C, 70% RH	Tested by	Chiming Li

#### Input DC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1, 2	(+)	+/-	Note	A
0.5, 1, 2	(-)	+/-	Note	A
0.5, 1, 2	(+)-(-)	+/-	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 5, 8, 9 & 10	Input Voltage	48Vdc
Environmental Conditions	23°C, 70% RH	Tested by	Chiming Li

#### Input DC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1, 2	(+)	+/-	Note	A
0.5, 1, 2	(-)	+/-	Note	A
0.5, 1, 2	(+)-(-)	+/-	Note	A

Note: The EUT function was correct during the test.

## 11 Surge Immunity Test

### 11.1 Test Specification

Product Standard:	EN 55024
Basic Standard:	EN/IEC 61000-4-5
Wave-Shape:	Signal / telecommunication port (direct to outdoor cables*): 10/700 $\mu$ s Open Circuit Voltage 5/320 $\mu$ s Short Circuit Current  Input DC power port (direct to outdoor cables*): 1.2/50 $\mu$ s Open Circuit Voltage 8/20 $\mu$ s Short Circuit Current  Input AC power port: 1.2/50 $\mu$ s Open Circuit Voltage 8/20 $\mu$ s Short Circuit Current
Test Voltage:	Signal and telecommunication ports**: w/o primary protectors: N/A with primary protectors fitted: N/A  Input DC power port: Line to earth or ground: $\pm 0.5$ kV, $\pm 1$ kV, $\pm 2$ kV  Input AC power ports: Line to line: N/A Line to earth or ground: N/A
AC Phase Angle (degree):	0°, 90°, 180°, 270°
Pulse Repetition Rate:	1 time / 20 sec.
Number of Tests:	5 positive and 5 negative at selected points

\* This test is only applicable only to ports, which according to the manufacturer's specification, may connect directly to outdoor cables.

\*\* For ports where primary protection is intended, surges are applied at voltages up to 4 kV with the primary protectors fitted. Otherwise the 1 kV test level is applied without primary protection in place.



Product Standard:	EN 55035
Basic Standard:	EN/IEC 61000-4-5
Wave-Shape:	Analogue/digital data ports (direct to outdoor cables*): Port type: unshielded symmetrical 10/700 $\mu$ s Open Circuit Voltage 5/320 $\mu$ s Short Circuit Current  Port type: coaxial or shielded 1.2/50 $\mu$ s Open Circuit Voltage 8/20 $\mu$ s Short Circuit Current  DC network power port (direct to outdoor cables*): 1.2/50 $\mu$ s Open Circuit Voltage 8/20 $\mu$ s Short Circuit Current  AC mains power port: 1.2/50 $\mu$ s Open Circuit Voltage 8/20 $\mu$ s Short Circuit Current
Test Voltage:	Analogue/digital data ports: Port type: unshielded symmetrical** w/o primary protectors (line to ground): N/A with primary protectors (line to ground): N/A Port type: coaxial or shielded shield to ground: N/A  DC network power port: $\pm 0.5$ kV, $\pm 1$ kV, $\pm 2$ kV  AC mains power ports: Line to line : N/A Line to ground : N/A
AC Phase Angle (degree):	90° / 270°
Pulse Repetition Rate:	1 time / 20 sec.
Number of Tests:	5 positive and 5 negative at selected points

\* This test is only applicable only to ports, which according to the manufacturer's specification, may connect directly to outdoor cables.

\*\* For ports where primary protection is intended, surges are applied at voltages up to 4 kV with the primary protectors. Otherwise the 1 kV test level is applied without primary protection in place.

## 11.2 Test Instruments

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
TESEQ, Surge Simulator	NSG 3060	1572	May 22, 2019	May 21, 2020
TESEQ, CDN	CDN 3083-100	1215	May 22, 2019	May 21, 2020
Coupling Decoupling Network	CDN-UTP8	045	Aug. 27, 2018	Aug. 26, 2019
TESEQ Coupling Decoupling Network	CDN HSS-2	41009	May 22, 2019	May 21, 2020
TESEQ Coupling Decoupling Network	CDN 118-T8	40386	Sep. 20, 2018	Sep. 19, 2019
TESEQ CDN for Unshielded Unsymmetrical Signal & Data Lines	CDN117	40144	Sep. 20, 2018	Sep. 19, 2019

Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
2. The test was performed in EMS Room No. 2.  
3. Tested Date: Jul. 12, 2019.

### 11.3 Test Arrangement

a. Input AC/DC Power ports:

The surge is to be applied to the EUT power supply terminals via the capacitive coupling network. Decoupling networks are required in order to avoid possible adverse effects on equipment not under test that may be powered by the same lines, and to provide sufficient decoupling impedance to the surge wave. The power cord between the EUT and the coupling/decoupling networks shall be 2 meters in length (or shorter).

For double-insulated products without PE or external earth connections, the test shall be done in a similar way as for grounded products but without adding any additional external grounded connections. If there are no other possible connections to earth, line-to-ground tests may be omitted.

b. Signal and telecommunication ports,

- Unshielded unsymmetrical interconnection lines:

The surge is applied to the lines via the capacitive coupling. The coupling / decoupling networks shall not influence the specified functional conditions of the EUT. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length.

- Unshielded symmetrical interconnections communication lines:

The surge is applied to the lines via gas arrestors coupling. Test levels below the ignition point of the coupling arrestor cannot be specified. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length.

- High speed communications lines

Prior to the test, the correct operation of the port shall be verified; the external connection shall then be removed and the surge applied directly to the port's terminals with no coupling /decoupling network. After the surge, the correct operation of the port shall again be verified.

- Shielded lines:

- Direct application,

The EUT is isolated from ground and the surge is applied to its metallic enclosure; the termination (or auxiliary equipment) at the port(s) under test is grounded. This test applies to equipment with single or multiple shielded cables.

Rules for application of the surge to shielded lines:

a) Shields grounded at both ends

- The surge injection on the shield.


b) Shields grounded at one end

- If in the installation the shield is connected only at the auxiliary equipment, test shall be done in that configuration but with the generator still connected to the EUT side. If cable lengths allow, the cables shall be on insulated supports 0,1 m above the ground plane or cable tray.

For products which do not have metallic enclosures, the surge is applied directly to the shielded cable.

- Alternative coupling method for testing single cables in a multi-shield configuration,

Surges are applied in close proximity to the interconnection cable under test by a wire. The length of the cable between the port(s) under test and the device attached to the other end of the cable shall be the lesser of: the maximum length permitted by the EUT's specification, or 20 m. Where the length exceeds 1 m, excess lengths of cables shall be bundled at the approximate centre of the cables with the bundles 30 cm to 40 cm in length.



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

#### 11.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

## 11.5 Test Results (With EFT & Surge Solution)

### For EN 55024 & EN 55035

Test mode	Mode 1 & 2	Input Voltage	12Vdc
Environmental Conditions	23°C, 70% RH	Tested by	Chiming Li

Input DC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1, 2	(+)-(-)	+/-	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 3, 4, 6 & 7	Input Voltage	24Vdc
Environmental Conditions	23°C, 70% RH	Tested by	Chiming Li

Input DC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1, 2	(+)-(-)	+/-	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 5, 8, 9 & 10	Input Voltage	48Vdc
Environmental Conditions	23°C, 70% RH	Tested by	Chiming Li

Input DC power port

Voltage (kV)	Test Point	Polarity (+/-)	Observation	Performance Criterion
0.5, 1, 2	(+)-(-)	+/-	Note	A

Note: The EUT function was correct during the test.

## 12 Immunity to Conducted Disturbances Induced by RF Fields (CS)

### 12.1 Test Specification

Product Standard:	EN 55024
Basic Standard:	EN/IEC 61000-4-6
Frequency Range:	0.15 MHz - 80 MHz
Voltage Level:	3 V, 10 V
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Dwell Time	3 seconds

Product Standard:	EN 55035
Basic Standard:	EN/IEC 61000-4-6
Frequency Range:	0.15 MHz - 80 MHz
Voltage Level:	0.15 MHz - 10 MHz: 3V 10 MHz - 30 MHz: 3-1 V 30 MHz - 80 MHz: 1V
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of preceding frequency value
Dwell Time	3 seconds

## 12.2 Test Instruments

### For EN 55024

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
ROHDE & SCHWARZ Signal Generator	SML03	101801	Jan. 14, 2019	Jan. 13, 2020
Digital Sweep Function Generator	8120	984801	NA	NA
AR Power Amplifier	75A250AM1	306331	NA	NA
FCC Coupling Decoupling Network	FCC-801-M2-16A	01047	Jun. 19, 2019	Jun. 18, 2020
FISCHER CUSTOM COMMUNICATIONS EM Injection Clamp	F-203I-23mm	455	NA	NA
FISCHER CUSTOM COMMUNICATIONS Current Injection Clamp	F-120-9A	361	Jul. 24, 2018	Jul. 23, 2019
B&K Ear Simulator	4185	2553594	NA	NA
EM TEST Coupling Decoupling Network	CDN M1/32A	306508	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN T800	34428	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN T800	29459	Jun. 19, 2019	Jun. 18, 2020
FCC Coupling Decoupling Network	FCC-801-T4	02031	Jun. 19, 2019	Jun. 18, 2020
EM TEST Coupling Decoupling Network	CDN T2	306509	Jun. 19, 2019	Jun. 18, 2020
R&S Power Sensor	NRV-Z5	837878/039	Nov. 10, 2018	Nov. 9, 2019
R&S Power Meter	NRVD	837794/040	Nov. 10, 2018	Nov. 9, 2019
TESEQ Coupling Decoupling Network	CDN M232	37702	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN M332	41258	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN M332	41256	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN T400A	28569	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN T8-10	40376	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	ISN ST08	41212	Jun. 19, 2019	Jun. 18, 2020
FCC Coupling Decoupling Network	FCC-801-M5-50A	100018	Jan. 21, 2019	Jan. 20, 2020
Software	CS_V7.4.2	NA	NA	NA

Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
2. The test was performed in CS Room No. 1.  
3. Tested Date: Jul. 12, 2019.

**For EN 55035**

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
ROHDE & SCHWARZ Signal Generator	SML03	101801	Jan. 14, 2019	Jan. 13, 2020
Digital Sweep Function Generator	8120	984801	NA	NA
AR Power Amplifier	75A250AM1	306331	NA	NA
FCC Coupling Decoupling Network	FCC-801-M2-16A	01047	Jun. 19, 2019	Jun. 18, 2020
FISCHER CUSTOM COMMUNICATIONS EM Injection Clamp	F-203I-23mm	455	NA	NA
FISCHER CUSTOM COMMUNICATIONS Current Injection Clamp	F-120-9A	361	Jul. 31, 2019	Jul. 30, 2020
B&K Ear Simulator	4185	2553594	NA	NA
EM TEST Coupling Decoupling Network	CDN M1/32A	306508	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN T800	34428	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN T800	29459	Jun. 19, 2019	Jun. 18, 2020
FCC Coupling Decoupling Network	FCC-801-T4	02031	Jun. 19, 2019	Jun. 18, 2020
EM TEST Coupling Decoupling Network	CDN T2	306509	Jun. 19, 2019	Jun. 18, 2020
R&S Power Sensor	NRV-Z5	837878/039	Nov. 10, 2018	Nov. 9, 2019
R&S Power Meter	NRVD	837794/040	Nov. 10, 2018	Nov. 9, 2019
TESEQ Coupling Decoupling Network	CDN M232	37702	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN M332	41258	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN M332	41256	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	CDN T8-10	40376	Jun. 19, 2019	Jun. 18, 2020
TESEQ Coupling Decoupling Network	ISN ST08	41212	Jun. 19, 2019	Jun. 18, 2020
FCC Coupling Decoupling Network	FCC-801-M5-50A	100018	Jan. 21, 2019	Jan. 20, 2020
Software	CS_V7.4.2	NA	NA	NA

Note: 1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.  
 2. The test was performed in CS Room No. 1.  
 3. Tested Date: Sep. 16, 2019.





## 12.5 Test Results

### For EN 55024

Test mode	Mode 1	Input Voltage	12Vdc
Environmental Conditions	25 °C, 67% RH	Tested by	Sean Chou

Frequency (MHz)	Level (Vrms)	Tested Line	Injection Method	Return Path	Observation	Performance Criterion
0.15 – 80	3, 10	DC power	CDN-M2	N/A	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 6	Input Voltage	24Vdc
Environmental Conditions	25 °C, 67% RH	Tested by	Sean Chou

Frequency (MHz)	Level (Vrms)	Tested Line	Injection Method	Return Path	Observation	Performance Criterion
0.15 – 80	3, 10	DC power	CDN-M2	N/A	Note	A

Note: The EUT function was correct during the test.

### For EN 55035

Test mode	Mode 1	Input Voltage	12Vdc
Environmental Conditions	25 °C, 67% RH	Tested by	Sean Chou

Frequency (MHz)	Level (Vrms)	Tested Line	Injection Method	Return Path	Observation	Performance Criterion
0.15 – 10	3	DC power	CDN-M2	N/A	Note	A
10 – 30	3 – 1	DC power	CDN-M2	N/A	Note	A
30 – 80	1	DC power	CDN-M2	N/A	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 6	Input Voltage	24Vdc
Environmental Conditions	25 °C, 67% RH	Tested by	Sean Chou

Frequency (MHz)	Level (Vrms)	Tested Line	Injection Method	Return Path	Observation	Performance Criterion
0.15 – 10	3	DC power	CDN-M2	N/A	Note	A
10 – 30	3 – 1	DC power	CDN-M2	N/A	Note	A
30 – 80	1	DC power	CDN-M2	N/A	Note	A

Note: The EUT function was correct during the test.

### 13 Power Frequency Magnetic Field Immunity Test

#### 13.1 Test Specification

Product Standard:	EN 55024
Basic Standard:	EN/IEC 61000-4-8
Frequency Range:	50Hz
Field Strength:	1A/m, 100A/m, 1000A/m
Observation Time:	1 minute for Field Strength 1A/m, 100A/m 1 second for Field Strength 1000A/m
Inductance Coil:	Rectangular type, 1 m x 1 m

Product Standard:	EN 55035
Basic Standard:	EN/IEC 61000-4-8
Frequency Range:	50Hz
Field Strength:	1A/m
Observation Time:	1 minute
Inductance Coil:	Rectangular type, 1 m x 1 m

#### 13.2 Test Instruments

##### For Field Strength: 1A/m

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
HAEFELY Magnetic Field Tester	MAG 100	083794-06	NA	NA
COMBINOVA Magnetic Field Meter	MFM10	224	Apr. 23, 2019	Apr. 22, 2020

- Note:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  2. The test was performed in EMS Room No. 1
  3. Tested Date: Jul. 12, 2019.


##### For Field Strength: 100A/m, 1000A/m

Description & Manufacturer	Model No.	Serial No.	Cal. Date	Cal. Due
Triaxial Elf Magnetic Field Meter BELL	4090	NA	Jan. 24, 2017	Jan. 23, 2018
Power frequency magnetic filed coil 3ctest	TCX30	EC1281401	Mar. 06, 2017	Mar. 05, 2018
Power frequency magnetic filed generator 3ctest	PFMF-1200G	EC0111401	Mar. 06, 2017	Mar. 05, 2018

- Notes:
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
  2. The test was performed in EMS-1 room. (TAF No.: 2022)
  3. Tested Date: Nov. 14, 2017

### 13.3 Test Arrangement

- The equipment is configured and connected to satisfy its functional requirements.
- The power supply, input and output circuits shall be connected to the sources of power supply, control and signal.
- The cables supplied or recommended by the equipment manufacturer shall be used. 1 meter of all cables used shall be exposed to the magnetic field.



#### TABLETOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

### 13.4 Supplementary Information

The requirement followed by the client's specification. (Refer to item 7.1)

### 13.5 Test Results

**For EN 55024 & EN 55035**

**For Field Strength: 1A/m**

Test mode	Mode 1	Input Voltage	12Vdc
Environmental Conditions	24°C, 50% RH	Tested by	Chiming Li

Application	Frequency (Hz)	Test Duration	Field Strength (A/m)	Observation	Performance Criterion
X - Axis	50	1 min.	1	Note	A
Y - Axis	50	1 min.	1	Note	A
Z - Axis	50	1 min.	1	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 6	Input Voltage	24Vdc
Environmental Conditions	24°C, 50% RH	Tested by	Chiming Li

Application	Frequency (Hz)	Test Duration	Field Strength (A/m)	Observation	Performance Criterion
X - Axis	50	1 min.	1	Note	A
Y - Axis	50	1 min.	1	Note	A
Z - Axis	50	1 min.	1	Note	A

Note: The EUT function was correct during the test.

# For EN 55024

## For Field Strength: 100A/m, 1000A/m

Test mode	Mode 1	Input Voltage	12Vdc
Environmental Conditions	23°C, 66% RH	Tested by	Terry Liao

Application	Frequency (Hz)	Test Duration	Field Strength (A/m)	Observation	Performance Criterion
X - Axis	50	1 min.	100	Note	A
Y - Axis	50	1 min.	100	Note	A
Z - Axis	50	1 min.	100	Note	A
X - Axis	50	1 sec.	1000	Note	A
Y - Axis	50	1 sec.	1000	Note	A
Z - Axis	50	1 sec.	1000	Note	A

Note: The EUT function was correct during the test.

Test mode	Mode 6	Input Voltage	24Vdc
Environmental Conditions	23°C, 66% RH	Tested by	Terry Liao


Application	Frequency (Hz)	Test Duration	Field Strength (A/m)	Observation	Performance Criterion
X - Axis	50	1 min.	100	Note	A
Y - Axis	50	1 min.	100	Note	A
Z - Axis	50	1 min.	100	Note	A
X - Axis	50	1 sec.	1000	Note	A
Y - Axis	50	1 sec.	1000	Note	A
Z - Axis	50	1 sec.	1000	Note	A

Note: The EUT function was correct during the test.

Remark: The test, calibration and test results are compliance with the TAF (TAF code: 2022).

## 14 Pictures of Test Arrangements

### 14.1 Conducted Emission from the Mains Power Port



## 14.2 Radiated Emission at Frequencies up to 1GHz





### 14.3 Electrostatic Discharge Immunity Test (ESD)







#### 14.4 Radio-frequency, Electromagnetic Field Immunity Test (RS)

For EN 55024





For EN 55035 (Field Strength: 3 V/m, 10 V/m)







For EN 55035 (Field Strength: 20 V/m)




#### 14.5 Electrical Fast Transient/Burst Immunity Test (EFT)



#### 14.6 Surge Immunity Test




#### 14.7 Conducted Disturbances Induced by RF Fields (CS)




#### 14.8 Power Frequency Magnetic Field Immunity Test (PFMF)

For Field Strength: 1A/m



For Field Strength: 100A/m, 1000A/m



## Appendix – Information of the Testing Laboratories

We, Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch, were founded in 1988 to provide our best service in EMC, Radio, Telecom and Safety consultation. Our laboratories are accredited and approved according to ISO/IEC 17025.

If you have any comments, please feel free to contact us at the following:

**Lin Kou EMC/RF Lab**

Tel: 886-2-26052180

Fax: 886-2-26051924

**Hsin Chu EMC/RF/Telecom Lab**

Tel: 886-3-6668565

Fax: 886-3-6668323

**Hwa Ya EMC/RF/Safety Lab**

Tel: 886-3-3183232

Fax: 886-3-3270892

**Email:** [service.adt@tw.bureauveritas.com](mailto:service.adt@tw.bureauveritas.com)

**Web Site:** [www.bureauveritas-adt.com](http://www.bureauveritas-adt.com)

The address and road map of all our labs can be found in our web site also.

--- END ---