

# Certificate

Issue Date: May 26, 2022  
Ref. Report No. ISL-21LE505CE-R1-MA  
Page1 of 2

Product Name : TEP 150UIR &TEP 200UIR Series  
Model(s) : TEP 200-7213UIR-N;TEP 150-7211UIR-N; TEP 150-7212UIR-N;  
TEP 150-7213UIR-N; TEP 150-7215UIR-N; TEP 150-7216UIR-N;  
TEP 150-7218UIR-N; TEP 150-72153UIR-N; TEP 200-7211UIR-N;  
TEP 200-7212UIR-N; TEP 200-7215UIR-N; TEP 200-7216UIR-N;  
TEP 200-7218UIR-N; TEP 200-72153UIR-N; TEP 150-7211UIR-AN;  
TEP 150-7212UIR-AN; TEP 150-7213UIR-AN; TEP 150-7215UIR-AN;  
TEP 150-7216UIR-AN; TEP 150-7218UIR-AN; TEP 150-72153UIRAN;  
TEP 200-7211UIR-AN; TEP 200-7212UIR-AN; TEP 200-7213UIR-AN;  
TEP 200-7215UIR-AN; TEP 200-7216UIR-AN; TEP 200-7218UIR-AN;  
TEP 200-72153UIRAN; TEP 150-7211UIR; TEP 150-7212UIR;  
TEP 150-7213UIR; TEP 150-7215UIR; TEP 150-7216UIR; TEP 150-7218UIR;  
TEP 150-72153UIR; TEP 200-7211UIR; TEP 200-7212UIR; TEP 200-7213UIR;  
TEP 200-7215UIR; TEP 200-7216UIR; TEP 200-7218UIR; TEP 200-72153UIR;  
TEP 150-7211UIR-A; TEP 150-7212UIR-A; TEP 150-7213UIR-A;  
TEP 150-7215UIR-A; TEP 150-7216UIR-A; TEP 150-7218UIR-A;  
TEP 150-72153UIR-A; TEP 200-7211UIR-A; TEP 200-7212UIR-A;  
TEP 200-7213UIR-A; TEP 200-7215UIR-A; TEP 200-7216UIR-A;  
TEP 200-7218UIR-A; TEP 200-72153UIR-A

Applicant : TRACO ELECTRONIC AG  
Address : Sihlbruggstrasse 111 CH-6340 Baar Switzerland

Brand : TRACO POWER



# Certificate

Issue Date: May 26, 2022  
Ref. Report No. ISL-21LE505CE-R1-MA  
Page 2 of 2

We, **International Standards Laboratory Corp.**, hereby certify that:

The sample ISL received which bearing the trade name and model specified above has been shown to comply with the applicable technical standards as indicated in the measurement report and was tested in accordance with the measurement procedures specified in European Council Directive EMC Directive 2014/30/EU and UK Directive Electromagnetic Compatibility Regulations 2016. And Our laboratories is the accredited laboratories and are approved according to ISO/IEC 17025. The device was passed the test performed according to :



#### Standards:

##### CE

EN 55032:2015+A11:2020 and CISPR 32:2015+A1:2019 Class B  
AS/NZS CISPR 32:2015+A1:2020 Class B  
EN 55024:2010+A1:2015 and CISPR 24:2010+A1:2015  
EN 61000-4-2:2009 and IEC 61000-4-2:2008  
EN 61000-4-3:2006+A1:2008 +A2:2010 and IEC 61000-4-3:2006+A1:2007+A2:2010  
EN 61000-4-4:2012 and IEC 61000-4-4:2012  
EN 61000-4-5:2014+A1:2017 and IEC 61000-4-5:2014+A1:2017  
EN 61000-4-6:2014+AC:2015 and IEC 61000-4-6:2013  
EN 61000-4-8:2010 and IEC 61000-4-8:2009

##### UK

BS EN 55032:2015+A11:2020 Class B  
BS EN 55024:2010+A1:2015  
BS EN 61000-4-2:2009  
BS EN 61000-4-3:2006+A2:2010  
BS EN 61000-4-4:2012  
BS EN 61000-4-5:2014+A1:2017  
BS EN 61000-4-6:2014  
BS EN 61000-4-8:2010

I attest to the accuracy of data and all measurements reported herein were performed by me or were made under my supervision and are correct to the best of my knowledge and belief. I assume full responsibility for the completeness of these measurements and vouch for the qualifications of all persons taking them.

The determination of the test results is determined by customer agreement, regulations or standard document specifications.

The Laboratory evaluates measurement inaccuracies based on regulatory or standard document specifications and is listed in the report for reference. The quantitative project part judges the conformity of the test results based on the evaluation results of the standard cited uncertainty, and the qualitative project does not temporarily evaluate the measurement uncertainty.

A handwritten signature in black ink that reads 'Angus Chu'.

Angus Chu / Sr. Manager

**International Standards Laboratory Corp. LT Lab.**

TEL: +886-3-263-8888 FAX: +886-3-263-8899

No. 120, Lane 180, Hsin Ho Rd., Lung-Tan Dist., Tao Yuan City 325, Taiwan

# TEST REPORT

of

**EN 55032 / CISPR 32 / BS EN 55032 /  
AS/NZS CISPR 32 Class B  
EN 55024 / CISPR 24 / BS EN 55024 / IMMUNITY**

Product : **TEP 150UIR & TEP 200UIR Series**  
Model(s): **TEP 200-7213UIR-N**  
(more serial models listed on Different Model list of  
this test report)



Brand: **TRACO POWER**  
Applicant: **TRACO ELECTRONIC AG**  
Address: **Sihlbruggstrasse 111 CH-6340 Baar Switzerland**

Test Performed by:



**International Standards Laboratory Corp. LT Lab.**

TEL: +886-3-263-8888 FAX: +886-3-263-8899

No. 120, Lane 180, Hsin Ho Rd., Lung-Tan Dist., Tao Yuan City 325, Taiwan

Report No.: **ISL-21LE505CE-R1-MA**  
Issue Date : **May 26, 2022**



Test results given in this report apply only to the specific sample(s) tested and are traceable to national or international standard through calibration of the equipment and evaluating measurement uncertainty herein. The uncertainty of the measurement does not include in consideration of the test result unless the customer required the determination of uncertainty via the agreement, regulation or standard document specification. This test report shall not be reproduced except in full, without the written approval of International Standards Laboratory Corp.

## Contents of Report

1.	General.....	1
1.1	Certification of Accuracy of Test Data .....	1
1.2	Test Standards .....	2
1.3	Description of EUT .....	4
1.4	Description of Support Equipment .....	10
2.	Power Main Port Conducted Emissions .....	11
2.1	Test Setup and Procedure .....	11
2.2	Conduction Test Data: Configuration 1 .....	13
2.3	Conduction Test Data: Configuration 2 .....	15
2.4	Test Setup Photo.....	17
3.	Telecommunication Port Conducted Emissions .....	19
3.1	Test Setup and Procedure .....	19
4.	Radiated Disturbance Emissions .....	21
4.1	Test Setup and Procedure .....	21
4.2	Limit .....	23
4.3	Radiation Test Data: Configuration 1.....	25
4.4	Radiation Test Data: Configuration 2.....	27
4.5	Test Setup Photo.....	29
5.	Voltage Disturbance Emissions at Antenna Terminals .....	30
5.1	Test Setup and Procedure .....	30
6.	Differential Voltage Emissions.....	32
6.1	Test Setup and Procedure .....	32
7.	Outdoor units of home satellite receiving systems .....	34
7.1	Test Setup and Procedure .....	34
8.	Electrostatic discharge (ESD) immunity .....	36
8.1	Test Specification and Setup .....	36
8.2	Test Data: Configuration 1 .....	37
8.3	Test Point.....	38
8.4	Test Setup Photo.....	39
9.	Radio-Frequency, Electromagnetic Field immunity.....	40
9.1	Test Specification and Setup .....	40
9.2	Test Data: Configuration 1 .....	41
9.3	Test Setup Photo.....	42
10.	Electrical Fast transients/burst immunity .....	43
10.1	Test Specification and Setup.....	43
10.2	Test Data: Configuration 1.....	45
10.3	Test Setup Photo .....	46

11.	Surge Immunity .....	47
11.1	Test Specification and Setup .....	47
11.2	Test Data: Configuration 1 .....	48
11.3	Test Setup Photo .....	49
12.	Immunity to Conductive Disturbance .....	50
12.1	Test Specification and Setup .....	50
12.2	Test Data: Configuration 1 .....	51
12.3	Test Setup Photo .....	52
13.	Power Frequency Magnetic Field immunity .....	53
13.1	Test Specification and Setup .....	53
13.2	Test Data: Configuration 1 .....	54
13.3	Test Setup Photo .....	55
14.	Appendix.....	56
14.1	Appendix A: Test Equipment.....	56
14.2	Appendix B: Uncertainty of Measurement .....	58
14.3	Appendix C: Photographs of EUT .....	59

# 1. General

## 1.1 Certification of Accuracy of Test Data

**Standards:** Please refer to 1.2

**Equipment Tested:** TEP 150UIR & TEP 200UIR Series

**Model:** TEP 200-7213UIR-N  
(more serial models listed on Different Model list of this test report)



**Brand:** TRACO POWER

**Applicant:** TRACO ELECTRONIC AG

**Sample received Date:** December 13, 2021

**Final test Date:** EMI: refer to the date of test data  
EMS: July 15, 2021

**Test Site:** Chamber 02; Conduction 03; Immunity02

**Test Distance:** 10m (EMI test)

**Temperature:** refer to each site test data

**Humidity:** refer to each site test data


**Atmospheric Pressure:** 86 kPa to 106 kPa

**Input power:** Radiation input power: DC 72 V; DC 110V  
Conduction input power: DC 72 V; DC 110V  
Immunity input power: DC 72 V

**Test Result:** PASS

**Report Engineer:** Cheryl Tung

**Test Engineer:**   
Sawyer Chiang

**Approved By:**   
Benson Chen / Manager

## 1.2 Test Standards

The tests which this report describes were conducted by an independent electromagnetic compatibility consultant, International Standards Laboratory Corp. in accordance with the following

EN 55032:2015+A11:2020 and CISPR 32:2015+A1:2019 and BS EN 55032:2015+A11:2020 Class B Electromagnetic compatibility of multimedia equipment - Emission requirements.  
AS/NZS CISPR 32:2015+A1:2020 Class B Electromagnetic compatibility of multimedia equipment- Emission requirements

Performed Item	Test Performed	Deviation	Result
Conducted emissions from the AC mains power ports	Yes	No	PASS
Telecommunication Port Conducted Emissions (asymmetric mode)	N/A	N/A	N/A
Radiated emissions at frequencies below 1 GHz	Yes	No	PASS
Radiated emissions at frequencies above 1 GHz	N/A	N/A	N/A
Radiated emissions from FM receivers	N/A	N/A	N/A
Voltage Disturbance Emissions at Antenna Terminals	N/A	N/A	N/A
Differential voltage emissions	N/A	N/A	N/A
Outdoor units of home satellite receiving systems	N/A	N/A	N/A

EN 55024:2010+A1:2015 and CISPR 24:2010+A1:2015 and BS EN 55024:2010+A1:2015 Information technology equipment-Immunity characteristics - Limits and methods of measurement.

Standard	Description	Results	Criteria
EN 61000-4-2:2009 IEC 61000-4-2:2008 BS EN 61000-4-2:2009	Electrostatic Discharge	Pass	B
EN 61000-4-3:2006+A1:2008 +A2:2010 IEC 61000-4-3:2006+A1:2007+A2:2010 BS EN 61000-4-3:2006+A2:2010	Radio-Frequency, Electromagnetic Field	Pass	A
EN 61000-4-4:2012 IEC 61000-4-4:2012 BS EN 61000-4-4:2012	Electrical Fast Transient/Burst	Pass	B
EN 61000-4-5:2014+A1:2017 IEC 61000-4-5:2014+A1:2017 BS EN 61000-4-5:2014+A1:2017	Surge	Pass	B
EN 61000-4-6:2014+AC:2015 IEC 61000-4-6:2013 BS EN 61000-4-6:2014	Conductive Disturbance	Pass	A
EN 61000-4-8:2010 IEC 61000-4-8:2009 BS EN 61000-4-8:2010	Power Frequency Magnetic Field	Pass	A

### 1.2.1 Performance Criteria for Compliance: EN 55024 and BS EN 55024

#### **Performance criterion A**

During and after the test the EUT shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed below a minimum performance level specified by the manufacturer when the EUT is used as intended. The performance level may be replaced by a permissible loss of performance. If the minimum performance level or the permissible performance loss is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the EUT if used as intended.

#### **Performance criterion B**

After the test, the EUT shall continue to operate as intended without operator intervention. No degradation of performance or loss of function is allowed, after the application of the phenomena below a performance level specified by the manufacturer, when the EUT is used as intended. The performance level may be replaced by a permissible loss of performance. During the test, degradation of performance is allowed. However, no change of operating state or stored data is allowed to persist after the test. If the minimum performance level (or the permissible performance loss) is not specified by the manufacturer, then either of these may be derived from the product description and documentation, and by what the user may reasonably expect from the EUT if used as intended.

#### **Performance criterion C**

During and after testing, a temporary loss of function is allowed, provided the function is self-recoverable, or can be restored by the operation of the controls or cycling of the power to the EUT by the user in accordance with the manufacturer's instructions.

Functions, and/or information stored in non-volatile memory, or protected by a battery backup, shall not be lost.

### 1.3 Description of EUT

## EUT

This report test data using the report number ISL-21LE505CE-R1.

Description	TEP 150UIR & TEP 200UIR Series	
Condition	Pre-Production	
Model	TEP 200-7213UIR-N (more serial models listed on Different Model list of this test report)	
Test Model	TEP 200-7213UIR-N	
Brand	TRACO POWER	
Serial Number	N/A	
Highest working frequency	Less than 108MHz	

All the devices listed below are chosen by the applicant to be the representative configuration for testing in this report.

#### Test configuration:

Configuration	Model Name	Input VDC	Output Voltage VDC
1	TEP 200-7213UIR-N	72	15
2		110	15

For EMS (Not Include Electrical Fast transients/burst immunity & Surge Immunity) test mode

Configuration	Model Name	Input VDC	Output Voltage VDC	With an aluminum electrolytic capacitor test board
1	TEP 200-7213UIR-N	72	15	No

For Electrical Fast transients/burst immunity & Surge Immunity test mode

Configuration	Model Name	Input VDC	Output Voltage VDC	With an aluminum electrolytic capacitor test board
1	TEP 200-7213UIR-N	72	15	Yes

**Different Model list:**

Model Name	Input Range (VDC)	Output Voltage (VDC)
TEP 150-7211UIR-N	14 ~ 160	5
TEP 150-7212UIR-N	14 ~ 160	12
TEP 150-7213UIR-N	14 ~ 160	15
TEP 150-7215UIR-N	14 ~ 160	24
TEP 150-7216UIR-N	14 ~ 160	28
TEP 150-7218UIR-N	14 ~ 160	48
TEP 150-72153UIR-N	14 ~ 160	53
TEP 200-7211UIR-N	14 ~ 160	5
TEP 200-7212UIR-N	14 ~ 160	12
TEP 200-7213UIR-N	14 ~ 160	15
TEP 200-7215UIR-N	14 ~ 160	24
TEP 200-7216UIR-N	14 ~ 160	28
TEP 200-7218UIR-N	14 ~ 160	48
TEP 200-72153UIR-N	14 ~ 160	53
TEP 150-7211UIR-AN	14 ~ 160	5
TEP 150-7212UIR-AN	14 ~ 160	12
TEP 150-7213UIR-AN	14 ~ 160	15
TEP 150-7215UIR-AN	14 ~ 160	24
TEP 150-7216UIR-AN	14 ~ 160	28
TEP 150-7218UIR-AN	14 ~ 160	48
TEP 150-72153UIRAN	14 ~ 160	53
TEP 200-7211UIR-AN	14 ~ 160	5
TEP 200-7212UIR-AN	14 ~ 160	12
TEP 200-7213UIR-AN	14 ~ 160	15
TEP 200-7215UIR-AN	14 ~ 160	24
TEP 200-7216UIR-AN	14 ~ 160	28
TEP 200-7218UIR-AN	14 ~ 160	48
TEP 200-72153UIRAN	14 ~ 160	53
TEP 150-7211UIR	14 ~ 160	5
TEP 150-7212UIR	14 ~ 160	12
TEP 150-7213UIR	14 ~ 160	15
TEP 150-7215UIR	14 ~ 160	24
TEP 150-7216UIR	14 ~ 160	28
TEP 150-7218UIR	14 ~ 160	48
TEP 150-72153UIR	14 ~ 160	53
TEP 200-7211UIR	14 ~ 160	5
TEP 200-7212UIR	14 ~ 160	12
TEP 200-7213UIR	14 ~ 160	15
TEP 200-7215UIR	14 ~ 160	24
TEP 200-7216UIR	14 ~ 160	28
TEP 200-7218UIR	14 ~ 160	48
TEP 200-72153UIR	14 ~ 160	53


Model Name	Input Range (VDC)	Output Voltage (VDC)
TEP 150-7211UIR-A	14 ~ 160	5
TEP 150-7212UIR-A	14 ~ 160	12
TEP 150-7213UIR-A	14 ~ 160	15
TEP 150-7215UIR-A	14 ~ 160	24
TEP 150-7216UIR-A	14 ~ 160	28
TEP 150-7218UIR-A	14 ~ 160	48
TEP 150-72153UIR-A	14 ~ 160	53
TEP 200-7211UIR-A	14 ~ 160	5
TEP 200-7212UIR-A	14 ~ 160	12
TEP 200-7213UIR-A	14 ~ 160	15
TEP 200-7215UIR-A	14 ~ 160	24
TEP 200-7216UIR-A	14 ~ 160	28
TEP 200-7218UIR-A	14 ~ 160	48
TEP 200-72153UIR-A	14 ~ 160	53

**EMI Noise Source:**

Please refer to the technical documents.

**Solution:**

**For EMI test requirements/Class B**



TEP 200-7211UIR/TEP 200-7211UIR-A/TEP 200-7211UIR-N/TEP 200-7211UIR-AN

L1	L2	C2, C7	C1, C3	C19, C24	C21, C22, C23	C11, C13, C20, C27, C28	C25, C29	C15, C16, C18	C5	C6	TVS, CEMS, C4, C8, C9, C10, C12, C17, C26, C30,
415uH	3.3uH	150uF/ 200V	1uF/ 250V	1000pF/ 250Vac	680pF/ 250Vac	330pF/ 250Vac	100pF/ 250Vac	4700pF/ Y1	2200pF/ Y1	1000pF/ Y1	N/A

TEP 200-7212UIR/ TEP 200-7213UIR/ TEP 200-7215UIR/ TEP 200-7216UIR/  
TEP 200-7212UIR-A/ TEP 200-7213UIR-A/ TEP 200-7215UIR-A/ TEP 200-7216UIR-A/  
TEP 200-7212UIR-N/ TEP 200-7213UIR-N/ TEP 200-7215UIR-N/ TEP 200-7216UIR-N/  
TEP 200-7212UIR-AN/ TEP 200-7213UIR-AN/ TEP 200-7215UIR-AN/ TEP 200-7216UIR-AN

L1	L2	C2, C7	C1, C3, C4	C19, C20, C21, C22, C23, C27	C11, C13	C24, C25, C28, C29	C15, C17	C5, C6, C16, C18	TVS, CEMS, C8, C9, C10, C12, C26, C30,
415uH	3.3uH	150uF/ 200V	1uF/ 250V	1000pF/ 250Vac	680pF/ 250Vac	100pF/ 250Vac	1000pF/ Y1	2200pF/ Y1	N/A

TEP 200-7218UIR/ TEP 200-72153UIR/ TEP 200-7218UIR-A/ TEP 200-72153UIR-A/  
TEP 200-7218UIR-N/ TEP 200-72153UIR-N/ TEP 200-7218UIR-AN/ TEP 200-72153UIR-AN

L1	L2	C2, C7	C1, C3, C9	C11, C13	C20, C22	C19, C21, C23, C24, C27, C28	C25, C29	C15, C17	C16, C18	TVS, CEMS, C4, C5, C6, C8, C10, C12, C26, C30,
415uH	3.3uH	150uF/ 200V	1uF/ 250V	680pF/ 250Vac	1000pF/ 250Vac	330pF/ 250Vac	100pF/ 250Vac	3300pF/ Y1	4700pF/ Y1	N/A


TEP 150-7211UIR/ TEP 150-7212UIR/ TEP 150-7213UIR/ TEP 150-7215UIR/  
TEP 150-7216UIR/  
TEP 150-7211UIR-A/ TEP 150-7212UIR-A/ TEP 150-7213UIR-A/ TEP 150-7215UIR-A/  
TEP 150-7216UIR-A/ TEP 150-7211UIR-N/ TEP 150-7212UIR-N/ TEP 150-7213UIR-N/  
TEP 150-7215UIR-N/ TEP 150-7216UIR-N/ TEP 150-7211UIR-AN/ TEP 150-7212UIR-AN/  
TEP 150-7213UIR-AN/ TEP 150-7215UIR-AN/  
TEP 150-7216UIR-AN

L1	L2	C2, C7	C1, C3, C9	C19, C21	C20, C22	C11, C13, C23, C24, C27, C28	C25, C29	C15, C17	C16, C18	TVS, CEMS, C4, C8, C10, C12, C26, C30,
545μH	4.7μH	150μF/200V	1μF/250V	680pF/250Va	1000pF/250Vac	330pF/250Vac	100pF/250Vac	3300pF/Y1	2200pF/Y1	N/A

TEP 150-7218UIR/ TEP 150-72153UIR/ TEP 150-7218UIR-A/ TEP 150-72153UIR-A/  
TEP 150-7218UIR-N/ TEP 150-72153UIR-N/ TEP 150-7218UIR-AN/ TEP 150-72153UIRAN

L1	L2	C2, C7	C1, C3, C9	C20, C22	C11, C13, C19, C21, C23, C24, C27, C28	C25, C29	C15, C17	C16, C18	TVS, CEMS, C4, C8, C10, C12, C26, C30,
545μH	4.7μH	150μF/200V	1μF/250V	680pF/250Vac	330pF/250Vac	100pF/250Vac	2200pF/Y1	3300pF/Y1	N/A

※ A C<sub>BUS</sub> should always be installed and connected to the BUS pin for module's stability.  
(C<sub>BUS</sub>: 150μF/200V)

**For Electrical Fast transient & Surge Immunity test requirements**


Model Reference	Increase countermeasure components
TEP 200UIR Series	With an external input filter Cin : 150 $\mu$ F/200V * 2PCS TVS : 170V/3000W Lin : 3.3 $\mu$ H
TEP 150UIR Series	With an external input filter Cin : 150 $\mu$ F/200V * 2PCS TVS : 170V/3000W Lin : 4.7 $\mu$ H

※ A C<sub>BUS</sub> should always be installed and connected to the BUS pin for module's stability.  
 (C<sub>BUS</sub>: 150 $\mu$ F/200V)

### 1.4 Description of Support Equipment

For EMI test Configuration Support unit: 1~2


For EMS test Configuration Support unit: 1~3

No	Unit	Model Serial No.	Brand	Power Cord	FCC ID
1	DC Power Source	GPD-4050D S/N: N/A	GW INSTEK	Non-shielded	FCC DOC
2	Dummy Load	N/A S/N: N/A	N/A	N/A	N/A
3	DC Voltage meter	BN-670 S/N: N/A	Bonny	N/A	N/A

## 2. Power Main Port Conducted Emissions

### 2.1 Test Setup and Procedure

#### 2.1.1 Test Setup



#### 2.1.2 Test Procedure

The measurements are performed in a shielded room test site. The EUT was placed on non-conduction 1.0m x 1.5m table, which is 0.8 meters above an earth-grounded.

Power to the EUT was provided through the AMN which has the Impedance (50ohm/50uH) vs. Frequency Characteristic in accordance with the standard. Power to the AMNs were filtered to eliminate ambient signal interference and these filters were bonded to the ground plane. Peripheral equipment required to provide a functional system (support equipment) for EUT testing was powered from the second AMN through a ganged, metal power outlet box which is bonded to the ground plane at the AMN.

The interconnecting cables were arranged and moved to get the maximum measurement. Both the line of power cord, live and neutral, were measured. All of the interface cables were manipulated according to EN 55032 / BS EN 55032 requirements.

The highest emissions were analyzed in details by operating the spectrum analyzer in fixed tuned mode to determine the nature of the emissions and to provide information which could be useful in reducing their amplitude.

#### 2.1.3 EMI Receiver/Spectrum Analyzer Configuration (for the frequencies tested)

Frequency Range:	150kHz--30MHz
Detector Function:	Quasi-Peak / Average Mode
Resolution Bandwidth:	9kHz

**2.1.4 Limit**


**Conducted emissions from the AC mains power ports of Class\_A equipment:**

Frequency	QP	AV
MHz	dB( $\mu$ V)	dB( $\mu$ V)
0.15-0.50	79	66
0.50-30	73	60
Note: The lower limit shall apply at the transition frequencies		

**Conducted emissions from the AC mains power ports of Class\_B equipment:**

Frequency	QP	AV
MHz	dB( $\mu$ V)	dB( $\mu$ V)
0.15-0.50	66-56	56-46
0.50-5.0	56	46
5.0-30	60	50
Note: The lower limit shall apply at the transition frequencies		

## 2.2 Conduction Test Data: Configuration 1 -Live



No.	Frequency (MHz)	QP_R (dBuV)	AVG_R (dBuV)	Correct Factor (dB)	QP Emission (dBuV)	QP Limit (dBuV)	QP Margin (dB)	AVG Emission (dBuV)	AVG Limit (dBuV)	AVG Margin (dB)
1	0.543	27.60	23.96	10.14	37.74	56.00	-18.26	34.10	46.00	-11.90
2	0.837	27.77	28.06	10.17	37.94	56.00	-18.06	38.23	46.00	-7.77
3	1.463	28.01	28.30	10.20	38.21	56.00	-17.79	38.50	46.00	-7.50
4	2.091	26.42	26.65	10.24	36.66	56.00	-19.34	36.89	46.00	-9.11
5	4.178	29.56	29.80	10.30	39.86	56.00	-16.14	40.10	46.00	-5.90
6	13.995	30.94	30.91	10.62	41.56	60.00	-18.44	41.53	50.00	-8.47

Note:

Margin = QP/AVG Emission - Limit

QP/AVG Emission = QP\_R/AVG\_R + Correct Factor

Correct Factor = LISN Loss + Cable Loss

A margin of -8dB means that the emission is 8dB below the limit


The frequency spectrum graph is for final peak graph, and the attached table is for QP/AVG test result.

If peak data can pass, it will be shown in "QP/AVG Correct" column, if not, QP/AVG data will instead.

- Neutral



Address: No. 120, Lane 180, Hsin Ho Rd., Lung-Tan Dist.,  
Tao Yuan City 325, Taiwan.  
Tel: 03-2638888



No.	Frequency (MHz)	QP_R (dBuV)	AVG_R (dBuV)	Correct Factor (dB)	QP Emission (dBuV)	QP Limit (dBuV)	QP Margin (dB)	AVG Emission (dBuV)	AVG Limit (dBuV)	AVG Margin (dB)
1	0.418	27.98	28.27	10.19	38.17	57.49	-19.32	38.46	47.49	-9.03
2	0.834	27.99	28.29	10.21	38.20	56.00	-17.80	38.50	46.00	-7.50
3	3.130	27.21	27.34	10.32	37.53	56.00	-18.47	37.66	46.00	-8.34
4	4.174	25.23	25.31	10.35	35.58	56.00	-20.42	35.66	46.00	-10.34
5	9.169	38.08	38.30	10.52	48.60	60.00	-11.40	48.82	50.00	-1.18
6	24.172	27.56	25.62	10.91	38.47	60.00	-21.53	36.53	50.00	-13.47

Note:

Margin = QP/AVG Emission - Limit

QP/AVG Emission = QP\_R/AVG\_R + Correct Factor

Correct Factor = LISN Loss + Cable Loss


A margin of -8dB means that the emission is 8dB below the limit

The frequency spectrum graph is for final peak graph, and the attached table is for QP/AVG test result.

If peak data can pass, it will be shown in "QP/AVG Correct" column, if not, QP/AVG data will instead.

### 2.3 Conduction Test Data: Configuration 2

-Live



No.	Frequency (MHz)	QP_R (dBuV)	AVG_R (dBuV)	Correct Factor (dB)	QP Emission (dBuV)	QP Limit (dBuV)	QP Margin (dB)	AVG Emission (dBuV)	AVG Limit (dBuV)	AVG Margin (dB)
1	1.040	29.79	30.09	10.18	39.97	56.00	-16.03	40.27	46.00	-5.73
2	1.875	31.36	31.66	10.24	41.60	56.00	-14.40	41.90	46.00	-4.10
3	2.497	31.81	32.06	10.26	42.07	56.00	-13.93	42.32	46.00	-3.68
4	3.329	31.94	32.19	10.28	42.22	56.00	-13.78	42.47	46.00	-3.53
5	13.526	33.72	33.92	10.61	44.33	60.00	-15.67	44.53	50.00	-5.47
6	14.358	34.06	34.18	10.62	44.68	60.00	-15.32	44.80	50.00	-5.20

Note:

Margin = QP/AVG Emission - Limit

QP/AVG Emission = QP\_R/AVG\_R + Correct Factor

Correct Factor = LISN Loss + Cable Loss

A margin of -8dB means that the emission is 8dB below the limit


The frequency spectrum graph is for final peak graph, and the attached table is for QP/AVG test result.

If peak data can pass, it will be shown in "QP/AVG Correct" column, if not, QP/AVG data will instead.

- Neutral



Address: No. 120, Lane 180, Hsin Ho Rd., Lung-Tan Dist.,  
Tao Yuan City 325, Taiwan.  
Tel: 03-2638888



No.	Frequency (MHz)	QP_R (dBuV)	AVG_R (dBuV)	Correct Factor (dB)	QP Emission (dBuV)	QP Limit (dBuV)	QP Margin (dB)	AVG Emission (dBuV)	AVG Limit (dBuV)	AVG Margin (dB)
1	1.250	28.33	28.64	10.24	38.57	56.00	-17.43	38.88	46.00	-7.12
2	2.498	29.42	29.67	10.30	39.72	56.00	-16.28	39.97	46.00	-6.03
3	3.330	29.50	29.70	10.33	39.83	56.00	-16.17	40.03	46.00	-5.97
4	6.242	26.74	26.60	10.42	37.16	60.00	-22.84	37.02	50.00	-12.98
5	9.151	40.19	39.39	10.52	50.71	60.00	-9.29	49.91	50.00	-0.09
6	14.346	31.06	31.16	10.67	41.73	60.00	-18.27	41.83	50.00	-8.17

Note:

Margin = QP/AVG Emission - Limit

QP/AVG Emission = QP\_R/AVG\_R + Correct Factor

Correct Factor = LISN Loss + Cable Loss

A margin of -8dB means that the emission is 8dB below the limit

The frequency spectrum graph is for final peak graph, and the attached table is for QP/AVG test result.


If peak data can pass, it will be shown in "QP/AVG Correct" column, if not, QP/AVG data will instead.

## 2.4 Test Setup Photo

Front View




Back View



### 3. Telecommunication Port Conducted Emissions

#### 3.1 Test Setup and Procedure

##### 3.1.1 Test Setup



##### 3.1.2 Test Procedure

The measurements are performed in a shielded room test site. The EUT was placed on non-conduction 1.0m x 1.5m table, which is 0.8 meters above an earth-grounded.

The EUT, any support equipment, and any interconnecting cables were arranged and moved to get the maximum measurement. All of the interface cables were manipulated according to EN 55032 / BS EN 55032 requirements.

The port of the EUT was connected to the support equipment through the AAN and linked in normal condition.

AC input power for the EUT & the support equipment power outlets were obtained from the same filtered source that provided input power to the AMN.

The highest emissions were analyzed in details by operating the spectrum analyzer in fixed tuned mode to determine the nature of the emissions and to provide information could be useful in reducing their amplitude.

##### 3.1.3 EMI Receiver/Spectrum Analyzer Configuration (for the frequencies tested)

Frequency Range:	150kHz--30MHz
Detector Function:	Quasi-Peak / Average Mode
Resolution Bandwidth:	9kHz

**3.1.4 Limit**

**Asymmetric mode conducted emissions from Class\_A equipment:**

**Applicable to**

1. wired network ports.
2. optical fibre ports with metallic shield or tension members.
3. antenna ports.

Frequency range MHz	Coupling device	Detector type / bandwidth	Class_A voltage limits dB(μV)	Class_A current limits dB(μA)
0.15-0.5	AAN	Quasi Peak / 9 kHz	97-87	n/a
0.5-30			87	
0.15-0.5	AAN	Average / 9 kHz	84-74	
0.5-30			74	
0.15-0.5	CVP and current probe	Quasi Peak / 9 kHz	97-87	53-43
0.5-30			87	43
0.15-0.5	CVP and current probe	Average / 9 kHz	84-74	40-30
0.5-30			74	30
0.15-0.5	Current Probe	Quasi Peak / 9 kHz	n/a	53-43
0.5-30				43
0.15-0.5	Current Probe	Average / 9 kHz		40-30
0.5-30				30

**Asymmetric mode conducted emissions from Class\_B equipment:**

**Applicable to:**

1. wired network ports.
2. optical fibre ports with metallic shield or tension members.
3. broadcast receiver tuner ports.
4. antenna ports.




Frequency range MHz	Coupling device	Detector type / bandwidth	Class_B voltage limits dB(μV)	Class_B current limits dB(μA)
0.15-0.5	AAN	Quasi Peak / 9 kHz	84-74	n/a
0.5-30			74	
0.15-0.5	AAN	Average / 9 kHz	74-64	
0.5-30			64	
0.15-0.5	CVP and current probe	Quasi Peak / 9 kHz	84-74	40-30
0.5-30			74	30
0.15-0.5	CVP and current probe	Average / 9 kHz	74-64	30-20
0.5-30			64	20
0.15-0.5	Current Probe	Quasi Peak / 9 kHz	n/a	40-30
0.5-30				30
0.15-0.5	Current Probe	Average / 9 kHz		30-20
0.5-30				20

**\*\*Remarks: It is not necessary to be tested on this item.**

## 4. Radiated Disturbance Emissions

### 4.1 Test Setup and Procedure

#### 4.1.1 Test Setup



The 3dB beam width of the horn antenna used for the test is as shown in the table below.

Frequency (GHz)	E-plane	H-plane	$\theta_{3dB}(\text{min})$	d= 3 m
				w (m)
1	88°	147°	88°	5.79
2	68°	119°	68°	4.04
3	73°	92°	73°	4.44
4	70°	89°	70°	4.20
5	55°	60°	55°	3.12
6	63°	62°	62°	3.60

#### 4.1.2 Test Procedure

The radiated emissions test will then be repeated on the chamber to measure the amplitudes accurately and without the multiple reflections existing in the shielded room. The EUT and support equipment are set up on the turntable of one of 10 meter chamber. Desktop EUT are set up on a FRP stand 0.8 meter above the ground or floor-standing arrangement shall be placed on the horizontal ground reference plane.

For the initial measurements, the receiving antenna is varied from 1-4 meter height and is changed in the vertical plane from vertical to horizontal polarization at each frequency. The highest emissions between 30 MHz to 1000 MHz were analyzed in details by operating the spectrum analyzer and/or EMI receiver in quasi-peak mode to determine the precise amplitude of the emissions. The highest emissions between 1 GHz to 6 GHz were analyzed in details by operating the spectrum analyzer in peak and average mode to determine the precise amplitude of the emissions. The test volume for a height of up to 30 cm may be obstructed by absorber placed on the ground plane.

At the highest amplitudes observed, the EUT is rotated in the horizontal plane while changing the antenna polarization in the vertical plane to maximize the reading. The interconnecting cables were arranged and moved to get the maximum measurement. Once the maximum reading is obtained, the antenna elevation and polarization will be varied between specified limits to maximize the readings. All of the interface cables were manipulated according to EN 55032 / BS EN 55032 requirements.

The highest internal source of an EUT is defined as the highest frequency generated or used within the EUT or on which the EUT operates or tunes.

If the highest frequency of the internal sources of the EUT is less than 108 MHz, the measurement shall only be made up to 1 GHz.

If the highest frequency of the internal sources of the EUT is between 108 MHz and 500 MHz, the measurement shall only be made up to 2 GHz.

If the highest frequency of the internal sources of the EUT is between 500 MHz and 1 GHz, the measurement shall only be made up to 5 GHz.

If the highest frequency of the internal sources of the EUT is above 1 GHz, the measurement shall be made up to 5 times the highest frequency or 6 GHz, whichever is less.

**4.1.3 Spectrum Analyzer Configuration (for the frequencies tested)**

Frequency Range: 30MHz--1000MHz  
 Detector Function: Quasi-Peak Mode  
 Resolution Bandwidth: 120kHz

Frequency Range: Above 1 GHz to 6 GHz  
 Detector Function: Peak/Average Mode  
 Resolution Bandwidth: 1MHz

**4.2 Limit**

**Radiated emissions at frequencies up to 1 GHz for Class A equipment:**

Frequency range MHz	Measurement		Class_A limits dB( $\mu$ V/m)
	Distance m	Detector type / bandwidth	OATS/SAC
30-230	10	Quasi Peak / 120 kHz	40
230-1000			47
30-230	3		50
230-1000			57

**Radiated emissions at frequencies above 1 GHz for Class A equipment:**

Frequency range MHz	Measurement		Class_A limits dB( $\mu$ V/m)
	Distance m	Detector type / bandwidth	FSOATS
1000-3000	3	Average / 1MHz	56
3000-6000			60
1000-3000		Peak / 1MHz	76
3000-6000			80

**Radiated emissions at frequencies up to 1 GHz for Class B equipment:**

Frequency range MHz	Measurement		Class_B limits dB( $\mu$ V/m)
	Distance m	Detector type / bandwidth	OATS/SAC
30-230	10	Quasi Peak / 120 kHz	30
230-1000			37
30-230	3		40
230-1000			47


**Radiated emissions at frequencies above 1 GHz for Class\_B equipment:**

Frequency range MHz	Measurement		Class_B limits dB( $\mu$ V/m)
	Distance m	Detector type / bandwidth	FSOATS
1000-3000	3	Average / 1MHz	50
3000-6000			54
1000-3000		Peak / 1MHz	70
3000-6000			74

**Radiated emissions from FM receivers:**

Frequency range MHz	Measurement		Class_B limits dB( $\mu$ V/m)		
	Distance m	Detector type / bandwidth	Fundamental	Harmonics	
			OATS/SAC	OATS/SAC	
30-230	10	Quasi Peak / 120 kHz	50	42	
230-300				42	
300-1000				46	
30-230	3		Quasi Peak / 120 kHz	60	52
230-300					52
300-1000					56

### 4.3 Radiation Test Data: Configuration 1 - Radiated Emissions (Horizontal)



Mk.	Frequency (MHz)	RX_R (dBuV)	Correct Factor (dB/m)	Emission (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Ant.Pos (cm)	Tab.Pos (deg.)	Detector
1	39.70	38.67	-17.52	21.15	30.00	-8.85	358	0	peak
2	106.63	39.13	-19.70	19.43	30.00	-10.57	400	204	peak
3	157.07	33.34	-15.54	17.80	30.00	-12.20	394	0	peak
4	253.10	35.53	-15.95	19.58	37.00	-17.42	300	0	peak
5	814.73	29.91	-3.30	26.61	37.00	-10.39	300	218	peak
6	960.23	29.74	-1.16	28.58	37.00	-8.42	400	232	peak

\* Note:

Margin = Emission – Limit

Emission = Radiated Amplitude + Correct Factor

Correct Factor = Antenna Correction Factor + Cable Loss – Pre-Amplifier Gain

A margin of -8dB means that the emission is 8dB below the limit

Antenna Distance: 10 meters

Below 1GHz test, if the peak measured value meets the QP limit, it is unnecessary to perform the QP measurement.

**- Radiated Emissions (Vertical)**




Address: No. 120, Lane 180, Hsin Ho Rd., Lung-Tan Dist.,  
Tao Yuan City 325, Taiwan.  
Tel: 03-2638888

Radiated Emission Measurement

Operator: Dan Lee  
Temperature: 18 °C  
Humidity: 76 %

Date: 2022/3/10



Site : Chamber 02

Polarization: Vertical

Mk.	Frequency (MHz)	RX_R (dBuV)	Correct Factor (dB/m)	Emission (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Ant.Pos (cm)	Tab.Pos (deg.)	Detector
1	32.91	46.00	-18.30	27.70	30.00	-2.30	100	355	peak
2	55.22	38.23	-16.66	21.57	30.00	-8.43	200	295	peak
3	78.50	42.54	-20.72	21.82	30.00	-8.18	200	42	peak
4	95.96	45.13	-21.40	23.73	30.00	-6.27	200	42	peak
5	822.49	29.95	-3.21	26.74	37.00	-10.26	400	130	peak
6	929.19	29.79	-1.67	28.12	37.00	-8.88	100	352	peak

\* Note:

Margin = Emission – Limit

Emission = Radiated Amplitude + Correct Factor


Correct Factor = Antenna Correction Factor + Cable Loss – Pre-Amplifier Gain

A margin of -8dB means that the emission is 8dB below the limit

Antenna Distance: 10 meters

Below 1GHz test, if the peak measured value meets the QP limit, it is unnecessary to perform the QP measurement.

### 4.4 Radiation Test Data: Configuration 2 - Radiated Emissions (Horizontal)



Mk.	Frequency (MHz)	RX_R (dBuV)	Correct Factor (dB/m)	Emission (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Ant.Pos (cm)	Tab.Pos (deg.)	Detector
1	30.97	35.29	-18.51	16.78	30.00	-13.22	383	0	peak
2	52.31	32.65	-16.50	16.15	30.00	-13.85	207	360	peak
3	106.63	37.38	-19.70	17.68	30.00	-12.32	400	216	peak
4	161.92	32.32	-15.67	16.65	30.00	-13.35	372	0	peak
5	757.50	30.32	-3.73	26.59	37.00	-10.41	300	359	peak
6	899.12	30.36	-2.24	28.12	37.00	-8.88	100	196	peak

\* Note:

Margin = Emission – Limit

Emission = Radiated Amplitude + Correct Factor

Correct Factor = Antenna Correction Factor + Cable Loss – Pre-Amplifier Gain

A margin of -8dB means that the emission is 8dB below the limit

Antenna Distance: 10 meters

Below 1GHz test, if the peak measured value meets the QP limit, it is unnecessary to perform the QP measurement.


**- Radiated Emissions (Vertical)**



Address: No. 120, Lane 180, Hsin Ho Rd., Lung-Tan Dist.,  
Tao Yuan City 325, Taiwan.  
Tel: 03-2638888

Radiated Emission Measurement  
Date: 2022/3/10

Operator: Dan Lee  
Temperature: 18 °C  
Humidity: 76 %



Site : Chamber 02

Polarization: Vertical

Mk.	Frequency (MHz)	RX_R (dBuV)	Correct Factor (dB/m)	Emission (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Ant.Pos (cm)	Tab.Pos (deg.)	Detector
1	37.76	43.63	-18.00	25.63	30.00	-4.37	300	360	peak
2	53.28	39.93	-16.42	23.51	30.00	-6.49	100	317	peak
3	80.44	42.69	-21.33	21.36	30.00	-8.64	172	0	peak
4	95.96	44.31	-21.40	22.91	30.00	-7.09	200	119	peak
5	171.62	34.22	-16.06	18.16	30.00	-11.84	100	258	peak
6	649.83	30.11	-5.80	24.31	37.00	-12.69	400	326	peak
7	938.89	30.07	-1.51	28.56	37.00	-8.44	394	0	peak

\* Note:

Margin = Emission – Limit

Emission = Radiated Amplitude + Correct Factor

Correct Factor = Antenna Correction Factor + Cable Loss – Pre-Amplifier Gain

A margin of -8dB means that the emission is 8dB below the limit

Antenna Distance: 10 meters


Below 1GHz test, if the peak measured value meets the QP limit, it is unnecessary to perform the QP measurement.

#### 4.5 Test Setup Photo

Front View (30MHz~1GHz)




Back View (30MHz~1GHz)



## 5. Voltage Disturbance Emissions at Antenna Terminals

### 5.1 Test Setup and Procedure

#### 5.1.1 Test Setup



#### 5.1.2 Test Procedure

The output level of the auxiliary signal generator was set to 70dBuV at the EUT antenna terminal with 75 ohms impedance with an un-modulated carrier.

The highest emissions were analyzed in details by operating the spectrum analyzer and/or EMI receiver in quasi-peak mode to determine the precise amplitude of the emissions. The power of EUT was switched off to make sure the emission was not contributed by the auxiliary signal generator. While doing so, the interconnecting cables and major parts of the system were moved around to maximize the emission.

#### 5.1.3 EMI Receiver Configuration (for the frequencies tested)

Frequency Range:	30MHz-2150MHz
Detector Function:	Quasi-Peak Mode
Resolution Bandwidth:	120kHz

**5.1.4 Limit**

**Applicable to:**

- 1. TV broadcast receiver tuner ports with an accessible connector.**
- 2. RF modulator output ports.**
- 3. FM broadcast receiver tuner ports with an accessible connector.**

Table clause	Frequency range MHz	Detector type/ bandwidth	Class B limits dB(μV) 75 Ω			Applicability
			Other	Local Oscillator Fundamental	Local Oscillator Harmonics	
A12.1	30 – 950	For frequencies ≤1 GHz	46	46	46	See a)
	950 – 2 150		46	54	54	
A12.2	950 – 2 150		46	54	54	See b)
A12.3	30 – 300		Quasi Peak/ 120 kHz	46	54	50
	300 – 1 000	52				
A12.4	30 – 300	For frequencies ≥1 GHz	46	66	59	See d)
	300 – 1 000				52	
A12.5	30 – 950	Peak/ 1 MHz	46	76	46	See e)
	950 – 2 150			n/a	54	

a) Television receivers (analogue or digital), video recorders and PC TV broadcast receiver tuner cards working in channels between 30 MHz and 1 GHz, and digital audio receivers.

b) Tuner units (not the LNB) for satellite signal reception.

c) Frequency modulation audio receivers and PC tuner cards.

d) Frequency modulation car radios.


e) Applicable to EUTs with RF modulator output ports (for example DVD equipment, video recorders, camcorders and decoders etc.) designed to connect to TV broadcast receiver tuner ports.

**\*\*Remarks: It is not necessary to be tested on this item.**

## 6. Differential Voltage Emissions

### 6.1 Test Setup and Procedure

#### 6.1.1 Test Setup



#### 6.1.2 Test Procedure

The output level of the auxiliary signal generator was set to 70dBuV at the EUT antenna terminal with 75 ohms impedance with an un-modulated carrier.

The highest emissions were analyzed in details by operating the spectrum analyzer and/or EMI receiver in quasi-peak mode to determine the precise amplitude of the emissions. The power of EUT was switched off to make sure the emission was not contributed by the auxiliary signal generator. While doing so, the interconnecting cables and major parts of the system were moved around to maximize the emission.

#### 6.1.3 EMI Receiver Configuration (for the frequencies tested)

Frequency Range:	30MHz-2150MHz
Detector Function:	Quasi-Peak Mode
Resolution Bandwidth:	120kHz

**6.1.4 Limit**

**Applicable to:**

- 1. TV broadcast receiver tuner ports with an accessible connector.**
- 2. RF modulator output ports.**
- 3. FM broadcast receiver tuner ports with an accessible connector.**

Table clause	Frequency range MHz	Detector type/ bandwidth	Class B limits dB(μV) 75 Ω			Applicability	
			Other	Local Oscillator Fundamental	Local Oscillator Harmonics		
A12.1	30 – 950	For frequencies ≤1 GHz	46	46	46	See a)	
	950 – 2 150		46	54	54		
A12.2	950 – 2 150		Quasi Peak/ 120 kHz	46	54	54	See b)
A12.3	30 – 300			46	54	50	
	300 – 1 000		52	See c)			
A12.4	30 – 300	For frequencies ≥1 GHz	46		66	59	See d)
	300 – 1 000			52			
A12.5	30 – 950	Peak/ 1 MHz	46	76	46	See e)	
	950 – 2 150			n/a	54		

a) Television receivers (analogue or digital), video recorders and PC TV broadcast receiver tuner cards working in channels between 30 MHz and 1 GHz, and digital audio receivers.

b) Tuner units (not the LNB) for satellite signal reception.

c) Frequency modulation audio receivers and PC tuner cards.

d) Frequency modulation car radios.



e) Applicable to EUTs with RF modulator output ports (for example DVD equipment, video recorders, camcorders and decoders etc.) designed to connect to TV broadcast receiver tuner ports.

**\*\*Remarks: It is not necessary to be tested on this item.**

## 7. Outdoor units of home satellite receiving systems

### 7.1 Test Setup and Procedure

#### 7.1.1 Test Setup

	
<p>Description of <math>\pm 7^\circ</math> of the main beam axis of the EUT</p>	<p>Measurement arrangements of transmit antenna for the wanted signal</p>

#### 7.1.2 Test Procedure

The input signal shall be adjusted to get the maximum rated output level from the EUT. For the measurement in the frequency range from 30 MHz to 18 GHz the input signal shall be adjusted so that the output frequency is within this frequency range. For the measurement in the frequency range above 1 GHz, the frequency of the input signal shall be adjusted in such a way that the EUT is measured, as a minimum, at the lowest, middle and highest rated output frequency within the measured frequency range.

#### 7.1.3 Spectrum Analyzer Configuration (for the frequencies tested)

Frequency Range: 30MHz--1000MHz  
 Detector Function: Quasi-Peak Mode  
 Resolution Bandwidth: 120kHz

Frequency Range: Above 1000MHz  
 Detector Function: Peak/Average Mode  
 Resolution Bandwidth: 1MHz

**7.1.4 Limit**

Table Clause	Frequency Range MHz	Measurement			Class B Limits	Applicable to
		Facility (see Table A.1)	Distance m	Detector type / Bandwidth		
A7.1	30 to 1 000	SAC / OATS / FAR	See Table A.4	Quasi Peak / 120 kHz	See Table A.4	
A7.2	1 000 to 2 500	FSOATS	3	Average / 1 MHz	50 dB(μV/m)	LO leakage and spurious radiated emissions from the EUT, in the region outside ±7° of the main beam axis. See Figure H.1
	2 500 to 18 000				64 dB(μV/m)	
A7.3	1 000 to 18 000	FSOATS	3	Average / 1 MHz	37 dB(μV/m)	LO leakage from the EUT, in the region within ±7° of the main beam axis. See Figure H.1
A7.4	1 000 to 18 000	Conducted (Clause H.4)	n/a	Average / 1 MHz	30 dBpW	

For details of the EUT configuration, see Annex H.

For radiated emissions measurements at frequencies up to 1 GHz, the requirements defined in Table A.4 shall be satisfied.

Apply the appropriate limits across the entire frequency range.

Apply the limits defined in table Clause A7.1 and A7.2. Also apply the limits defined in either table Clause A7.3 or A7.4.

**\*\*Remarks: It is not necessary to be tested on this item.**

## 8. Electrostatic discharge (ESD) immunity

### 8.1 Test Specification and Setup

#### 8.1.1 Test Specification

Port:	Enclosure
Basic Standard:	EN 61000-4-2 / IEC 61000-4-2 / BS EN 61000-4-2 (details referred to Sec 1.2)
Test Level: (By manufacture reference)	Air +/- 2 kV, +/- 4 kV, +/- 8 kV Contact +/- 4 kV, +/- 6 kV
Criteria:	B
Test Procedure:	refer to ISL QA -T4-E-S7

#### Selected Test Point


Air: discharges were applied to slots, aperture or insulating surfaces. 10 single air discharges were applied to each selected points.

Contact: Total 200 discharges minimum were to the selected contact points.

Indirect Contact Points: 25 discharges were applied to center of one edge of VCP and each EUT side of HCP with 10 cm away from EUT.

#### 8.1.2 Test Setup

EUT is 1m from the wall and other metallic structure. When Battery test mode is needed, a cable with one 470kΩ resistor at two rare ends is connected from metallic part of EUT and screwed to HCP.



#### 8.1.3 Test Result

**Performance of EUT complies with the given specification.**

**8.2 Test Data: Configuration 1**

Basic Standard	EN 61000-4-2					Date				
EUT Model Name	TEP 200-7213UIR-N					2021-06-21				
Barometer Pressure	100.3kPa					Engineer				
Temperature	22°C					Jeff Liang				
Humidity	40%					Equipment & Test Site				
Voltage	72Vdc									
<p><b>A=criteria A, B=criteria B, C=criteria C</b>                  → Blue arrow represent Air discharge point                  → Red arrow represent Contact discharge point                  ND=No Discharge, No Arcing; Meets criteria but unable to obtain an electrostatic discharge (ESD) at this test point.                  X=EUT DOES NOT meet the acceptance criteria                  A=criteria A, B=criteria B, C=criteria C</p>										
Contact Discharge	Voltage kV 25 Discharge @ 1 PPS									
Test Location	+4	-4	+6	-6						Comments
1	ND	ND	ND	ND						
2	ND	ND	ND	ND						
3	A	A	A	A						
4	A	A	A	A						
5	A	A	A	A						
6	A	A	A	A						
7	A	A	A	A						
8	ND	ND	ND	ND						
9	ND	ND	ND	ND						
Air Discharge	Voltage kV 10 Discharge @ 1 PPS									
Test Location	+2	-2	+4	-4	+8	-8				Comments
1	ND	ND	ND	ND	A	A				
2	ND	ND	ND	ND	A	A				
3	A	A	A	A	A	A				
4	A	A	A	A	A	A				
5	A	A	A	A	A	A				
6	A	A	A	A	A	A				
7	A	A	A	A	A	A				
8	ND	ND	ND	ND	A	A				
9	ND	ND	ND	ND	A	A				
Indirect Discharge	Voltage kV 25 Discharge @ 1 PPS									
Test Location	+4	-4	+6	-6						Comments
VCP Front	A	A	A	A						
VCP Right	A	A	A	A						
VCP Left	A	A	A	A						
VCP Back	A	A	A	A						
Test Location	+4	-4	+6	-6						Comments
HCP Front	A	A	A	A						
HCP Right	A	A	A	A						
HCP Left	A	A	A	A						
HCP Back	A	A	A	A						
<b>Additional Notes: A=criteria A, B=criteria B, C=criteria C</b>										
Note: Test points are according to customer requirements.										

### 8.3 Test Point

Red arrow lines indicate the contact points, and blue arrow lines indicate the air points.  
Figure 1 : Test Point Assignments Discharge:





Figure 2 : Test Point Assignments Discharge:



#### 8.4 Test Setup Photo



## 9. Radio-Frequency, Electromagnetic Field immunity


### 9.1 Test Specification and Setup

#### 9.1.1 Test Specification

Port:	Enclosure
Basic Standard:	EN 61000-4-3 / IEC 61000-4-3 / BS EN 61000-4-3 (details referred to Sec 1.2)
Test Level: (By manufacture reference)	20 V/m
Modulation:	AM 1kHz 80%
Frequency range:	80 MHz~1 GHz
Frequency Step:	1% of last step frequency
Dwell time:	2s
Polarization:	Vertical and Horizontal
EUT Azimuth Angle:	<input checked="" type="checkbox"/> 0° <input checked="" type="checkbox"/> 90° <input checked="" type="checkbox"/> 180° <input checked="" type="checkbox"/> 270°
Criteria:	A
Test Procedure:	refer to ISL QA -T4-E-S8

#### 9.1.2 Test Setup

The field sensor is placed at one calibration grid point to check the intensity of the established fields on both polarizations. EUT is adjusted to have each side of EUT face coincident with the calibration plane. A CCD camera and speakers are used to monitor the condition of EUT for the performance judgment.



#### 9.1.3 Test Result

**Performance of EUT complies with the given specification.**

**9.2 Test Data: Configuration 1**

Basic Standard	EN 61000-4-3		Date					
EUT Model Name	TEP 200-7213UIR-N		2021-06-29					
Barometer Pressure	102.2kPa		Engineer					
Temperature	23°C		SAWYER					
Humidity	55%		Equipment & Test Site					
Voltage/Freq.	72 Vdc		Chamber 15					
<b>A=criteria A, B=criteria B, C=criteria C</b>								
EUT Angle	Frequency		Dwell time	Modulation	Level (V/m)	Antenna Polarization	EUT Status	Comments
	Range (MHz)	Steps %						
0°(front)	80-1000	1	2s	80% @ 1kHz	20	Vertical	A	
90°(left)	80-1000	1	2s	80% @ 1kHz	20	Vertical	A	
180°(back)	80-1000	1	2s	80% @ 1kHz	20	Vertical	A	
270°(right)	80-1000	1	2s	80% @ 1kHz	20	Vertical	A	
0°(front)	80-1000	1	2s	80% @ 1kHz	20	Horizontal	A	
90°(left)	80-1000	1	2s	80% @ 1kHz	20	Horizontal	A	
180°(back)	80-1000	1	2s	80% @ 1kHz	20	Horizontal	A	
270°(right)	80-1000	1	2s	80% @ 1kHz	20	Horizontal	A	
<b>Additional Notes: A=criteria A, B=criteria B, C=criteria C</b>								

### 9.3 Test Setup Photo



## 10. Electrical Fast transients/burst immunity

### 10.1 Test Specification and Setup

#### 10.1.1 Test Specification

Port:	DC mains
Basic Standard:	EN 61000-4-4 / IEC 61000-4-4 / BS EN 61000-4-4 (details referred to Sec 1.2)
Test Level: (By manufacture reference)	DC Power Port: +/- 2 kV
Rise Time:	5ns
Hold Time:	50ns
Burst Period:	300ms
Repetition Frequency:	5kHz
Criteria:	B
Test Procedure:	refer to ISL QA -T4-E-S9

#### Test Procedure


The EUT was setup on a nonconductive table 0.1 m above a reference ground plane.

Test Points	Polarity	Result	Comment
Line	+	N	60 sec
	-	N	60 sec
Neutral	+	N	60 sec
	-	N	60 sec
Line to Neutral	+	N	60 sec
	-	N	60 sec

Note: 'N' means normal, the EUT function is correct during the test.

### 10.1.2 Test Setup

EUT is at least 50cm from the conductive structure.



### 10.1.3 Test Result


Performance of EUT complies with the given specification.

**10.2 Test Data: Configuration 1**

Basic Standard	EN 61000-4-4	Date					
EUT Model Name	TEP 200-7213UIR-N	2021-06-21					
		Engineer					
Barometer Pressure	102.3kPa	SAWYER					
Temperature	24°C	Equipment & Test Site					
Humidity	52%	EMC-PARTNER (Model:					
Voltage/Freq.	72 Vdc	IMU3000)					
<b>A=criteria A, B=criteria B, C=criteria C</b>							
AC Power Port: <input type="checkbox"/>	DC Power Port: <input checked="" type="checkbox"/>	LAN Port: <input type="checkbox"/>	Telephone Port: <input type="checkbox"/>				
<b>DC Power Port</b>							
Line Under Test	Voltage Level	Severity Level	Pulse Polarity	Burst Repetition Rate	Test Duration	EUT Status	Comments
Line	2.0kV	3	+	300ms / 5.0kHz	1 Minutes	A	
Line	2.0kV	3	-	300ms / 5.0kHz	1 Minutes	A	
Neutral	2.0kV	3	+	300ms / 5.0kHz	1 Minutes	A	
Neutral	2.0kV	3	-	300ms / 5.0kHz	1 Minutes	A	
Line- Neutral	2.0kV	3	+	300ms / 5.0kHz	1 Minutes	A	
Line- Neutral	2.0kV	3	-	300ms / 5.0kHz	1 Minutes	A	
<b>Additional Notes: A=criteria A, B=criteria B, C=criteria C</b>							
NOTE: For the countermeasure components, please refer to Solution:” For Electrical Fast transient & Surge Immunity test requirements”							



### 10.3 Test Setup Photo




# 11. Surge Immunity

## 11.1 Test Specification and Setup

### 11.1.1 Test Specification

Port:	DC mains
Basic Standard:	EN 61000-4-5 / IEC 61000-4-5 / BS EN 61000-4-5 (details referred to Sec 1.2)
Test Level: (By manufacture reference)	Line to Line: +/- 0.5 kV, +/- 1 kV, +/- 2 kV
Rise Time:	1.2us
Hold Time:	50us
Repetition Rate:	60 seconds
Angle:	<input type="checkbox"/> 0° <input type="checkbox"/> 90° <input type="checkbox"/> 180° <input type="checkbox"/> 270°
Criteria:	B
Test Procedure:	refer to ISL QA -T4-E-S10


### 11.1.2 Test Setup



### 11.1.3 Test Result


**Performance of EUT complies with the given specification.**

**11.2 Test Data: Configuration 1**

Basic Standard	EN 61000-4-5	Date							
EUT Model Name	TEP 200-7213UIR-N	2021-06-21							
Barometer Pressure	102.3kPa	Engineer	SAWYER						
Temperature	24°C	Equipment & Test Site							
Humidity	52%	EMC-PARTNER (Model: IMU3000)							
Voltage/Freq.	72 Vdc								
<b>A=criteria A, B=criteria B, C=criteria C</b>									
AC Power Port: <input type="checkbox"/>	DC Power Port: <input checked="" type="checkbox"/>	LAN Port: <input type="checkbox"/>	Telephone Port: <input type="checkbox"/>						
<b>DC Power Port</b>									
Line Under Test	Voltage	Level	Polarity	Repetition Rate	Cycle	Pulse Position	EUT Status	Comments	
Line-Neutral	0.5kV	1	+	60 sec	5		A		
Line-Neutral	0.5kV	1	-	60 sec	5		A		
Line- Neutral	1.0kV	2	+	60 sec	5		A		
Line- Neutral	1.0kV	2	-	60 sec	5		A		
Line- Neutral	2.0kV	2	+	60 sec	5		A		
Line- Neutral	2.0kV	2	-	60 sec	5		A		
<b>Additional Notes: A=criteria A, B=criteria B, C=criteria C</b>									
<b>NOTE:</b>					For the countermeasure components, please refer to Solution:” For Electrical Fast transient & Surge Immunity test requirements”				



### 11.3 Test Setup Photo




## 12. Immunity to Conductive Disturbance

### 12.1 Test Specification and Setup

#### 12.1.1 Test Specification

Port:	DC mains
Basic Standard:	EN 61000-4-6 / IEC 61000-4-6 / BS EN 61000-4-6 (details referred to Sec 1.2)
Test Level: (By manufacture reference)	0.15MHz to 80MHz: 10 Vrms
Modulation:	AM 1kHz 80%
Frequency range:	0.15 MHz - 80MHz
Frequency Step:	1% of last Frequency
Dwell time:	2s
Criteria:	A
CDN Type:	CDN M2+M3
Test Procedure:	refer to ISL QA -T4-E-S11

#### 12.1.2 Test Setup



#### 12.1.3 Test Result

**Performance of EUT complies with the given specification.**

**12.2 Test Data: Configuration 1**

Basic Standard	EN 61000-4-6		Date				
EUT Model Name	TEP 200-7213UIR-N		2021-06-29				
			Engineer				
Barometer Pressure	102.2kPa		SAWYER				
Temperature	24°C		Equipment & Test Site				
Humidity	57%		FRANKONIA (Model: CIT-10/75)				
Voltage/Freq.	72 Vdc						
<b>A=criteria A, B=criteria B, C=criteria C</b>							
<b>DC Power Port</b>							
Line Under Test	Frequency		Level	Modulation	Dwell time	EUT Status	Comments
	Range (MHz)	Steps %					
DC Power Port	0.15 to 80	1	10V	80% @ 1kHz	2s	A	
<b>Additional Notes: A=criteria A, B=criteria B, C=criteria C</b>							

### 12.3 Test Setup Photo




## 13. Power Frequency Magnetic Field immunity

### 13.1 Test Specification and Setup

#### 13.1.1 Test Specification

Port:	Enclosure
Basic Standard:	EN 61000-4-8 / IEC 61000-4-8 / BS EN 61000-4-8 (details referred to Sec 1.2)
Test Level: (By manufacture reference)	100 A/m, 1000 A/m
Polarization:	X, Y, Z
Criteria:	A
Test Procedure:	refer to ISL QA -T4-E-S12

#### 13.1.2 Test Setup



#### 13.1.3 Test Result

**Performance of EUT complies with the given specification.**

**13.2 Test Data: Configuration 1**

Basic Standard	EN 61000-4-8		Date	2021-06-29	
EUT Model Name	TEP 200-7213UIR-N		Engineer	SAWYER	
Barometer Pressure	102.3kPa		Equipment & Test Site	Magnetic Field Immunity Loop Brand: Pic Model:PMF1000 & Magnetic Field Test AC Power Source Brand: Pic Model: AC Power Source	
Temperature	24°C				
Humidity	55%				
Voltage/Freq.	72Vdc				
<b>A=criteria A, B=criteria B, C=criteria C</b>					
Antenna Polarization	Frequency (Hz)	Test Level	Test Duration	EUT Status	Comment
X	0	100 A/m	1 Minutes	A	
Y	0	100 A/m	1 Minutes	A	
Z	0	100 A/m	1 Minutes	A	
X	0	1000 A/m	1 Second	A	
Y	0	1000 A/m	1 Second	A	
Z	0	1000 A/m	1 Second	A	
<b>Additional Notes: A=criteria A, B=criteria B, C=criteria C</b>					

### 13.3 Test Setup Photo



## 14. Appendix

### 14.1 Appendix A: Test Equipment

#### 14.1.1 Test Equipment List

Location Chamber02	Equipment Name	Brand	Model	S/N	Last Cal. Date	Next Cal. Date
Radiation (Chamber02)	BILOG Antenna 17 (30MHz~1GHz)	Schwarzbeck	Schwarzbeck VULB 9168+EMCI-N-6-05	645	04/13/2021	04/13/2022
Radiation (Chamber02)	Preamplifier 25	EMCI	EMC9135	980295	04/03/2021	04/03/2022
Radiation (Chamber02)	Coaxial Cable Chmb 02-10M-02	EMC	RG214U	Chmb 02-10M-02	10/14/2020	10/14/2021
Radiation (Chamber02)	EMI Receiver 12	ROHDE & SCHWARZ	ESCI	100804	08/19/2020	08/19/2021

Location	Equipment Name	Brand	Model	S/N	Last Cal. Date	Next Cal. Date
EN61K-4-2	ESD Gun 12	EM TEST	Dito	P1650188689	05/05/2021	05/05/2022
EN61K-4-3	Broadband Log-Periodic Antenna	AR	AT1080	310698	N/A	N/A
EN61K-4-3	Horn Antenna RF-01	AR	ATS700M11 G	0335864	N/A	N/A
EN61K-4-3	Amplifier 80Mz~1GHz 250W	AR	250W1000A	312494	N/A	N/A
EN61K-4-3	Amplifier 800MHz~4.2GHz 50W	AR	50S1G4M1	312762	N/A	N/A
EN61K-4-3	Amplifier 4.0~8.0GHz 35W	AR	35S4G8AM1	0335752	N/A	N/A
EN61K-4-3	Broadband Coupler 80M~1GHz	Amplifier Research	DC6180A	0341805	N/A	N/A
EN61K-4-3	Coaxial Cable	INSULATED	NPS-4806-23 60-NP3	108599.003.01 .03	N/A	N/A
EN61K-4-3	Broadband Coupler 0.8G~4.26GHz	AR	DC7144A	0335226	N/A	N/A
EN61K-4-3	Broadband Coupler 4G~8GHz	AR	DC7350A	0335817	N/A	N/A
EN61K-4-3	Signal Generator 07	ROHDE& SCHWARZ	SMB100A	107780	11/29/2020	11/29/2021
EN61K-4-4 EN61K-4-5	Signal Generator 10	EMC Partner	IMU3000	1547	09/15/2020	03/15/2022
EN61K-4-6	CDN M2+M3 04	TESEQ	CDN M016	43257	09/03/2020	09/03/2021
EN61K-4-6	Coaxial Cable 4-6 02-1			4-6 02-1	N/A	N/A
EN61K-4-6	Conducted Immunity Test System 03	Frankonia	CIT-10-75	126B1151	01/08/2021	01/08/2022
EN61K-4-8	Magnetic Field Test Generator 02	PIC	PMF-1000	ANT150701	05/31/2021	05/31/2022

PS: N/A => The equipment does not need calibration.

**\*\*Software for Controlling Spectrum/Receiver and Calculating Test Data**

Test Item	Filename	Version
EN 61000-4-2	N/A	2.0
EN 61000-4-3	i2	529b
EN 61000-4-4	TEM A3000	v4.6.1
EN 61000-4-5	TEM A3000	v4.6.1
EN 61000-4-6	FRANKONIA CD-LAB	V5.221
EN 61000-4-8	N/A	

Site	Filename	Version	Issue Date
Radiation	EZ EMC	ISL-03A2	3/6/2013
Conduction	EZ EMC	ISL-03A2	3/6/2013

## 14.2 Appendix B: Uncertainty of Measurement

The laboratory measurement uncertainty accordance with refers to CISPR 16-4-2. If U<sub>lab</sub> is less than or equal to U<sub>cispr</sub> in Table 1, then the test report may either state the value of U<sub>lab</sub> or state that U<sub>lab</sub> is less than U<sub>cispr</sub>.

The coverage factor k = 2 yields approximately a 95 % level of confidence.

<Conduction 03>

AMN: ±2.90dB

<Chamber 02 (10m)>

Horizontal

30MHz~200MHz: ±4.52dB

200MHz~1000MHz: ±4.42dB

Vertical

30MHz~200MHz: ±4.51dB

200MHz~1000MHz: ±4.70dB

<Immunity 02>

Test item	Uncertainty	Test item	Uncertainty
EN 61000-4-2 (ESD)		EN 61000-4-6 (CS)	
Rise time tr	≤ 9.81%	CDN	± 1.74dB
Peak current I <sub>p</sub>	≤ 5.54%	EM Clamp	± 3.36dB
current at 30 ns	≤ 5.55%	EN 61000-4-8 (Magnetic)	± 6.53%
current at 60 ns	≤ 5.55%		
EN 61000-4-3 (RS)	± 1.89dB		
EN 61000-4-4 (EFT)			
voltage rise time (tr)	± 5.1%		
peak voltage value (VP)	± 6.39%		
voltage pulse width (tw)	± 5.0%		
EN 61000-4-5 (Surge)			
open-circuit voltage front time	±13.5%		
open-circuit voltage peak value	±6.6%		
open-circuit voltage duration (Td)	53.33μs		

### 14.3 Appendix C: Photographs of EUT

Please refer to the File of **ISL-21LE505P-R1-MA**

--- END ---