



CE EMC TEST REPORT

REPORT NO.: CE980317A04A-1

MODEL NO.: TMP 60105 -*multiple listing on page 9*

RECEIVED: March 17, 2009

TESTED: April 7 ~ 13, 2009

ISSUED: April 22, 2009

APPLICANT: TRACO ELECTRONIC AG

ADDRESS: P.O. Box Jenatschstrasse 1 CH - 8002 Zurich
Switzerland

ISSUED BY: Bureau Veritas Consumer Products Services (H.K.)
Ltd., Taoyuan Branch

LAB LOCATION: No. 47, 14th Ling, Chia Pau Tsuen, Lin Kou Hsiang,
Taipei Hsien 244, Taiwan

This test report consists of 96 pages in total. It may be duplicated completely for legal use with the approval of the applicant. It should not be reproduced except in full, without the written approval of our laboratory. The client should not use it to claim product endorsement by TAF, NVLAP or any government agencies. The test results in the report only apply to the tested sample. The test results in this report are traceable to the national or international standards.





Table of Contents

1	CERTIFICATION.....	5
2	SUMMARY OF TEST RESULTS.....	7
2.1	MEASUREMENT UNCERTAINTY	8
3	GENERAL INFORMATION	9
3.1	GENERAL DESCRIPTION OF EUT.....	9
3.2	DESCRIPTION OF TEST MODES.....	10
3.3	GENERAL DESCRIPTION OF APPLIED STANDARDS	11
3.4	DESCRIPTION OF SUPPORT UNITS.....	12
3.4.1	FOR EMISSION TEST	12
3.4.2	FOR HARMONICS / FLICKER / IMMUNITY TEST	13
4	EMISSION TEST.....	14
4.1	CONDUCTED EMISSION MEASUREMENT	14
4.1.1	LIMITS OF CONDUCTED EMISSION MEASUREMENT.....	14
4.1.2	TEST INSTRUMENTS	15
4.1.3	TEST PROCEDURE	15
4.1.4	DEVIATION FROM TEST STANDARD	16
4.1.5	TEST SETUP	16
4.1.6	EUT OPERATING CONDITIONS.....	16
4.1.7	TEST RESULTS (1)	17
4.1.8	TEST RESULTS (2)	19
4.1.9	TEST RESULTS (3)	21
4.1.10	TEST RESULTS (4)	23
4.1.11	TEST RESULTS (5)	25
4.1.12	TEST RESULTS (6)	27
4.1.13	TEST RESULTS (7)	29
4.1.14	TEST RESULTS (8)	31
4.1.15	TEST RESULTS (9)	33
4.1.16	TEST RESULTS (10)	35
4.1.17	TEST RESULTS (11).....	37
4.1.18	TEST RESULTS (12)	39
4.2	RADIATED EMISSION MEASUREMENT	41
4.2.1	LIMITS OF RADIATED EMISSION MEASUREMENT.....	41
4.2.2	TEST INSTRUMENTS	42
4.2.3	TEST PROCEDURE	42
4.2.4	DEVIATION FROM TEST STANDARD	43
4.2.5	TEST SETUP	43
4.2.6	EUT OPERATING CONDITIONS.....	43
4.2.7	TEST RESULTS (1)	44
4.2.8	TEST RESULTS (2)	46
4.2.9	TEST RESULTS (3)	48
4.3	HARMONICS CURRENT MEASUREMENT	50
4.3.1	LIMITS OF HARMONICS CURRENT MEASUREMENT.....	50
4.3.2	TEST INSTRUMENTS	50



4.3.3	TEST PROCEDURE	51
4.3.4	DEVIATION FROM TEST STANDARD	51
4.3.5	TEST SETUP	51
4.3.6	EUT OPERATING CONDITIONS.....	51
4.3.7	TEST RESULTS (1)	52
4.3.8	TEST RESULTS (2)	52
4.3.9	TEST RESULTS (3)	53
4.4	VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT	54
4.4.1	LIMITS OF VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT	54
4.4.2	TEST INSTRUMENTS	54
4.4.3	TEST PROCEDURE	54
4.4.4	DEVIATION FROM TEST STANDARD	55
4.4.5	TEST SETUP	55
4.4.6	EUT OPERATING CONDITIONS.....	55
4.4.7	TEST RESULTS (1)	56
4.4.8	TEST RESULTS (2)	57
4.4.9	TEST RESULTS (3)	58
5	IMMUNITY TEST	59
5.1	GENERAL DESCRIPTION.....	59
5.2	GENERAL PERFORMANCE CRITERIA DESCRIPTION	60
5.3	EUT OPERATING CONDITION	60
5.4	ELECTROSTATIC DISCHARGE IMMUNITY TEST (ESD).....	61
5.4.1	TEST SPECIFICATION	61
5.4.2	TEST INSTRUMENTS	61
5.4.3	TEST PROCEDURE	61
5.4.4	DEVIATION FROM TEST STANDARD	62
5.4.5	TEST SETUP	63
5.4.6	TEST RESULTS.....	64
5.4.7	RADIATED, RADIO-FREQUENCY, ELECTROMAGNETIC FIELD IMMUNITY TEST (RS).....	65
5.4.8	TEST SPECIFICATION	65
5.4.9	TEST INSTRUMENTS	65
5.4.10	TEST PROCEDURE	66
5.4.11	DEVIATION FROM TEST STANDARD	66
5.4.12	TEST SETUP	67
5.4.13	TEST RESULTS.....	68
5.5	ELECTRICAL FAST TRANSIENT/BURST IMMUNITY TEST (EFT)	69
5.5.1	TEST SPECIFICATION	69
5.5.2	TEST INSTRUMENTS	69
5.5.3	TEST PROCEDURE	69
5.5.4	DEVIATION FROM TEST STANDARD	69
5.5.5	TEST SETUP	70
5.5.6	TEST RESULTS (1)	71
5.5.7	TEST RESULTS (2)	71
5.5.8	TEST RESULTS (3)	72
5.6	SURGE IMMUNITY TEST.....	73
5.6.1	TEST SPECIFICATION.....	73



5.6.2	TEST INSTRUMENTS	73
5.6.3	TEST PROCEDURE	74
5.6.4	DEVIATION FROM TEST STANDARD	74
5.6.5	TEST SETUP	74
5.6.6	TEST RESULTS.....	75
5.7	IMMUNITY TO CONDUCTED DISTURBANCES INDUCED BY RF FIELDS (CS).....	76
5.7.1	TEST SPECIFICATION	76
5.7.2	TEST INSTRUMENTS	76
5.7.3	TEST PROCEDURE	77
5.7.4	DEVIATION FROM TEST STANDARD	77
5.7.5	TEST SETUP	78
5.7.6	TEST RESULTS.....	79
5.8	POWER FREQUENCY MAGNETIC FIELD IMMUNITY TEST.....	80
5.8.1	TEST SPECIFICATION	80
5.8.2	TEST INSTRUMENTS	80
5.8.3	TEST PROCEDURE	80
5.8.4	DEVIATION FROM TEST STANDARD	80
5.8.5	TEST SETUP	81
5.8.6	TEST RESULTS.....	82
5.9	VOLTAGE DIP/SHORT INTERRUPTIONS/VOLTAGE VARIATIONS (DIP) IMMUNITY TEST	83
5.9.1	TEST SPECIFICATION.....	83
5.9.2	TEST INSTRUMENTS	83
5.9.3	TEST PROCEDURE	83
5.9.4	DEVIATION FROM TEST STANDARD	83
5.9.5	TEST SETUP	84
5.9.6	TEST RESULTS.....	85
6	PHOTOGRAPHS OF THE TEST CONFIGURATION.....	86
7	APPENDIX - INFORMATION ON THE TESTING LABORATORIES.....	96



1 CERTIFICATION

PRODUCT: AC/DC Power Modules
BRAND NAME: TRACO
MODEL NO.: TMP 60105 - *multiple listing on page 9*
TEST ITEM: R & D SAMPLE
APPLICANT: TRACO ELECTRONIC AG
TESTED: April 7 ~ 13, 2009

STANDARDS:

EN 61000-6-4: 2007	EN 61000-6-2: 2005
EN 55011:1998+A1:1999	IEC 61000-4-2: 2001 ED.1.2
+A2: 2002, Group I, Class A	IEC 61000-4-3: 2006 +A1: 2007 ED.3.0
EN 61000-3-2: 2006	IEC 61000-4-4: 2004 ED.2.0
<i>(refer to Note* below)</i>	IEC 61000-4-5: 2005 ED.2.0
EN 61000-3-3: 1995+A1: 2001	IEC 61000-4-6: 2006 ED.2.2
+A2:2005	IEC 61000-4-8: 2001 ED.1.1
	IEC 61000-4-11: 2004 ED.2.0

Note*: The power consumption is 73.26W which is less than 75W, and no limits apply.
Therefore it is deemed to comply with the EN 61000-3-2 without any testing.

The above equipment has been tested by **Advance Data Technology Corporation**, and found compliance with the requirement of the above standards.

Approval signature – on next page



CERTIFICATION – Continued

The test record, data evaluation & Equipment Under Test (EUT) configurations represented herein are true and accurate accounts of the measurements of the sample's EMC characteristics under the conditions specified in this report.

PREPARED BY : Vivian Chen , **DATE:** April 22, 2009
(Vivian Chen / Specialist)

TECHNICAL ACCEPTANCE : Joyce Chen , **DATE:** April 22, 2009
(Joyce Chen / Senior Engineer)

APPROVED BY : Kenny Meng , **DATE:** April 22, 2009
(Kenny Meng / Assistant Manager)

2 SUMMARY OF TEST RESULTS

The EUT has been tested according to the following specifications:

EMISSION			
Standard	Test Type	Result	Remarks
EN 61000-6-4: 2007	Conducted Test	PASS	Meets Class A Limit Minimum passing margin is -18.94 dB at 0.279 MHz
EN 55011: 1998 +A1: 1999+A2: 2002, Group I, Class A	Radiated Test	PASS	Meets Class A Limit Minimum passing margin is -10.53 dB at 51.23 MHz
EN 61000-3-2:2006	Harmonic current emissions	PASS	The power consumption of EUT is less than 75W and no limits apply
EN 61000-3-3:1995 +A1:2001+A2:2005	Voltage fluctuations & flicker	PASS	Meets the requirements.



A D T

IMMUNITY			
Standard	Test Type	Result	Remarks
IEC 61000-4-2: 2001 ED.1.2	Electrostatic discharge immunity test	PASS	Meets the requirements of Performance Criterion A
IEC 61000-4-3: 2006 +A1: 2007 ED.3.0	Radiated, radio-frequency, electromagnetic field immunity test	PASS	Meets the requirements of Performance Criterion A
IEC 61000-4-4: 2004 ED.2.0	Electrical fast transient / burst immunity test.	PASS	Meets the requirements of Performance Criterion B
IEC 61000-4-5: 2005 ED.2.0	Surge immunity test	PASS	Meets the requirements of Performance Criterion A
IEC 61000-4-6: 2006 ED.2.2	Immunity to conducted disturbances, induced by radio-frequency fields	PASS	Meets the requirements of Performance Criterion A
IEC 61000-4-8: 2001 ED.1.1	Power frequency magnetic field immunity test.	PASS	Meets the requirements of Performance Criterion A
IEC 61000-4-11: 2004 ED.2.0	Voltage dips, short interruptions and voltage variations immunity tests	PASS	Voltage Dips: i) 0% residual - Performance Criterion A ii) 40% residual – Performance Criterion B iii) 70% residual – Performance Criterion A Voltage Interruptions: i) 0% residual – Performance Criterion B

2.1 MEASUREMENT UNCERTAINTY

Where relevant, the following measurement uncertainty levels have been estimated for tests performed on the EUT as specified in CISPR 16-4-2:

This uncertainty represents an expanded uncertainty expressed at approximately the 95% confidence level using a coverage factor of $k=2$.

MEASUREMENT	UNCERTAINTY
Conducted emissions	2.46dB
Radiated emissions	3.71dB



3 GENERAL INFORMATION

3.1 GENERAL DESCRIPTION OF EUT

PRODUCT	AC/DC Power Modules
MODEL NO.	TMP 60105 - <i>multiple listing as below</i>
POWER SUPPLY	Switching: Rating: refer to Note as below
DATA CABLE SUPPLIED	N/A

NOTE:

1. The EUT is a AC/DC Power Modules (AC 2 Pin), and It has several models, which are identical to each other except for their output rating differences, as below:

Model No.	AC I/P	DC O/P
TMP 60105, TMP 60105C	230Vac, 50Hz	5.1Vdc
TMP 60112, TMP 60112C		12Vdc
TMP 60115, TMP 60115C		15Vdc
TMP 60124, TMP 60124C		24Vdc
TMP 60136, TMP 60136C		36Vdc
TMP 60148, TMP 60148C		48Vdc

2. For a more detailed features description, please refer to the manufacturer's specifications or the User's Manual.

3.2 DESCRIPTION OF TEST MODES

During the test, the above models were pre-tested, and the worst radiated emission levels were found on **Model: TMP 60112, TMP 60115, TMP 60124** therefore the final test modes are as the following:

Test Item	Test Mode	Model No.	Test Condition
Conducted Test	Mode 1	TMP 60105	Full load
	Mode 2	TMP 60105C	
	Mode 3	TMP 60112	
	Mode 4	TMP 60112C	
	Mode 5	TMP 60115	
	Mode 6	TMP 60115C	
	Mode 7	TMP 60124	
	Mode 8	TMP 60124C	
	Mode 9	TMP 60136	
	Mode 10	TMP 60136C	
	Mode 11	TMP 60148	
	Mode 12	TMP 60148C	
Radiated, Harmonic, Flicker, Immunity Tests	Mode 1	TMP 60112	Full load
	Mode 2	TMP 60115	
	Mode 3	TMP 60124	

3.3 GENERAL DESCRIPTION OF APPLIED STANDARDS

The EUT has been tested and complied with the requirements of the following standards:

EN 61000-6-4: 2007

**EN 55011: 1998+A1: 1999+A2: 2002,
Group I Class A**

EN 61000-3-2: 2006

EN 61000-3-3: 1995+A1: 2001+A2:2005

EN 61000-6-2: 2005

IEC 61000-4-2: 2001 ED.1.2

IEC 61000-4-3: 2006+A1:2007 ED.3.0

IEC 61000-4-4: 2004 ED.2.0

IEC 61000-4-5: 2005 ED.2.0

IEC 61000-4-6: 2006 ED.2.2

IEC 61000-4-8: 2001 ED.1.1

IEC 61000-4-11: 2004 ED.2.0

All tests have been performed and recorded as per the above standards.

3.4 DESCRIPTION OF SUPPORT UNITS


The EUT has been tested as an independent unit together with other necessary accessories or support units. The following support units or accessories were used to form a representative test configuration during the tests.

3.4.1 FOR EMISSION TEST

NO.	PRODUCT	BRAND	MODEL NO.	SERIAL NO.	FCC ID
1	RESISTOR LOAD	N/A	N/A	N/A	N/A

Note: The support unit 1 was provided by client.

Test Configuration






A D T

3.4.2 FOR HARMONICS / FLICKER / IMMUNITY TEST


NO.	PRODUCT	BRAND	MODEL NO.	SERIAL NO.	FCC ID
1	RESISTOR LOAD	N/A	N/A	N/A	N/A
2	Multimeter	YFE	YF-370A	N/A	N/A

Note: The support unit 1 was provided by client.

TEST CONFIGURATION - for HARMONIC & FLICKER TEST



TEST CONFIGURATION - for IMMUNITY TEST



4 EMISSION TEST

4.1 CONDUCTED EMISSION MEASUREMENT

4.1.1 LIMITS OF CONDUCTED EMISSION MEASUREMENT

TEST STANDARD: EN 61000-6-4

FREQUENCY (MHz)	Quasi-peak dB(uV)	Average dB(uV)
0.15 - 0.5	79	66
0.5 - 30	73	60

- NOTE:**
- (1) The lower limit shall apply at the transition frequencies.
 - (2) The limit decreases in line with the logarithm of the frequency in the range of 0.15 to 0.50 MHz.

TEST STANDARD: EN 55011

FREQUENCY (MHz)	Group 1			
	Class A (dBuV)		Class B (dBuV)	
	Quasi-peak	Average	Quasi-peak	Average
0.15 - 0.5	79	66	66 - 56	56 - 46
0.50 - 5.0	73	60	56	46
5.0 - 30.0	73	60	60	50

- NOTE:**
- (1) The lower limit shall apply at the transition frequencies.
 - (2) The limit decreases in line with the logarithm of the frequency in the range of 0.15 to 0.50 MHz.
 - (3) All emanations from a class A/B digital device or system, including any network of conductors and apparatus connected thereto, shall not exceed the level of field strengths specified above.

4.1.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
ROHDE & SCHWARZ Test Receiver	ESCS30	100275	Oct. 28, 2008	Oct. 27, 2009
ROHDE & SCHWARZ Artificial Mains Network (for EUT)	ESH2-Z5	828075/003	Jun. 19, 2008	Jun. 18, 2009
LISN With Adapter (for EUT)	AD10	C05Ada-001	Jun. 19, 2008	Jun. 18, 2009
ROHDE & SCHWARZ 200-A Four-line V-Network	ENV4200	830326/018	Sep. 08, 2008	Sep. 07, 2009
ROHDE & SCHWARZ Artificial Mains Network (for peripherals)	ESH3-Z5	847265/023	Oct. 20, 2008	Oct. 19, 2009
Software	ADT_Cond_V7.3 .7	NA	NA	NA
RF cable (JYEBAO)	5D-FB	Cable-C05.01	Feb. 13, 2009	Feb. 12, 2010
LYNICS Terminator (For R & S LISN)	0900510	E1-01-305	Feb. 19, 2009	Feb. 18, 2010

- NOTE:**
1. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 2. The test was performed in Shielded Room No. 5.
 3. The VCCI Site Registration No. C-1093.
 4. The Industry Canada Reference No. IC 3789-5.


4.1.3 TEST PROCEDURE

- a. The EUT was placed 0.4 meters from the conducting wall of the shielded room with EUT being connected to the power mains through a line impedance stabilization network (LISN). Other support units were connected to the power mains through another LISN. The two LISNs provide 50 Ohm/ 50uH of coupling impedance for the measuring instrument.
- b. Both lines of the power mains connected to the EUT were checked for maximum conducted interference.
- c. The frequency range from 150 kHz to 30 MHz was searched. Emission levels under (Limit -20dB) were not recorded.

4.1.4 DEVIATION FROM TEST STANDARD

No deviation

4.1.5 TEST SETUP



- Note:**
1. Support units were connected to second LISN.
 2. Both of LISNs (AMN) are 80cm from EUT and at least 80cm from other units and other metal planes support units.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

4.1.6 EUT OPERATING CONDITIONS

Set the EUT under full resistor load.




A D T

4.1.7 TEST RESULTS (1)

TEST MODE	Mode 1	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.279	0.35	59.71	-	60.06	-	79.00	66.00	-18.94	-
2	0.408	0.36	56.60	-	56.96	-	79.00	66.00	-22.04	-
3	0.701	0.38	52.40	-	52.78	-	73.00	60.00	-20.22	-
4	0.838	0.38	51.83	-	52.21	-	73.00	60.00	-20.79	-
5	1.562	0.46	47.46	-	47.92	-	73.00	60.00	-25.08	-
6	2.656	0.55	45.91	-	46.46	-	73.00	60.00	-26.54	-
7	15.230	1.38	28.61	-	29.99	-	73.00	60.00	-43.01	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 1	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.271	0.24	51.82	-	52.06	-	79.00	66.00	-26.94	-
2	0.404	0.25	50.58	-	50.83	-	79.00	66.00	-28.17	-
3	0.552	0.26	49.73	-	49.99	-	73.00	60.00	-23.01	-
4	0.705	0.27	49.58	-	49.85	-	73.00	60.00	-23.15	-
5	0.841	0.27	49.24	-	49.51	-	73.00	60.00	-23.49	-
6	0.966	0.28	49.51	-	49.79	-	73.00	60.00	-23.21	-
7	2.195	0.42	43.96	-	44.38	-	73.00	60.00	-28.62	-
8	14.293	1.06	28.26	-	29.32	-	73.00	60.00	-43.68	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.8 TEST RESULTS (2)

TEST MODE	Mode 2	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.283	0.35	55.79	-	56.14	-	79.00	66.00	-22.86	-
2	0.412	0.36	52.13	-	52.49	-	79.00	66.00	-26.51	-
3	0.671	0.37	50.92	-	51.29	-	73.00	60.00	-21.71	-
4	0.854	0.38	49.86	-	50.24	-	73.00	60.00	-22.76	-
5	1.543	0.46	44.67	-	45.13	-	73.00	60.00	-27.87	-
6	2.582	0.54	44.01	-	44.55	-	73.00	60.00	-28.45	-
7	4.656	0.64	37.71	-	38.35	-	73.00	60.00	-34.65	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 2	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.279	0.24	55.79	-	56.03	-	79.00	66.00	-22.97	-
2	0.410	0.25	52.79	-	53.04	-	79.00	66.00	-25.96	-
3	0.548	0.26	50.05	-	50.31	-	73.00	60.00	-22.69	-
4	0.685	0.26	49.40	-	49.66	-	73.00	60.00	-23.34	-
5	0.810	0.27	49.40	-	49.67	-	73.00	60.00	-23.33	-
6	0.966	0.28	47.54	-	47.82	-	73.00	60.00	-25.18	-
7	1.574	0.35	41.68	-	42.03	-	73.00	60.00	-30.97	-
8	15.316	1.14	31.19	-	32.33	-	73.00	60.00	-40.67	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.9 TEST RESULTS (3)

TEST MODE	Mode 3	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.271	0.35	58.85	-	59.20	-	79.00	66.00	-19.80	-
2	0.400	0.36	50.72	-	51.08	-	79.00	66.00	-27.92	-
3	0.548	0.37	51.62	-	51.99	-	73.00	60.00	-21.01	-
4	0.670	0.37	51.53	-	51.90	-	73.00	60.00	-21.10	-
5	1.676	0.48	44.47	-	44.95	-	73.00	60.00	-28.05	-
6	2.645	0.55	42.56	-	43.11	-	73.00	60.00	-29.89	-
7	21.660	2.02	32.88	-	34.90	-	73.00	60.00	-38.10	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 3	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value [dB (uV)]		Emission Level [dB (uV)]		Limit [dB (uV)]		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
	1	0.270	0.24	52.38	-	52.62	-	79.00	66.00	-26.38
2	0.399	0.25	50.74	-	50.99	-	79.00	66.00	-28.01	-
3	0.697	0.26	46.95	-	47.21	-	73.00	60.00	-25.79	-
4	0.806	0.27	49.97	-	50.24	-	73.00	60.00	-22.76	-
5	1.578	0.36	47.36	-	47.72	-	73.00	60.00	-25.28	-
6	18.035	1.37	35.83	-	37.20	-	73.00	60.00	-35.80	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.10 TEST RESULTS (4)

TEST MODE	Mode 4	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.271	0.35	57.48	-	57.83	-	79.00	66.00	-21.17	-
2	0.420	0.36	49.66	-	50.02	-	79.00	66.00	-28.98	-
3	0.552	0.37	50.33	-	50.70	-	73.00	60.00	-22.30	-
4	0.670	0.37	50.21	-	50.58	-	73.00	60.00	-22.42	-
5	1.664	0.48	42.65	-	43.13	-	73.00	60.00	-29.87	-
6	2.480	0.54	41.04	-	41.58	-	73.00	60.00	-31.42	-
7	21.262	1.99	34.41	-	36.40	-	73.00	60.00	-36.60	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 4	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.279	0.24	50.24	-	50.48	-	79.00	66.00	-28.52	-
2	0.404	0.25	49.28	-	49.53	-	79.00	66.00	-29.47	-
3	0.810	0.27	47.60	-	47.87	-	73.00	60.00	-25.13	-
4	1.199	0.31	46.07	-	46.38	-	73.00	60.00	-26.62	-
5	2.031	0.41	41.64	-	42.05	-	73.00	60.00	-30.95	-
6	17.719	1.34	37.07	-	38.41	-	73.00	60.00	-34.59	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.11 TEST RESULTS (5)

TEST MODE	Mode 5	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.268	0.35	57.70	-	58.05	-	79.00	66.00	-20.95	-
2	0.416	0.36	47.92	-	48.28	-	79.00	66.00	-30.72	-
3	0.533	0.37	50.57	-	50.94	-	73.00	60.00	-22.06	-
4	0.661	0.37	51.10	-	51.47	-	73.00	60.00	-21.53	-
5	1.195	0.42	42.61	-	43.03	-	73.00	60.00	-29.97	-
6	1.984	0.52	45.98	-	46.50	-	73.00	60.00	-26.50	-
7	20.320	1.91	32.14	-	34.05	-	73.00	60.00	-38.95	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 5	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.263	0.24	49.83	-	50.07	-	79.00	66.00	-28.93	-
2	0.392	0.25	49.87	-	50.12	-	79.00	66.00	-28.88	-
3	0.669	0.26	46.24	-	46.50	-	73.00	60.00	-26.50	-
4	0.791	0.27	46.47	-	46.74	-	73.00	60.00	-26.26	-
5	1.574	0.35	45.04	-	45.39	-	73.00	60.00	-27.61	-
6	23.250	1.57	30.41	-	31.98	-	73.00	60.00	-41.02	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.12 TEST RESULTS (6)

TEST MODE	Mode 6	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.263	0.35	53.70	-	54.05	-	79.00	66.00	-24.95	-
2	0.525	0.37	48.14	-	48.51	-	73.00	60.00	-24.49	-
3	0.670	0.37	47.77	-	48.14	-	73.00	60.00	-24.86	-
4	1.023	0.39	43.78	-	44.17	-	73.00	60.00	-28.83	-
5	2.398	0.54	41.72	-	42.26	-	73.00	60.00	-30.74	-
6	24.160	2.24	26.81	-	29.05	-	73.00	60.00	-43.95	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 6	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value [dB (uV)]		Emission Level [dB (uV)]		Limit [dB (uV)]		Margin (dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
	1	0.279	0.24	51.53	-	51.77	-	79.00	66.00	-27.23
2	0.408	0.25	48.26	-	48.51	-	79.00	66.00	-30.49	-
3	0.548	0.26	46.99	-	47.25	-	73.00	60.00	-25.75	-
4	0.826	0.27	45.45	-	45.72	-	73.00	60.00	-27.28	-
5	1.609	0.36	41.14	-	41.50	-	73.00	60.00	-31.50	-
6	18.699	1.43	36.15	-	37.58	-	73.00	60.00	-35.42	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.13 TEST RESULTS (7)

TEST MODE	Mode 7	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.267	0.35	58.12	-	58.47	-	79.00	66.00	-20.53	-
2	0.412	0.36	51.28	-	51.64	-	79.00	66.00	-27.36	-
3	0.658	0.37	51.08	-	51.45	-	73.00	60.00	-21.55	-
4	0.827	0.38	47.40	-	47.78	-	73.00	60.00	-25.22	-
5	1.184	0.41	48.05	-	48.46	-	73.00	60.00	-24.54	-
6	1.961	0.51	47.34	-	47.85	-	73.00	60.00	-25.15	-
7	21.086	1.97	34.07	-	36.04	-	73.00	60.00	-36.96	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 7	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.267	0.24	52.68	-	52.92	-	79.00	66.00	-26.08	-
2	0.408	0.25	48.65	-	48.90	-	79.00	66.00	-30.10	-
3	0.677	0.26	48.42	-	48.68	-	73.00	60.00	-24.32	-
4	0.829	0.27	47.10	-	47.37	-	73.00	60.00	-25.63	-
5	1.230	0.31	47.26	-	47.57	-	73.00	60.00	-25.43	-
6	2.207	0.42	44.78	-	45.20	-	73.00	60.00	-27.80	-
7	16.965	1.28	34.81	-	36.09	-	73.00	60.00	-36.91	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.14 TEST RESULTS (8)

TEST MODE	Mode 8	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.271	0.35	57.19	-	57.54	-	79.00	66.00	-21.46	-
2	0.392	0.36	51.09	-	51.45	-	79.00	66.00	-27.55	-
3	0.666	0.37	49.68	-	50.05	-	73.00	60.00	-22.95	-
4	0.810	0.38	45.96	-	46.34	-	73.00	60.00	-26.66	-
5	1.078	0.40	45.68	-	46.08	-	73.00	60.00	-26.92	-
6	1.602	0.47	45.92	-	46.39	-	73.00	60.00	-26.61	-
7	21.195	1.98	33.94	-	35.92	-	73.00	60.00	-37.08	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 8	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.267	0.24	52.28	-	52.52	-	79.00	66.00	-26.48	-
2	0.400	0.25	47.44	-	47.69	-	79.00	66.00	-31.31	-
3	0.662	0.26	47.90	-	48.16	-	73.00	60.00	-24.84	-
4	1.508	0.35	41.38	-	41.73	-	73.00	60.00	-31.27	-
5	3.598	0.47	39.65	-	40.12	-	73.00	60.00	-32.88	-
6	16.316	1.22	35.09	-	36.31	-	73.00	60.00	-36.69	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.15 TEST RESULTS (9)

TEST MODE	Mode 9	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.257	0.35	58.14	-	58.49	-	79.00	66.00	-20.51	-
2	0.380	0.36	51.36	-	51.72	-	79.00	66.00	-27.28	-
3	0.656	0.37	51.71	-	52.08	-	73.00	60.00	-20.92	-
4	0.787	0.38	48.72	-	49.10	-	73.00	60.00	-23.90	-
5	1.461	0.45	44.17	-	44.62	-	73.00	60.00	-28.38	-
6	2.055	0.52	47.62	-	48.14	-	73.00	60.00	-24.86	-
7	3.355	0.57	43.56	-	44.13	-	73.00	60.00	-28.87	-
8	21.176	1.98	33.22	-	35.20	-	73.00	60.00	-37.80	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 9	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.257	0.24	51.86	-	52.10	-	79.00	66.00	-26.90	-
2	0.384	0.25	48.27	-	48.52	-	79.00	66.00	-30.48	-
3	0.505	0.26	46.61	-	46.87	-	73.00	60.00	-26.13	-
4	0.638	0.26	48.83	-	49.09	-	73.00	60.00	-23.91	-
5	1.043	0.29	47.10	-	47.39	-	73.00	60.00	-25.61	-
6	1.449	0.34	43.87	-	44.21	-	73.00	60.00	-28.79	-
7	2.074	0.41	44.73	-	45.14	-	73.00	60.00	-27.86	-
8	10.906	0.84	38.00	-	38.84	-	73.00	60.00	-34.16	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.16 TEST RESULTS (10)

TEST MODE	Mode 10	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.252	0.35	57.48	-	57.83	-	79.00	66.00	-21.17	-
2	0.391	0.36	50.64	-	51.00	-	79.00	66.00	-28.00	-
3	0.630	0.37	50.57	-	50.94	-	73.00	60.00	-22.06	-
4	1.895	0.51	47.01	-	47.52	-	73.00	60.00	-25.48	-
5	2.523	0.54	40.24	-	40.78	-	73.00	60.00	-32.22	-
6	3.836	0.59	39.24	-	39.83	-	73.00	60.00	-33.17	-
7	21.012	1.97	33.21	-	35.18	-	73.00	60.00	-37.82	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 10	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.259	0.24	52.04	-	52.28	-	79.00	66.00	-26.72	-
2	0.380	0.25	46.92	-	47.17	-	79.00	66.00	-31.83	-
3	0.505	0.26	46.39	-	46.65	-	73.00	60.00	-26.35	-
4	0.658	0.26	48.96	-	49.22	-	73.00	60.00	-23.78	-
5	0.994	0.28	45.01	-	45.29	-	73.00	60.00	-27.71	-
6	1.988	0.41	46.74	-	47.15	-	73.00	60.00	-25.85	-
7	11.305	0.87	38.80	-	39.67	-	73.00	60.00	-33.33	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

4.1.17 TEST RESULTS (11)

TEST MODE	Mode 11	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.281	0.35	58.39	-	58.74	-	79.00	66.00	-20.26	-
2	0.420	0.36	51.99	-	52.35	-	79.00	66.00	-26.65	-
3	0.685	0.37	51.25	-	51.62	-	73.00	60.00	-21.38	-
4	0.845	0.38	48.95	-	49.33	-	73.00	60.00	-23.67	-
5	1.270	0.43	49.36	-	49.79	-	73.00	60.00	-23.21	-
6	1.715	0.48	46.97	-	47.45	-	73.00	60.00	-25.55	-
7	2.156	0.53	48.24	-	48.77	-	73.00	60.00	-24.23	-
8	2.609	0.54	47.30	-	47.84	-	73.00	60.00	-25.16	-
9	18.648	1.74	31.29	-	33.03	-	73.00	60.00	-39.97	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 11	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.275	0.24	53.26	-	53.50	-	79.00	66.00	-25.50	-
2	0.545	0.26	52.13	-	52.39	-	73.00	60.00	-20.61	-
3	0.689	0.26	50.09	-	50.35	-	73.00	60.00	-22.65	-
4	1.086	0.29	46.04	-	46.33	-	73.00	60.00	-26.67	-
5	1.590	0.36	48.83	-	49.19	-	73.00	60.00	-23.81	-
6	2.133	0.42	45.00	-	45.42	-	73.00	60.00	-27.58	-
7	11.934	0.91	32.22	-	33.13	-	73.00	60.00	-39.87	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.




4.1.18 TEST RESULTS (12)

TEST MODE	Mode 12	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Line (L)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
			Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.271	0.35	56.40	-	56.75	-	79.00	66.00	-22.25	-
2	0.404	0.36	49.35	-	49.71	-	79.00	66.00	-29.29	-
3	0.677	0.37	48.48	-	48.85	-	73.00	60.00	-24.15	-
4	1.215	0.42	43.92	-	44.34	-	73.00	60.00	-28.66	-
5	1.555	0.46	45.82	-	46.28	-	73.00	60.00	-26.72	-
6	2.105	0.52	49.24	-	49.76	-	73.00	60.00	-23.24	-
7	3.941	0.60	42.20	-	42.80	-	73.00	60.00	-30.20	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.






A D T

TEST MODE	Mode 12	6dB BANDWIDTH	9 kHz
INPUT POWER	230Vac, 50 Hz	PHASE	Neutral (N)
ENVIRONMENTAL CONDITIONS	20deg. C, 79% RH, 1018 hPa	TESTED BY: John Liao	

No	Freq. [MHz]	Corr. Factor (dB)	Reading Value		Emission Level		Limit		Margin	
			[dB (uV)]		[dB (uV)]		[dB (uV)]		(dB)	
	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.	Q.P.	AV.
1	0.271	0.24	55.40	-	55.64	-	79.00	66.00	-23.36	-
2	0.412	0.25	49.72	-	49.97	-	79.00	66.00	-29.03	-
3	0.556	0.26	49.83	-	50.09	-	73.00	60.00	-22.91	-
4	0.709	0.27	51.52	-	51.79	-	73.00	60.00	-21.21	-
5	1.070	0.29	47.78	-	48.07	-	73.00	60.00	-24.93	-
6	2.035	0.41	45.49	-	45.90	-	73.00	60.00	-27.10	-
7	20.266	1.54	31.10	-	32.64	-	73.00	60.00	-40.36	-

- REMARKS:**
1. Q.P. and AV. are abbreviations of quasi-peak and average individually.
 2. "-": The Quasi-peak reading value also meets average limit and measurement with the average detector is unnecessary.
 3. The emission levels of other frequencies were very low against the limit.
 4. Margin value = Emission level - Limit value
 5. Correction factor = Insertion loss + Cable loss
 6. Emission Level = Correction Factor + Reading Value.



4.2 RADIATED EMISSION MEASUREMENT

4.2.1 LIMITS OF RADIATED EMISSION MEASUREMENT

TEST STANDARD: EN 61000-6-4

FREQUENCY (MHz)	Quasi-peak dB(uV/m) at 10 m
30 – 230	40
230 – 1000	47

- NOTE:** (1) The lower limit shall apply at the transition frequencies.
- (2) If the internal emission source(s) is operating at a frequency below 9kHz then measurements shall only be performed up to 230MHz.

TEST STANDARD: EN 55011

FREQUENCY (MHz)	Group 1	
	Class A (at 10m)	Class B (at 10m)
	dBuV/m	dBuV/m
30 – 230	40	30
230 - 1000	47	37

- NOTE:** (1) The lower limit shall apply at the transition frequencies.
- (2) Emission level (dBuV/m) = 20 log Emission level (uV/m).
- (3) All emanations from a class A/B digital device or system, including any network of conductors and apparatus connected thereto, shall not exceed the level of field strengths specified above.

4.2.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
ROHDE & SCHWARZ TEST RECEIVER	ESVS 10	840241/010	Sep. 04, 2008	Sep. 03, 2009
Schaffner BILOG Antenna	CBL6111C	2728	Apr. 25, 2008	Apr. 24, 2009
CT Turn Table	TT100	CT-080	NA	NA
CT Tower	AT100	CT-080	NA	NA
Software	ADT_Radiated_V7.6.15.9.2	NA	NA	NA
ANRITSU RF Switches	MP59B	6100259081	Sep. 16, 2008	Sep. 15, 2009
WOKEN RF cable	8D	CABLE-ST3-01	Sep. 17, 2008	Sep. 16, 2009

- NOTE:**
1. The calibration interval of the above test instruments is 12 months. And the calibrations are traceable to NML/ROC and NIST/USA.
 2. The test was performed in Open Site No. 3.
 3. The VCCI Site Registration No. is R-269.
 4. The FCC Site Registration No. 90424.

4.2.3 TEST PROCEDURE


- a. The EUT was placed on the top of a rotating table 0.8 meters above the ground at a 10 meter open area test site. The table was rotated 360 degrees to determine the position of the highest radiation.
- b. The EUT was set 10 meters away from the interference-receiving antenna, which was mounted on the top of a variable-height antenna tower.
- c. The height of antenna is varied from one meter to four meters above the ground to determine the maximum value of the field strength. Both horizontal and vertical polarizations of the antenna are set to make the measurement.
- d. For each suspected emission, the EUT was arranged to its worst case and then the antenna was tuned to heights from 1 meter to 4 meters and the rotatable table was turned from 0 degrees to 360 degrees to find the maximum reading.
- e. The test-receiver system was set to quasi-peak detect function and specified bandwidth with maximum hold mode when the test frequency is below 1 GHz.

- NOTE:** The resolution bandwidth of test receiver/spectrum analyzer is 120kHz for Quasi-peak detection (QP) at frequency below 1GHz.

4.2.4 DEVIATION FROM TEST STANDARD

No deviation

4.2.5 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

4.2.6 EUT OPERATING CONDITIONS

Same as item 4.1.6.



A D T


4.2.7 TEST RESULTS (1)

TEST MODE	Mode 1	FREQUENCY RANGE	30-1000 MHz
INPUT POWER	230Vac, 50 Hz	DETECTOR FUNCTION & BANDWIDTH	Quasi-Peak, 120kHz
ENVIRONMENTAL CONDITIONS	19deg. C, 75% RH, 1015 hPa	TESTED BY: Ty Lai	

ANTENNA POLARITY & TEST DISTANCE: HORIZONTAL AT 10 M

No.	Freq. (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	65.31	20.36 QP	40.00	-19.64	4.00 H	144	12.78	7.58
2	127.09	18.36 QP	40.00	-21.64	4.00 H	82	4.86	13.50
3	194.94	19.36 QP	40.00	-20.64	4.00 H	269	8.38	10.98
4	220.02	23.00 QP	40.00	-17.00	4.00 H	346	10.18	12.82
5	225.32	26.46 QP	40.00	-13.54	4.00 H	316	13.15	13.31
6	295.55	23.59 QP	47.00	-23.41	4.00 H	106	7.10	16.49

- REMARKS:**
1. Emission level(dBuV/m)=Raw Value(dBuV) + Correction Factor(dB/m)
 2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
 3. The other emission levels were very low against the limit.
 4. Margin value = Emission level – Limit value.






A D T

TEST MODE	Mode 1	FREQUENCY RANGE	30-1000 MHz
INPUT POWER	230Vac, 50 Hz	DETECTOR FUNCTION & BANDWIDTH	Quasi-Peak, 120kHz
ENVIRONMENTAL CONDITIONS	19deg. C, 75% RH, 1015 hPa	TESTED BY: Ty Lai	

ANTENNA POLARITY & TEST DISTANCE: VERTICAL AT 10 M

No.	Freq. (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	51.63	29.35 QP	40.00	-10.65	1.00 V	19	20.23	9.12
2	59.15	28.43 QP	40.00	-11.57	1.00 V	173	21.22	7.21
3	61.88	26.24 QP	40.00	-13.76	1.00 V	262	19.04	7.20
4	138.77	25.18 QP	40.00	-14.82	1.00 V	111	11.72	13.46
5	150.00	25.46 QP	40.00	-14.54	1.45 V	355	12.65	12.81
6	223.80	25.32 QP	40.00	-14.68	1.44 V	106	12.15	13.17

- REMARKS:**
1. Emission level(dBuV/m)=Raw Value(dBuV) + Correction Factor(dB/m)
 2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
 3. The other emission levels were very low against the limit.
 4. Margin value = Emission level – Limit value.





A D T


4.2.8 TEST RESULTS (2)

TEST MODE	Mode 2	FREQUENCY RANGE	30-1000 MHz
INPUT POWER	230Vac, 50 Hz	DETECTOR FUNCTION & BANDWIDTH	Quasi-Peak, 120kHz
ENVIRONMENTAL CONDITIONS	19deg. C, 75% RH, 1015 hPa	TESTED BY: Ty Lai	

ANTENNA POLARITY & TEST DISTANCE: HORIZONTAL AT 10 M

No.	Freq. (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	50.19	20.36 QP	40.00	-19.64	4.00 H	25	10.87	9.49
2	70.33	18.16 QP	40.00	-21.84	4.00 H	210	10.03	8.13
3	126.17	19.57 QP	40.00	-20.43	4.00 H	236	6.07	13.50
4	194.48	17.69 QP	40.00	-22.31	4.00 H	151	6.71	10.98
5	231.31	23.14 QP	47.00	-23.86	4.00 H	134	9.28	13.86
6	260.02	22.97 QP	47.00	-24.03	4.00 H	319	7.22	15.75

- REMARKS:**
1. Emission level(dBuV/m)=Raw Value(dBuV) + Correction Factor(dB/m)
 2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
 3. The other emission levels were very low against the limit.
 4. Margin value = Emission level – Limit value.






A D T

TEST MODE	Mode 2	FREQUENCY RANGE	30-1000 MHz
INPUT POWER	230Vac, 50 Hz	DETECTOR FUNCTION & BANDWIDTH	Quasi-Peak, 120kHz
ENVIRONMENTAL CONDITIONS	19deg. C, 75% RH, 1015 hPa	TESTED BY: Ty Lai	

ANTENNA POLARITY & TEST DISTANCE: VERTICAL AT 10 M

No.	Freq. (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	51.01	28.83 QP	40.00	-11.17	1.27 V	234	19.55	9.28
2	55.73	26.56 QP	40.00	-13.44	1.00 V	350	18.48	8.08
3	58.48	23.95 QP	40.00	-16.05	1.00 V	289	16.57	7.38
4	69.03	20.46 QP	40.00	-19.54	1.00 V	53	12.47	7.99
5	150.78	22.46 QP	40.00	-17.54	1.36 V	202	9.67	12.79
6	299.36	23.93 QP	47.00	-23.07	1.00 V	137	7.35	16.58

- REMARKS:**
1. Emission level(dBuV/m)=Raw Value(dBuV) + Correction Factor(dB/m)
 2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
 3. The other emission levels were very low against the limit.
 4. Margin value = Emission level – Limit value.





A D T


4.2.9 TEST RESULTS (3)

TEST MODE	Mode 3	FREQUENCY RANGE	30-1000 MHz
INPUT POWER	230Vac, 50 Hz	DETECTOR FUNCTION & BANDWIDTH	Quasi-Peak, 120kHz
ENVIRONMENTAL CONDITIONS	19deg. C, 75% RH, 1015 hPa	TESTED BY: Ty Lai	

ANTENNA POLARITY & TEST DISTANCE: HORIZONTAL AT 10 M

No.	Freq. (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	52.28	17.13 QP	40.00	-22.87	4.00 H	267	8.17	8.96
2	69.76	18.01 QP	40.00	-21.99	4.00 H	87	9.94	8.07
3	127.78	20.13 QP	40.00	-19.87	4.00 H	324	6.63	13.50
4	170.33	17.21 QP	40.00	-22.79	4.00 H	169	5.39	11.82
5	228.37	23.69 QP	40.00	-16.31	4.00 H	272	10.10	13.59
6	297.51	25.74 QP	47.00	-21.26	4.00 H	207	9.20	16.54

- REMARKS:**
1. Emission level(dBuV/m)=Raw Value(dBuV) + Correction Factor(dB/m)
 2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
 3. The other emission levels were very low against the limit.
 4. Margin value = Emission level – Limit value.






A D T

TEST MODE	Mode 3	FREQUENCY RANGE	30-1000 MHz
INPUT POWER	230Vac, 50 Hz	DETECTOR FUNCTION & BANDWIDTH	Quasi-Peak, 120kHz
ENVIRONMENTAL CONDITIONS	19deg. C, 75% RH, 1015 hP	TESTED BY: Ty Lai	

ANTENNA POLARITY & TEST DISTANCE: VERTICAL AT 10 M

No.	Freq. (MHz)	Emission Level (dBuV/m)	Limit (dBuV/m)	Margin (dB)	Antenna Height (m)	Table Angle (Degree)	Raw Value (dBuV)	Correction Factor (dB/m)
1	51.23	29.47 QP	40.00	-10.53	1.00 V	288	20.24	9.23
2	54.05	27.35 QP	40.00	-12.65	1.00 V	292	18.84	8.51
3	56.08	28.24 QP	40.00	-11.76	1.00 V	163	20.25	7.99
4	70.43	21.92 QP	40.00	-18.08	1.22 V	161	13.78	8.14
5	139.05	21.41 QP	40.00	-18.59	1.55 V	332	7.95	13.46
6	299.84	24.95 QP	47.00	-22.05	1.00 V	276	8.36	16.59

- REMARKS:**
1. Emission level(dBuV/m)=Raw Value(dBuV) + Correction Factor(dB/m)
 2. Correction Factor(dB/m) = Antenna Factor (dB/m) + Cable Factor (dB)
 3. The other emission levels were very low against the limit.
 4. Margin value = Emission level – Limit value.



4.3 HARMONICS CURRENT MEASUREMENT

4.3.1 LIMITS OF HARMONICS CURRENT MEASUREMENT

TEST STANDARD: EN 61000-3-2

Limits for Class A equipment	
Harmonics Order n	Max. permissible harmonics current A
Odd harmonics	
3	2.30
5	1.14
7	0.77
9	0.40
11	0.33
13	0.21
15<=n<=39	0.15x15/n
Even harmonics	
2	1.08
4	0.43
6	0.30
8<=n<=40	0.23x8/n

Limits for Class D equipment		
Harmonics Order n	Max. permissible harmonics current per watt mAW	Max. permissible harmonics current A
Odd Harmonics only		
3	3.4	2.30
5	1.9	1.14
7	1.0	0.77
9	0.5	0.40
11	0.35	0.33
13	0.30	0.21
15<=n<=39	3.85/n	0.15x15/n

- NOTE:** 1. Class A and Class D are classified according to section 5 of EN 61000-3-2: 2006.
2. According to section 7 of EN 61000-3-2: 2006, the above limits for all equipment except for lighting equipment are for all applications having an active input power > 75 W and no limits apply for equipment with an active input power up to and including 75 W.

4.3.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
EMC PARTNER EMC Emission Tester	H1000	078	Sep. 03, 2008	Sep. 02, 2009
Software	HARCS	NA	NA	NA

- NOTE:** 1. The test was performed in EMS Room No. 2.
2. The calibration interval of the above test instruments is 24 months and the calibrations are traceable to NML/ROC and NIST/USA.


4.3.3 TEST PROCEDURE

- a. The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the maximum harmonic components under normal operating conditions for each successive harmonic component in turn.
- b. The classification of EUT is according to section 5 of EN 61000-3-2: 2006.
The EUT is classified as follows:
 - Class A: Balanced three-phase equipment, Household appliances excluding equipment as Class D, Tools excluding portable tools, Dimmers for incandescent lamps, audio equipment, equipment not specified in one of the three other classes.
 - Class B: Portable tools. ; Arc welding equipment which is not professional equipment
 - Class C: Lighting equipment.
 - Class D: Equipment having a specified power less than or equal to 600 W of the following types: Personal computers and personal computer monitors and television receivers.
- c. The correspondent test program of test instrument to measure the current harmonics emanated from EUT is chosen. The measure time shall be not less than the time necessary for the EUT to be exercised.

4.3.4 DEVIATION FROM TEST STANDARD

No deviation

4.3.5 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

4.3.6 EUT OPERATING CONDITIONS

Connected a resistor loads to DC output port of EUT to make EUT have maximum power consumption.



A D T

4.3.7 TEST RESULTS (1)

TEST MODE	Mode 1		
FUNDAMENTAL VOLTAGE/AMPERE	229.7Vrms/ 0.667Arms	POWER FREQUENCY	50.013Hz
POWER CONSUMPTION	73.26W	POWER FACTOR	0.478
ENVIRONMENTAL CONDITIONS	21deg. C, 75% RH, 1020hPa	TESTED BY: Andy Cheng	

NOTE: Limits are not specified for equipment with a rated power of 75W or less (other than lighting equipment).

4.3.8 TEST RESULTS (2)

TEST MODE	Mode 2		
FUNDAMENTAL VOLTAGE/AMPERE	229.7Vrms/ 0.669Arms	POWER FREQUENCY	50.013Hz
POWER CONSUMPTION	70.68W	POWER FACTOR	0.460
ENVIRONMENTAL CONDITIONS	21deg. C, 73% RH, 1020hPa	TESTED BY: Andy Cheng	

NOTE: Limits are not specified for equipment with a rated power of 75W or less (other than lighting equipment).

4.3.9 TEST RESULTS (3)

TEST MODE	Mode 3		
FUNDAMENTAL VOLTAGE/AMPERE	229.7Vrms/ 0.659Arms	POWER FREQUENCY	50.013Hz
POWER CONSUMPTION	69.82W	POWER FACTOR	0.461
ENVIRONMENTAL CONDITIONS	21deg. C, 73% RH, 1020hPa	TESTED BY: Andy Cheng	

NOTE: Limits are not specified for equipment with a rated power of 75W or less (other than lighting equipment).

4.4 VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT

4.4.1 LIMITS OF VOLTAGE FLUCTUATION AND FLICKS MEASUREMENT

TEST STANDARD: EN 61000-3-3

TEST ITEM	LIMIT	NOTE
P_{st}	1.0	P_{st} means short-term flicker indicator.
P_{lt}	0.65	P_{lt} means long-term flicker indicator.
$d(t)$ (%)	3.3%	$d(t)$ means maximum time that not exceeds 500 ms.
d_{max} (%)	4%	d_{max} means maximum relative voltage change.
dc (%)	3.3%	dc means relative steady-state voltage change

4.4.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
EMC PARTNER EMC Emission Tester	H1000	078	Sep. 03, 2008	Sep. 02, 2009
Software	HARCS	NA	NA	NA

NOTE: 1. The test was performed in EMS Room No. 2.
2. The calibration interval of the above test instruments is 24 months and the calibrations are traceable to NML/ROC and NIST/USA.


4.4.3 TEST PROCEDURE

- a. The EUT was placed on the top of a wooden table 0.8 meters above the ground and operated to produce the most unfavorable sequence of voltage changes under normal operating conditions.
- b. During the flick measurement, the measure time shall include that part of whole operation cycle in which the EUT produce the most unfavorable sequence of voltage changes. The observation period for short-term flicker indicator is 10 minutes and the observation period for long-term flicker indicator is 2 hours.

4.4.4 DEVIATION FROM TEST STANDARD

No deviation

4.4.5 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

4.4.6 EUT OPERATING CONDITIONS

Same as item 4.3.6

4.4.7 TEST RESULTS (1)

TEST MODE	Mode 1		
FUNDAMENTAL VOLTAGE/AMPERE	229.7Vrms/ 0.640Arms	POWER FREQUENCY	50.000Hz
OBSERVATOPM PERIOD (Tp)	10 min	POWER FACTOR	0.489
ENVIRONMENTAL CONDITIONS	21deg. C, 75% RH, 1020hPa	TESTED BY: Andy Cheng	

TEST PARAMETER	MEASUREMENT VALUE	LIMIT	REMARKS
P _{st}	0.072	1.0	Pass
P _{lt}	0.072	0.65	Pass
d(t) (%)	0	3.3	Pass
d _{max} (%)	0	4	Pass
dc (%)	0.020	3.3	Pass

- NOTE:**
- (1) P_{st} means short-term flicker indicator.
 - (2) P_{lt} means long-term flicker indicator.
 - (3) d(t) means maximum time that not exceeds 500ms.
 - (4) d_{max} means maximum relative voltage change.
 - (5) dc means relative steady-state voltage change.



A D T

4.4.8 TEST RESULTS (2)

TEST MODE	Mode 2		
FUNDAMENTAL VOLTAGE/AMPERE	229.7Vrms/ 0.645Arms	POWER FREQUENCY	50.013Hz
OBSERVATOPM PERIOD (Tp)	10 min	POWER FACTOR	0.482
ENVIRONMENTAL CONDITIONS	21deg. C, 73% RH, 1020hPa	TESTED BY: Andy Cheng	

TEST PARAMETER	MEASUREMENT VALUE	LIMIT	REMARKS
P _{st}	0.072	1.0	Pass
P _{lt}	0.072	0.65	Pass
d(t) (%)	0	3.3	Pass
d _{max} (%)	0.030	4	Pass
dc (%)	0.010	3.3	Pass

- NOTE:**
- (1) P_{st} means short-term flicker indicator.
 - (2) P_{lt} means long-term flicker indicator.
 - (3) d(t) means maximum time that not exceeds 500ms.
 - (4) d_{max} means maximum relative voltage change.
 - (5) dc means relative steady-state voltage change.

4.4.9 TEST RESULTS (3)

TEST MODE	Mode 3		
FUNDAMENTAL VOLTAGE/AMPERE	229.7Vrms/ 0.635Arms	POWER FREQUENCY	50.000Hz
OBSERVATOPM PERIOD (Tp)	10 min	POWER FACTOR	0.480
ENVIRONMENTAL CONDITIONS	21deg. C, 73% RH, 1020hPa	TESTED BY: Andy Cheng	

TEST PARAMETER	MEASUREMENT VALUE	LIMIT	REMARKS
P _{st}	0.072	1.0	Pass
P _{lt}	0.072	0.65	Pass
d(t) (%)	0	3.3	Pass
d _{max} (%)	0	4	Pass
dc (%)	0.010	3.3	Pass

- NOTE:**
- (1) P_{st} means short-term flicker indicator.
 - (2) P_{lt} means long-term flicker indicator.
 - (3) d(t) means maximum time that not exceeds 500ms.
 - (4) d_{max} means maximum relative voltage change.
 - (5) dc means relative steady-state voltage change.

5 IMMUNITY TEST

5.1 GENERAL DESCRIPTION

Generic Standard:	EN 61000-6-2: 2005	
Basic Standard, specification requirement, and Performance Criteria:	IEC 61000-4-2	Electrostatic Discharge – ESD: 8kV air discharge, 4kV Contact discharge, Performance Criterion B
	IEC 61000-4-3	Radio-Frequency Electromagnetic Field Susceptibility Test – RS: 80-1000 MHz, 10V/m, 80% AM (1kHz), 1.4-2.0 GHz, 3V/m, 80% AM (1kHz), 2.0-2.7 GHz, 1V/m, 80% AM (1kHz), Performance Criterion A
	IEC 61000-4-4	Electrical Fast Transient/Burst - EFT, AC Power line : 2kV, Signal line : 1kV, DC Power line : 2kV, Performance Criterion B
	IEC 61000-4-5	Surge Immunity Test: 1.2/50 us Open Circuit Voltage, 8/20 us Short Circuit Current, AC Power Line : line to line : 1 kV, line to earth : 2kV DC Power Line : line to line : 0.5kV, line to earth : 0.5kV Performance Criterion B
	IEC 61000-4-6	Conducted Radio Frequency Disturbances Test – CS: 0.15-80 MHz, 10Vrms, 80% AM, 1kHz, Performance Criterion A
	IEC 61000-4-8	Power Frequency Magnetic Field Test, 50 Hz, 30A/m, 60 Hz, 30 A/m, Performance Criterion A
	IEC 61000-4-11	Voltage Dips: i) 0% residual -1 period, Performance Criterion B ii) 40% residual – 10, 12 period, Performance Criterion C iii) 70% residual – 25, 30 period, Performance Criterion C Voltage Interruptions: i) 0% residual – 250, 300 period, Performance Criterion C

5.2 GENERAL PERFORMANCE CRITERIA DESCRIPTION

CRITERION A	The equipment shall continue to operate as intended during the test. No degradation of performance or loss of function is allowed below a performance level (or permissible loss of performance) specified by the client/customer, when the equipment is used as intended. If the minimum performance level or the permissible performance loss is not specified by the client/customer, then either of these may be derived from the product description and documentation, or from what the user may reasonably expect from the apparatus is used as intended.
CRITERION B	The equipment shall continue to operate as intended after the test. No degradation of performance or loss of function is allowed below a performance level (or permissible loss of performance) specified by the client/customer, when the equipment is used as intended. During the test, degradation of performance is allowed, however, no change of actual; operating state or stored data is allowed. If the minimum performance level or the permissible performance loss is not specified by the client/customer, then either of these may be derived from the product description and documentation, or from what the user may reasonably expect from the equipment if used as intended.
CRITERION C	Temporary loss of function is allowed, provided the function is self-recoverable or can be restored by the operation of the controls, or by any operation specified in the instructions for use.

5.3 EUT OPERATING CONDITION

Connected a resistor load to DC output port of EUT to make EUT have maximum power consumption and a multimeter was used to monitor voltage of output.

5.4 ELECTROSTATIC DISCHARGE IMMUNITY TEST (ESD)

5.4.1 TEST SPECIFICATION

Basic Standard:	IEC 61000-4-2
Discharge Impedance:	330 ohm / 150 pF
Discharge Voltage:	Air Discharge: 2kV/ 4kV/ 8kV (Direct) Contact Discharge: 2kV/ 4kV (Indirect / Direct)
Polarity:	Positive & Negative
Number of Discharge:	Air Discharge: min. 20 times at each test point Contact Discharge: min. 200 times in total
Discharge Mode:	Single Discharge
Discharge Period:	1 second minimum

5.4.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
EM Test ESD Simulator	ESD 30C	1101-18	Jun. 16, 2008	Jun. 15, 2009
EM Test ESD Discharge Unit	P30C	1101-18	Jun. 16, 2008	Jun. 15, 2009
EM Test ESD Discharge Unit	P30C-RFCI	1101-181	Jun. 16, 2008	Jun. 15, 2009

- NOTE:** 1. The test was performed in ESD Room No. 2.
2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

5.4.3 TEST PROCEDURE

The discharges shall be applied in two ways:

- a. Contact discharges to the conductive surfaces and coupling planes:

The EUT shall be exposed to at least 200 discharges, 100 each at negative and positive polarity, at a minimum of four test points. One of the test points shall be subjected to at least 50 indirect discharges to the center of the front edge of the horizontal coupling plane. The remaining three test points shall each receive at least 50 direct contact discharges. If no direct contact test points are available, then at least 200 indirect discharges shall be applied in the indirect mode. Test shall be performed at a maximum repetition rate of one discharge per second.

b. Air discharges at slots and apertures and insulating surfaces:

On those parts of the EUT where it is not possible to perform contact discharge testing, the equipment should be investigated to identify user accessible points where breakdown may occur. Such points are tested using the air discharge method. This investigation should be restricted to those area normally handled by the user. A minimum of 10 single air discharges shall be applied to the selected test point for each such area.


The basic test procedure was in accordance with IEC 61000-4-2:

- a. Electrostatic discharges were applied only to those points and surfaces of the EUT that are accessible to users during normal operation.
- b. The test was performed with at least ten single discharges on the pre-selected points in the most sensitive polarity.
- c. The time interval between two successive single discharges was at least 1 second.
- d. The ESD generator was held perpendicularly to the surface to which the discharge was applied and the return cable was at least 0.2 meters from the EUT.
- e. Contact discharges were applied to the non-insulating coating, with the pointed tip of the generator penetrating the coating and contacting the conducting substrate.
- f. Air discharges were applied with the round discharge tip of the discharge electrode approaching the EUT as fast as possible (without causing mechanical damage) to touch the EUT. After each discharge, the ESD generator was removed from the EUT and re-triggered for a new single discharge. The test was repeated until all discharges were complete.
- g. At least ten single discharges (in the most sensitive polarity) were applied to the **Horizontal Coupling Plane** at points on each side of the EUT. The ESD generator was positioned vertically at a distance of 0.1 meters from the EUT with the discharge electrode touching the **HCP**.
- h. At least ten single discharges (in the most sensitive polarity) were applied to the center of one vertical edge of the **Vertical Coupling Plane** in sufficiently different positions that the four faces of the EUT were completely illuminated. The **VCP** (dimensions 0.5m x 0.5m) was placed vertically to and 0.1 meters from the EUT.

5.4.4 DEVIATION FROM TEST STANDARD

No deviation

5.4.5 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

TABLE-TOP EQUIPMENT

The configuration consisted of a wooden table 0.8 meters high standing on the **Ground Reference Plane**. The **GRP** consisted of a sheet of aluminum at least 0.25mm thick, and 2.5 meters square connected to the protective grounding system. A **Horizontal Coupling Plane** (1.6m x 0.8m) was placed on the table and attached to the **GRP** by means of a cable with 940kΩ total impedance. The equipment under test, was installed in a representative system as described in section 7 of IEC 61000-4-2, and its cables were placed on the **HCP** and isolated by an insulating support of 0.5mm thickness. A distance of 1-meter minimum was provided between the EUT and the walls of the laboratory and any other metallic structure.

FLOOR-STANDING EQUIPMENT

The equipment under test was installed in a representative system as described in section 7 of IEC 61000-4-2, and its cables were isolated from the Ground Reference Plane by an insulating support of 0.1-meter thickness. The GRP consisted of a sheet of aluminum that is at least 0.25mm thick, and 2.5 meters square connected to the protective grounding system and extended at least 0.5 meters from the EUT on all sides.



A D T

5.4.6 TEST RESULTS

TEST MODE	Mode 1 ~ 3	INPUT POWER	230Vac, 50 Hz
ENVIRONMENTAL CONDITIONS	24 deg. C, 48% RH, 1019 hPa	TESTED BY: Andy Cheng	

TEST RESULTS OF DIRECT APPLICATION					
Discharge Level (kV)	Polarity (+/-)	Test Point	Contact Discharge	Air Discharge	Performance Criterion
2, 4	+/-	1, 2	Note	N/A	A
2, 4, 8	+/-	3	N/A	Note	A

Description of test point: Please refer to ESD test photo for representative mark only.

TEST RESULTS OF INDIRECT APPLICATION					
Discharge Level (kV)	Polarity (+/-)	Test Point	Horizontal Coupling Plane	Vertical Coupling Plane	Performance Criterion
2, 4	+/-	1 ~ 4	Note	Note	A

Description of test point:

1. Left side
2. Right side
3. Front side
4. Rear side

NOTE: There was no change compared with initial operation during the test.

5.4.7 RADIATED, RADIO-FREQUENCY, ELECTROMAGNETIC FIELD IMMUNITY TEST (RS)

5.4.8 TEST SPECIFICATION

Basic Standard:	IEC 61000-4-3
Frequency Range:	80-1000MHz, 1400-2000MHz, 2000-2700MHz
Field Strength:	10 V/m, 3 V/m, 1 V/m
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of fundamental
Polarity of Antenna:	Horizontal and Vertical
Antenna Height:	1.5m
Dwell Time:	3 seconds

5.4.9 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
R&S Signal Generator	SML03	101074	Nov. 04, 2008	Nov. 03, 2009
AR RF Amplifier	60S1G3	304334	NA	NA
BOONTON RF Meter	4232A	94901	Jun. 05, 2008	Jun. 04, 2009
BOONTON Power Sensor	51011-EMC	32832	Jun. 05, 2008	Jun. 04, 2009
BOONTON Power Sensor	51011-EMC	32807	Jun. 05, 2008	Jun. 04, 2009
FRANKONIA Power Amplifier	FLH 100	0042	NA	NA
Dell Antenna	NA	NA	NA	NA
HP-IB Extender	37204	3212U26684	NA	NA
ADVANTEST Spectrum Analyzer	R3261C	81720152	NA	NA
COMTEST Compact Full Anechoic Chamber (7x3x3 m)	CFAC	RS-001	Oct. 21, 2008	Oct. 20, 2009
Software	ADT_RS_V7.6	NA	NA	NA

- NOTE:**
1. The test was performed in RS Room No.1.
 2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.
 3. The transmit antenna was located at a distance of 3 meters from the EUT.

5.4.10 TEST PROCEDURE


The test procedure was in accordance with IEC 61000-4-3

- a. The testing was performed in a fully-anechoic chamber.
- b. The frequency range is swept from 80 MHz to 1000 MHz, 1400 MHz to 2000 MHz, 2000MHz to 2700MHz with the signal 80% amplitude modulated with a 1kHz sine wave.
- c. The dwell time at each frequency shall not be less than the time necessary for the EUT to be exercised and to respond, but shall in no case be less than 0,5s.
- d. The field strength levels were 10V/m, 3V/m, 1V/m.
- e. The test was performed with the EUT exposed to both vertically and horizontally polarized fields on each of the four sides.

5.4.11 DEVIATION FROM TEST STANDARD

No deviation

5.4.12 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

TABLETOP EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-3 was placed on a non-conductive table 0.8 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.

FLOOR STANDING EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-3 was placed on a non-conductive wood support 0.1 meters in height. The system under test was connected to the power and signal wire according to relevant installation instructions.



A D T

5.4.13 TEST RESULTS

TEST MODE	Mode 1 ~ 3	INPUT POWER	230Vac, 50 Hz
ENVIRONMENTAL CONDITIONS	25deg. C, 82% RH, 1007 hPa	TESTED BY: Andy Cheng	

Frequency (MHz)	Polarity	Azimuth	Field Strength (V/m)	Observation	Performance Criterion
80 -1000	V&H	0, 90, 180, 270	10	Note	A
1400 -2000	V&H	0, 90, 180, 270	3	Note	A
2000 -2700	V&H	0, 90, 180, 270	1	Note	A

NOTE: There was no change compared with initial operation during the test.



A D T

5.5 ELECTRICAL FAST TRANSIENT/BURST IMMUNITY TEST (EFT)

5.5.1 TEST SPECIFICATION

Basic Standard:	IEC 61000-4-4
Test Voltage:	Power Line: 2kV Signal/Control Line: N/A
Polarity:	Positive & Negative
Impulse Frequency:	5 kHz
Impulse Waveshape :	5/50 ns
Burst Duration:	15 ms
Burst Period:	300 ms
Test Duration:	than 1 min.

5.5.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
KeyTek, EFT Generator	EMC Pro	9902207	Feb. 16, 2009	Feb. 15, 2010
KeyTek, Capacitive Clamp	CE-40-CCL	9508259	NA	NA
EFT Cable	WE-4	EF1Cab-001	NA	NA
EFT Adapter WONPRO	WA-9	EF1ADA-002	NA	NA
Software	CEWAVE32	NA	NA	NA

- NOTE:** 1. The test was performed in EMS Room No. 2.
2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.


5.5.3 TEST PROCEDURE

- Both positive and negative polarity discharges were applied.
- The length of the “hot wire” from the coaxial output of the EFT generator to the terminals on the EUT should not exceed 0.5 meter \pm 0.05 meter.
- The duration time of each test sequential was 1 minute.
- The transient/burst waveform was in accordance with IEC 61000-4-4, 5/50ns.

5.5.4 DEVIATION FROM TEST STANDARD

No deviation

5.5.5 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE: **TABLETOP EQUIPMENT**

The configuration consisted of a wooden table standing on the Ground Reference Plane and should be located 0.1m +/- 0.01m above the Ground Reference Plane. The GRP consisted of a sheet of aluminum (at least 0.25mm thick and 2.5m square) connected to the protective grounding system. A minimum distance of 0.5m was provided between the EUT and the walls of the laboratory or any other metallic structure.

FLOOR STANDING EQUIPMENT

The EUT installed in a representative system as described in section 7 of IEC 61000-4-4 and its cables, were isolated from the Ground Reference Plane by an insulating support that is 0.1-meter thick. The GRP consisted of a sheet of aluminum (at least 0.25mm thick and 2.5m square) connected to the protective grounding system.



5.5.6 TEST RESULTS (1)

TEST MODE	Mode 1	INPUT POWER	230Vac, 50Hz
ENVIRONMENTAL CONDITIONS	21 deg. C, 65 % RH, 1019 hPa	TESTED BY: Andy Cheng	

Test Point	Polarity	Test Level (kV)	Observation	Performance Criterion
L1	+/-	2	Note	B
L2	+/-	2	Note	B
L1-L2	+/-	2	Note	B

NOTE: The voltage (11.91V) of EUT changed to 11.91V ~ 12.07V during the test, but self-recoverable after the test.

5.5.7 TEST RESULTS (2)

TEST MODE	Mode 2	INPUT POWER	230Vac, 50Hz
ENVIRONMENTAL CONDITIONS	21 deg. C, 65 % RH, 1019 hPa	TESTED BY: Andy Cheng	

Test Point	Polarity	Test Level (kV)	Observation	Performance Criterion
L1	+/-	2	Note	B
L2	+/-	2	Note	B
L1-L2	+/-	2	Note	B

NOTE: The voltage (14.84V) of EUT changed to 14.84V ~ 15.02V during the test, but self-recoverable after the test.

5.5.8 TEST RESULTS (3)

TEST MODE	Mode 3	INPUT POWER	230Vac, 50Hz
ENVIRONMENTAL CONDITIONS	21 deg. C, 65 % RH, 1019 hPa	TESTED BY: Andy Cheng	

Test Point	Polarity	Test Level (kV)	Observation	Performance Criterion
L1	+/-	2	Note	B
L2	+/-	2	Note	B
L1-L2	+/-	2	Note	B

NOTE: The voltage (23.54V) of EUT changed to 23.47V ~ 23.71V during the test, but self-recoverable after the test.

5.6 SURGE IMMUNITY TEST

5.6.1 TEST SPECIFICATION

Basic Standard:	IEC 61000-4-5
Wave-Shape:	Combination Wave 1.2/50 us Open Circuit Voltage 8 /20 us Short Circuit Current
Test Voltage:	Power Line: 0.5kV/ 1kV
Surge Input/Output:	L1-L2
Generator Source	2 ohm between networks
Impedance:	12 ohm between network and ground
Polarity:	Positive/Negative
Phase Angle:	0° /90°/180°/270°
Pulse Repetition Rate:	1 time / 20 sec.
Number of Tests:	5 positive and 5 negative at selected points

5.6.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATION DATE	CALIBRATION UNTIL
KeyTek, EMS Simulator	EMC Pro	9902207	Feb. 16, 2009	Feb. 15, 2010
Surge Cable	WE-4	SU2Cab-001	NA	NA
Surge Adapter WONPRO	WA-9	SU2ADA-002	NA	NA
KeyTek External Coupler/Decoupler for Telecom Lines	CM-TELCD	9906194	NA	NA
Software	CEWare32	NA	NA	NA

- NOTE:** 1. The test was performed in EMS Room No. 2.
2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.

5.6.3 TEST PROCEDURE

a. For EUT power supply:

The surge is to be applied to the EUT power supply terminals via the capacitive coupling network. Decoupling networks are required in order to avoid possible adverse effects on equipment not under test that may be powered by the same lines, and to provide sufficient decoupling impedance to the surge wave. The power cord between the EUT and the coupling/decoupling networks shall be 2 meters in length (or shorter).

b. For test applied to unshielded unsymmetrically operated interconnection lines of EUT:

The surge is applied to the lines via the capacitive coupling. The coupling / decoupling networks shall not influence the specified functional conditions of the EUT. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length (or shorter).


c. For test applied to unshielded symmetrically operated interconnection / telecommunication lines of EUT:

The surge is applied to the lines via gas arrestors coupling. Test levels below the ignition point of the coupling arrestor cannot be specified. The interconnection line between the EUT and the coupling/decoupling networks shall be 2 meters in length (or shorter).

5.6.4 DEVIATION FROM TEST STANDARD

No deviation

5.6.5 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

5.6.6 TEST RESULTS

TEST MODE	Mode 1 ~ 3	INPUT POWER	230Vac, 50Hz
ENVIRONMENTAL CONDITIONS	19deg. C, 80 % RH, 1018 hPa	TESTED BY: Andy Cheng	

VOLTAGE (kV)	TEST POINT	POLARITY (+/-)	OBSERVATION	PERFORMANCE CRITERION
0.5, 1	L1-L2	+/-	Note	A

NOTE: There was no change compared with the initial operation during the test.



A D T

5.7 IMMUNITY TO CONDUCTED DISTURBANCES INDUCED BY RF FIELDS (CS)

5.7.1 TEST SPECIFICATION

Basic Standard:	IEC 61000-4-6
Frequency Range:	0.15 MHz - 80 MHz
Field Strength:	10 V _{r.m.s}
Modulation:	1kHz Sine Wave, 80%, AM Modulation
Frequency Step:	1 % of fundamental
Coupled Cable:	Power Mains
Coupling Device:	CDN-M2 (2 wires)

5.7.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
ROHDE & SCHWARZ Signal Generator	SMY01	841104/033	Nov. 17, 2008	Nov. 16, 2009
AR Power Amplifier	75A250AM1	306331	NA	NA
EM TEST Coupling Decoupling Network	CDN M3	306511	Mar. 12, 2009	Mar. 11, 2010
EM TEST Coupling Decoupling Network	CDN M2	306510	Apr. 07, 2009	Apr. 06, 2010
EM TEST Coupling Decoupling Network	CDN M1	306508	Apr. 07, 2009	Apr. 06, 2010
FISCHER CUSTOM COMMUNICATIONS EM Injection Clamp	F-120-9A	361	NA	NA
EM TEST Coupling Decoupling Network	CDN T2	306509	Apr. 07, 2009	Apr. 06, 2010
EM TEST Coupling Decoupling Network	CDN T4	306506	Mar. 12, 2009	Mar. 11, 2010
EM TEST Coupling Decoupling Network	CDN T8	306507	Mar. 12, 2009	Mar. 11, 2010
BOONTON RF Voltage Meter	9200B	331801AE	Jul. 05, 2008	Jul. 04, 2009
Software	ADT_CS_V7.4.2	NA	NA	NA

- NOTE:** 1. The test was performed in CS Room 2.
2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.


5.7.3 TEST PROCEDURE

- a. The EUT shall be tested within its intended operating and climatic conditions.
- b. An artificial hand was placed on the hand-held accessory and connected to the ground reference plane.
- c. The test shall be performed with the test generator connected to each of the coupling and decoupling devices in turn, while the other non-excited RF input ports of the coupling devices are terminated by a 50-ohm load resistor.
- d. The frequency range is swept from 150 kHz to 80 MHz, using the signal level established during the setting process and with a disturbance signal of 80 % amplitude. The signal is modulated with a 1 kHz sine wave, pausing to adjust the RF signal level or the switch coupling devices as necessary. Where the frequency is swept incrementally, the step size shall not exceed 1 % of the preceding frequency value.
- e. The dwell time of the amplitude modulated carrier at each frequency shall not be less than the time necessary for the EUT to be exercised and to respond, but shall in no case be less than 0,5 s. The sensitive frequencies (e.g. clock frequencies) shall be analyzed separately.
- f. Attempts should be made to fully exercise the EUT during testing, and to fully interrogate all exercise modes selected for susceptibility.

5.7.4 DEVIATION FROM TEST STANDARD

No deviation

5.7.5 TEST SETUP



NOTE: The EUT clearance from any metallic obstacles shall be at least 0.5m.
All non-excited input ports of the CDNs shall be terminated by 50Ω loads.

For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

FLOOR-STANDING EQUIPMENT

The equipment to be tested is placed on an insulating support of 0.1 meters height above a ground reference plane. All relevant cables shall be provided with the appropriate coupling and decoupling devices at a distance between 0.1 meters and 0.3 meters from the projected geometry of the EUT on the ground reference plane.

5.7.6 TEST RESULTS

TEST MODE	Mode 1 ~ 3	INPUT POWER	230Vac, 50 Hz
ENVIRONMENTAL CONDITIONS	20 deg. C, 78 % RH, 1019 hPa	TESTED BY: Andy Cheng	

Frequency (MHz)	Field Strength (V _{r.m.s.})	Cable	Injection Method	Observation	Performance Criterion
0.15 – 80	10	AC power line	CDN-M2	Note	A

NOTE: There was no change compared with the initial operation during the test.

5.8 POWER FREQUENCY MAGNETIC FIELD IMMUNITY TEST

5.8.1 TEST SPECIFICATION

Basic Standard:	IEC 61000-4-8
Frequency Range:	50Hz, 60Hz
Field Strength:	30A/m
Observation Time:	1 minute
Inductance Coil:	Rectangular type, 1mx1m

5.8.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
HAEFELY Magnetic Field Tester	ADT	001	NA	NA

NOTE: 1. The test was performed in EMS Room No. 2.
2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.


5.8.3 TEST PROCEDURE

- The equipment is configured and connected to satisfy its functional requirements.
- The power supply, input and output circuits shall be connected to the sources of power supply, control and signal.
- The cables supplied or recommended by the equipment manufacturer shall be used. 1 meter of all cables used shall be exposed to the magnetic field.

5.8.4 DEVIATION FROM TEST STANDARD

No deviation

5.8.5 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.

NOTE:

TABLETOP EQUIPMENT

The equipment shall be subjected to the test magnetic field by using the induction coil of standard dimension (1 m x 1 m). The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

FLOOR-STANDING EQUIPMENT

The equipment shall be subjected to the test magnetic field by using induction coils of suitable dimensions. The test shall be repeated by moving and shifting the induction coils, in order to test the whole volume of the EUT for each orthogonal direction. The test shall be repeated with the coil shifted to different positions along the side of the EUT, in steps corresponding to 50 % of the shortest side of the coil. The induction coil shall then be rotated by 90 degrees in order to expose the EUT to the test field with different orientations.

5.8.6 TEST RESULTS

TEST MODE	Mode 1 ~ 3	INPUT POWER	230Vac, 50 Hz
ENVIRONMENTAL CONDITIONS	22 deg. C, 68 % RH, 1020 hPa	TESTED BY: Andy Cheng	

Direction	Field Strength (A/m)	Frequency Range (Hz)	Observation	Performance Criterion
X -Axis	30	50, 60	Note	A
Y -Axis	30	50, 60	Note	A
Z -Axis	30	50, 60	Note	A

NOTE: There was no change compared with the initial operation during the test.

5.9 VOLTAGE DIP/SHORT INTERRUPTIONS/VOLTAGE VARIATIONS (DIP) IMMUNITY TEST

5.9.1 TEST SPECIFICATION

Basic Standard:	IEC 61000-4-11
Test Duration Time:	Minimum three test events in sequence
Interval between Event:	Minimum ten seconds
Phase Angle:	0° & 180°
Test Cycle:	3 times

5.9.2 TEST INSTRUMENTS

DESCRIPTION & MANUFACTURER	MODEL NO.	SERIAL NO.	CALIBRATED DATE	CALIBRATED UNTIL
KeyTek EMS Simulator	EMCPro	9902207	Feb. 16, 2009	Feb. 15, 2010

- NOTE:** 1. The test was performed in EMS Room No. 2.
2. The calibration interval of the above test instruments is 12 months and the calibrations are traceable to NML/ROC and NIST/USA.


5.9.3 TEST PROCEDURE

The EUT shall be tested for each selected combination of test levels and duration with a sequence of three dips/interruptions with intervals of 10 s minimum (between each test event). Each representative mode of operation shall be tested. Abrupt changes in supply voltage shall occur at zero crossings of the voltage waveform.

5.9.4 DEVIATION FROM TEST STANDARD

No deviation

5.9.5 TEST SETUP



For the actual test configuration, please refer to the related item – Photographs of the Test Configuration.



5.9.6 TEST RESULTS

TEST MODE	Mode 1 ~ 3	INPUT POWER	230Vac, 50Hz, 220Vac, 60Hz, 110Vac, 60Hz, 100Vac, 50Hz
ENVIRONMENTAL CONDITIONS	26 deg. C, 63 RH, 998 hPa	TESTED BY:	Andy Cheng


Input Power for testing: 230Vac, 50Hz			
VOLTAGE % RESIDUAL	PERIODS	OBSERVATION	PERFORMANCE CRITERION
0	1	Note (1)	A
40	10	Note (1)	A
70	25	Note (1)	A
0	250	Note (2)	B
Input Power for testing: 220Vac, 60Hz			
VOLTAGE % RESIDUAL	PERIODS	OBSERVATION	PERFORMANCE CRITERION
0	1	Note (1)	A
40	12	Note (1)	A
70	30	Note (1)	A
0	300	Note (2)	B
Input Power for testing: 110Vac, 60Hz			
VOLTAGE % RESIDUAL	PERIODS	OBSERVATION	PERFORMANCE CRITERION
0	1	Note (1)	A
40	12	Note (2)	B
70	30	Note (1)	A
0	300	Note (2)	B
Input Power for testing: 100Vac, 50Hz			
VOLTAGE % RESIDUAL	PERIODS	OBSERVATION	PERFORMANCE CRITERION
0	1	Note (1)	A
40	10	Note (2)	B
70	25	Note (1)	A
0	250	Note (2)	B

NOTE: (1) There was no change compared with the initial operation during the test.
(2) The EUT reset during the test.

6 PHOTOGRAPHS OF THE TEST CONFIGURATION CONDUCTED EMISSION TEST



RADIATED EMISSION TEST



HARMONICS EMISSION TEST & VOLTAGE FLUCTUATIONS AND FLICKER TEST



ESD TEST



ESD TEST (For Mode 1)




ESD TEST (For Mode 2)





ESD TEST (For Mode 3)




ESD TEST POINT




RS TEST



EFT TEST



SURGE TEST



CONDUCTED SUSCEPTIBILITY TEST



POWER-FREQUENCY MAGNETIC FIELDS TEST



VOLTAGE DIPS AND INTERRUPTIONS TEST





A D T

7 APPENDIX - INFORMATION ON THE TESTING LABORATORIES

We, Bureau Veritas Consumer Products Services (H.K.) Ltd., Taoyuan Branch, were founded in 1988 to provide our best service in EMC, Radio, Telecom and Safety consultation. Our laboratories are accredited and approved by the following approval agencies according to ISO/IEC 17025:

USA	FCC, NVLAP
Germany	TUV Rheinland
Japan	VCCI
Norway	NEMKO
Canada	INDUSTRY CANADA, CSA
R.O.C.	TAF, BSMI, NCC
Netherlands	Telefication
Singapore	GOST-ASIA(MOU)
Russia	CERTIS(MOU)

Copies of accreditation certificates of our laboratories obtained from approval agencies can be downloaded from our web site: www.adt.com.tw/index.5/phtml.

If you have any comments, please feel free to contact us at the following:

Linko EMC/RF Lab:

Tel: 886-2-26052180

Fax: 886-2-26051924

Hsin Chu EMC/RF Lab:

Tel: 886-3-5935343

Fax: 886-3-5935342

Hwa Ya EMC/RF/Safety/Telecom Lab:

Tel: 886-3-3183232

Fax: 886-3-3185050

Email: service@adt.com.tw

Web Site: www.adt.com.tw

The address and road map of all our labs can be found in our web site also.

---END---