



## Tube Package

Standard Packaging - Tube


- 1 Tube contains 10 converters

Procedure:

1. Putting the power module into the tube (10pcs/ tube)




2. Putting the labels of product name and MSL 2A on the vacuum bag



3. Putting the desiccant and the humidity indicator cards




put the desiccant into the tube




put the humidity indicator outside the tube

4. Putting the tube into the vacuum bag (this process only for PDS type product)




5. Put the vacuum bag at the vacuum machine under packing condition: pressure 520 mm-Hg for 2.5 sec.

6. Putting the tube into the inner box (30 tubes / inner box)



7. Putting the inner box into the outside carton (4 inner box / outside carton)




## Tape & Reel Package


### Optional Packaging - Tape & Reel

Procedure:



1. Putting the power module into the REEL (200pcs/reel)





- Specifications according IEC 286-3
- 1 Reel contains 200 converters
- Use appendix «-TR» on order code




2. Putting the reel into the vacuum bag (200pcs/reel/vacuum bag)



3. Putting the humidity indicator and desiccant into the vacuum bag (Position A)  
Stick the Label A and Label B on the vacuum bag after vacuum process operation.



4. Putting the reel bag into the inner box  
(1 vacuum bag / inner box)



Specifications can be changed any time without notice.

Dimensions in [mm], Tolerance  $\pm 0.1$ mm